

OUTDOOR CONDENSER MOTORS (208/230V)



TRIPSAVER Condenser Motor (208/230V)

Designed with a high degree of versatility, these motors will cover the vast majority of service applications requiring a direct drive motor. Stock these reliable motors on your service truck and you'll virtually eliminate those unnecessary trips to get the right motor. A definite must for your service vehicle stocking. Replaces most residential furnace motors; features include:

- Replaces 208-230V motors from 1/3 to 1/5 horsepower
- 2 speed taps/reversible rotation
- Operates in all positions
- 36 inch leads with easy to use quick-connect flag terminals



PART NO	HP	HIGH SPEED (RPM)	NO OF SPEEDS	INPUT VOLTAGE	NO OF PHASES	FREQ (Hz)	ROTATION DIRECTION (OSE)	RUN CAPACITOR (uF/V)	FLA AT 230V (A)
51-23053-21	1/6 - 1/3	1075	2	208,230	1	60	Reversible	5/370 (230V), 7.5/370 (208V)	2.60



PROTECH W51 Condenser Motors (208/230V)

A line of HVAC replacement motors, manufactured under strict quality standards at one of the world's largest and most modern motor production facilities. Every motor undergoes a variety of stringent tests before it leaves the assembly line.



PART NO	HP	HIGH SPEED (RPM)	NO OF SPEEDS	INPUT VOLTAGE	NO OF PHASES	FREQ (Hz)	ROTATION DIRECTION (OSE)	RUN CAPACITOR (uF/V)	FLA AT 230V (A)
W51-12CJA1-02	1/2	1075	1	208,230	1	60	Reversible	15/370	2.5
W51-13CJA1-02	1/3	1075	1	208,230	1	60	Reversible	10/370	1.7
W51-14CJA1-02	1/4	1075	1	208,230	1	60	Reversible	10/370	1.40
W51-MHCJJ1-02	1/5-1/3	825	1	208,230	1	60	Reversible	7.5/370	1.40
W51-16CJA1-02	1/6	1075	1	208,230	1	60	Reversible	10/370	1.20
W51-MHCJA1-02	1/6-1/3	1075	1	208,230	1	60	Reversible	10/370	1.30



PROTECH Wholesale Condenser Motors (208/230V)

Designed to fit a variety of common aftermarket applications. Additionally, they are approved as OEM replacements for many Rheem, Ruud, and WeatherKing models; see unit parts lists for cross-reference.



PART NO	HP	HIGH SPEED (RPM)	NO OF SPEEDS	INPUT VOLTAGE	NO OF PHASES	FREQ (Hz)	ROTATION DIRECTION (OSE)	RUN CAPACITOR (uF/V)	FLA AT 230V (A)
51-23055-12	1/5	825	1	208,230	1	60	Reversible	5/370	1.30
51-23055-11	1/5	1075	1	208,230	1	60	Reversible	3/370 (230V), 5/370 (208V)	1.30
51-23054-13	1/4	825	1	208,230	1	60	Reversible	5/370	1.80
51-23054-11	1/4	1075	1	208,230	1	60	Reversible	5/370	1.80
51-23053-11	1/3	1075	1	208,230	1	60	Reversible	5/370	1.75
51-23053-12	1/3	1075	1	208,230	1	60	Reversible	5/370	2.50
51-23052-11	1/2	1075	1	208,230	1	60	Reversible	7.5/370	2.90



US Motors Wholesale Condenser Motors (208/230V)



PART NO	HP	HIGH SPEED (RPM)	NO OF SPEEDS	INPUT VOLTAGE	NO OF PHASES	FREQ (Hz)	ROTATION DIRECTION (OSE)	RUN CAPACITOR (uF/V)	FLA AT 230V (A)
1859	1/6	1075	1	208,230	1	60	Reversible	5/370	0.50
1860	1/4	1075	1	208,230	1	60	Reversible	5/370	1.70
3323	1/6 - 1/3	1075	1	208,230	1	60	Reversible	7.5/370	2.00
1861	1/3	1075	1	208,230	1	60	Reversible	7.5/370 (230V), 10/370 (208V)	2.10
1862	1/2	1075	1	208,230	1	60	Reversible	10/370	3.00
1868	3/4	1075	1	208,230	1	60	Reversible	10/370 (230V), 7.5/370 (208V)	4.50