BVA300 series

pneumatic rotary actuators









BVA300 series

The BVA300 series pneumatic rotary actuators are manufactured in 12 different sizes. These actuators can be used with either ball valves or butterfly valves for on/off control or modulating control applications. They are provided with two bi-directional travel stops and travel adjustment, with torque figures up to 4000 Nm.

Technical information and materials

- Hard anodized aluminium body
- Stainless steel bolts, studs and nuts
- Maximum operating pressure: 8 bar g (116 psi g)
- Working temperature range: -30°C to +100°C (-22°F to +212°F)
- Mounting of solenoid valves according to NAMUR standard
- Position indicator and mechanical limit switches (bi-directional pinion travel stops)
- Carbon steel pinion with Electroless Nickel Plated (ENP) treatment

Models and configurations

Double acting	Single acting Spring configuration					
BVA310D	BVA310S → 4	6	8			
BVA315D	BVA315S →		8	10	12	14
BVA320D	BVA320S →		8	10	12	14
BVA325D	BVA325S →		8	10	12	14
BVA330D	BVA330S →		8	10	12	14
BVA335D	BVA335S →		8	10	12	14
BVA340D	BVA340S →		8	10	12	14
BVA345D	BVA345S →		8	10	12	14
BVA350D	BVA350S →		8	10	12	14
BVA355D	BVA355S →		8	10	12	14
BVA360D	BVA360S →		8	10	12	14
BVA365D	BVA365S →		8	10	12	14

BVA300 series











Features and benefits	Versatile actuator selection, Quick and easy selection based on size and the available air pressure		
	Internal spring configuration modified	Easy to maintain	
	Pre-compressed springs	Safe to configure and maintain	
	Antifriction sliding bearings/Slide guide	Long service life	
	Bi-directional travel stops	Allows a full ±5° travel adjustment between 85° and 95°	
	Centring ring	Easy to mount and ensures better stability during operation	
	Assembly variations: normally open (N/0) or normally closed (N/C)	Open or closed configuration available	

Spring configurations

Features

A new pinion design involves modifications to the internal springs. The BVA300 has pre-compressed springs which allows different configurations. In this way, springs can be adapted to different air pressures, facilitating safe, simple and fast maintenance.

Benefits

ISO	Spirax Sarco is certified by ISO 9001:2002		
PED	BVA310 to BVA335 are classified as Category SEP (PED 97/23/EC)		
	BVA340 to BVA365 are classified as Category 1, procedure module A.		
ATEX	BVA300 are classified for use in potentially explosive atmospheres as Group II		
	Category 2, suitable for zones 1, 2, 21 and 22 in accordance with Annex VIII -		
	Directive 94/9/CE.		

Bi-directional travel stops

Certificates

The BVA300 pneumatic actuators are provided with bi-directional pinion travel stops which allow a travel adjustment between 85° and 95°. These travel stops avoid superfluous forces and torques which otherwise reduce an actuator's service life.

Body labels

Double acting and single acting BVA300 actuators include labels which identify them.

ATEX EX Proof certification for use in explosive atmospheres is printed on the label.

Single acting actuators detail the quantity of springs according to the actuator configuration.

Group companies

Africa

Americas

Argentina Brazil Canada Mexico USA

Asia

China India Japan Korea Malaysia Singapore Taiwan Thailand

Australasia

New Zealand

Europe

Austria Belgium Denmark Finland France Germany Italy Norway Poland Portugal Russia Spain

Sales offices

Africa

Egypt Kenya Nigeria

Americas

Colombia Venezuela

Asia

Hong Kong Indonesia Pakistan **Philippines** Vietnam

Europe

Austria Hungary Ireland

Middle East

UAE

South Africa Australia

Czech republic Slovak republic Sweden Switzerland

HK

Distributors

Africa

Algeria Cameroon Ethiopia Ghana Ivory Coast Libya Malawi Mauritius Morocco Namibia Senegal Sudan Tanzania Tunisia Uganda Zambia Zimbabwe

Americas

Bolivia Chile Colombia Costa Rica Dominican Rep Ecuador El Salvador Guatemala Honduras Jamaica Nicaragua Panama Paraguay Peru

Trinidad and Tobago

Uruguay Venezuela

Asia

Bangladesh

Australasia

Fiji

Europe


Bulgaria Croatia Cyprus Estonia Greece Iceland Latvia Lithuania Malta Netherlands Romania Slovenia Turkey

Middle East

Bahrain Iran Jordan Kuwait Lebanon Oman Qatar Saudi Arabia Syria



Not all associates can offer all services/solutions detailed in this sales brochure



Spirax-Sarco Limited Cheltenham UK **GL53 8ER** t: +44 (0)1242 521361 f: +44 (0)1242 573342 e: controls@SpiraxSarco.com www.SpiraxSarco.com/controls

