

## **DIVERTER**

#### **Features**

- · Solid brass construction
- · Counter clockwise flow on direction.
- High Torque Quarter-turn washerless ceramic valve cartridge.
- 3/4" NPT female thread (inlet and outlet) valve body
- 12.5 gpm (gallons per minute) flow rate (@ 40 psi)
- Requires Newport Brass Handle Trim (many options available, sold-separately)

### Flow Control Valve

1-607HT



### **Codes / Standards Compliance**

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/Cupc
- IPC
- ASSE 1016
- All applicable US Federal and State material regulations



# Specified Model Model Description Colors | Finishes 1-607HT Diverter/Flow Control Valve NA

### **Product Specification**: Add "Color / Finish" suffix to Model number, below.

The Flow Control Valve for wall installations shall be made of solid brass construction. Valve body shall incorporate high torque quarter-turn washerless ceramic disc valve cartridges. Valve shall have a maximum flow rate of 12.5 gpm (gallons per minute) @ 40 psi. Valve body shall have 3/4" NPT female thread for inlet

and outlet. The Flow Control Valve for wall installations shall be Newport Brass Model 1-607HT.

# 1-607HT

## **PRODUCT DIMENSIONS** (Units are in inches)

