



SUBMITTAL INFORMATION

40 Series Resetter - (VB43-xxW-FP-NL style)



FULL PORT ANGLE BALL VALVE BY METER NUT (3/4" METER)

METER THREAD INLET AND OUTLET



Resetter Part Number

HEIGHT (INCHES)	APPROX. WT. LBS.	CATALOG NUMBER	✓ SUBMITTED ITEM(S)
8	5.8	VB43-8W-FP-NL	
12	6.1	VB43-12W-FP-NL	
15	6.4	VB43-15W-FP-NL	
18	7.3	VB43-18W-FP-NL	
21	7.6	VB43-21W-FP-NL	
24	8.7	VB43-24W-FP-NL	
27	9.1	VB43-27W-FP-NL	
30	9.5	VB43-30W-FP-NL	

Meter Thread Size

INLET	OUTLET
3/4"	3/4"

FEATURES

- All brass that comes in contact with potable water conforms to AWWA Standard C800 (ASTM B584, UNS C89833)
- The product has the letters "NL" cast into the main body for lead-free identification
- Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B62 and ASTM B584, UNS C83600, 85-5-5-5)
- Copper conforms to ASTM B75 or B88, UNS C12200
- Saddle nuts hold the meter in place for tightening
- Tie bar is standard for 18" and taller Resetter heights (40 Series)
- Conforms to AWWA C700 for meter threads
- 15/16" O.D. copper risers provide more flow capacity
- All Ford setters are assembled with lead-free solder

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



The Ford Meter Box Company, Inc.
P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443
Phone: 260-563-3171 / Fax: 800-826-3487
Overseas Fax: 260-563-0167
www.fordmeterbox.com

12/02/16

Submitted By: