



SUBMITTAL INFORMATION

40 Series Resetter - (VBB47-xxHB-NL style)



FLANGED ANGLE BALL VALVE BY FLANGED ANGLE BALL VALVE WITH HIGH BY-PASS (2" METER)

METER FLANGE INLET AND OUTLET



METER FLANGE INLET	METER FLANGE OUTLET	HEIGHT (INCHES)	APPROX. WT. LBS.	CATALOG NUMBER	✓ SUBMITTED ITEM
2"	2"	18"	53.0	VBB47-18HB-NL	
		24"	56.0	VBB47-24HB-NL	
		27"	57.0	VBB47-27HB-NL	

FEATURES

- All brass components that come in contact with potable water conform to AWWA Standard C800 (UNS NO C89833)
- The product has the letters "NL" cast into the main body for proper identification
- Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B-62 and ASTM B-584, UNS NO C83600 - 85-5-5-5)
- Constructed with Type K Copper and conforms to ASTM B-88, Copper Alloy #122
- All Ford Setters are assembled with lead-free solder
- Bracing Eyes are standard
- Meter support Brackets are standard
- Padlock Wing is standard on all Angle Meter Ball Valves or Key Valves
- Outlet ball valve may be used as customer shut-off up to 300 PSI

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



The Ford Meter Box Company, Inc.

P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443

Phone: 260-563-3171 / Fax: 800-826-3487

Overseas Fax: 260-563-0167

www.fordmeterbox.com

03/14/14

Submitted By: