



# SUBMITTAL INFORMATION

## 40 Series Resetter - (VHC42-xxW-NL style)



ANGLE KEY VALVE BY ANGLE CARTRIDGE DUAL CHECK VALVE (5/8" X 3/4" METER)

METER THREAD INLET AND OUTLET



### Resetter Part Number

HEIGHT (INCHES)	APPROX. Wt. LBS.	CATALOG NUMBER	✓ SUBMITTED ITEM(S)
9	5.6	VHC42-9W-NL	
12	5.8	VHC42-12W-NL	
15	6.0	VHC42-15W-NL	
18	6.7	VHC42-18W-NL	
21	6.9	VHC42-21W-NL	
24	7.2	VHC42-24W-NL	
27	7.4	VHC42-27W-NL	
30	7.7	VHC42-30W-NL	

### Meter Thread Size

INLET	OUTLET
3/4"	3/4"

### FEATURES

- All brass that comes in contact with potable water conforms to AWWA Standard C800 (ASTM B584, UNS C89833)
- The product has the letters "NL" cast into the main body for lead-free identification
- Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B62 and ASTM B584, UNS C83600, 85-5-5-5)
- Saddle nuts hold the meter in place for tightening
- Tie bar is standard for 18" and taller resetter heights (40 Series)
- Conforms to AWWA C700 for meter threads
- 13/16" Copper risers provide more flow capacity
- All Ford Setters are assembled with lead-free solder
- Copper conforms to ASTM B75, UNS C12200
- ASSE 1024 approved cartridge dual check valve

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



#### The Ford Meter Box Company, Inc.

P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443  
 Phone: 260-563-3171 / Fax: 800-826-3487  
 Overseas Fax: 260-563-0167  
 www.fordmeterbox.com

11/29/16

Submitted By: