

# SUBMITTAL INFORMATION





#### **TAPPED STAINLESS STEEL SADDLE**



| Nom. | SADDLE      | TAP SIZE 3/4" & 1" |      |          | TAP SIZE 1-1/4", 1-1/2" & 2" |      |          | Caraloo           | / C         |
|------|-------------|--------------------|------|----------|------------------------------|------|----------|-------------------|-------------|
| PIPE | O.D.        | BAND               | Вост | APPROX.  | BAND                         | Вост | APPROX.  | Catalog<br>Number | ✓ SUBMITTED |
| SIZE | RANGE       | <b>W</b> IDTH      | SIZE | WT. LBS. | <b>W</b> IDTH                | SIZE | WT. LBS. | NUMBER            | ITEM(S)     |
| 4"   | 4.74-5.54   | 6"                 | 5/8" | 5.2      | 7-1/2"                       | 5/8" | 5.7      | FS323-554-TAP     |             |
| 6"   | 6.40-7.20   | 6"                 | 5/8" | 5.1      | 7-1/2"                       | 5/8" | 5.8      | FS323-720-TAP     |             |
| 8"   | 8.40-9.20   | 6"                 | 5/8" | 6.3      | 7-1/2"                       | 5/8" | 7.8      | FS323-920-TAP     |             |
| 10"  | 10.70-11.50 | 6"                 | 5/8" | 7.0      | 7-1/2"                       | 5/8" | 9.0      | FS323-1150-TAP    |             |
| 12"  | 12.70-13.50 | 6"                 | 5/8" | 9.0      | 7-1/2"                       | 5/8" | 11.0     | FS323-1350-TAP    |             |
|      | 14.00-14.80 | 6"                 | 5/8" | 9.0      | 7-1/2"                       | 5/8" |          | FS323-1480-TAP    |             |
| 14"  | 14.95-15.75 | 6"                 | 5/8" | 10.0     | 7-1/2"                       | 5/8" | 12.0     | FS323-1575-TAP    |             |
|      | 15.60-16.40 | 6"                 | 5/8" |          | 7-1/2"                       | 5/8" |          | FS323-1640-TAP    |             |
|      | 15.75-16.55 | 6"                 | 5/8" |          | 7-1/2"                       | 5/8" |          | FS323-1655-TAP    |             |
| 16"  | 16.40-17.20 | 6"                 | 5/8" | 10.5     | 7-1/2"                       | 5/8" | 12.5     | FS323-1720-TAP    |             |
|      | 17.20-18.00 | 6"                 | 5/8" |          | 7-1/2"                       | 5/8" |          | FS323-1800-TAP    |             |
|      | 17.60-18.40 | 6"                 | 5/8" |          | 7-1/2"                       | 5/8" |          | FS323-1840-TAP    |             |
|      | 18.00-18.80 | 6"                 | 5/8" |          | 7-1/2"                       | 5/8" |          | FS323-1880-TAP    |             |
| 18"  | 18.40-19.20 | 6"                 | 5/8" |          | 7-1/2"                       | 5/8" | 12.5     | FS323-1920-TAP    |             |
|      | 18.80-19.60 | 6"                 | 5/8" | 10.5     | 7-1/2"                       | 5/8" |          | FS323-1960-TAP    |             |
|      | 19.20-20.00 | 6"                 | 5/8" |          | 7-1/2"                       | 5/8" |          | FS323-2000-TAP    |             |

### **OUTLET TAP CODE**

| CC (AWWA) THREAD |          |                     |  | IP THREAD |          |                     |  |
|------------------|----------|---------------------|--|-----------|----------|---------------------|--|
| THREAD           | CODE No. | ✓ SUBMITTED ITEM(S) |  | THREAD    | CODE No. | ✓ SUBMITTED ITEM(S) |  |
| 3/4" CC          | CC3      |                     |  | 3/4" IP   | IP3      |                     |  |
| 1" CC            | CC4      |                     |  | 1" IP     | IP4      |                     |  |
| 1-1/4" CC        | CC5      |                     |  | 1-1/4" IP | IP5      |                     |  |
| 1-1/2" CC        | CC6      |                     |  | 1-1/2" IP | IP6      |                     |  |
| 2" CC            | CC7      |                     |  | 2" IP     | IP7      |                     |  |

To Order: Select the catalog number for the desired pipe range and complete the catalog number by adding the outlet thread tap code. Example: A double band saddle for 9.05 O.D. pipe with a 3/4" CC thread would be FS323-920-CC3.

#### **FEATURES**

- Body, Bands and threaded studs are made of 18-8 Type 304 stainless steel
- All welds are fully passivated for corrosion resistance
- Coined body for gasket retention
- Buna-N rubber pad gasket per (ASTM D2000) with raised compression seal
- Rated for 250 psi working pressure
- UL Classified to ANSI/NSF Standard 61

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



## The Ford Meter Box Company, Inc.

P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443

Phone: 260-563-3171 / Fax: 800-826-3487

Overseas Fax: 260-563-0167 www.fordmeterbox.com

07/09/15

| $\overline{}$ | _  | • • • • | ]   |
|---------------|----|---------|-----|
| ธน            | nn | nitted  | ΙBV |