

Water-Saving Bath/Shower Trim

with Double Ceramic Pressure Balance Cartridge

MODEL NUMBER:

TRIM KITS:


☐ TU052508 Delancey Bath/Shower Trim Kit with **Pressure Balance Cartridge**

Lever handle. Water-saving showerhead. LESS valve body.

☐ TU052507 Delancey Shower ONLY Trim Kit with Pressure Balance Cartridge

Lever handle. Water-saving showerhead. LESS valve body.

For use with Flash™ Rough Valve Bodies



TU052508 Bath/Shower Trim Shown

GENERAL DESCRIPTION:

Double Ceramic Pressure Balance Cartridge: Features one-piece design with ceramic discs and ceramic balancing spool. Includes integrated check valves and hot limit safety stop. Cartridge capable of back to back capability. Ceramic balancing spool maintains constant output temperature in response to changes in relative hot and cold supply pressure. Washerless ceramic discs provide smooth handle movement and are unaffected by harsh water conditions.

Trim: Features 7-1/4" water-saving showerhead with a maximum 1.8 gpm/6.8 L/min. flow rate. Metal slip-on diverter spout. Metal wall valve trim with metal lever.

PRODUCT FEATURES

One-Piece Cartridge: Simplifies installation and maintenance.

Double Ceramic Pressure Balance Cartridge:

Combination of Ceramic Disc Mixing Valve and a Ceramic Balancing Spool in a one-piece cartridge.

Ceramic Disc Mixing Valve: Assures a lifetime of drip-free performance and smooth handle operation.

Ceramic Balancing Spool: Maintains a constant output temperature in response to changes in relative hot and cold supply pressure. Ceramic material is unaffected by mineral deposits and harsh water conditions.

Integrated Check Valves: Engineered to eliminate cross flow. Adjustable Hot Limit Safety Stop: Limits the amount of hot water allowed to mix with cold. Reduces the risk of accidental scalding.

Comfort Zone: Offers a wider shower range to fine tune the desired temperature within the useful temperature zone.

Back-to-Back Capability: Hot and cold can be reversed quickly and easily.

Water Saving: Saves 28% water usage.

FINISHED WALL -2" TO 3" (51 TO 76 mm) 9-1/2" (241 mm) 1/2" NPT 3-7/8" (100 mm) 2-3/16 (56 mm) 7-5/8" OPTIONAL TO FINISHED FLOOR USUALLY BETWEEN 65" AND 78" (1651 AND 1981 mm) . 7-1/4" 7-7-16 2-3/4" MAX (69 mm) (192 mm) 1-3/4" MIN. (45 mm) 74" (1879 mm) FOR HEAD CLEARANCE 7-13/16" DIA. 4-11/16" (121 mm) 18" (457 mm) OPTIONAL (207 mm) 3-1/4" (83 mm) FOR SLIP-ON SPOUT (177 mm) TOP OF TUB RIM BOTTOM OF TUB

SUGGESTED SPECIFICATION

Bath/shower fitting shall feature water saving showerhead with Max. 1.8 gpm/6.8 L/min. flow rate. Shall feature double ceramic pressure balance cartridge. Cartridge is capable of back to back installation and shall feature integrated check valves to eliminate cross flow. Capable of meeting ASSE1016 @1.3gpm. Cartridge shall also feature hot limit safety stop. Fitting shall be: American Standard - Trim Kit Model # TU05250_ and Flash Valve Body Model # RU10

5/20 © 2020 AS America, Inc.



Delancey®


Water-Saving Bath/Shower Trim with Double Ceramic Pressure Balance Cartridge

CODES AND STANDARDS

These products meet or exceed the following codes and standards:

ASSE 1016 / ASME A112.18.1016 / CSA B125.16 ASME A112.18.1 / CSA B125.1 Rated to meet ASSE 1016 @ 1.3gpm

CEC



			Finish Options			
*	Product		Polished Chrome	PVD Polished Nickel	Legacy Bronze	PVD Brushed Nickel
X	Number	Description	002	013	278	295
TRIM	TU052508	Bath/Shower Trim Kit. Metal lever handle. Water-saving showerhead. Includes cartridge. LESS valve body.				
	TU052507	Shower Only Trim Kit. Metal lever handle. Water-saving showerhead. Includes cartridge. LESS valve body.				

* TRIM & ROUGH MUST BE ORDERED SEPARATELY.

DIES	Product Description	Without Screwdriver Stops	With Screwdriver Stops
BO	Rough Valve Body. Universal* inlets/outlets.	RU101	RU101SS
VE	Rough Valve Body. Stub-out inlets/outlets for Press-Fit Fittings.	RU102	RU102SS
VAL	Rough Valve Body. PEX inlets/Universal outlets for Crimp Ring PEX system (ASTM F1807).	RU107	RU107SS
ИСН	Rough Valve Body. PEX Elbow inlets/Universal outlets for Crimp Ring PEX system (ASTM F1807).	RU107E	RU107ESS
™ RO	Rough Valve Body. PEX inlets/Universal outlets for Cold Expansion PEX system (ASTM F1960).	RU108	RU108SS
Flash	Rough Valve Body. PEX Elbow inlets/Universal outlets for Cold Expansion PEX system (ASTM F1960).	RU108E	RU108ESS
	Rough Valve Body. CPVC inlets/Universal outlets.	RU109	RU109SS

TIONAL	Product Number	Product Description
OP1 ACC	M970649-YYY0A	Deep Rough-In Kit

ÁDA

Meets the American Disabilities Act Guidelines and **ANSI A117.1** Requirements for the physically challenged.

PART OF LIXIL

© 2020 AS America, Inc. 5/20