

Lavatory Ensemble Model D139_015

FEATURES

- Style: Modern Momentum
- Collection: Basic
- Temperature controlled by handles
- 1-1/16" (27mm) hole size for spout
- 1-1/16" (27mm) hole size for valves
- 12" (305mm) maximum centers
- Pop-up drain with lift rod and tailpiece
- 1.5 gpm @ 60 psi
- With Blade Cross Handles

COLOR FINISHES

- Polished Nickel (D139_014)
- Satin Nickel (D139_015)
- Pewter (D139_15A)
- Polished Chrome (D139_026)
- Polished Brass (D139_003)
- Old English Brass (D139_OEB)
- Antique Brass (D139_047)
- Antique Bronze (D139_11B)

WARRANTY

- Limited Lifetime

COMPLIES WITH

- CA AB 1953-CERTIFIED
- ANSI/NSF61-CERTIFIED
- A112.18.1-05/CSA B125.1-2005-CERTIFIED
- cUPC-CERTIFIED
- UPC-CERTIFIED
- VT S152



Image shown may not be in the finish selected

