
## Systems for Floor-Mounted, Back Outlet Toilets, 2x6 Installation

Style

Material Finish

Concealed Tank, Sigma 2x6 Installation と



Concealed tank shipped dual-flush ready 1.

- 2. Tank for floor-mounted, back outlet washdown style toilet fixtures only
- 3 Refer to → geberit.us for latest list of code approved compatible toilet fixtures,
- including certified WaterSense® combinations

Note: For System Accessories see pages 16-18.

#### Dual-Flush Actuators, Sigma 2x6 Installation

Style	Material	Finish	Model No.	List Price
Sigma01	Plastic	Alpine White	115.770.11.5	\$89.00
		Polished Chrome	115.770.21.5	121.00
$ \mathcal{O} $		Matte Chrome	115.770.46.5	121.00
Sigma20	Metal	Br Ni-Polished Ni-Br Ni*	115.882.ID.1	251.00
		Br SS-Polished SS-Br SS*	115.882.SN.1	252.00
00		Br Ni-Polished Ni-Br Ni* VR	115.889.ID.1	290.00
		Br SS-Polished SS-Br SS* VR	115.889.SN.1	290.00
	Plastic	Polished Chr-Matte Chr- Polished Chr*	115.882.KH.1	187.00
		White-Polished Chrome-White*	115.882.KJ.1	129.00
		White-Polished Gold-White*	115.882.KK.1	595.00
		White-Matte Chr-Matte Chr*	115.882.KL.1	159.00
		Black-Polished Chrome-Black*	115.882.KM.1	159.00
		Matte Chr-Pol Chr-Matte Chr*	115.882.KN.1	187.00
Sigma30	Plastic	Polished Chr-Matte Chr- Polished Chr***	115.883.KH.1	210.00
		White-Polished Chrome-White***	115.883.KJ.1	131.00
		White-Polished Gold-White***	115.883.KK.1	170.00
		White-Matte Chr-Matte Chr***	115.883.KL.1	170.00
		Black-Polished Chrome-Black***	115.883.KM.1	170.00
		Matte Chr-Polished Chr- Matte Chr***	115.883.KN.1	210.00

115.788.00.5 Sigma50 Die Cast Customer supplied inlay \$366.00 115.788.11.5 Alpine White 366.00 Polished Chrome 115.788.21.5 472.00 Black 115.788.DW.5 366.00 Brushed Chrome 115.788.GH.5 472.00 Smoke Glass 115.788.SD.5 472.00 Green Satin Glass 115.788.SE.5 472.00 Umber Glass 115.788.SQ.5 472.00 Sigma60<sup>+</sup> Die Cast Brushed chrome 115.640.GH.1 618.00 White Glass 115.640.SI.1 Glass 618.00 Black Glass 115.640.SJ.1 618.00 Umber Glass 115.640.SQ.1 618.00 Rough-in set 243.168.00.1 16.00 (REQUIRED accessory) Cover frame (optional accessory) 115.641.21.1 160.00 Polished Chrome Cover frame (optional accessory) 115.641.GH.1 160.00 Brushed Chrome Sigma70 Die Cast Customizable 115.620.00.1 523.00 Br SS 115.620.FW.1 Metal 694.00 Glass White Glass 115.620.SI.1 612.00

Dual-Flush Actuators, Sigma 2x6 Installation (continued)

Model No.

115.620.SJ.1

115.620.SQ.1

List Price

612.00

612.00

#### Single-Flush Actuators, Sigma 2x6 Installation

Black Glass

Umber Glass

Sigma10 <sup>‡</sup> Metal		Br SS	115.758.SN.5	\$252.00
		Br SS VR	115.787.SN.5	286.00
$ \mathcal{O} $	Plastic	Pol Chr-Matte Chr-Pol Chr*	115.758.KH.5	187.00
		White-Polished Chrome-White*	115.758.KJ.5	130.00
		White-Polished Gold-White*	115.758.KK.5	371.00
		White-Matte Chr-Matte Chr*	115.758.KL.5	159.00
		Black-Polished Chrome-Black*	115.758.KM.5	159.00
		Matte Chr-Polished Chr- Matte Chr*	115.758.KN.5	187.00
Sigma30 <sup>‡</sup>	Die Cast	Polished Gold***	115.893.45.1	594.00
$\square$		White-Polished Chr-White***	115.893.KJ.1	246.00
		Br Chrome-Pol Chr-Br Chrome***	115.893.KX.1	361.00
		Pol Chr-Br Chrome-Pol Chr***	115.893.KY.1	361.00

### Hands-Free Actuators and Transformer, Sigma 2x6 Installation

Sigma10 <sup>‡</sup>	Metal	Br SS (AC Power)	115.890.SN.5	\$858.00
	Single-	Br SS (Battery/DC Power)	115.891.SN.5	858.00
	Flush			
Sigma80	Glass	Black (AC Power)	116.090.SG.1	1,448.00
	Dual- Mirror (AC Power)		116.090.SM.1	1,448.00
1000000000000	Flush			
		Connection cable	242.658.00.1	42.00
	S.	(optional accessory) length length 78–3/4" (2 m)		
	P	Extension mains cable	241.831.00.1	58.00
		(optional accessory for Sigma10 and Sigma80)		
		length 78–3/4" (2 m)		
		Transformer for AC powered	115.861.00.1	145.00
	) I	hands-free actuator.		
		(For Sigma10 and Sigma80)		

Finishes follow this pattern = Plate-Ring-Button

\*\* Finishes follow this pattern = Frame-Button

\*\*\* Finishes follow this pattern = Frame-Button Edge Trim-Button

† Note: For tile, stone or other hard surfaced walls only!

Not intended to be sold in California

VR = Vandal Resistant

Br SS = Brushed Stainless Steel

Br Ni = Brushed Nickel


Products marked with 🛃 comply with the American Disabilities Act (ADA) when installed per the requirements of the latest ADA Accessibility Guidelines (ADAAG) and/or ICC/ANSI A117.1.

### **Replacement Parts**

### Geberit Sigma Concealed Tank 109.304.00.5, 2x6 Installation

Item	Model No.	Description	List Price
1	240.923.00.1	Fixation clip for filling valve	\$6.00
2	241.469.00.1	Filling valve Type 380 for Sigma, Omega and Kappa Concealed Tanks	26.00
2.1	240.771.00.1	Seal kit for filling valve Type 380	11.00
3	241.858.00.1	Dual-flush valve complete with valve seat basket	21.00
4	240.622.00.1	Dual-flush valve for Sigma Concealed Tank	14.00
4.1	241.167.00.1	Yoke set for flush valves	9.00
4.2	816.418.00.1	Flat gasket for flush valve	2.00
5	241.859.00.1	Valve seat basket and noise bushing for flush valv	e 10.00
5.1	241.868.00.1	U-cup seal for valve basket	2.00
6	243.345.00.1 or 243.168.00.1	Mud guard protection housing for Sigma Concealed Tanks 2x6 and 2x4, plastic	16.00
7	242.315.00.1	Splash guard protection cover for Sigma Concealed Tank 2x6	6.00
8	241.829.00.1	Flush actuator gear box	6.00

Item	Model No.	Description	List Price
9	362.771.00.1	Seal for concealed flush pipe, EPDM	\$2.00
10	362.796.92.1	Protection plug, plastic	5.00
11	240.921.00.1	Connection hose for Sigma Concealed Tank, 3/8"	14.00
	241.854.00.1	Connection hose for Sigma Concealed Tank, 3/8" dezincification resistant	- 21.00
11.1	240.922.00.1	Seal kit for braided hose, EPDM O-ring	9.00
12	240.853.00.1	Supply angle stop (black handle)	14.00
12.1	240.851.00.1	Drop ear elbow, copper	11.00
13	152.404.46.1	Connector set with mounting hardware (bowl installation kit), HDPE; Matte Chrome cover caps	42.00
13.1	217.713.46.1	Cover caps with leveling washer, plastic, Matte Chrome	7.00
13.2	119.668.00.1	Seal for supply inlet tube, EPDM	2.00
13.3	152.424.00.1	Seal for toilet outlet connector, EPDM	3.00



### **System Accessories**

#### **Geberit Optional and Required Accessories** for Installation

Geberit Optional for Installation	and Required Accessories										Ţ
Description		Model Number	List Price	111.335	111.798	111.012	111.520	111.524	111.490	111.625	109.304
	ection Sets and Accessories for Fi	nished Walls	up to 3.5" (	(9cm) Th	ick						
	Connector set with mounting hardware (bowl installation kit), HDPE; Alpine White cover caps	152.404.11.1	\$42.00	$\checkmark$	$\checkmark$	$\checkmark$					
Ô	PE syphon trap with horizontal outlet and seal; Ø1.96" (Ø50 mm) outlet	152.950.11.1	35.00							$\checkmark$	
Č	PE syphon trap with vertical outlet and seal; Ø1.97" (Ø50 mm) outlet	152.951.11.1	35.00							$\checkmark$	

	PE syphon trap with vertical outlet and seal; Ø1.97″ (Ø50 mm) outlet	152.951.11.1	35.00							~	
0 () 8.	Acoustic insulation set for wall-hung toilets and bidets	156.050.00.1	18.00	$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$			
0000	Cover caps with leveling washer, plastic, Alpine White	217.713.11.1	7.00	$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$		
	HDPE connection set with 1" (2.5 cm) offset and mounting hardware (bowl installation kit); with socket for Ø3.50" (Ø90 mm) push fit piping and Ø55 supply inlet; Matte Chrome cover caps	405.116.00.1	218.00	~	~	$\checkmark$					$\checkmark$

REQUIRED Connection Sets and Accessories for Finished Walls 3.5" - 7.0" (9-18cm) Thick

6000 6000	HDPE Connector set for extended installation and mounting hardware (bowl installation kit), with socket for Ø3.50" (Ø90 mm) push fit piping and Ø2.16" (Ø55 mm) supply inlet; Matte Chrome cover caps	152.438.46.1	54.00	$\checkmark$	$\checkmark$	$\checkmark$					$\checkmark$
J.J.J.J.J.J.J.J.J.J.J.J.J.J.J.J.J.J.J.	Extension set for actuator plates for Sigma Concealed Tanks 2x6 and 2x4, Kappa and Omega Concealed Tanks	240.938.00.1	22.00	$\checkmark$	$\checkmark$	$\checkmark$					$\checkmark$
	Mud guard protection housing for Sigma Concealed Tanks 2x6 and 2x4, plastic, 4 inch (10 cm)	241.826.00.1	13.00	$\checkmark$	$\checkmark$						$\checkmark$
	Mud guard protection housing and extension set for urinal carrier	241.930.00.1	19.00							$\checkmark$	
100	Mounting rod M12 x 10" long. Not supplied.	M12 x 10"		$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$			
<b>`</b>	Mounting rod M10 x 10" long. Not supplied.	M10 x 10"	_						$\checkmark$		
	Mounting rod M8 x 10" long. Not supplied.	M8 x 10"	_							$\checkmark$	

# Geberit Optional and Required Accessories for Installation

Geberit Optional for Installation	and Required Accessories										Ĩ
Description		Model Number	List Price	111.335	111.798	111.012	111.520	111.524	111.490	111.625	109.304
<b>OPTIONAL</b> Instal	lation Accessories for Bidet Seat	5									
( the second sec	Water supply hose for bidet seat for Kappa and Omega Concealed Tank pre-wall. For adding bidet seat to an installed carrier. For complete installation, must order with 249.801.00.1.	240.839.00.1	\$57.00			$\checkmark$					
	Water supply hose for bidet seat for 111.798.00.1 carrier with Sigma Concealed Tank 2x4. For adding bidet seat to an installed carrier. For complete installation, must order with 249.801.00.1.	243.173.00.1	46.00		$\checkmark$						
	HDPE connection set with 1" (2.5 cm) offset and mounting hardware (bowl installation kit); with socket for Ø3.50" (Ø90 mm) push fit piping and Ø55 supply inlet; Matte Chrome cover caps	249.801.00.1	111.00	$\checkmark$	$\checkmark$	$\checkmark$					$\checkmark$
<b>OPTIONAL</b> Instal	lation Accessories for Geberit Du	ofix Carrier Fi	rames								
Le de la companya de	Frame to wall anchoring for 5.125"- 7.875" (13-20 cm) thick unfinished pre-wall	111.013.00.1	22.00		$\checkmark$						
ERRETRA	Frame to wall anchoring for 5.125"- 7.875" (13-20 cm) thick unfinished pre-wall	111.815.00.1	34.00	$\checkmark$		$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$	$\checkmark$	
Contraction of the second seco	Frame to wall anchoring for 5.125"- 7.875" (13-20 cm) thick unfinished pre-wall corner installations	111.835.00.1	34.00	$\checkmark$							
ŬŬ	Support brackets for wall-hung toilets with small contact surface (thin profiles)	111.847.00.1	44.00	$\checkmark$		$\checkmark$					
	Fire protection set for Sigma Concealed Tank 90 min. fire resistance to DIN EN 1364-1:1999-10	111.863.00.1	490.00	$\checkmark$							
	Frame to wall anchoring where foot installations into floor are not allowed for 5.125"-7.875" (13-20 cm)	111.867.00.1	65.00	$\checkmark$							
	Fastening set for sinks with 14.9"-22.8" (38-58 cm) mounting centers	111.868.00.1	111.00						$\checkmark$		
	Frame to stud fastening set for extended stud spacing from 19.75"- 25.56" (50-65 cm)	111.869.00.1	34.00	$\checkmark$							
	Frame to wall anchoring extensions for 7.875"-15.75" (20-40 cm) thick (unfinished pre-wall)	111.887.00.1	14.00	$\checkmark$							
	Crossbar for inlet 1/2" thread	242.042.00.1	69.00							$\checkmark$	
60 60 60	Elbow supply fitting set, Gun Metal	465.034.00.1	37.00				$\checkmark$	$\checkmark$	$\checkmark$		

## **System Accessories**


#### **Geberit Optional and Required Accessories** for Installation

Geberit Optional for Installation	and Required Accessories										P
Description		Model Number	List Price	111.335	111.798	111.012	111.520	111.524	111.490	111.625	109.304
<b>OPTIONAL</b> Instal	lation Waste Fitting Accessories										
	PP connector set with bend for floor-mount toilets with mounting hardware, 1 x 90° bends with socket for Ø4.375" (Ø110 mm) push fit piping for Ø3.82"-4.21" (Ø97–107 mm) male connection and expansion to Ø4.375" (Ø110 mm) outlet	152.647.00.1	\$111.00								(For A or B discharge. See below)
	HDPE waste fitting outlet bend, 1 x 90° bend with socket for Ø3.50" (Ø90 mm) push fit piping and Ø3.50" (Ø90 mm) outlet	366.061.16.1	22.00								(For A discharge. See below)
	HDPE straight connector with socket for Ø3.50" (Ø90 mm) push fit piping and Ø3.50" (Ø90 mm) outlet x 12" (31 cm) long	366.887.16.1	34.00	$\checkmark$	$\checkmark$	$\checkmark$					(For A discharge. See below)
	HDPE connector with offset for LH horizontal drain connections (as viewed from sitting position), 1 × 90° bend with socket for Ø3.50° (Ø90 mm) push fit piping, with 45° offset and Ø3.50° (Ø90 mm) outlet for 5.5° (13.97 cm) minimum walls only.	366.913.16.1	71.00	$\checkmark$	$\checkmark$	~					(For A discharge. See below)
	HDPE connector with offset for RH horizontal drain connections (as viewed from sitting position), 1 × 90° bend with socket for Ø3.50″ (Ø90 mm) push fit piping, with 45° offset and Ø3.50″ (Ø90 mm) outlet for 5.5″ (13.97 cm) minimum walls only.	366.914.16.1	71.00	$\checkmark$	~	~					(For A discharge. See below)
	Cast iron outlet bend; 1 x 90° bend with socket for Ø3.50″ (Ø90 mm) push fit piping and 3″ CIP outlet	367.071.18.1	147.00	$\checkmark$	$\checkmark$	$\checkmark$					(For A discharge. See below)
	HDPE "Back-to-back" connector for horizontal drain connections; 2 x 90° bends with sockets for Ø3.50" (Ø90 mm) push fit piping, with 45° offset and expansion to Ø4.375" (Ø110 mm) outlet for 10.75" (27.31 cm) minimum walls only.	367.485.16.1	147.00	~	$\checkmark$	$\checkmark$					(For A or B discharge. See below)
	HDPE "Back-to-back" connector for vertical drain connections; 2 x 90° bends with sockets for Ø3.50" (Ø90 mm) push fit piping and expansion to Ø4.375" (Ø110 mm) outlet for 10.75" (27.31 cm) minimum walls only.	367.923.16.1	147.00	$\checkmark$	$\checkmark$	$\checkmark$					(For A or B discharge See below)

Note: Any of these fittings in combination with carrier 111.798.00.1 are cUPC and IPC listed.

# Waste Fitting Discharge Configurations for Floor Mount Back Outlet Toilets

Note: Mounting collar/clamp by installer



A. Floor-Mount Rear Discharge into Wall

B. Floor-Mount
Rear Discharge
into Floor