


PRODUCT
SPECIFICATIONS

EZ
KLEEN
AIR FILTERS



KLEEN-
GARD
GREASE FILTERS

EZ KLEEN® AIR FILTERS

AIR FILTER	STOCK SIZE (H x W x D) Nominal	STOCK NO.	PERFORMANCE		
EZ KLEEN® <i>UL Class 2 Filter</i> Rated Velocity 150-650 FPM (0.76-3.31 m/s) Optimum Velocity 350-520 FPM (1.78-2.64 m/s)			1" EZ Klean Filters		
	20" x 25" x 1"	9801	1" (25mm) & 3/32 (2.4mm)	At 350 fpm (1.78 m/s)	At 520 fpm (2.64 m/s)
	20" x 20" x 1"	9802			
	16" x 25" x 1"	9803	Average Arrestance	54%	48%
	16" x 20" x 1"	9804	Clean Resistance	0.045" w.c. 0.011 kPa	0.09" w.c. 0.023 kPa
	15" x 20" x 1"	9805			
	10" x 20" x 1"	9806	Dust-Holding Capacity	95 gms/ft ² (1023 gms/m ²)	67 gms/ft ² (721 gms/m ²)
MV EZ KLEEN® <i>UL Class 2 Filter</i> Rated Velocity 150-650 FPM (0.76-4.58 m/s) Optimum Velocity 350-520 FPM (1.78-2.64 m/s)			2" MV EZ Klean Filters		
	20" x 25" x 2"	9151		At 350 fpm (1.78 m/s)	At 520 fpm (2.64 m/s)
	20" x 20" x 2"	9152			
	16" x 25" x 2"	9153	Average Arrestance	72%	68%
	16" x 20" x 2"	9154	Clean Resistance	0.07 w.c. 0.018 kPa	0.14" w.c. 0.035 kPa
	15" x 20" x 2"	9155			
	10" x 20" x 2"	9156	Dust-Holding Capacity	130 gms/ft ² (1399 gms/m ²)	91 gms/ft ² (980 gms/m ²)
	24" x 24" x 2"	9157			
INDUSTRIAL EZ KLEEN® <i>UL Class 2 Filter</i> Rated Velocity 150-900 FPM (0.76-4.58 m/s) Optimum Velocity 350-520 FPM (1.78-2.64 m/s)			2" Industrial Filters		
	20" x 25" x 2"	901		At 350 fpm (1.78 m/s)	At 520 fpm (2.64 m/s)
	20" x 20" x 2"	902			
	16" x 25" x 2"	903	Average Arrestance	67%	64%
	16" x 20" x 2"	904	Clean Resistance	0.05 w.c. 0.013 kPa	0.10" w.c. 0.025 kPa
	15" x 20" x 2"	905			
	10" x 20" x 2"	906	Dust-Holding Capacity	143 gms/ft ² (1539 gms/m ²)	117 gms/ft ² (1259 gms/m ²)
TRIM-TO-SIZE EZ KLEEN® <i>UL Class 2 Filter</i>				1/4" Trim-To-Size	5/8" Trim-To-Size*
	15" x 24" x 1/4"	9200		At 350 fpm (1.78 m/s)	At 350 fpm (1.78 m/s)
	40" x 64" x 1/4"	9250			
	40" x 64" x 5/8"	9251	Average Arrestance	61%	54%
	40" x 50" x 1/4"	9260			
	40" x 50" x 5/8"	9261	Clean Resistance	0.07 w.c. 0.018 kPa	0.45" w.c. 0.011 kPa
MADE-TO-ORDER EZ KLEEN® <i>UL Class 2 Filter</i> Minimum quantities may apply.			Dust-Holding Capacity	100 gms/ft ² (1075 gms/m ²)	95 gms/ft ² (1023 gms/m ²)
			EZ Klean Filters 3/32," 3/8," 1/2"		
			3/32," 3/8," 1/2" Nominal Frame Thickness	At 350 fpm (1.78 m/s)	
			Average Arrestance	64%	
			Clean Resistance	0.06 w.c. 0.016 kPa	
			Dust-Holding Capacity	44 gms/ft ² (474 gms/m ²)	

*See 1" EZ Klean performance for 520 fpm

ALUMINUM KLEEN-GARD® GREASE FILTERS

BAFFLE-TYPE

STAINLESS STEEL KLEEN-GARD® GREASE FILTERS

BAFFLE-TYPE

RATED VELOCITY 150-400 FPM (0.76-2.04 m/s)
OPTIMUM VELOCITY 300 FPM (1.53 m/s)


(W X H X D) Nominal	STOCK NO.		(W X H X D) Nominal	STOCK NO.
Without Handles				
20" x 25" x 2"	951		20" x 25" x 2"	961
20" x 20" x 2"	952		20" x 20" x 2"	962
16" x 25" x 2"	953		16" x 25" x 2"	963
16" x 20" x 2"	954		16" x 20" x 2"	964
10" x 20" x 2"	956		10" x 20" x 2"	966
16" x 16" x 2"	957		16" x 16" x 2"	967
25" x 20" x 2"	958		25" x 20" x 2"	968
With No. 994 Handles				
20" x 25" x 2"	9511		20" x 25" x 2"	9611
20" x 20" x 2"	9522		20" x 20" x 2"	9622
16" x 25" x 2"	9533		16" x 25" x 2"	9633
16" x 20" x 2"	9544		16" x 20" x 2"	9644
10" x 20" x 2"	9566		10" x 20" x 2"	9666
16" x 16" x 2"	9577		16" x 16" x 2"	9677
25" x 20" x 2"	9588		25" x 20" x 2"	9688

ALWAYS ORDER BY STOCK NUMBER

Kleen-Gard Baffle Filters

- + Stainless steel provides added durability and corrosion resistance
- + Promotes sanitation by removing grease from the air flowing through filters and draining it safely away
- + Prevents spread of range-top fires
- + Kleen-Gard is UL classified and meets requirements of [NFPA Standard 96](#) when properly installed
- + Protects blower equipment and prolongs motor life
- + Handles up to 400 fpm (2.04 m/s)

Resistance Vs. Airflow — 2" Kleen-Gard Baffle Type Grease Filters




Kleen-Gard Spark Arrestor Filters

Stainless Steel Kleen-Gard Grease Filter with Spark Arrestor available to meet NFPA 96 standard for its solid fuel cooking applications.

- + Spark Arrestor constructed of stainless steel mesh in tin-plated steel frame
- + All in one construction for ease of handling
- + Supplied with Snap-In Handles for easy installation and removal
- + Available in same sizes as baffle filters, as well as special sizes

Customized Services for Our Customers

- + Stock filters are shipped within 24 hours with over 97% of these shipments being made the same day the order is received
- + Special size filters are shipped within 10 business days
- + To avoid a line shutdown, a partial shipment can be made of special sizes within 48 hours
- + Safety stock program
- + No charge samples of the actual filter size which are shipped within only 48 hours
- + Additional filter types are available: foam, charcoal and polyester
- + No expediting fees
- + Special freight rates negotiated through designated carriers
- + International quality standards established
- + Electronic Data Interchange (EDI) and bar coding capabilities for simpler ordering and receiving
- + Alternative product designs to offer economies



RESEARCH PRODUCTS CORPORATION

P.O. Box 1467 • Madison, WI 53701-1467

888.742.2402 • fax: 608.257.4357

RPEZKLEEN.COM

