



Clamp Fittings



Stainless Steel Flow Control Equipment for the
Food, Beverage, Dairy, Cosmetics, Biotechnology,
Pharmaceutical and Electronics Processing Industries

www.toplineonline.com

Clamp Fittings

Top Line precision crafted clamp fittings provide fast, sanitary and secure connections. Polished fittings come standard with the No. 7 ID/OD finish (32R_a ID/OD) finish which meets or exceeds FDA and 3-A regulatory standards.

Specifications:

Size Range: 1/2" OD - 12" OD

Wall Thickness: .065 (1/2" - 3")
.083 (4")
.109 (6" - 8")
.109 (10" - 12")

Materials: 304 (Stock No. prefix 32) as shown in part number matrix


316L (Stock No. prefix 38) as shown in part number matrix

Other materials grades are available upon request




2CMP – Elbow 90° Clamp Ends (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	R	304 STOCK NO.	316L STOCK NO.
1/2	3-1/2	1-1/8	–	38705-7
3/4	3-1/2	1-1/8	–	38707-7
1	2	1-1/2	32710-7	38710-7
1-1/2	2-3/4	2-1/4	32715-7	38715-7
2	3-1/2	3	32720-7	38720-7
2-1/2	4-1/4	3-3/4	32725-7	38725-7
3	5	4-1/2	32730-7	38730-7
4	6-5/8	6	32740-7	38740-7
6	9-3/4	9	32760-7	38760-7
8	12-7/8	12	32780-7	38780-7
10	15-7/8	15	327100-7	387100-7
12	19	18	327120-7	387120-7




2FMP – 14 Elbow 90° Clamp End x Bevel Seat Plain End with Hex Nut (3-A) 32R_a ID/ 32R_a OD

SIZE (TUBE O.D.)	A	B	304 STOCK NO.
1	2	2-3/16	327010
1-1/2	2-3/4	2-31/32	327015
2	3-1/2	3-23/32	327020
2-1/2	4-1/4	4-19/32	327025
3	5	5-13/32	327030
4	6-5/8	7-7/32	327040



2FMP – 15 Elbow 90° Clamp End x Bevel Seat Threaded End (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	304 STOCK NO.
1	2	2-3/16	327110
1-1/2	2-3/4	2-31/32	327115
2	3-1/2	3-31/32	327120
2-1/2	4-1/4	4-19/32	327125
3	5	5-13/32	327130
4	6-5/8	7-7/32	327140




NOTE: 1" CLAMP FITTINGS USE 1-1/2" CLAMPS

topln.co/clampfittings


2CMP – 31MP Elbow 90° Reducing Concentric Clamp End x Clamp End (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	304 STOCK NO.	316L STOCK NO.
2 X 1	2	2	327220	387220
2 X 1-1/2	2-3/4	2-3/4	327220A	387220A
2-1/2 X 1-1/2	2-3/4	2-3/4	327225	387225
2-1/2 X 2	3-1/2	3-1/2	327225A	387225A
3 X 1-1/2	2-3/4	2-3/4	327230	387230
3 X 2	3-1/2	3-1/2	327230A	387230A
3 X 2-1/2	4-1/4	4-1/4	327230B	387230B
4 X 2-1/2	4-3/8	4-1/4	327240	387240
4 X 3	5-1/8	5	327240A	387240A




2FMP-31MP – Elbow 90° Reducing Concentric Clamp End x Bevel Seat Plain End (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	304 STOCK NO.
2 X 1	2	1-9/16	327420
2 X 1-1/2	2-3/4	2-5/16	327420A
2-1/2 X 1-1/2	2-3/4	2-5/16	327425
2-1/2 X 2	3-1/2	3-1/16	327425A
3 X 1-1/2	2-3/4	2-5/16	327430
3 X 2	3-1/2	3-1/16	327430A
3 X 2-1/2	4-1/4	3-13/16	327430B
4 X 2-1/2	4-1/4	3-13/16	327440
4 X 3	5	4-9/16	327440A



2KMP – Elbow 45° Clamp Ends (3-A) 32R_a ID/32R_a OD


SIZE (TUBE O.D.)	A	R	304 STOCK NO.	316L STOCK NO.
1/2	2-3/4	1-1/8	—	38805-7
3/4	2-3/4	1-1/8	—	38807-7
1	1-1/8	1-1/2	32810-7	38810-7
1-1/2	1-7/16	2-1/4	32815-7	38815-7
2	1-3/4	3	32820-7	38820-7
2-1/2	2-1/16	3-3/4	32825-7	38825-7
3	2-3/8	4-1/2	32830-7	38830-7
4	3-1/8	6	32840-7	38840-7
6	4-1/2	9	32860-7	38860-7
8	5-7/8	12	32880-7	38880-7
10	7-1/8	15	—	—
12	8-1/2	18	—	—



7MP – Tee Clamp Ends (3-A) 32R_a ID/32R_a OD


SIZE (TUBE O.D.)	A	B	304 STOCK NO.	316L STOCK NO.
1/2	2-5/8	5-1/4	–	381105-7
3/4	2-5/8	5-1/4	–	381107-7
1	2-3/8	4-3/4	321110-7	381110-7
1-1/2	2-3/4	5-1/2	321115-7	381115-7
2	3-1/2	7	321120-7	381120-7
2-1/2	3-1/2	7	321125-7	381125-7
3	3-3/4	7-1/2	321130-7	381130-7
4	4-1/2	9	321140-7	381140-7
6	5-3/4	11-1/2	321160-7	381160-7
8	7-7/8	15-3/4	321180-7	381180-7
10	9-3/8	18-3/4	3211100-7	3811100-7
12	11	22	3211120-7	3811120-7

NOTE: 1" CLAMP FITTINGS USE 1-1/2" CLAMPS




7RMP – Tee Reducing Clamp Ends (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	C	304 STOCK NO.	316L STOCK NO.
3/4 X 1/2	5	2-1/2	2-1/2	–	381107R05-7
1 X 1/2	5-1/4	2-5/8	2-5/8	–	381110R05-7
1 X 3/4	5-1/4	2-5/8	2-5/8	–	381110R07-7
1-1/2 X 1/2	5-3/4	2-7/8	2-7/8	–	381115R05-7
1-1/2 X 3/4	5-3/4	2-7/8	2-7/8	–	381115R07-7
1-1/2 X 1	4-5/16	2-5/32	1-7/8	321115R10	381115R10
2 X 1/2	6-3/4	3-3/8	3-1/8	–	381120R05-7
2 X 3/4	6-3/4	3-3/8	3-1/8	–	381120R07-7
2 X 1	5-1/8	2-9/16	2-1/8	321120R10	381120R10
2 X 1-1/2	5-1/8	2-9/16	2-13/32	321120R15	381120R15
2-1/2 X 1	5-11/16	2-27/32	2-13/16	–	381125R10
2-1/2 X 1-1/2	5-11/16	2-27/32	2-13/16	321125R15	381125R15
2-1/2 X 2	5-11/16	2-27/32	2-13/16	321125R20	381125R20
3 X 1	6-3/16	3-3/32	3-1/16	321130R10	381130R10
3 X 1-1/2	6-3/16	3-3/32	3-1/16	321130R15	381130R15
3 X 2	6-3/16	3-3/32	3-1/16	321130R20	381130R20
3 X 2-1/2	6-3/16	3-3/32	3-3/32	321130R25	381130R25
4 X 1	8-1/8	4-1/16	4-7/8	–	381140R10
4 X 1-1/2	8-1/8	4-1/16	4-7/8	321140R15	381140R15
4 X 2	8-1/8	4-1/16	4-7/8	321140R20	381140R20
4 X 2-1/2	8-1/8	4-1/16	4-7/8	321140R25	381140R25
4 X 3	8-1/8	4-1/16	4-7/8	321140R30	381140R30
6 X 3	11-1/2	5-3/4	5-1/2	321160R30-7	381160R30-7
6 X 4	11-1/2	5-3/4	5-5/8	321160R40-7	381160R40-7
8 X 3	15-3/4	7-7/8	7-1/2	–	381180R30-7
8 X 4	15-3/4	7-7/8	7-5/8	321180R40-7	381180R40-7
8 X 6	15-3/4	7-7/8	7-3/4	321180R60-7	381180R60-7
10 X 3	18-3/4	9-3/8	9	–	–
10 X 4	18-3/4	9-3/8	9-1/8	–	–
10 X 6	18-3/4	9-3/8	9-1/4	–	–
10 X 8	18-3/4	9-3/8	9-3/8	3211100R80-7	–
12 X 3	22	11	10-1/2	–	–
12 X 4	22	11	10-5/8	3211120R40-7	–
12 X 6	22	11	10-3/4	3211120R60-7	–
12 X 8	22	11	10-7/8	–	–
12 X 10	22	11	10-7/8	–	–



L14AM7 – Ferrule Long Clamp End x Weld End (3-A) 32R_a ID/32R_a OD


SIZE (TUBE O.D.)	A	B	C	304 STOCK NO.	316L STOCK NO.
1/2	1-1/8	.370	1/2	–	387505
3/4	1-1/8	.620	3/4	–	387507
1	1-1/8	.870	1	327510	387510
1-1/2	1-1/8	1.370	1-1/2	327515	387515
2	1-1/8	1.870	2	327520	387520
2-1/2	1-1/8	2.370	2-1/2	327525	387525
3	1-1/8	2.870	3	327530	387530
4	1-1/8	3.834	4	327540	387540
6	1-1/2	5.782	6	327560	387560
8	1-1/2	7.782	8	327580	387580
10	1-1/2	9.782	10	3275100	3875100
12	1-1/2	11.782	12	3275120	3875120



NOTE: 1" CLAMP FITTINGS USE 1-1/2" CLAMPS


14RMP – Ferrule Recessless x Clamp End (3-A) 32R_a OD

SIZE (TUBE O.D.)	A	B	304 STOCK NO.	316L STOCK NO.
1	3/4	1	32110	38110
1-1/2	1-1/8	1-1/2	32115	38115
2	1-5/16	2	32120	38120
2-1/2	1-3/8	2-1/2	32125	38125
3	1-7/16	3	32130	38130
4	1-1/2	4	32140	38140



14MPW – Ferrule Tank Spud Clamp End x Weld End (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	C	304 STOCK NO.	316L STOCK NO.
1	1-5/8	.870	1.160	327610	387610
1-1/2	1-5/8	1.370	1.676	327615	387615
2	1-3/4	1.870	2.192	327620	387620
2-1/2	1-3/4	2.370	2.708	327625	387625
3	1-13/16	2.870	3.224	327630	387630
4	2-1/8	3.834	4.256	327640	387640



SA-479 material available upon request

Ferrules, & Cross

Clamp Fittings


TOP LINE

14WLMP – Ferrule Tank Spud Light Clamp End x Weld End (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	C	304 STOCK NO.	316L STOCK NO.
1	3	.870	1	327710	387710
1-1/2	3	1.370	1-1/2	327715	387715
2	3	1.870	2	327720	387720
2-1/2	3	2.370	2-1/2	327725	387725
3	4	2.870	3	327730	387730
4	4	3.834	4	327740	387740
6	6	5.782	6	327760-7	387760-7
8	6	7.782	8	327780-7	387780-7
10	6	9.782	10	3277100-7	3877100-7
12	6	11.782	12	3277120-7	3877120-7

SA-479 material available upon request

A[®]
3




14WMP – Ferrule Short Clamp End x Weld End (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	C	304 STOCK NO.	316L STOCK NO.
1/2	1/2	.370	1/2	–	38205
3/4	1/2	.620	3/4	–	38207
1	1/2	.870	1	32210	38210
1-1/2	1/2	1.370	1-1/2	32215	38215
2	1/2	1.870	2	32220	38220
2-1/2	1/2	2.370	2-1/2	32225	38225
3	1/2	2.870	3	32230	38230
4	5/8	3.834	4	32240	38240
6	3/4	5.782	6	32260	38260
8	7/8	7.782	8	32280	38280
10	7/8	9.782	10	322100	382100
12	1	11.782	12	322120	382120

NOTE: 1" CLAMP FITTINGS USE 1-1/2" CLAMPS


A[®]
3



9MP – Cross Clamp Ends (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	304 STOCK NO.	316L STOCK NO.
1	2-3/8	4-3/4	3210110	3810110
1-1/2	2-3/4	5-1/2	3210115	3810115
2	3-1/2	7	3210120	3810120
2-1/2	3-1/2	7	3210125	3810125
3	3-3/4	7-1/2	3210130	3810130
4	4-1/2	9	3210140	3810140
6	5-3/4	11-1/2	3210160	3810160
8	7-7/8	15-3/4	3210180	3810180
10	9-3/8	18-3/4	32101100	38101100
12	11	22	32101120	38101120


A[®]
3



23BMP – Thermometer Cap x Clamp End 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	304 STOCK NO.	316L STOCK NO.
1	1-63/64	329810B	389810B
1-1/2	1-63/64	329815B	389815B
2	2-33/64	329820B	389820B
2-1/2	3-3/64	329825B	389825B
3	3-37/64	329830B	389830B
4	4-11/16	329840B	389840B

NOTE: 1" TAPPED 1/2" NPT; ALL OTHERS 3/4" NPT




31-14MP & 32-14MP – Reducer Concentric & Eccentric Clamp Ends (3-A) 32R_a ID/32R_a OD

31-14MP CONCENTRIC				32-14MP ECCENTRIC	
SIZE (TUBE O.D.)	A	304 STOCK NO.	316L STOCK NO.	304 STOCK NO.	316L STOCK NO.
3/4 X 1/2	2	—	3884-0705-7	—	3885-0705-7
1 X 1/2	2-1/2	—	3884-1005-7	—	3885-1005-7
1 X 3/4	2	—	3884-1007-7	—	3885-1007-7
1-1/2 X 1/2	3-1/2	—	3884-1505-7	—	3885-1505-7
1-1/2 X 3/4	3	—	3884-1507-7	—	3885-1507-7
1-1/2 X 1	3	328415	388415-7	328515	388515-7
2 X 1/2	5-1/2	—	3884-2005-7	—	3885-2005-7
2 X 3/4	3	—	3884-2007-7	—	3885-2007-7
2 X 1	5	328420	388420-7	328520	388520-7
2 X 1-1/2	3	328420A	388420A-7	328520A	388520A-7
2-1/2 X 1	7	328425	388425-7	328525B	388525-7
2-1/2 X 1-1/2	5	328425A	388425A-7	328525	388525A-7
2-1/2 X 2	3	328425B	388425B-7	328525A	388525B-7
3 X 1	9	—	—	—	388530C-7
3 X 1-1/2	7	328430	388430-7	328530	388530-7
3 X 2	5	328430A	388430A-7	328530A	388530A-7
3 X 2-1/2	3	328430B	388430B-7	328530B	388530B-7
4 X 1-1/2	11-1/8	32844015-7	—	32854015	—
4 X 2	9-1/8	328440	388440-7	328540	388540-7
4 X 2-1/2	7-1/8	328440A	388440A-7	328540A	388540A-7
4 X 3	5-1/8	328440B	388440B-7	328540B	388540B-7
6 X 3	7-1/4	328460	388460-7	328560-7	388560-7
6 X 4	5-3/8	328460A	388460A-7	328560A-7	388560A-7
8 X 3	7-3/8	328480B-7	388480B-7	328580-7	—
8 X 4	7-1/2	328480-7	388480-7	328580A-7	—
8 X 6	7-5/8	328480A-7	388480A-7	328580B-7	388580B-7
10 X 6	8-5/8	3284100A-7	3884100A-7	—	—
10 X 8	8-3/4	3284100-7	3884100-7	—	—
12 X 8	9-7/8	—	—	—	—
12 X 10	9-7/8	—	3884120-7	—	—


NOTE: 1" CLAMP FITTINGS USE 1-1/2" CLAMPS



CONCENTRIC




ECCENTRIC



21MP – ADAPTER Clamp End x Male NPT 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	304 STOCK NO.	316L STOCK NO.
1/2 X 1/8	2	0.3924	–	38820500
1/2 X 1/4	2	0.5946	–	38820500A
1/2 X 3/8	2	0.6006	–	38820500B
1/2 X 1/2	2	0.7815	–	38820505
1/2 X 3/4	2	0.7935	–	38820507
3/4 X 1/8	2	0.3924	–	38820700
3/4 X 1/4	2	0.5946	–	38820700A
3/4 X 3/8	2	0.6006	–	38820700B
3/4 X 1/2	2	0.7815	–	38820705
3/4 X 3/4	2	0.7935	–	38820707
1 X 1/2	2-3/16	0.7815	–	38821005
1 X 3/4	2-3/16	0.7935	328210	38821007
1 X 1	2-1/4	0.9845	328210A	38821010
1 X 1-1/4	2-7/16	1.0085	328210D	–
1 X 1-1/2	2-7/16	1.0252	328210B	38821015
1 X 2	2-5/8	1.0582	328210C	38821020
1-1/2 X 1/2	2-3/16	0.7815	32821505	38821505
1-1/2 X 3/4	2-3/16	0.7935	328215	38821507
1-1/2 X 1	2-5/16	0.9845	328215A	38821510
1-1/2 X 1-1/4	2-7/16	1.0085	328215B	38821510A
1-1/2 X 1-1/2	2-7/16	1.0252	328215C	38821515
1-1/2 X 2	2-5/8	1.0582	328215D	38821520
2 X 1/2	2-1/4	0.7815	–	38822005
2 X 3/4	2-9/32	0.7935	–	38822007
2 X 1	2-15/32	0.9845	328220D	38822010
2 X 1-1/4	2-15/32	1.0085	328220	38822010A
2 X 1-1/2	2-15/32	1.0252	328220A	38822015
2 X 2	2-21/32	1.0582	328220B	38822020
2 X 2-1/2	3-1/8	1.5712	328220C	38822025
2-1/2 X 1	2-25/32	0.9845	328225	–
2-1/2 X 1-1/2	2-25/32	1.0252	328225A	38822515
2-1/2 X 2	2-25/32	1.0582	328225B	38822520
2-1/2 X 2-1/2	3-9/32	1.5712	328225C	38822525
3 X 2-1/2	3-1/2	1.5712	328230A	–
3 X 3	3-1/2	1.6337	328230	38823030
4 X 2	3-13/16	1.0582	328240A	–
4 X 3	4-13/16	1.6337	328240B	–
4 X 4	3-13/16	1.7337	328240	38824040




21MP (MALE)

NOTE: WHEN ADAPTER DIMENSIONS ARE GIVEN, SANITARY STYLE END IS ALWAYS INDICATED FIRST
OTHER SIZES AVAILABLE UPON REQUEST

22MP – ADAPTER Clamp End x Female NPT 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	304 STOCK NO.	316L STOCK NO.
1/2 X 1/8	1-1/8	—	38830500
1/2 X 1/4	1-1/2	—	38830500A
1/2 X 3/8	1-1/2	—	38830500B
1/2 X 1/2	1-1/2	—	38830505
1/2 X 3/4	1-5/8	—	38830507
3/4 X 1/8	1-1/8	—	38830700
3/4 X 1/4	1-1/2	—	38830700A
3/4 X 3/8	1-1/2	—	38830700B
3/4 X 1/2	1-1/2	—	38830700C
3/4 X 3/4	1-5/8	—	38830707
1 X 1/2	1-5/8	—	38831005
1 X 3/4	1-5/8	328310	38831007
1 X 1	1-5/8	328310A	38831010
1 X 1-1/2	2-1/4	328310B	38831015
1 X 2	2-1/4	328310C	38831020
1-1/2 X 1/2	1-5/8	32831505	38831505
1-1/2 X 3/4	1-5/8	328315	38831507
1-1/2 X 1	1-5/8	328315A	38831510
1-1/2 X 1-1/4	2-1/4	328315B	38831510A
1-1/2 X 1-1/2	2-1/4	328315C	38831515
1-1/2 X 2	2-1/4	328315D	38831520
2 X 1/2	1-11/16	32832005	38832005
2 X 1	1-11/16	32832010	38832010
2 X 1-1/4	1-11/16	328320	38832010A
2 X 1-1/2	1-11/16	328320A	38832015
2 X 2	2-11/32	328320B	38832020
2 X 2-1/2	2-13/32	328320C	38832025
2-1/2 X 1	1-5/16	328325	—
2-1/2 X 1-1/2	1-21/32	328325A	38832515
2-1/2 X 2	1-23/32	328325B	38832520
2-1/2 X 2-1/2	1-23/32	328325C	38832525
3 X 3	2-3/16	328330	38833030
4 X 3	2-3/16	328340B	—
4 X 4	2-5/8	328340	38834040


NOTE: WHEN ADAPTER DIMENSIONS ARE GIVEN, SANITARY STYLE END IS ALWAYS INDICATED FIRST
OTHER SIZES AVAILABLE UPON REQUEST



14MPHR – Adapter Clamp End x Rubber Hose Barb 32R_a ID

SIZE (TUBE O.D.)	A	B	C	304 STOCK NO.	316L STOCK NO.
1/2 X 1/8	1-1/2	.147	.062	—	387800
1/2 X 1/4	1-1/2	.312	.187	—	387800A
1/2 X 3/8	1-1/2	.405	.218	—	387800B
1/2 X 1/2	1-1/2	.540	.375	—	387805
1/2 X 3/4	1-1/2	.840	.625	—	387805A
3/4 X 1/8	1-1/2	.147	.062	—	3878007
3/4 X 1/4	1-1/2	.312	.187	—	387807A
3/4 X 3/8	1-1/2	.405	.218	—	387807B
3/4 X 1/2	1-1/2	.540	.375	—	387807C
3/4 X 3/4	1-1/2	.840	.625	—	387807
1	1-11/16	1	13/16	327810	387810
1-1/2	1-11/16	1-1/2	1-5/16	327815	387815
2	2-5/16	2	1-13/16	327820	387820
2-1/2	2-11/32	2-1/2	2-5/16	327825	387825
3	3-3/32	3	2-27/32	327830	387830
4	3-13/32	4	3-27/32	327840	387840

OTHER SIZES AVAILABLE UPON REQUEST




Adapter & Cap

Clamp Fittings

TOP LINE

14MPHT – Adapter Clamp End x Long Tube End for Tygon Hose 32R_a ID/32R_a OD


SIZE (TUBE O.D.)	A	B	C	304 STOCK NO.	316L STOCK NO.
1	4-1/2	7/8	1	327910	387910
1-1/2	4-1/2	1-3/8	1-1/2	327915	387915
2	4-1/2	1-7/8	2	327920	387920
2-1/2	4-1/2	2-3/8	2-1/2	327925	387925
3	4-1/2	2-7/8	3	327930	387930
4	4-5/8	3-27/32	4	327940	387940



17MP-14 – Adapter Clamp End x Bevel Seat Plain End with Hex Nut (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	304 STOCK NO.	316L STOCK NO.
1	3	328010	388010
1-1/2	3	328015	388015
2	3	328020	388020
2-1/2	3-1/2	328025	388025
3	3-3/4	328030	388030
4	4	328040	388040


HEX NUT INCLUDED



17MP-15 – Adapter Clamp End x Bevel Seat Threaded End (3-A) 32R_a ID/32R_a OD


SIZE (TUBE O.D.)	A	304 STOCK NO.	316L STOCK NO.
1	1-11/16	328110	388110
1-1/2	1-23/32	328115	388115
2	1-23/32	328120	388120
2-1/2	1-27/32	328125	388125
3	1-29/32	328130	388130
4	2-11/32	328140	388140

NOTE: 1" CLAMP FITTINGS USE 1-1/2" CLAMPS




16AMP – Cap Solid End Type Clamp (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	304 STOCK NO.	316L STOCK NO.
1/2 & 3/4	.187	—	389807
1 & 1-1/2	.250	329815	389815
2	.250	329820	389820
2-1/2	.250	329825	389825
3	.250	329830	389830
4	.312	329840	389840
6	.437	329860	389860
8	.500	329880	389880
10	.500	3298100	3898100
12	.437	3298120	3898120




2WUMP – U-Bend 180° Clamp End (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	304 STOCK NO.	316L STOCK NO.
1	3	2-1/2	32910-7	38910-7
1-1/2	4-1/2	3-1/2	32915-7	38915-7
2	6	4-1/2	32920-7	38920-7
2-1/2	7-1/2	5-1/2	32925-7	38925-7
3	9	6-1/2	32930-7	38930-7
4	12	8-5/8	32940-7	38940-7




Line Splitter – Clamp Ends (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	R	304 STOCK NO.	316L STOCK NO.
1-1/2	3-1/16	7-1/2	2-1/4	32515-7	38515-7
2	3-7/8	9	3	32520-7	38520-7
2-1/2	5-7/8	11-3/4	3-3/4	32525-7	38525-7
3	6-1/2	13	4-1/2	32530-7	38530-7
4	8-5/8	17-1/4	6	32540-7	38540-7




True "Wye" – Wye True Clamp Ends (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	316L STOCK NO.
1	2-1/2	2-7/8	381810-7
1-1/2	2-1/2	2-15/16	381815-7
2	3-1/8	3-3/4	381820-7
2-1/2	3-7/8	4-5/8	381825-7
3	4-1/2	5-3/8	381830-7
4	6	7-3/16	381840-7
6	7	8-11/16	381860-7



Lateral "Wye" – Wye Lateral Clamp Ends (3-A) 32R_a ID/32R_a OD

SIZE (TUBE O.D.)	A	B	C	D	E	316L STOCK NO.
1/2	4	2-7/32	1-3/4	2-1/4	3-1/8	381705-7
3/4	4	2-7/32	2 1-3/4	2-1/4	3-1/8	381707-7
1	5-1/2	2-1/4	1-3/4	2-15/16	3-7/16	381710-7
1-1/2	5-1/2	2-1/4	1-3/4	3-9/16	4-5/16	381715-7
2	6-5/8	3-1/8	2-3/8	4-13/16	5-9/16	381720-7
2-1/2	7-7/8	3-7/8	2-7/8	5-7/8	6-7/8	381725-7
3	9	4-1/2	3-5/16	6-29/32	8-3/32	381730-7
4	13-1/4	6	4-7/16	9-5/16	10-13/16	381740-7
6	22-1/2	11-3/32	8	15-1/4	18-11/32	381760-7



AVAILABLE IN 316L ONLY

Gasket Clamp Type FDA Compliant



O-ring

40MP-U BUNA N
40MP-UW BUNA WHITE
40RX-PX SILICONE
40MP-E EPDM
40MP-G PTFE
40MP-SFY FKM



FLANGED (TYPE 2)

40MPF-U BUNA N
40RX-PX SILICONE
40MPF-E EPDM
40MPF-SFY FKM



ENVELOPE (TYPE 3)

A40MP-GR PTFE

ALSO AVAILABLE

BEVEL SEAT
JOHN PERRY

Clamps

Clamp Fittings




13MHM - Clamp Heavy Duty Double Pin Tumble Finish

SIZE RANGE: 1" - 10" TUBE O.D.

SIZE (TUBE O.D.)	A	304 STOCK NO.
1 & 1-1/2	2.140	329915
2	2.610	329920
2-1/2	3.141	329925
3	3.673	329930
4	4.776	329940
8	8.695	329980
10	10.695	3299100

NOTE: ROCKET STYLE WING NUT AVAILABLE UPON REQUEST - GO TO topln.co/rocket




Clamp Heavy Two Piece Double Wing Nut Tumble Finish

12" TUBE O.D.

SIZE (TUBE O.D.)	304 STOCK NO.
12	32992120

NOTE: ROCKET STYLE WING NUT AVAILABLE UPON REQUEST - GO TO topln.co/rocket




13LAH – Clamp Heavy Duty Single Pin Tumble Finish

SIZE RANGE: 1/2" - 8" TUBE O.D.

SIZE (TUBE O.D.)	A	304 STOCK NO.
1/2 & 3/4	1.125	389905B
1 & 1-1/2	2.140	3299915
2	2.610	3299920
2-1/2	3.141	3299925
3	3.673	3299930
4	4.776	3299940
6	6.695	3299960
8	8.700	3299980

NOTE: ROCKET STYLE WING NUT AVAILABLE UPON REQUEST - GO TO topln.co/rocket




13MHP – Clamp High Pressure with Aluminum Bronze Nuts Tumble Finish

SIZE RANGE: 1/2" - 6" TUBE O.D.

SIZE (TUBE O.D.)	A	304 STOCK NO.
1/2 & 3/4	1.125	329907HP
1 & 1-1/2	2.046	329915HP
2	2.578	329920HP
2-1/2	3.110	329925HP
3	3.640	329930HP
4	4.744	329940HP
6	6.632	329960HP


WITH ALUMINUM BRONZE NUTS



13MHHS – Clamp Heavy Duty 3-Segmented Tumble Finish

SIZE RANGE: 1" - 4" TUBE O.D.

SIZE (TUBE O.D.)	A	304 STOCK NO.
1 & 1-1/2	2.140	3299153
2	2.610	3299203
2-1/2	3.141	3299253
3	3.673	3299303
4	4.776	3299403



for psi clamp service rating go to topln.co/clamppsi



Always Giving You
Top of the Line Service
and Quality

Contact your Top Line Representative for Assistance

Office: P.O. Box 264 • Bradford, PA 16701

Plant: 21 Valley Hunt Drive • Lewis Run, PA 16738

800-458-6095

814-362-4626

Fax: 814-362-4453

Top Line is a leading supplier of sanitary stainless steel process equipment. Serving the food, beverage, dairy, pharmaceutical, biotechnological and personal care industries. For over 50 years we've provided our customers with exceptional customer service and quality products. We are committed to meeting the fastest delivery, new product development and application engineering to meet all our customer's needs with our extensive inventory and expert sales team.

Top Line specializes in stainless steel materials – type 304 and 316L. Our modern, well equipped manufacturing facilities are staffed by skilled and dedicated craftsmen. Consistently meeting important tolerances and finish specifications is of primary concern to us. Before any products leave our plant they are subjected to rigid quality assurance checks.

Top Line should always be considered your first choice for both standard and custom fabricated stainless steel products.

Limited Warranty

Top Line Process Equipment Company products are warranted to be free of defects in material or workmanship for a period of one year from date of shipment. Warranty covers those Top Line products used in an approved installation and maintained in strict accordance with recognized standard industry practice. If, after properly authorized return, Top Line determines that products are defective, Top Line may at its option, repair or replace such defective products.

Top Line shall not be liable for consequential, indirect or incidental damages. The above warranty is in lieu of all other warranties, expressed or implied.

www.toplineonline.com