

REPLACEMENT PARTS LIST

Residential Gas Manufactured Home Direct Vent Models



"RG2DVMH" MODELS


Effective: June, 2018 ECO 8195


NOTE: BOTH MODEL AND SERIAL NUMBERS ARE REQUIRED FOR ORDERING REPLACEMENT PARTS


Dimensions and specifications subject to change without notice.



As required by the state of California Proposition 65.









Item	Description	Model	Model
		RG2DVMH30T*(N,X)	RG2DVMH40T*(N,X)
1	Heat Trap Insert (Outlet)	239-45167-00	239-45167-00
2	Nipple outlet 3/4 NPT X 3	229-50053-03	229-50053-03
3	Hole Closure	239-31547-02	239-31547-02
4	Flue Baffle	243-37307-00	243-37307-00
5	Hex Anode (Magnesium) #	224-47782-08	224-47782-08
	Hex Anode (Aluminum) #	224-47783-08	224-47783-08
	Hex Anode (A420 Aluminum) #	224-49559-04	224-49559-04
6	T & P Valve	230-40594-02	230-40594-02
7	Inner Door Assembly	243-42658-00	243-42658-00
8	Outer Door	243-41061-00	243-41061-00
9	Brass Drain Valve	265-42351-02	265-42351-02
10	Nat. Gas Thermostat (W.R.)***	265-40595-03	265-40595-03
	L.P. Gas Thermostat (W.R.)***	265-40595-04	265-40595-04
11	ASSE Approved Mixing Valve (Optional)	239-51778-00	239-51778-00
12	Roof Jack 12" (Fixed)	239-37022-01	239-37022-01
	Roof Jack 18-32" (Adjustable)	239-37022-02	239-37022-02
	Roof Jack 32-60" (Adjustable)	239-37022-03	239-37022-03
	Roof Jack 48-95" (Adjustable)	239-37022-04	239-37022-04
13	Nat. Gas Burner Assembly Complete***	265-43980-02-40	265-43980-03-40
	LP Gas Burner Assembly Complete***	265-43981-02-52	265-43981-03-52
14	Gas Burner	228-41174-00	228-41174-00
15	Nat. Gas Main Burner Orifice 0 Ft. to 2,000 Ft.	234-37171-40	234-37171-40
	Nat. Gas High Altitude 0 Ft. to 7,000 Ft. (-475 model suffixes)	234-37171-43	234-37171-43
	LP Gas Main Burner Orifice 0 Ft. to 2,000 Ft.	234-37171-52	234-37171-52
	LP Gas High Altitude 0 Ft. to 7,000 Ft. (-475 model suffixes)	234-37171-53	234-37171-53
16	Nat. Gas Pilot Assembly	233-40248-05	233-40248-05
	LP Gas Pilot Assembly	233-40261-03	233-40261-03
17	Gas Feedline	233-41819-04	233-41819-05
	LP to NAT gas conversion kit	243-36998-04	243-36998-04
	LP to NAT Gas Conversion kit for 0 Ft. to 7,000 Ft. (-475 model suffixes)	243-36998-05	243-36998-06
	NAT to LP gas conversion kit	243-36999-07	243-36999-07
	NAT to LP Gas Conversion kit for 0 Ft. to 7,000 Ft. (-475 model suffixes)	243-36999-08	243-36999-09
18	Air intake kit gasket	265-41135-00	265-41135-00
10	Telescoping air intake kit	265-41142-00	265-41142-00
19	releacuping an indre rit	200-41142-00	203-41142-00

*Applies to all warranties

***Ordering a complete burner assembly may increase delivery time.

Please order the specific component required for the quickest delivery.

Anode may need to be cut to length





Ambler, PA

For U.S. and Canada field service, contact your professional installer or local Bradford White sales representative.

Sales/800-523-2931

Technical Support/800-334-3393 Email/techserv@bradfordwhite.com

Warranty/**800-531-2111** Email/**warranty@bradfordwhite.com**

Service Parts/800-538-2020 Email/Parts@bradfordwhite.com

International: international@bradfordwhite.com



Halton Hills, Ontario, Canada

Sales & Technical Support/866-690-0961 905-203-0600

Fax/905-636-0666

Email

Warranty/**bwccwarranty@bradfordwhite.com** Technical Support/**BWCCTech@bradfordwhite.com** Parts/**orders@bradfordwhitecanada.com** Orders/**ca.orders@bradfordwhite.com**

www.bradfordwhite.com