



9W LED MR16 3000K FLOOD DIMMABLE 80CRI 12V

Item #771327

Ordering Code LED9MR16FL35/75/830/D

UPC 739698771359

- Chip on board (COB) design presents a clean, appealing look
- Rated for use in totally enclosed fixtures
- Dimmable on a wide variety of dimmer types
- Compatible with a wide variety of transformers
- UL rated for damp locations
- 9W LED = 75W HALOGEN



## TECHNICAL SPECIFICATIONS

Item #	Watts	Bulb Type	Base	Volts	Finish/Description	Beam Angle (°)	Color Temperature (CCT)
771327	9	MR16	GU5.3	12	N/A	35	3000K
Color	CRI	Lumens	CBCP	Average Hours	M.O.L. (inches)	M.O.D. (inches)	Incandescent Equivalent
Soft White Light	80	685	1850	25000	1.870	1.970	75W
Energy Star	DLC	Title 24 Compliant	Safety Rated	Safety Rating Type	Enclosed Rated	Dimmable	Warranty
Y	N	N	UL	DAMP	Y	Y	5

Order Multiple  
QTY  
10

## APPLICATION SUGGESTIONS



Landscape



Pendant /  
Downlight



Recessed



Track