BULBRITE® LED Filaments

featuring

The Largest Collection of Nostalgic LED Filaments on the Market

Limitless options inspire limitless design



BULBRITE® LED Filaments

featuring
The Largest Collection of Nostalgic LED Filaments on the Market
from the Nostalgic Experts
Nostalgic and Clear Finishes | Candelabra or Medium Base | Dimmable



Nostalgic LED Filaments



Standard LED Filaments
pages 10 - 15



A small step toward design excellence

- Candelabra base for use in chandeliers and sconces.

- Ideal for decorative lighting in homes and commercial areas
 Long life LEDs for lasting vintage appeal 15,000 hours
 Antique finish for authentic vintage feel with very warm 2200K LED filaments
 Dimmable with Electronic Low Voltage (ELV) dimmers
- UL rated for damp locations







miniNostalgic Tubular **LED Filament**

LED2T6/22K/FIL-NOS



miniNostalgic Globe **LED Filament**

G16 LED2G16/22K/FIL-NOS

miniNOSTALGIC CHANDELIER CA10 miniNOSTALGIC TUBULAR T6 miniNOSTALGIC GLOBE G16 WATTS **BULB TYPE CA10** Т6 G16 E12 BASE ITEM # 776503 776504 776506 ORDERING CODE LED2CA10/22K/FIL-NOS LED2T6/22K/FIL-NOS LED2G16/22K/FIL-NOS **LUMENS** 180 180 180 LENGTH 3 %" 3 3/8" 3 1/8"





A classic shape to add nostalgic flare

- Medium base for use in outdoor lanterns, ceiling fixtures and pendants
- Designed with extra long filaments for authenticity
- Long life LEDs for lasting vintage appeal 15,000 hours
- Antique finish for authentic vintage feel with very warm 2200K LED filaments
- Dimmable with Electronic Low Voltage (ELV) dimmers

UL rated for damp locations



Nostalgic Signature LED Filament

ST18

LED4ST18/22K/FIL-NOS


	NOSTALGIC SIGNATURE ST18		
WATTS	4		
BULB TYPE	ST18		
BASE	E26		
ITEM #	776501		
ORDERING CODE	LED4ST18/22K/FIL-NOS		
LUMENS	350		
LENGTH	5"		





Create a vintage focal point

- Medium base for use in outdoor lanterns, ceiling fixtures and pendants
- Designed with extra long filaments for authenticity
- Long life LEDs for lasting vintage appeal 15,000 hours
- Antique finish for authentic vintage feel with very warm 2200K LED filaments
- Dimmable with Electronic Low Voltage (ELV) dimmers
- UL rated for damp locations








BULBRITE

Traditional shape with a sophisticated design

- Medium base for use in outdoor lanterns, ceiling fixtures and pendants
- Long life LEDs for lasting vintage appeal 15,000 hours
- Antique finish for authentic vintage feel with very warm 2200K LED filaments
- Dimmable with Electronic Low Voltage (ELV) dimmers
- UL rated for damp locations



	NOSTALGIC A19	
WATTS	4	
BULB TYPE	A19	
BASE	E26	
ITEM #	776502	
ORDERING CODE	LED4A19/22K/FIL-NOS	
LUMENS	300	
LENGTH	4 1/8"	





Functional light with an attractive look

- Chandelier options with a candelabra base for use in chandeliers and sconces
- Chandelier options with a medium base for use in outdoor lanterns and sconces
- Collared chandelier replicates incandescent dimming and works with a wide variety of dimmers
- Non-collared chandeliers dimmable on Electronic Low Voltage (ELV) dimmers
- Long life LEDs for lasting vintage appeal 15,000 hours
- Clear finish for a traditional look with warm 2700K LED filaments
- UL rated for damp locations



	DIMMABLE CHANDELIER B11	NON-DIMMABLE CHANDELIER B11	NON-DIMMABLE CHANDELIER B11	NON-DIMMABLE CHANDELIER B11
WATTS	4	2	4	4
BULB TYPE	B11	B11	B11	B11
BASE	E12	E12	E12	E26
ITEM #	776552	776555	776556	776557
ORDERING CODE	LED4B11/27K/FIL/D	LED2B11/27K/FIL/E12	LED4B11/27K/FIL/E12	LED4B11/27K/FIL
LUMENS	400	200	350	350
LENGTH	4 ¼"	3 %"	3 %"	3 ¼"





BULBRITE


General purpose lighting with the look your used to

- Medium base for use in outdoor lanterns, ceiling fixtures and pendants
- Dimmable A-Shape replicates incandescent dimming and works with a wide variety of dimmers
- Long life LEDs for lasting vintage appeal 15,000 hours
- Clear finish for a traditional look with warm 2700K LED filaments
- LED Filament bulbs are UL damp listed



	DIMMABLE A-SHAPE A19		
WATTS	7		
BULB TYPE	A19		
BASE	E26		
ITEM #	776550		
ORDERING CODE	LED7A19/27K/FIL/D		
LUMENS	700		
LENGTH	4 1/4"		





Longer lasting for more reliabe lighting

- Ideal for amusement and theatrical lighting
- Long life LEDs for lasting vintage appeal 15,000 hours
- Dimmable with Electronic Low Voltage (ELV) dimmers
- Clear finish for a traditional look with warm 2700K LED filaments
- UL rated for damp locations



S-Shape LED Filament S14 LED2S14/27K/FIL



BULBRITE® LED Filaments

Limitless options inspire limitless design

Bulbrite's LED Filament series replicates the look and feel of traditional incandescent lighting. Providing warm lighting in a shape you're used to, these bulbs are an easy step into energy efficient lighting that looks good. Featuring the largest collection of Nostalgic LED Filament bulbs, these bulbs are the perfect complement to any décor.

LED Filaments At A Glance:

- Variety of shapes, bulb types, bases and finishes
- Collared LED Filaments replicate incandescent dimming and works with a wide variety of dimmers
- Non-collared LED Filaments dimmable on Electronic Low Voltage (ELV) dimmers
- Excellent LED replica of antique bulbs
- Nostalgic varieties feature extra long filaments for authenticity
- Ideal for pendants, outdoor lanterns, chandelier, sconces, ceiling fixtures and retail, restaurant and hotel applications

Contact our American Lighting Association (ALA) and Lightopedia.com Certified Lighting Specialists at 800-528-5555 or info@bulbrite.com to find out which LED Filament bulbs can make an impact on your design today.





145 West Commercial Ave • Moonachie, NJ 07074 | info@bulbrite.com | 800-528-5555