

A man in a blue and white checkered shirt and khaki shorts is sitting in a black leather chair, reading a newspaper. He is holding a glass of coffee with a straw. The chair is positioned in front of a fireplace. A Casablanca ceiling fan with five wooden blades and a central light fixture is mounted on the ceiling. The scene is set in a living room with a fireplace, a vase of dried flowers, and a coffee table.

CRAFTED *to*  
PERFECTION

CASABLANCA®  
FAN COMPANY



## INSPIRED BY THE WORLD AROUND US. CRAFTED FOR YOUR LIVING ROOM.

We've never been ones to blindly follow the latest trends. We prefer to explore, imagine, lead and set the trends ourselves. Our world-class designers stay away from the safe confines of the status quo, seeking inspiration in the world around them. And as we begin to turn that inspiration into something beautiful and exquisite, we don't use computers or restrictive templates. Each design is hand sketched to capture every painstaking detail of our vision.

After inspiration finds its way onto paper, we build the fan out ourselves to guarantee every aspect of the fan is crafted to perfection. We guide the entire process, assuring each model lives up to our reputation of breathtaking design, highest-quality materials, innovative engineering and flawless functionality. And then, we put each fan through the most rigorous testing the industry has ever known. The result is a fan that's not just a fan, but a conversation-generating centerpiece of any room in your home.

**CASABLANCA**<sup>®</sup>  
FAN COMPANY



ELEGANCE  
with a personal touch.

## WHY CASABLANCA IS THE WORLD'S FINEST CEILING FAN.

### INSPIRED DESIGN

Our designers put their stamp on each fan, taking inspiration from the world's most celebrated architecture. Designs are hand sketched to give every model an organic look that our artisans bring to life.

### METICULOUS DETAILS

From premium materials and ornate design to seamless transitions and hidden hardware, we fret over each and every detail to deliver your home's newest masterpiece.

### CUSTOM BEAUTY

A wide variety of blade styles that are compatible with all new fans makes it easier than ever to add your very own personal touch. And with a streamlined offering of light fixtures, you'll find the perfect lighting option to complement your style and taste.

### RIGOROUS TESTING

We hold ourselves to a much higher standard than the industry does. A 20,000 repetitions shake test, a drop test that's six inches higher than regulation, UV chamber testing and random quality assurance tests that aren't required. These are just a few of the ways we stand above the competition to assure your fan will last.

### THE VERY BEST MOTORS

Engineered to work flawlessly over the life of your fan, our high-end motors are ENERGY STAR® qualified and at the top of their class in air movement. All while being the industry's most quiet designs.

### INNOVATIVE CONTROLS

Highly advanced yet simple to use, our all-in-one control makes it extremely easy to get the most out of your Casablanca ceiling fan.





## DESIGNED FOR YOU AND THE WORLD YOU LIVE IN.

Seeking excellence doesn't stop with design and engineering. We put thousands of hours into developing a fan that's more efficient, so you can feel good about your energy savings and your contribution to the environment. Casablanca motors move more cubic feet of air per minute (CFM) while using significantly less energy. Fan blades are set at the optimum pitch to deliver maximum airflow at any speed. Even at the highest setting, each fan uses about the same amount of power as a 100-watt lightbulb.



Our new fans are ENERGY STAR® qualified along with many that were already part of the Casablanca collection. This means they provide even greater energy efficiency. Look for the ENERGY STAR logo throughout the catalog. Specific fan models are equipped with highly efficient compact fluorescent bulbs, and are California 24 compliant for maximum energy savings.

To simplify things, we've included this informational energy chart for every fan:

Airflow:	Electricity Use:	Airflow Efficiency:
X,XXX cfm	XX w	XX cfm/w

*38" to 48" ceiling fans have airflow efficiencies ranging from approximately 71 to 86 cubic feet per minute per watt at high speed.*

*49" to 60" ceiling fans have airflow efficiencies ranging from approximately 51 to 176 cubic feet per minute per watt at high speed.*

CONSERVATION TIP: Operating a fan in an unoccupied room wastes energy, so turn it off when leaving the room.

### QUALITY CRAFTSMANSHIP BACKED BY 120-DAY IN-HOME SERVICE

Attention to detail continues past the design and creation of our fans. Should you have any concerns with your Casablanca fan, a trained representative will be sent to your home to service it. Simply call us at 1-888-227-2178 for referral to your local Authorized Service Center. If In-Home Service is not available in your area, Casablanca offers pre-paid freight for you to send the fan to the Casablanca Factory Service Center. It will be repaired and returned to you at no charge.

Casablanca's Comprehensive Warranty, the most extensive in the industry, also includes:

### LIFETIME MOTOR WARRANTY

All Casablanca fan motors, even on Damp- and Wet-rated models, are guaranteed for life.

### ONE-YEAR PARTS AND ELECTRONICS WARRANTY

Each fan includes a one-year warranty on finish, component parts, accessories and electronics.

With this extensive coverage, you can enjoy the beauty, quality and performance of your Casablanca products for decades to come.



# TABLE OF CONTENTS

## CEILING FANS

### CUSTOM CASABLANCA

Introduction & Blade Choices	10-13
Holliston	14
Coletti	15
Areto	16
Adelaide	17
Capistrano	18
Brescia Control	19
Brescia Pullchain	20
Academy	21
Charthouse	22
Panama Control	23
Panama Pullchain	24
Panama XLP Control	25
Compass Point	26

### TRADITIONAL

Fordham	29
Alessandria	30
Ainsworth 60"	31
Ainsworth Gallery 60"	32
Ainsworth 54"	33
Ainsworth Gallery 54"	34
Concentra	35
Concentra Gallery	36
Panama Gallery	37-38
Panama DC	39
Capistrano Gallery	40
Victorian	41
19th Century	42

### TRANSITIONAL

Academy Gallery	45
Holliston Gallery	46
Whitman	47
Bel Air	48
Fellini	49
Fellini DC	50
Utopian	51
Utopian Gallery	52

### CONTEMPORARY

Zudio	55
Aris	56
Riello	57
Stealth DC	58
Stealth	59-60
Bullet	61

Tercera	62
Tribeca 60"	63
Tribeca 52"	64
Malibu Star	65
Trident	66

### LOW PROFILE

Durant (with Light Kit) 54"	69
Durant (w/o Light Kit) 54"	70
Durant 44"	71
Caledonia	72
Isotope 52"	73
Isotope 44"	74

### DÉCOR SPECIFIC

Candelier II	77
Mission	78

### OUTDOOR

Heathridge	81
Caneel Bay	82
Heritage	83
Atria	84
Wailea	85
Charthouse	86
Compass Point	87
Capistrano	88
Utopian	89
Utopian Gallery	90
Aris	91
Panama Pullchain	92
Panama Control	92

## ACCESSORIES

Lighting	95-98
Controls	99-100
Lighting Compatibility Guide	101-102
Hanging System	103-104

## SPECIFICATIONS

Ceiling Fan Specs	105-108
Motor Finish Reference Chart	109-110
Motor Finishes	111

## INDEXES

Numerical and Alphabetical . . . . . Inside Back Cover

## ICON LEGEND

### SPECIAL FEATURES

	INCLUDES XLP MOTOR
	INCLUDES DC MOTOR
	ENERGY STAR® QUALIFIED
	ETL WET RATED FAN
	ETL DAMP RATED FAN
	CUSTOM CASABLANCA

### BLADES

	COMPATIBLE WITH CUSTOM CASABLANCA AND OTHER NEW COLLECTIONS
	COMPATIBLE WITH EXCLUSIVE BLADES
	COMPATIBLE WITH BADGE-STYLE BLADES
	DUST ARMOR

### LIGHTING

	INCLUDES DOWNLIGHT
	INCLUDES UPLIGHT OR ACCENT LIGHT
	INCLUDES LED LIGHT



# CUSTOM CASABLANCA

## BLADES any style

CHOOSE YOUR BLADE INSIDE





# BUILD YOUR DREAM FAN

## STEP 1



**DETERMINE IF YOUR FAN IS FOR INDOOR OR OUTDOOR USE**  
Any Casablanca fan can be installed indoors, but look for these icons to quickly see if the fan is also rated for outdoor use.

## STEP 2

**SELECT YOUR MOTOR DESIGN AND FINISH**  
Each collection page shows available motor styles and finishes.

## STEP 3

**CHOOSE YOUR BLADE FINISH AND SHAPE**  
The foldout on page 11 will serve as an easy side-by-side reference to help you select the perfect blade set for your fan.

## STEP 4

**SELECT YOUR LIGHT FIXTURE AND GLASS**  
Look for our design team's lighting recommendation for each collection, or choose from all available options shown on pages 95-98.

## STEP 5

**DECIDE IF YOU NEED AN ACCESSORY CONTROL**  
Every fan comes with either a wall control or 4-speed pullchain, but you can choose to add the optional remote control.

Get help creating your dream fan at [www.customcasablanca.com](http://www.customcasablanca.com)



### 59534

Brushed Nickel motor

Not included (shown with):  
99007 Smoked Walnut / Espresso veneer blades

The Holliston ceiling fan combines classic style with ultimate performance and convenience.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- 188 x 20 motor
- Light kits sold separately

## HOLLISTON



### MOTOR FINISHES



#### A: 59533

Snow White motor shown with 99005 Matte Snow White / Cottage White blades

#### B: 59534

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades

#### C: 59535

Antique Brass motor shown with 99006 Walnut / Burnt Walnut veneer blades

### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



### LIGHTING

Our design team's recommended lighting option.

#### 99103

Four-Light Fitter in Brushed Nickel



#### 99041

2 1/4" Side Glass with Slant Shape in Cased White

For all other compatible light fixtures, see pages 95-98.

### CONTROLS



**Included**  
4-Speed Pullchain



#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)

Dimensions		Airflow
A:	12.47"	7,001 cfm
B:	10.50"	Electricity Use
C:	2.75"	85 w
D:	13.94"	Airflow Efficiency
E:	6.49"	82.37 cfm/w
F:	-	

\*Energy information based on 99004 blade set.



### 55056

Cottage White motor

Not included (shown with):  
99017 Cottage White All-Weather blades

Old World collides with New in this simple—yet elegant—design. Add class and style to both traditional and modern interiors.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- 188 x 20 motor
- Light kits sold separately

COLETTI



### 54121

Industrial Rust motor

Not included (shown with):  
99006 Walnut / Burnt Walnut veneer blades

For a modern look you can still make your own, the Areto can't be beat. Custom Casablanca's most contemporary fan design to date.


#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- 172 x 20 motor
- Light kits sold separately

ARETO



#### MOTOR FINISHES



#### A: 55054

Aged Bronze motor shown with 99011 carved wood blades


#### B: 55055

Brushed Cocoa motor shown with 99015 Distressed Antique Halifax All-Weather blades

#### C: 55056

Cottage White motor shown with 99017 Cottage White All-Weather blades

#### MOTOR FINISHES



#### A: 54120

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades

#### B: 54121

Industrial Rust motor shown with 99006 Walnut / Burnt Walnut veneer blades

#### C: 54122

Snow White motor shown with 99005 Matte Snow White / Cottage White blades

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99023

Glass Bowl Fitter

#### 99062

Toffee Glass Bowl

For all other compatible light fixtures, see pages 95-98.

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99023

Glass Bowl Fitter

#### 99059

Cased White Glass Bowl

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS




Included  
4-Speed Pullchain



#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



\*Energy information based on 99004 blade set.

#### CONTROLS




Included  
4-Speed Pullchain



#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



\*Energy information based on 99004 blade set.



### 54117

Aged Bronze motor

Not included (shown with):  
99015 Distressed Antique Halifax All-Weather blades

When a room beckons for something simple, this new customizable fan answers the call. Introducing the industry's simplest "design your fan" system.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- 172 x 20 motor
- Light kits sold separately

ADELAIDE



### 54029

Brushed Nickel motor

Not included (shown with):  
99007 Smoked Walnut / Espresso veneer blades

Subtle sophistication is a dominant theme in today's décor. Nothing complements this attitude like the Capistrano, with a soft, sculpted look and the nautical suggestion of seashells.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- Select models ETL rated for damp or humid locations
- 172 x 20 motor
- Light kits sold separately

CAPISTRANO®



#### MOTOR FINISHES



A

B

C

#### A: 54116

Antique Brass motor shown with 99002 veneer blades


#### B: 54117

Aged Bronze motor shown with 99015 Distressed Antique Halifax All-Weather blades

#### C: 54118

Snow White motor shown with 99017 Cottage White All-Weather blades

#### MOTOR FINISHES



A

B

C

#### A: 54028

Snow White motor shown with 99001 Matte Snow White / Cottage White blades



#### B: 54029

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades

#### C: 54030

Brushed Cocoa motor shown with 99003 Vintage Rosewood / Wine Country Distressed veneer blades



#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99091

Outdoor Four-Light Fixture in Maiden Bronze

For all other compatible light fixtures, see pages 95-98.

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99023

Glass Bowl Fitter

#### 99062

Toffee Glass Bowl

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS

Included  
4-Speed Pullchain



#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)

Dimensions		Airflow
A:	13.11"	6,289 cfm
B:	11.70"	Electricity Use
C:	2.75"	80.4 w
D:	13.99"	Airflow Efficiency
E:	6.49"	78.23 cfm/w
F:	-	

\*Energy information based on 99004 blade set.

#### CONTROLS

Included  
4-Speed Pullchain



#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)

Dimensions		Airflow
A:	13.12"	6,496 cfm
B:	11.67"	Electricity Use
C:	2.75"	82.5 w
D:	12.50"	Airflow Efficiency
E:	6.50"	78.7 cfm/w
F:	-	

\*Energy information based on 99004 blade set.



### 55019

Brushed Nickel motor

Not included (shown with):  
99007 Smoked Walnut / Espresso veneer blades

Traditional style meets modern functionality. The same artisan-inspired feel of the classic Brescia with innovative four-speed wall control.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade finish choices available (blades sold separately)
- 188 x 20 motor
- Light kits sold separately

## BRESCIA CONTROL



### 55015

Brushed Cocoa motor

Not included (shown with):  
99009 Walnut / Burnt Walnut veneer blades

The Brescia fan brings warmth and beauty to any room setting. For Arts and Crafts-inspired look, select richly toned wood blades.


#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade finish choices available (blades sold separately)
- 188 x 20 motor
- Light kits sold separately

## BRESCIA PULLCHAIN



#### MOTOR FINISHES




#### A: 55019

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades

#### B: 55020

Maiden Bronze motor shown with 99006 Walnut / Burnt Walnut veneer blades

#### MOTOR FINISHES



#### A: 55015

Brushed Cocoa motor shown with 99009 Walnut / Burnt Walnut veneer blades

#### B: 55016

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99103

Four-Light Fitter in Brushed Nickel

#### 99041

2 1/4" Side Glass with Slant Shape in Cased White

For all other compatible light fixtures, see pages 95-98.

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99090

Outdoor Four-Light Fixture in Brushed Cocoa

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS



#### Included


New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



#### 99020 (optional)

New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	12.12"	7,282 cfm
B:	10.54"	Electricity Use
C:	2.75"	88 w
D:	14.04"	Airflow Efficiency
E:	6.49"	83 cfm/w
F:	-	

\*Energy information based on 99004 blade set.

#### CONTROLS



#### Included


4-Speed Pullchain



#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	12.12"	7,533 cfm
B:	10.54"	Electricity Use
C:	2.75"	86 w
D:	14.04"	Airflow Efficiency
E:	6.49"	87.7 cfm/w
F:	-	

\*Energy information based on 99004 blade set.



### 54084

Brushed Nickel motor

Not included (shown with):  
99007 Smoked Walnut / Espresso veneer blades

The smart-looking Academy teaches an important lesson in design flexibility. Its transitional styling and wide selection of finish options make this ceiling fan a scholarly choice for living rooms, great rooms, bedrooms or almost any other room in the house.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- 172 x 20 motor
- Light kits sold separately

ACADEMY™



### 55012

Cottage White motor

Not included (shown with):  
99014 Cottage White Beadboard All-Weather blades

Transport yourself to a secluded beach house from any room in your home. With its delightfully simple styling, the Charthouse creates a relaxed, airy feel that will truly take you away. Choose the perfect blade and finish combination to match your style.


#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- ETL rated for wet locations
- 188 x 20 motor
- Light kits sold separately

CHARTHOUSE™



#### MOTOR FINISHES



A

B

C

#### A: 54083

Snow White motor shown with 99005 Matte Snow White / Cottage White blades


#### B: 54084

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades

#### C: 54085

Maiden Bronze motor shown with 99006 Walnut / Burnt Walnut veneer blades

#### MOTOR FINISHES



A

B

C

#### A: 55010

Maiden Bronze motor shown with 99016 Plantation Wicker All-Weather blades

#### B: 55011

Aged Bronze motor shown with 99018 Espresso All-Weather blades

#### C: 55012

Cottage White motor shown with 99014 Cottage White Beadboard All-Weather blades

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99103

Four-Light Fitter in Brushed Nickel

#### 99041

2 1/4" Side Glass with Slant Shape in Cased White

For all other compatible light fixtures, see pages 95-98.

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99077

Low Profile Fitter in Maiden Bronze

#### 99084

Low Profile Glass in Toffee

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS

Included  
4-Speed Pullchain




#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)\*



\*Energy information based on 99004 blade set.

#### CONTROLS

Included  
4-Speed Pullchain




#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)\*



\*Energy information based on 99004 blade set.



### 55032

Antique Brass motor

Not included (shown with):  
99003 Wine Country Distressed / Vintage Rosewood Distressed veneer blades

Everything you could possibly want in a fan—timeless classic design, superb air movement, energy efficiency and a variety of motor finish, blade and lighting options. The Panama Control could be the only fan you ever need.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 52"-58" blade span
- Multiple blade finish choices available (blades sold separately)
- Select models ETL rated for damp or humid locations
- 188 x 20 motor
- Light kits sold separately

## PANAMA® CONTROL



### 55023

Aged Bronze motor

Not included (shown with):  
99002 Walnut / Burnt Walnut veneer blades

All the pluses of the Panama with an added pullchain. Classic design, excellent air movement, energy efficiency and a wide variety of motor finish, blade and lighting options. No need to look any further.


#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 52"-58" blade span
- Multiple blade finish choices available (blades sold separately)
- Select models ETL rated for damp or humid locations
- 188 x 20 motor
- Light kits sold separately

## PANAMA® PULLCHAIN



#### MOTOR FINISHES




#### A: 55027

Snow White motor shown with 99001 Matte Snow White / Cottage White blades



#### B: 55028

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades



#### C: 55029

Aged Bronze motor shown with 99002 Walnut / Burnt Walnut veneer blades



#### D: 55030

Brushed Cocoa motor shown with 99002 Walnut / Burnt Walnut veneer blades



#### E: 55031

Cottage White motor shown with 99014 Cottage White Beadboard All-Weather blades



#### F: 55032

Antique Brass motor shown with 99003 Wine Country Distressed / Vintage Rosewood Distressed veneer blades

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99052

Globe Fixture in Brushed Cocoa

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.


#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)\*



Dimensions	Airflow
A: 11.20"	7,375 cfm
B: 12.40"	Electricity Use 84 w
C: 2.75"	Airflow Efficiency 88 cfm/w
D: 12.00"	
E: 6.50"	
F: -	

\*Energy information based on 99004 blade set.

#### MOTOR FINISHES




#### A: 55021

Snow White motor shown with 99001 Matte Snow White / Cottage White blades



#### B: 55022

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades



#### C: 55023

Aged Bronze motor shown with 99002 Walnut / Burnt Walnut veneer blades



#### D: 55024

Brushed Cocoa motor shown with 99002 Walnut / Burnt Walnut veneer blades



#### E: 55025

Cottage White motor shown with 99014 Cottage White Beadboard All-Weather blades



#### F: 55026

Antique Brass motor shown with 99003 Wine Country Distressed / Vintage Rosewood Distressed veneer blades

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99087

Outdoor Four-Light Fixture in Aged Bronze

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS




**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions	Airflow
A: 11.20"	7,264 cfm
B: 12.40"	Electricity Use 91 w
C: 2.75"	Airflow Efficiency 80 cfm/w
D: 12.00"	
E: 6.50"	
F: -	

\*Energy information based on 99004 blade set.



### 59095

Cottage White motor

Not included (shown with):  
99001 Matte Snow White / Cottage White blades

Everything you could possibly want in a fan—timeless classic design, superb air movement, energy efficiency and a variety of motor finish, blade and lighting options. The Panama XLP Control could be the only fan you ever need.

#### FEATURES

- XLP 2000 / lifetime motor warranty
- 52"-58" blade span
- Multiple blade choices available (blades sold separately)
- Light kits sold separately

## PANAMA® XLP CONTROL



### 54011

Maiden Bronze motor

Not included (shown with):  
99015 Distressed Antique Halifax All-Weather blades

Amazing how something so simple can add so much to a room. One of our most distinctive designs. Built to last outside, making it a fine choice for covered porches and sunrooms. Available in two finishes with a wide range of accessory blade options.


#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- ETL rated for damp or humid locations
- 172 x 20 motor
- Light kits sold separately

## COMPASS POINT™



#### MOTOR FINISHES



#### A: 59095

Cottage White motor shown with 99001 Matte Snow White / Cottage White blades

#### B: 59096

Maiden Bronze motor shown with 99002 Walnut / Burnt Walnut veneer blades


#### C: 59097

Snow White motor shown with 99001 Matte Snow White / Cottage White blades

#### D: 59098

Brushed Nickel motor shown with 99007 Smoked Walnut / Espresso veneer blades

#### MOTOR FINISHES



#### A: 54010

Cottage White motor shown with 99017 Cottage White All-Weather blades

#### B: 54011

Maiden Bronze motor shown with 99015 Distressed Antique Halifax All-Weather blades

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99052

Globe Fixture in Brushed Cocoa

For all other compatible light fixtures, see pages 95-98.

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



#### 99091

Outdoor Four-Light Fixture in Maiden Bronze

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS



#### Included


New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



#### 99020 (optional)

New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)\*



\*Energy information based on 99004 blade set.

#### CONTROLS



#### Included


4-Speed Pullchain



#### 99019 (optional)

New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)\*



\*Energy information based on 99004 blade set.



TRADITIONAL

PANAMA GALLERY CEILING FAN  
*Inspired by your living room*



**53194**

Cottage White motor with Cottage White / Cottage White veneer blades

Just the right size and price. Add a touch of class to smaller rooms with this new fan that features intricate details on the housing.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 44" blade span
- Set of 5 blades included
- 172 x 12 motor
- Light kits sold separately

FORDHAM



MOTOR & BLADE FINISHES



A



B

**A: 53194**

Cottage White motor shown with Cottage White / Cottage White veneer blades

**B: 53195**

Brushed Cocoa motor shown with Distressed Walnut / Dark Walnut veneer blades

CONTROLS



**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

LIGHTING

Our design team's recommended lighting option.



**99105**


Four-Light Fitter in Brushed Cocoa

**99036**

2 1/4" Side Glass with Bell Shape in Amber Linen

For all other compatible light fixtures, see pages 95-98.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



**59057**

Brushed Cocoa motor with Reclaimed Antique blades

With a rich finish and exquisite detailing that echo the medallions and paneling of neoclassical architecture, the Alessandria ceiling fan is a timeless accent for the home. The fan's carved featherwood blades and fully dimmable lighting with Scavo glass add Old World warmth, elegance and comfort to interior settings.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span / 14° blade pitch
- Set of 5 exclusive carved featherwood blades included
- Integrated 75-watt uplight with five 15-watt bulbs included
- Integrated 100-watt downlight with two 50-watt T4 halogen bulbs included
- 172 x 20 motor

ALESSANDRIA



CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





### 55002

Provence Crackle motor with reversible Smoked Walnut / Espresso blades

It's all in the details. Painstakingly meticulous columns grace the motor housing to create a sophisticated, timeless look. A quality great room fan at an excellent value.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 60" blade span
- Set of 5 blades included
- Includes low-ceiling hanging option
- 188 x 20 motor
- Light kits sold separately

AINS WORTH 60"



### 55006

Onyx Bengal motor with reversible Distressed Walnut / Dark Walnut blades and Toffee glass

The classic architectural style of the Ainsworth, with a simple yet tasteful bowl light fixture. The perfect complement to any room. Comes with wall-mounted control.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 60" blade span
- Set of 5 blades included
- Includes three-light fitter with three 60-watt incandescent bulbs
- Includes low-ceiling hanging option
- 188 x 20 motor

AINS WORTH GALLERY 60"



#### MOTOR & BLADE FINISHES



#### A: 55000

Cottage White motor with Cottage White blades

#### B: 55001

Brushed Cocoa motor with reversible Dark Walnut / Distressed Walnut blades

#### C: 55002

Provence Crackle motor with reversible Smoked Walnut / Espresso blades

#### MOTOR & BLADE FINISHES



#### A: 55005

Cottage White motor with Cottage White blades and Snowflake Linen glass

#### B: 55006

Onyx Bengal motor with reversible Distressed Walnut / Dark Walnut blades and Toffee glass

#### C: 55007

Basque Black motor with reversible Smoked Walnut / Espresso blades and Champagne Scavo glass

#### CONTROLS



**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### LIGHTING

Our design team's recommended lighting option.



#### 99105


Four-Light Fitter in Brushed Cocoa

#### 99044

2 1/4" Side Glass with Ribbed Deco Shape in Cased White

For all other compatible light fixtures, see pages 95-98.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





### 54002

Basque Black motor with reversible Smoked Walnut / Espresso blades

The simple, timeless beauty of the Ainsworth in just the size you're looking for.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- Includes low-ceiling hanging option
- 172 x 20 motor
- Light kits sold separately

AINSWORTH 54"



### 54006

Onyx Bengal motor with reversible Distressed Walnut / Dark Walnut blades and Toffee glass

A truly distinguished look at just the right size. Complete with our ornate three-light fixture—one of Casablanca's finest.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- Includes three-light fitter with three medium-based CFL bulbs
- Includes low-ceiling hanging option
- 172 x 20 motor

AINSWORTH GALLERY 54"



#### MOTOR & BLADE FINISHES



A



B



C

#### A: 54000

Cottage White motor with Cottage White blades

#### B: 54001

Brushed Cocoa motor with reversible Dark Walnut / Distressed Walnut blades

#### C: 54002

Basque Black motor with reversible Smoked Walnut / Espresso blades

#### MOTOR & BLADE FINISHES



A



B



C

#### A: 54005

Cottage White motor with Cottage White blades and Snowflake Linen glass

#### B: 54006

Onyx Bengal motor with reversible Distressed Walnut / Dark Walnut blades and Toffee glass

#### C: 54007

Basque Black motor with reversible Smoked Walnut / Espresso blades and Champagne Scavo glass

#### CONTROLS



**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### LIGHTING

Our design team's recommended lighting option.



#### 99023


Glass Bowl Fitter in Brushed Cocoa

#### 99058

Glass Bowl in Tea Stain

For all other compatible light fixtures, see pages 95-98.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions	Airflow
A: 13.11"	6,125 cfm
B: 11.73"	Electricity Use
C: 2.75"	77.8 w
D: 12.41"	Airflow Efficiency
E: 6.49"	79 cfm/w
F: -	

#### CONTROLS




**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions	Airflow
A: 13.11"	6,125 cfm
B: 11.73"	Electricity Use
C: 2.75"	78 w
D: 12.41"	Airflow Efficiency
E: 6.49"	78.74 cfm/w
F: 19.56"	



**54021**

Brushed Nickel motor with reversible Walnut / Burnt Walnut blades

Traditional meets transitional in this simple, high-functioning fan. Outstanding air movement, ENERGY STAR® rated efficiency and Casablanca durability—all at the lowest price of any of our collections.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- 172 x 20 motor
- Light kits sold separately

CONCENTRA™



**54024**

Acadia motor with reversible Clove / Smoked Walnut blades and Tea Stain glass

The simple, chic combination of traditional and transitional design that you get from the Concentra fan, with an added bowl light fixture. And like the Concentra fan, it's one of our best values.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- Includes bowl light fixture with two medium-base CFL bulbs
- 172 x 20 motor

CONCENTRA™ GALLERY



**MOTOR & BLADE FINISHES**



**A: 54019**

Snow White motor shown with Matte Snow White blades

**B: 54020**

Brushed Cocoa motor shown with reversible Dark Walnut / Distressed Walnut blades

**C: 54021**

Brushed Nickel motor shown with reversible Walnut / Burnt Walnut blades

**MOTOR & BLADE FINISHES**



**A: 54022**

Snow White motor with Matte Snow White blades and Cased White glass

**B: 54023**

Brushed Nickel motor with reversible Walnut / Burnt Walnut blades and Cased White glass

**C: 54024**

Acadia motor with reversible Clove / Smoked Walnut blades and Tea Stain glass

**D: 54025**

Antique Brass motor with reversible Clove / Smoked Walnut blades and Champagne Scavo glass

**CONTROLS**



**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

**LIGHTING**

Our design team's recommended lighting option.



**99103**


Four-Light Fitter in Brushed Nickel

**99035**

2 1/4" Side Glass with Bell Shape in Cased White

For all other compatible light fixtures, see pages 95-98.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**



**CONTROLS**





**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**





PANAMA GALLERY    

**55060**


Maiden Bronze motor with Reclaimed Antique blades and Tea Stain glass

A classic, long-standing design is now an updated, modern model with five blades. Loaded with stylish, practical features, the Panama Gallery fan includes a four-light fixture perfect for the traditional look you are designing for.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- Includes four-light fitter with four candelabra incandescent bulbs
- 188 x 20 motor

MOTOR & BLADE FINISHES



A



B



C



D

- A: 55058**  
Architectural White motor with Architectural White blades and Cased White glass 
- B: 55059**  
Antique Pewter motor with Espresso blades and Cased White glass 
- C: 55060**  
Maiden Bronze motor with Reclaimed Antique and Tea Stain glass 
- D: 55061**  
Bright Brass Walnut motor with reversible Walnut / Burnt Walnut blades and Tea Stain glass

CONTROLS



**Included**


New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**

New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





**59512**

Brushed Cocoa motor with reversible Distressed Walnut / Burnt Walnut blades

A new spin on the original five-bladed fan, the Panama DC features a larger, 54-inch span and our extremely powerful DC motor. That means it can accommodate a larger room with higher efficiency—and it's ENERGY STAR® qualified. A new, true classic.

**FEATURES**

- DC motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- Light kits sold separately

PANAMA® DC



**54032**

Antique Pewter motor with reversible Smoked Walnut / Medium Chestnut blades and Cased White glass

A classic, long-standing design in an updated, modern model with five blades. Loaded with stylish, practical features, the Capistrano Gallery fan includes a four-light fixture and is known for being an excellent value.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- Includes four-light fitter with four candelabra incandescent bulbs
- 172 x 20 motor

CAPISTRANO® GALLERY




**MOTOR & BLADE FINISHES**



- A: 59510**  
Snow White motor with Matte Snow White blades
- B: 59511**  
Brushed Nickel motor with reversible Walnut / Burnt Walnut blades
- C: 59512**  
Brushed Cocoa motor with reversible Distressed Walnut / Burnt Walnut blades

**MOTOR & BLADE FINISHES**



- A: 54031**  
Acadia motor with reversible Smoked Walnut / Dark Walnut blades and Toffee glass
- B: 54032**  
Antique Pewter motor with reversible Smoked Walnut / Medium Chestnut blades and Cased White glass
- C: 54033**  
Snow White motor with Snow White blades and Cased White glass

**CONTROLS**



**Included**  
DC 6-speed  
Six-speed control with full-range light dimming and reversing.

**LIGHTING**

Our design team's recommended lighting option.



- 99255**  
CFL Low Profile Fitter in Brushed Cocoa
- 99073**  
Low Profile Glass in Cased White  
For all other compatible light fixtures, see pages 95-98.



**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**

		<b>Dimensions</b> A: 13.29" B: 11.69" C: 2.75" D: 12.00" E: 6.49" F: -	<b>Airflow</b> 6,675 cfm <b>Electricity Use</b> 32.4 w <b>Airflow Efficiency</b> 206 cfm/w
--	--	--	---

**CONTROLS**



**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**

		<b>Dimensions</b> A: 13.12" B: 11.67" C: 2.75" D: 12.50" E: 6.50" F: 19.00"	<b>Airflow</b> 5,965 cfm <b>Electricity Use</b> 83.1 w <b>Airflow Efficiency</b> 71.8 cfm/w
--	--	---	--



### 60129 (6373Z)

Oil-Rubbed Bronze motor

Not included (shown with):  
BIO3 Walnut blades

This is where it all began...the original Casablanca fan. The Victorian series marries classic turn-of-the-century appeal with contemporary innovation and convenience. The richness of the ornate design is enhanced with badge-style blade holders. Optimum performance is achieved with a 15° blade pitch.

#### FEATURES

- XLP-2000™ motor / lifetime motor warranty
- 54" blade span
- 4- or 5-blade configuration
- Multiple blade finish choices available (blades sold separately)

VICTORIAN®   sold separately



### 62063 (99U69Z)

Burnished Brass motor with Mahogany blades and optional exclusive KG99A-69 light fixture

In the electric era of the 1800s, fans were characterized by spiral ceiling rods and centrally placed blade holders. The 19th Century fan pays tribute to these early traditions and adds elements of classic gaslight designs. The intricate, ornate patterns recall decorative influences of cast metal parts and tin-type moldings reminiscent of the period.

#### FEATURES

- XLP-2000™ motor / lifetime motor warranty
- 54" blade span
- Set of 4 exclusive blades included
- Requires additional hanging support (included)
- Minimum 9' ceiling required
- Decorative canopy cover may not be used on a sloped ceiling or with a Sloped Ceiling Adapter (SCA)

19TH CENTURY®   included

#### MOTOR FINISHES



A

#### A: 61937 (6344Z)

Antique Brass motor shown with BB21-WD Dark Walnut blades, K164A-4 fitter with 99038 Toffee side glass




B

#### B: 60129 (6373Z)

Oil-Rubbed Bronze motor shown with BIO3 Walnut blades

#### BLADES

Customize your fan with blades that reflect your style. Choose from three finishes.



A

B

C

A: **B103**  
Walnut

B: **B522**  
Antique Oak

C: **BB21-WD**  
Dark Walnut

#### ACCESSORIES

##### 63315

8" sleeve for  
12" extension downrod

##### 62292

14" sleeve for  
18" extension downrod

##### 63316

20" sleeve for  
24" extension downrod

##### 63366

26" sleeve for  
30" extension downrod

##### 63317

32" sleeve for  
36" extension downrod

##### 62248

44" sleeve for  
48" extension downrod

##### 62249

56" sleeve for  
60" extension downrod

##### 62250

68" sleeve for  
72" extension downrod

#### LIGHTING

Our design team's recommended lighting option.



##### 99023

Glass Bowl Fitter

##### 99062

Toffee Glass Bowl

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS



##### W-85 (included)

Inteli-Touch3®

Six-speed wall control with full-range light dimming and reversing.



##### W-65 (optional)

Inteli-Touch3®

Six-speed remote control with LCD display screen, full-range light dimming and reversing. Includes wall plate bracket.

#### LIGHTING



##### KG99A-69

19th Century Exclusive  
Four-Light CFL Fixture with Vianne Glass  
56 watts  
Burnished Brass

#### CONTROLS



##### W-85 (included)

Inteli-Touch3®

Six-speed wall control with full-range light dimming and reversing.




##### W-65 (optional)


Inteli-Touch3®

Six-speed remote control with LCD display screen, full-range light dimming and reversing. Includes wall plate bracket.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





TRANSITIONAL

ACADEMY GALLERY CEILING FAN  
*Inspired by classical European design*



**54081**

Antique Pewter motor with reversible Espresso / Smoked Walnut blades and Cased White glass

Talk about your overachievers. The Academy Gallery takes honors for best all-around with transitional styling, a wide selection of finish options and an integrated light bowl fixture.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 reversible blades included
- Integrated 180-watt downlight with three 60-watt bulbs included
- 172 x 20 motor

ACADEMY GALLERY



**59536**

Bronze Patina motor with Burnt Walnut veneer blades and Amber Rain glass

The Holliston Gallery ceiling fan combines classical styling with the ultimate performance and convenience. This fan comes furnished with an elegant four-light fitter and universal wall control, offering a full range of lighting options.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 60" blade span
- Set of 5 exclusive blades included
- Includes four-light fitter with four medium-based CFL bulbs
- 188 x 20 motor

HOLLISTON™ GALLERY



MOTOR & BLADE FINISHES



**A: 54080**

Bronze Patina motor with reversible Walnut / Burnt Walnut blades and Cased White glass

**B: 54081**

Antique Pewter motor with reversible Espresso / Smoked Walnut blades and Cased White glass

MOTOR & BLADE FINISHES



**A: 59536**

Bronze Patina motor with Burnt Walnut veneer blades and Amber Rain glass

**B: 59537**

Bullion Black motor with Reclaimed Antique veneer blades and Cased White glass

CONTROLS




**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





### 59060

Brushed Cocoa motor with Walnut ABS blades and Cased White glass

With its versatile design and quality craftsmanship, the Whitman ceiling fan brings year-round comfort and seamless performance to almost any room in the home. The fan incorporates carved featherwood blades reminiscent of the woodwork on fine cabinetry and a fully dimmable uplight and downlight that add gentle ambience.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- Integrated 75-watt incandescent uplight with five 15-watt bulbs included
- Integrated 100-watt downlight with two 50-watt T4 halogen bulbs included
- 172 x 20 motor



### 59076

Brushed Nickel motor with Cherrywood blades and Cased White glass

The popular Bel Air is the essence of Casablanca beauty. The housing and halogen light form a design continuum, helping to create a compelling and sophisticated presence. Uniquely cast blade holders lend a classic yet transitional look.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 56" blade span
- 5-blade configuration (exclusive blades sold separately)
- Integrated 100-watt downlight with one T4 halogen bulb included
- 188 x 20 motor



#### MOTOR & BLADE FINISHES



- A: 59059**  
Brushed Nickel motor with Reclaimed Antique hand-carved wood blades and Cased White glass
- B: 59060**  
Brushed Cocoa motor with Walnut ABS blades and Cased White glass
- C: 59061**  
Bronze Patina motor with Walnut carved wood blades and Cased White glass
- D: 59062**  
Antique Pewter motor with Rosewood ABS blades and Cased White glass

#### MOTOR & BLADE FINISHES



- A: 59076**  
Brushed Nickel motor shown with Cherrywood blades and Cased White glass
- B: 59077**  
Snow White motor shown with Snow White blades and Cased White glass
- C: 59078**  
Brushed Cocoa motor shown with Walnut blades and Cased White glass

#### CONTROLS

**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.

**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)

		Dimensions A: — B: 11.54" C: 2.75" D: 13.10" E: 6.49" F: 17.00"	Airflow 6,692 cfm  Electricity Use 84.4 w  Airflow Efficiency 79.3 cfm/w
--	--	---	---

#### CONTROLS

**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.

**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)

		Dimensions A: — B: 9.86" C: 2.75" D: 12.19" E: 6.49" F: 14.29"	Airflow 7,133 cfm  Electricity Use 86 w  Airflow Efficiency 83 cfm/w
--	--	--	---



### 55035

Brushed Cocoa motor with Walnut Regal-Style hand-carved wood blades

A 60-inch blade span makes this edition of the Fellini ideal for a wide variety of rooms. Hand-carved wood blades enrich the fan's character, while subtle finishing touches please the eye without overwhelming the beholder.

#### FEATURES


- Direct Drive™ motor / lifetime motor warranty
- 60" blade span
- Set of 5 exclusive hand-carved wood blades included
- 188 x 20 motor
- Light kits sold separately



#### MOTOR & BLADE FINISHES



A



B

#### A: 55035

Brushed Cocoa motor with Walnut Regal-Style hand-carved wood blades

#### B: 55036

Provence Crackle motor with Aged Oak hand-carved wood blades

#### CONTROLS



**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### LIGHTING

Our design team's recommended lighting option.



#### 99105


Four-Light Fitter in Brushed Cocoa

#### 99044

2 1/4" Side Glass with Ribbed Deco Shape in Cased White

For all other compatible light fixtures, see pages 95-98.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow	
A:	14.96"	6,351 cfm	
B:	12.50"	Electricity Use	
C:	2.75"	87 w	
D:	14.20"	Airflow Efficiency	
E:	6.49"	72.9 cfm/w	
F:	-		



### 59518

Provence Crackle motor with Distressed Walnut / Dark Walnut veneer blades

A new addition to the Fellini family, this fan boasts a powerful DC motor, a 66-inch blade span and DC 6-speed fan control. This model is ideal for a wide variety of rooms. Real wood blades enrich the fan's character, while subtle finishing touches please the eye without overwhelming the beholder.

#### FEATURES

- DC-165 motor / lifetime motor warranty
- 66" blade span
- Set of 5 exclusive blades included



#### CONTROL



**Included**  
DC 6-speed  
Six-speed control with full-range light dimming and reversing.

#### LIGHTING

Our design team's recommended lighting option.



#### 99104


Four-Light Fitter in Provence Crackle

#### 99045

2 1/4" Side Glass with Ribbed Deco Shape in Toffee

For all other compatible light fixtures, see pages 95-98.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow	
A:	15.13"	8,651 cfm	
B:	11.88"	Electricity Use	
C:	2.75"	34.8 w	
D:	14.20"	Airflow Efficiency	
E:	6.49"	248.6 cfm/w	
F:	-		



### 54036

Aged Bronze motor with Dark Walnut All-Weather Blades

The versatile Utopian fan is ideally suited for humid environments. Smooth contours and simple lines provide a clean, progressive look that enhances décor without distraction. For bathrooms, kitchens and verandas, the Utopian is the perfect choice.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 52" blade span
- Set of 5 blades included
- Select models ETL rated for damp or humid locations
- 172 x 20 motor
- Light kits sold separately

UTOPIAN®



### 54039

Brushed Cocoa motor with Antique Halifax All-Weather blades and Tea Stain glass

Clean, progressive design. Everything that's attractive about the Utopian fan—with a simple bowl light and four-speed wall-mount control. Ideal for humid environments.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 52" blade span
- Set of 5 blades included
- Select models ETL rated for damp or humid locations
- 172 x 20 motor

UTOPIAN® GALLERY



#### MOTOR & BLADE FINISHES



A



B



C



D

**A: 54035**  
Brushed Cocoa motor with Antique Halifax All-Weather blades



**B: 54036**  
Aged Bronze motor with Dark Walnut All-Weather blades



**C: 54037**  
Snow White motor with Matte Snow White All-Weather blades



**D: 54038**  
Brushed Nickel motor with reversible Walnut / Burnt Walnut blades

#### CONTROLS



**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### LIGHTING

Our design team's recommended lighting option.




**99079**  
Low Profile Fitter in Aged Bronze

**99084**  
Low Profile Glass in Toffee

For all other compatible light fixtures, see pages 95-98.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	12.86"	6,424 cfm
B:	11.64"	Electricity Use
C:	2.75"	81 w
D:	11.24"	Airflow Efficiency
E:	6.49"	79 cfm/w
F:	-	

#### MOTOR & BLADE FINISHES




A



B



C



D

**A: 54039**  
Brushed Cocoa motor with Antique Halifax All-Weather blades and Tea Stain glass



**B: 54040**  
Aged Bronze motor with Dark Walnut All-Weather blades and Champagne Scavo glass



**C: 54041**  
Snow White motor with Matte Snow White All-Weather blades and Cased White glass



**D: 54042**  
Brushed Nickel with reversible Walnut / Burnt Walnut blades and Cased White glass

#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	12.86"	6,503 cfm
B:	11.64"	Electricity Use
C:	2.75"	84.5 w
D:	11.24"	Airflow Efficiency
E:	6.49"	77 cfm/w
F:	18.33"	



# CONTEMPORARY

ZUDIO CEILING FAN  
*Inspired by modern art*



### 59109

Brushed Nickel motor with reversible Walnut / Burnt Walnut blades and Clear Frosted glass

From its name to its edgy design, the new Zudio is simply unique. Contemporary design featuring blade holders that spin around the entire fan body.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 56" blade span
- Set of 5 blades included
- Integrated LED light kit
- 188 x 20 motor



### 59124

Brushed Cocoa motor with Burnished Mahogany blades

Clean and simple design that appeals to the senses. Wood-tone finishes dipped in film put the exclamation point on this new, contemporary model.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 4 exclusive blades included
- 172 x 20 motor
- Light kits sold separately



#### MOTOR & BLADE FINISHES



A



B


#### A: 59109

Brushed Nickel motor with reversible Walnut / Burnt Walnut blades and Clear Frosted glass

#### B: 59110

Snow White motor with Snow White blades and Clear Frosted glass

#### MOTOR & BLADE FINISHES



A



B

#### A: 59123

Brushed Nickel motor with Mayse blades

#### B: 59124

Brushed Cocoa motor with Burnished Mahogany blades

#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





### 59121

Snow White motor with Snow White blades and Clear Frosted glass

Formed blades and LED lighting add something special to this new, modern fan. Simple, sophisticated and designed to elicit compliments.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 60" blade span
- Set of 3 exclusive blades included
- Integrated LED light kit
- 188 x 20 motor



### 59107

Maiden Bronze motor with Dark Walnut blades and Cased White glass

Now more than ever, the Stealth DC lives up to its name, featuring our quietest motor yet. Casablanca's new DC technology is also extremely powerful and highly efficient—four to five times more than other motors. So while the fan may be quiet, the news won't be for long.

#### FEATURES

- DC-165 motor / lifetime motor warranty
- 54" blade span
- Set of 5 exclusive blades included
- Integrated 100-watt downlight with one T4 halogen bulb included



#### MOTOR & BLADE FINISHES



#### A: 59119

Maiden Bronze motor with Walnut blades and Clear Frosted glass

#### B: 59121

Snow White motor with Snow White blades and Clear Frosted glass

#### MOTOR & BLADE FINISHES



#### A: 59105

Snow White motor with Hi-Gloss Snow White blades and Cased White glass

#### B: 59106

Brushed Nickel motor with Espresso blades and Cased White glass

#### C: 59107

Maiden Bronze motor with Dark Walnut blades and Cased White glass

#### CONTROL



**Included**  
DC 6-speed  
Six-speed control with full-range light dimming and reversing.

#### ACCESSORIES

**STLHC-11**  
Snow White no-light cap

**STLHC-45**  
Brushed Nickel no-light cap

#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.




**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





STEALTH™     

### 59092

Industrial Rust motor with River Timber blades and Cased White glass

Don't let the name fool you—this impeccably finished fan is sure to get noticed. New, improved version of one of our proven, contemporary designs.

#### FEATURES

- 54" blade span
- Set of 5 blades included
- Integrated LED light kit
- 188 x 20 motor

#### MOTOR & BLADE FINISHES



- A: 59090**  
Brushed Nickel motor with Dark Walnut blades and Cased White glass
- B: 59091**  
Snow White motor with Hi-Gloss Snow White blades and Cased White glass
- C: 59092**  
Industrial Rust motor with River Timber blades and Cased White glass
- D: 59093**  
Aged Steel motor with Grey Washed Veneer blades and Cased White glass
- E: 59094**  
Brushed Nickel motor with Platinum blades and Cased White glass

#### CONTROLS



**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### ACCESSORIES

**STLHC-11**  
Snow White no-light cap

**STLHC-45**  
Brushed Nickel no-light cap

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)

Dimensions		Airflow
A:	11.24"	6,565 cfm
B:	2.75"	Electricity Use
C:	11.06"	90 w
D:	6.49"	Airflow Efficiency
E:	13.98"	73 cfm/w
F:		



Shown without downrod cover

### 59068

Brushed Nickel motor with reversible Walnut / Burnt Walnut blades

Inspired by the world-famous train, the Bullet is all about speed. This powerful performer moves a lot of air with maximum style. For unmatched performance in spacious loft environments, get on board.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 4 exclusive blades included
- Includes 2.5" and 12" downrods
- Integrated 100-watt downlight with one R7S halogen bulb included
- Minimum 9' ceiling required when using downrod cover
- Requires additional hanging support (included)
- 172 x 20 motor

BULLET



### 59064

Brushed Nickel motor with reversible Espresso / Walnut blades and Cased White glass

Tercera may mean "third," but it should be first on your list for a small or medium-sized room. With its sleek triple-blade configuration and vintage curves, this contemporary classic combines the best of old and new.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 52" blade span
- Set of 3 exclusive blades included
- Integrated 100-watt dimmable downlight with two 50-watt T4 halogen bulbs included
- 172 x 20 motor

TERCERA™



#### MOTOR & BLADE FINISHES



#### A: 59068

Brushed Nickel motor with reversible Walnut / Burnt Walnut blades

#### B: 59069

Brushed Cocoa motor with reversible Walnut / Burnt Walnut blades

#### C: 59070

Snow White motor with Snow White blades

#### MOTOR & BLADE FINISHES



#### A: 59064

Brushed Nickel motor with reversible Espresso / Walnut blades and Cased White glass

#### B: 59065

Snow White motor with Snow White blades and Cased White glass

#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





### 59504

Brushed Nickel motor with reversible  
Burnt Walnut / Walnut blades

From a loft in Soho to a gallery in Frisco, this versatile fan is at home anywhere that the love of industrially influenced urban design flourishes. Sleek, minimalist design with an impressive blade span.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 60" blade span
- Set of 3 exclusive reversible blades included
- Includes 7" downrod
- Minimum 9' ceiling required
- 172 x 18 motor
- Light kits sold separately

TRIBECA 60"



### 59500

Snow White motor with Matte Snow  
White blades

For those who have the same great taste in urban design, but a little less room. This fan delivers the sleek, modern style of the original Tribeca with a more space-friendly 52" blade span.


#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 52" blade span
- Set of 3 exclusive reversible blades included
- Includes 7" downrod
- Minimum 9' ceiling required
- 172 x 18 motor
- Light kits sold separately

TRIBECA 52"



#### MOTOR & BLADE FINISHES



#### A: 59503

Snow White motor with Snow White blades

#### B: 59504

Brushed Nickel motor with reversible  
Burnt Walnut / Walnut blades

#### C: 59505

Graphite motor with reversible  
Walnut / Graphite blades

#### MOTOR & BLADE FINISHES



#### A: 59500

Snow White motor with  
Matte Snow White blades

#### B: 59501

Brushed Nickel motor with reversible  
Walnut / Burnt Walnut blades

#### CONTROLS



#### Included

New Universal Control  
Four-speed wall control with  
full-range light dimming,  
reversing and CFL mode.



#### 99020 (optional)

New Universal Remote  
Four-speed remote control  
with full-range light dimming,  
reversing and CFL mode.

#### LIGHTING

Our design team's recommended  
lighting option.



#### 99254

CFL Low Profile Fitter in  
Brushed Nickel

#### 99073

Low Profile Glass in Cased White

For all other compatible light fixtures,  
see pages 95-98.

#### CONTROLS



#### Included

4-Speed Pullchain



#### 99019 (optional)

New Universal  
Control System  
Four-speed remote control and  
receiver with full-range light  
dimming and CFL mode.

#### LIGHTING

Our design team's recommended  
lighting option.




#### 99050


Incandescent Globe  
Fixture in Snow White

For all other compatible light  
fixtures, see pages 95-98.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





### 60334 (23B002)

Snow White motor

Not included (shown with):  
MS2 White Cloth blades

The refreshing design of the Malibu Star will captivate your imagination. A bicycle sprocket serves as the hub, and the nautical look results from the airy silk fabric blades tensioned by fiberglass fishing rods. This large fan will become the focal point of any room.

#### FEATURES

- XLP-2000™ motor / lifetime motor warranty
- 84" blade span
- Set of 5 exclusive cloth blades sold separately
- Chrome hardware accents
- Minimum 9' ceiling required
- Uses 12" downrod (included)

MALIBU STAR®



EXCLUSIVE  
sold  
separately

#### BLADES

MS2  
White Cloth



#### CONTROLS




**W-81 (included)**  
Adapt•Touch™  
Four-speed wall control with  
full-range light dimming.



**W-52 (optional)**  
Adapt•Touch™  
Three-speed remote control  
with full-range light dimming.  
Includes wall plate bracket.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	21.00"	5,170 cfm
B:	23.00"	Electricity Use
C:	3.00"	109 w
D:	6.25"	Airflow Efficiency
E:	5.60"	47.4 cfm/w
F:	-	



### 59081

Graphite motor with reversible Walnut / Graphite blades and Cased White glass

Casablanca's Trident ceiling fan epitomizes clean contemporary design and seamless performance. Its streamlined three-blade configuration, integrated halogen light and matching no-light cap have been engineered to echo the agile grace of an airplane propeller.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 3 exclusive reversible blades included
- Integrated 100-watt downlight with one T4 halogen bulb included
- Optional no-light cap included
- 172 x 20 motor

TRIDENT®



EXCLUSIVE  
included

#### MOTOR & BLADE FINISHES



#### A: 59081

Graphite motor with reversible Walnut / Graphite blades and Cased White glass

#### B: 59082

Snow White motor with reversible Maple / Snow White blades and Cased White glass

#### C: 59083

Brushed Nickel motor with reversible Espresso / Smoked Walnut blades and Cased White glass

#### CONTROLS




**Included**  
New Universal Control  
Four-speed wall control with  
full-range light dimming,  
reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control  
with full-range light dimming,  
reversing and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	-	7,010 cfm
B:	10.08"	Electricity Use
C:	2.75"	86 w
D:	10.20"	Airflow Efficiency
E:	6.49"	82 cfm/w
F:	14.15"	



LOW PROFILE



### 54101

Brushed Nickel motor with Walnut / Burnt Walnut reversible blades and Cased White glass

Simple, clean styling that works almost anywhere. And don't be fooled by its sophisticated look—this new model comes at an excellent value.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- 4-speed pullchain
- 172 x 20 motor

DURANT 54"



### 54103

Snow White motor with Matte Snow White blades

Simple, clean styling that works almost anywhere. And don't be fooled by its sophisticated look—this new model comes at an excellent value.


#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- 172 x 20 motor
- Light kits sold separately

DURANT 54"



#### MOTOR & BLADE FINISHES



- A: 54101**  
Brushed Nickel motor with Walnut / Burnt Walnut reversible blades and Cased White glass
- B: 54102**  
Maiden Bronze motor with Walnut / Smoked Walnut blades and Tea Stain glass

#### CONTROLS



**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### LIGHTING

Our design team's recommended lighting option.



- 99023**  
Glass Bowl Fitter
- 99059**  
Cased White Glass Bowl

For all other compatible light fixtures, see pages 95-98.

#### CONTROLS




**Included**  
4-Speed Pullchain




**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	8.90"	4,249 cfm
B:	7.81"	
C:	-	Electricity Use
D:	12.50"	81 w
E:	-	Airflow Efficiency
F:	14.80"	53 cfm/w

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	8.90"	4,412 cfm
B:	7.81"	
C:	-	Electricity Use
D:	12.50"	82 w
E:	-	Airflow Efficiency
F:	-	54 cfm/w



**53188**

Maiden Bronze motor with reversible Walnut / Smoked Walnut blades and Tea Stain glass

Simple, clean styling that works almost anywhere. And don't be fooled by its sophisticated look—this new model comes at an excellent value.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 44" blade span
- Set of 5 blades included
- Includes three-light fitter with three medium-based CFL bulbs
- 172 x 12 motor

DURANT 44"



**54105**

Brushed Cocoa motor with reversible Distressed Walnut / Smoked Walnut blades and Toffee glass

It's all in the details. Painstakingly meticulous columns grace the motor housing to create a sophisticated, timeless look. A quality great room fan at an excellent value.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 5 blades included
- Includes three-light fitter with three medium-based CFL bulbs
- 172 x 20 motor

CALEDONIA



MOTOR & BLADE FINISHES



A



B

**A: 53187**

Brushed Nickel motor with reversible Walnut / Burnt Walnut blades and Cased White glass

**B: 53188**

Maiden Bronze motor with reversible Walnut / Smoked Walnut blades and Tea Stain glass

MOTOR & BLADE FINISHES



A



B

**A: 54105**

Brushed Cocoa motor with reversible Distressed Walnut / Walnut blades and Toffee glass

**B: 54106**

Burnished Creme motor with White Washed Oak blades and Cased White glass

CONTROLS




**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	8.90"	3,375 cfm
B:	7.75"	Electricity Use
C:	-	61 w
D:	12.50"	Airflow Efficiency
E:	-	55.30 cfm/w
F:	14.80"	

CONTROLS




**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions		Airflow
A:	9.15"	4,388 cfm
B:	7.97"	Electricity Use
C:	-	78.3 w
D:	12.50"	Airflow Efficiency
E:	-	56 cfm/w
F:	15.02"	



**59023**

Brushed Cocoa motor with Espresso blades and Cased White glass

Superior air circulation in a sleek, contemporary design. With a low profile and swept-wing blade configuration, the Isotope is ideal for flush-mount installation in interiors with lower ceilings.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 52" blade span
- Set of 5 exclusive blades included
- Integrated 100-watt downlight with one T4 halogen bulb included
- Not suitable for installation on a sloped ceiling
- 188 x 20 motor

ISOTOPE® 52"



**59019**

Brushed Nickel motor with Espresso blades and Cased White glass

This smaller blade version allows you to take the sleek, contemporary styling and superior functionality of the Isotope to almost any room in your home. A superior option for flush-mount installation in lower ceilings.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 44" blade span
- Set of 5 exclusive blades included
- Integrated 100-watt downlight with one T4 halogen bulb included
- Not suitable for installation on a sloped ceiling
- 188 x 20 motor

ISOTOPE® 44"



**MOTOR & BLADE FINISHES**



- A: 59021**  
Snow White motor with Snow White blades and Cased White glass
- B: 59022**  
Brushed Nickel motor with Espresso blades and Cased White glass
- C: 59023**  
Brushed Cocoa motor with Espresso blades and Cased White glass

**MOTOR & BLADE FINISHES**



- A: 59018**  
Snow White motor with Snow White blades and Cased White glass
- B: 59019**  
Brushed Nickel motor with Espresso blades and Cased White glass
- C: 59020**  
Brushed Cocoa motor with Espresso blades and Cased White glass

**CONTROLS**



**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**

		<b>Dimensions</b> A: — B: 9.59" C: — D: 10.20" E: — F: 12.76"	<b>Airflow</b> 3,859 cfm  <b>Electricity Use</b> 68.9 w  <b>Airflow Efficiency</b> 55.9 cfm/w
--	--	---	--

**CONTROLS**



**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**

		<b>Dimensions</b> A: — B: 9.59" C: — D: 10.20" E: — F: 12.76"	<b>Airflow</b> 3,784 cfm  <b>Electricity Use</b> 68.1 w  <b>Airflow Efficiency</b> 55.6 cfm/w
--	--	---	--



# DÉCOR SPECIFIC

CANDELIER II CEILING FAN  
*Inspired by rustic medieval chandeliers*



**NEW**  
Long-life LED  
flickering bulbs



### 66083 (C16G73L)

Oil-Rubbed Bronze fixture and motor with Candelier Dark Walnut blades

Add the warm, intimate ambience of candlelight to a spacious room with the Candelier II ceiling fan. The fixture's ingenious design features 48 candles in varying heights and colors nestled around an Oil-Rubbed Bronze ring that houses a sleek, three-blade ceiling fan. Candles are fitted with LED bulbs that effectively capture the natural flickering motion and incandescent glow of real candles.

#### FEATURES

- XLP-2000™ motor / lifetime motor warranty
- 48" diameter / 30" blade span
- Set of 3 exclusive Candelier Dark Walnut blades included
- Includes uplight with 48 LED flickering bulbs and 48 candles
- Includes eight 10-watt halogen downlights with bulbs
- Minimum 9' ceiling required
- Includes exclusive hanging system
- Sloped Ceiling Adapter (SCA) is not compatible

CANDELIER II™ XLP EXCLUSIVE included



### 64831 (97052Z)

Bronze Patina motor with Teak blades

Simplicity. Craftsmanship. Elegance. The Mission fan captures the original inspiration of the Arts and Crafts movement. Share in this historic period of home decoration with a Casablanca masterpiece that reveals geometric design elements, genuine art glass and natural metal finishes.

#### FEATURES

- XLP-2100™ motor / lifetime motor warranty
- 56" blade span
- Set of 5 exclusive blades included
- Integrated 120-watt incandescent downlight with two 60-watt bulbs included
- Sloped Ceiling Adapter (SCA) is not compatible without part 19222Oxx (see pages 103-104)
- Requires additional hanging support (included)

MISSION® XLP EXCLUSIVE included

#### CONTROLS



**Included**  
Direct-Touch®  
Four-speed wall control with full-range light dimming, reversing and CFL mode. Independent uplight and downlight operation.




**W-75DL (optional)**  
Direct-Touch®  
Four-speed remote control with full-range light dimming, reversing and CFL mode. Independent uplight and downlight operation.

#### ACCESSORIES

- |                                       |  |
|---------------------------------------|--|
| <b>64684</b><br>12" extension downrod | <b>64690</b><br>60" extension downrod  |
| <b>64685</b><br>18" extension downrod | <b>64691</b><br>72" extension downrod  |
| <b>64686</b><br>24" extension downrod | <b>64692</b><br>96" extension downrod  |
| <b>64688</b><br>36" extension downrod | <b>64693</b><br>117" extension downrod |
| <b>64689</b><br>48" extension downrod |  |

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



#### CONTROLS




**W-85 (included)**  
Inteli-Touch3®  
Six-speed wall control with full-range light dimming and reversing.



**W-65 (optional)**  
Inteli-Touch3®  
Six-speed remote control with LCD display screen, full-range light dimming and reversing. Includes wall plate bracket.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





OUTDOOR

WAILEA CEILING FAN

*Inspired by seashells along the Hawaiian islands*



**55051**

Aged Steel motor with River Timber blades and Sepia glass

Inspired by the latest high-end furniture trends, the Heathridge's body has the appearance of turned wood and complements its solid wood blades. Simple, sophisticated and perfect for updating any room.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 60" blade span
- Set of 5 solid featherwood blades
- 188 x 20 motor
- Includes four-light fitter with four 40-watt incandescent bulbs

HEATHRIDGE



**59114**

Maiden Bronze motor with Smoked Walnut blades and Cased White glass

Damp-rated with an imaginative style. This new, practical model was inspired by modern industrial design for a look that's all its own.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 56" blade span
- Set of 5 reversible blades included
- 188 x 20 motor
- Integrated light kit with two 50-watt halogen bulbs

CANEEL BAY



MOTOR & BLADE FINISHES



A



B

**A: 55051**

Aged Steel motor with River Timber blades and Sepia glass

**B: 55052**

Tahoe motor with Mountain Timber blades and Sepia glass

MOTOR & BLADE FINISHES



A



B

**A: 59113**

Aged Steel motor with White Washed Distressed Oak blades and Cased White glass

**B: 59114**

Maiden Bronze motor with Smoked Walnut blades and Cased White glass

CONTROLS



**Included**


New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**

New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions

- A: 13.12"
- B: 11.76"
- C: 2.75"
- D: 15.21"
- E: 6.49"
- F: 20.32"

Airflow

6,191 cfm

Electricity Use

87.7 w

Airflow Efficiency

70.6 cfm/w

CONTROLS



**Included**


New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**

New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



Dimensions

- A: -
- B: 13.04"
- C: 2.75"
- D: 10.03"
- E: 6.49"
- F: 16.79"

Airflow

6,585 cfm

Electricity Use

87.4 w

Airflow Efficiency

75.35 cfm/w



### 59527

Aged Bronze motor with Adirondack outdoor carved featherwood blades in Reclaimed Antique

During the Industrial Revolution, innovations in manufacturing enabled artisans to create furniture from cast iron. The Heritage fan incorporates many of the design details featured in antique castings, including vertical ribbing on its motor housing, raised type on the switch cap, and a custom cobblestone texture on the fan body, cap and inset portions of the blade medallions.

#### FEATURES

- Direct Drive™ / lifetime motor warranty
- 60" blade span
- Set of 5 exclusive outdoor blades
- Moisture-resistant motor and enclosed housing
- Stainless steel hardware
- Minimum 8' ceiling required
- 188 x 20 motor
- Light kits sold separately

HERITAGE™



### 64395 (C18G500F)

Aged Bronze motor with outdoor carved featherwood blades in Reclaimed Antique

Make a statement of graceful refinement on a grand scale with the damp-rated Atria ceiling fan. The faux alabaster motor housing includes an uplight and a downlight that illuminate the entire fan body with a warm, ambient glow.


#### FEATURES

- XTR200™ 30mm motor / lifetime motor warranty
- ETL rated for damp or humid locations
- 68" blade span
- Set of 5 exclusive outdoor carved featherwood blades included
- Integrated 120-watt uplight with eight 15-watt bulbs included
- Integrated 100-watt downlight with two 50-watt T4 halogen bulbs included
- Moisture-resistant motor / stainless steel hardware
- Minimum 9' ceiling required
- Requires additional hanging support (included)
- 200 x 30 motor

ATRIA®



#### MOTOR & BLADE FINISHES



A

**A: 59527**

Aged Bronze motor with Adirondack outdoor carved featherwood blades in Reclaimed Antique

B

**B: 59528**

Brushed Cocoa motor with Adirondack outdoor carved featherwood blades in Reclaimed Antique

#### LIGHTING

Our design team's recommended lighting option.



**99087**

Outdoor Four-Light Fixture in Aged Bronze

For all other compatible light fixtures, see pages 95-98.

#### CONTROL



**W-81 (included)**

Four-speed wall control with full-range light dimming. No reversing function.

#### CONTROLS




**Included**  
4-Speed Pullchain




**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)





**59525**

Brushed Cocoa motor with  
Brushed Cocoa All-Weather blades

The ETL damp-rated Wailea fan, inspired by Casablanca's popular Capistrano fan, is perfectly suited for small spaces. This 31-inch-wide fan is ideal for bathrooms, laundry rooms, walk-in closets and kitchens where ventilation is needed.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 31" blade span / 25° blade pitch (optimized for maximum air movement)
- Set of 6 exclusive All-Weather ABS blades included
- Moisture-resistant motor / stainless steel hardware
- Use only damp- or wet-rated light fixtures in damp locations
- 172 x 12 motor
- Light kits sold separately

WAILEA™



**55011**

Aged Bronze motor

Not included (shown with):  
99018 Espresso All-Weather blades

Transport yourself to a secluded beach house from any room in your home. With its delightfully simple styling, the Charhouse creates a relaxed, airy feel that will truly take you away. Choose the perfect blade and finish combination to match your style.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- ETL rated for wet locations
- 188 x 20 motor
- Light kits sold separately

CHARHOUSE™



**MOTOR & BLADE FINISHES**



A



B



C

**A: 59523**

Snow White motor with  
Snow White All-Weather blades


**B: 59524**

Brushed Nickel motor with  
Dark Walnut blades

**C: 59525**

Brushed Cocoa motor with  
Dark Walnut blades

**MOTOR FINISHES**



A



B



C

**A: 55010**

Maiden Bronze motor shown with  
99016 Plantation Wicker All-Weather blades

**B: 55011**

Aged Bronze motor shown with  
99018 Espresso All-Weather blades

**C: 55012**

Cottage White motor shown with  
99014 Cottage White Beadboard  
All-Weather blades

**CONTROLS**



**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal  
Control System  
Four-speed remote control and  
receiver with full-range light  
dimming and CFL mode.

**LIGHTING**

Our design team's recommended  
lighting option.



**99078**

Low Profile Fitter in Brushed Cocoa

**99084**

Low Profile Glass in Toffee

For all other compatible light fixtures,  
see pages 95-98.

**BLADES**

Customize your fan with blades that reflect your style. Choose  
from a variety of finishes and shapes. See foldout on page 11.



**LIGHTING**

Our design team's recommended  
lighting option.



**99079**


Low Profile Fitter in Aged Bronze

**99084**

Low Profile Glass in Toffee

For all other compatible light fixtures,  
see pages 95-98.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**



**CONTROLS**




**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal  
Control System  
Four-speed remote control and  
receiver with full-range light  
dimming and CFL mode.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**



\*Energy information based on 99004 blade set.



### 54010

Cottage White motor

Not included (shown with):  
99017 Cottage White All-Weather blades

Amazing how something so simple can add so much to a room. One of our distinctive designs. Built to last outside, making it a fine choice for covered porches and sunrooms. Available in two finishes with a wide range of accessory blade options.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- ETL rated for damp or humid locations
- 172 x 20 motor
- Light kits sold separately

COMPASS POINT™



### 54030

Brushed Cocoa motor

Not included (shown with):  
99003 Vintage Rosewood / Wine Country Distressed veneer blades

Subtle sophistication is a dominant theme in today's décor. Nothing complements this attitude like the Capistrano, with a soft, sculpted look and the nautical suggestion of seashells.

#### FEATURES

- Direct Drive™ motor / lifetime motor warranty
- 54"-60" blade span
- Multiple blade choices available (blades sold separately)
- Select models ETL rated for damp or humid locations
- 172 x 20 motor
- Light kits sold separately

CAPISTRANO®



#### MOTOR FINISHES



**A: 54010**  
Cottage White motor shown with  
99017 Cottage White All-Weather blades

**B: 54011**  
Maiden Bronze motor shown with  
99015 Distressed Antique Halifax  
All-Weather blades

#### MOTOR FINISHES



**A: 54028**  
Snow White motor shown with  
99001 Matte Snow White /  
Cottage White blades

**B: 54030**  
Brushed Cocoa motor shown with  
99003 Vintage Rosewood / Wine  
Country Distressed veneer blades

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



**99091**  
Outdoor Four-Light Fixture in  
Maiden Bronze

For all other compatible light fixtures,  
see pages 95-98.

#### BLADES

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



#### LIGHTING

Our design team's recommended lighting option.



**99023**  
Glass Bowl Fitter

**99062**  
Toffee Glass Bowl

For all other compatible light fixtures,  
see pages 95-98.

#### CONTROLS

**Included**  
4-Speed Pullchain



**99019 (optional)**

New Universal  
Control System  
Four-speed remote control and  
receiver with full-range light  
dimming and CFL mode.



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)\*

Dimensions		Airflow
A:	13.11"	6,590 cfm
B:	11.58"	Electricity Use
C:	2.75"	83 w
D:	9.17"	Airflow Efficiency
E:	6.49"	80 cfm/w
F:	-	

\*Energy information based on 99004 blade set.

#### CONTROLS

**Included**  
4-Speed Pullchain



**99019 (optional)**

New Universal  
Control System  
Four-speed remote control and  
receiver with full-range light  
dimming and CFL mode.



#### DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)\*

Dimensions		Airflow
A:	13.12"	6,496 cfm
B:	11.67"	Electricity Use
C:	2.75"	82.5 w
D:	12.50"	Airflow Efficiency
E:	6.50"	78.7 cfm/w
F:	-	

\*Energy information based on 99004 blade set.



**54036**

Aged Bronze motor with Dark Walnut All-Weather Blades

The versatile Utopian fan is ideally suited for humid environments. Smooth contours and simple lines provide a clean, progressive look that enhances décor without distraction. For bathrooms, kitchens and verandas, the Utopian is the perfect choice.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 52" blade span
- Set of 5 blades included
- Select models ETL rated for damp or humid locations
- 172 x 20 motor
- Light kits sold separately

UTOPIAN®



**54039**

Brushed Cocoa motor with Antique Halifax All-Weather blades

Clean, progressive design. Everything that's attractive about the Utopian fan—with a simple bowl light and four-speed wall-mount control. Ideal for humid environments.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 52" blade span
- Set of 5 blades included
- Select models ETL rated for damp or humid locations
- 172 x 20 motor

UTOPIAN® GALLERY



**MOTOR & BLADE FINISHES**



A B



C

- A: 54035**  
Brushed Cocoa motor with Antique Halifax All-Weather blades
- B: 54036**  
Aged Bronze motor with Dark Walnut All-Weather blades
- C: 54037**  
Snow White motor with Matte Snow White All-Weather blades

**CONTROLS**



**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

**LIGHTING**

Our design team's recommended lighting option.



**99079**  
Low Profile Fitter in Aged Bronze

**99084**  
Low Profile Glass in Toffee

For all other compatible light fixtures, see pages 95-98.


**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**

		Dimensions A: 12.86" B: 11.64" C: 2.75" D: 11.24" E: 6.49" F: -	Airflow 6,424 cfm  Electricity Use 81 w  Airflow Efficiency 79 cfm/w
--	--	---	---

**MOTOR & BLADE FINISHES**



A B



C

- A: 54039**  
Brushed Cocoa motor with Antique Halifax All-Weather blades
- B: 54040**  
Aged Bronze motor with Dark Walnut All-Weather blades
- C: 54041**  
Snow White motor with Matte Snow White All-Weather blades

**CONTROLS**



**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**

		Dimensions A: 12.86" B: 11.64" C: 2.75" D: 11.24" E: 6.49" F: 18.33"	Airflow 6,503 cfm  Electricity Use 84.5 w  Airflow Efficiency 77 cfm/w
--	--	--	---



**59124**

Brushed Cocoa motor with Burnished Mahogany blades

Clean and simple design that appeals to the senses. Wood-tone finishes dipped in film put the exclamation point on this new, contemporary model.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 54" blade span
- Set of 4 exclusive blades included
- 172 x 20 motor
- Light kits sold separately



**55023**

Aged Bronze motor

Not included (shown with): 99002 Walnut / Burnt Walnut veneer blades


All the pluses of the Panama with an added pullchain. Classic design, excellent air movement, energy efficient and available in a wide variety of motor finish, blade and lighting options. No need to look any further.

**FEATURES**

- Direct Drive™ motor / lifetime motor warranty
- 52"-58" blade span
- Multiple blade finish choices available (blades sold separately)
- Select models ETL rated for damp or humid locations
- 188 x 20 motor



**MOTOR & BLADE FINISHES**



A

B


**A: 59123**

Brushed Nickel motor with Mayse blades

**B: 59124**

Brushed Cocoa motor with Burnished Mahogany blades

**MOTOR FINISHES**



A

B

C

D

**A: 55021**

Snow White motor shown with 99001 Matte Snow White / Cottage White blades

**B: 55023**

Aged Bronze motor shown with 99002 Walnut / Burnt Walnut veneer blades

**C: 55024**

Brushed Cocoa motor shown with 99002 Walnut / Burnt Walnut veneer blades

**D: 55025**

Cottage White motor shown with 99014 Cottage White Beadboard All-Weather blades

\*Also available in outdoor damp finishes. Panama Control 55027, 55029, 55030, 55031.

**BLADES**

Customize your fan with blades that reflect your style. Choose from a variety of finishes and shapes. See foldout on page 11.



**LIGHTING**

Our design team's recommended lighting option.



**99087**

Outdoor Four-Light Fixture in Aged Bronze

For all other compatible light fixtures, see pages 95-98.

**CONTROLS**




**Included**  
New Universal Control  
Four-speed wall control with full-range light dimming, reversing and CFL mode.



**99020 (optional)**  
New Universal Remote  
Four-speed remote control with full-range light dimming, reversing and CFL mode.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)**



**CONTROLS**




**Included**  
4-Speed Pullchain



**99019 (optional)**  
New Universal Control System  
Four-speed remote control and receiver with full-range light dimming and CFL mode.

**DIMENSIONS AND ENERGY INFORMATION (AT HIGH SPEED)\***



\*Energy information based on 99004 blade set.



ACCESSORIES

OUTDOOR FOUR-LIGHT FIXTURES & FITTERS



A



B



C



D



E



- A: 99087**  
Outdoor Four-Light Fixture, 56 watts, Aged Bronze with Tea Stain glass
- B: 99088**  
Outdoor Four-Light Fixture, 56 watts, Snow White with Cased White glass
- C: 99089**  
Outdoor Four-Light Fixture, 56 watts, Cottage White with Cased White glass
- D: 99090**  
Outdoor Four-Light Fixture, 56 watts, Brushed Cocoa with Cased White glass
- E: 99091**  
Outdoor Four-Light Fixture, 56 watts, Maiden Bronze with Cased White glass

FOUR-LIGHT FITTER



F

- F: 99033**  
Four-Light Fitter, 56 watts, Maiden Bronze
- Other available finishes:
- 99029 Snow White
  - 99030 Basque Black
  - 99031 Cottage White
  - 99032 Antique Brass
  - 99033 Maiden Bronze
  - 99034 Aged Bronze
  - 99103 Brushed Nickel
  - 99104 Provence Crackle
  - 99105 Brushed Cocoa

For all compatible light fixtures, see pages 101-102.

SIDE GLASS



A



B



C



D



E



F



G



H



I



J



K

- A: 99035**  
2 1/4" Side Glass with Bell Shape Cased White, Set of 4
- B: 99036**  
2 1/4" Side Glass with Bell Shape Amber Linen, Set of 4
- C: 99037**  
2 1/4" Side Glass with Bell Shape Swirled Marble, Set of 4
- D: 99038**  
2 1/4" Side Glass with Bell Shape Toffee, Set of 4
- E: 99039**  
2 1/4" Side Glass with Square Shape Cased White, Set of 4
- F: 99040**  
2 1/4" Side Glass with Square Shape Frosted Amber Speckled, Set of 4
- G: 99041**  
2 1/4" Side Glass with Slant Shape Cased White, Set of 4
- H: 99042**  
2 1/4" Side Glass Cased White, Set of 4
- I: 99043**  
2 1/4" Side Glass Tea Stain, Set of 4
- J: 99044**  
2 1/4" Side Glass with Ribbed Deco Shape Cased White, Set of 4
- K: 99045**  
2 1/4" Side Glass with Ribbed Deco Shape Toffee, Set of 4

For all compatible light fixtures, see pages 101-102.

LOW PROFILE FITTERS & GLASS



- A: 99077**  
Incandescent Low Profile Fitter  
120 watts, Maiden Bronze
- Other available finishes:
- 99075 Cottage White
  - 99076 Snow White
  - 99077 Maiden Bronze
  - 99078 Brushed Cocoa
  - 99079 Aged Bronze
  - 99080 Brushed Nickel (Indoor only)

(Image not available)

- B: 99253** NEW (Image not available)  
CFL Low Profile Fitter  
(2) GU-24 CFL Bulbs, Snow White
- Other available finishes:
- 99252 Antique Brass
  - 99253 Snow White
  - 99254 Brushed Nickel
  - 99255 Brushed Cocoa
  - 99256 Maiden Bronze

- C: 99072**  
Low Profile Glass  
Cased White

- D: 99073**  
Low Profile Glass  
Cased White

- E: 99082**  
Low Profile Glass  
Cased White

- F: 99083**  
Low Profile Glass  
Cased White

- G: 99084**  
Low Profile Glass  
Toffee



For all compatible light fixtures, see pages 101-102.

BOWL FITTERS & GLASS



- A: 99023**  
Bowl Fitter, 28 watts

- B: 99183**  
LED Bowl Fitter

- C: 99057**  
Swirled Marble Glass Bowl

- D: 99058**  
Tea Stain Glass Bowl

- E: 99059**  
Cased White Glass Bowl

- F: 99060**  
Toffee Glass Bowl

- G: 99061**  
Cased White Glass Bowl

- H: 99062**  
Toffee Glass Bowl

- I: 99063**  
Tropical Leaf Glass Bowl

Bowl Caps & Finial Packs (not shown)

- 99128 Cottage White
- 99129 Aged Bronze
- 99130 Maiden Bronze
- 99131 Antique Brass
- 99132 Provence Crackle
- 99133 Industrial Rust



COMPLETE GLOBE LIGHT FIXTURES



- J: 99050**  
Globe Fixture with Cased White glass,  
120 watts, Snow White

- Other available finishes:
- 99050 Snow White
  - 99051 Brushed Nickel
  - 99052 Brushed Cocoa
  - 99053 Maiden Bronze
  - 99054 Aged Bronze
  - 99055 Antique Brass

For all compatible light fixtures, see pages 101-102.

INTEGRATED CONTROLS

With simple two-wire installation and intuitive integrated controls designed exclusively for—and included with—specific fan models, Casablanca fans are easy to install and even easier to use. The integrated controls are available in wall-mounted or hand-held models and offer adjustable fan speed, direction settings and lighting levels. Select models also offer the following advanced programmable features for total environmental enhancement:

**Safe-Exit™** – provides 20 seconds of gradual light dimming, showing you safely to the door

**Home-Safe™** – controls lights in an irregular sequence, making a home appear occupied

**Fan Minder™** – incrementally reduces fan speed to maintain comfort at night

**Light Minder™** – saves energy by turning lights off automatically after two hours



A



B



C

**A: New Universal Control**

- Wall-mounted control
- Battery-powered
- Four forward and reverse fan speeds
- Full-range light dimming
- CFL auto detect
- Damp Rated
- Safe-Exit™

**B: DC 6-Speed**

- Hand-held remote
- Six forward and reverse fan speeds
- Full-range light dimming

**C: Intelli-Touch3® (W-84 Dual Light, W-85 Single Light)**

- Wall-mounted control
- Six forward and reverse fan speeds
- Full-range light dimming
- Safe-Exit™
- Home-Safe™
- Fan Minder™
- Light Minder™

ACCESSORY CONTROLS

Casablanca also offers a complete line of optional accessory controls, which allow homeowners to optimize the functionality of their fans based upon personal preferences.



A



B



C



D



E



F



G

**A: New Universal Control System (99019)**

- Hand-held remote and canopy-mount receiver
- Four forward fan speeds
- Full-range light dimming
- CFL auto detect
- Damp Rated

*Compatible with all 5xxxx fans.*

**B: New Universal Remote (99020)**

- Hand-held remote only
- Four forward and reverse fan speeds
- Full-range light dimming
- CFL auto detect
- Damp Rated

*Compatible with all 5xxxx fans.*

**C: Intelli-Touch3® (W-64 Dual Light, W-65 Single Light)**

- Wall-mounted control
- Six forward and reverse fan speeds
- Full-range light dimming
- Safe-Exit™
- Home-Safe™

**D: Direct-Touch® (W-75 Dual Light, W-75 Single Light)**

- Hand-held remote
- Four forward and reverse fan speeds
- Full-range light dimming
- CFL mode
- Safe-Exit™
- Home-Safe™
- Fan Minder™
- Light Minder™

**E: Single (W-41) and Dual (W-81) Rotary Controls**

- Wall-mounted control (almond and white)
- Four forward fan speeds
- Full-range light dimming (W-81 only—requires third wire for installation)

*Compatible with 3-Speed and 4-Speed pullchain models with XTR200™ and XLP-2000™ motors.*

**F: Single (W-24W) and Dual (W-28W) Slide Controls**

- Wall-mounted control (almond and white)
- Four forward fan speeds
- Full-range light dimming (W-28W only—requires third wire for installation)

*Compatible with 3-Speed and 4-Speed pullchain models. Not for use on XTR200™ motors.*

**G: Adapt-Touch® (W-52)**

- Hand-held remote (optional wall plate bracket included)
- Three forward fan speeds
- Full-range light dimming

*Compatible with 3-Speed and 4-Speed pullchain models equipped with a Hang-Tru® canopy. Not recommended for use in outdoor locations.*



HANGING SYSTEM



Just how you want it. Most fans include three-position mounting (flush, standard or angled) and can be installed with or without a light kit. Plus, we've designed all of our blades to be interchangeable, allowing you the freedom to switch things up.



Casablanca's new hands-free operation makes installation easier than ever. Our patented triangular hanger-ball system reduces torque for maximum stability and unmatched performance. An improved owner's manual puts you in control.



Our latest universal controls come loaded with new innovative features: automatic pairing, secure programming to eliminate interference, auto detect and longer range (up to 75 feet). And they're damp rated for use on covered porches.

**Sloped Ceiling Adapter (SCA-P)**


Use Model SCA-P for slopes from 32 degrees to 56 degrees. Specify finish to match fan. Use hanger pack included with fan.



Sloped Ceiling Adapter (SCA)

DOWNRODS


	DOWNROD LENGTH							
	12"	18"	24"	36"	48"	60"	72"	96"
Acadia	99235	99236	99237	99238	99239	99240	99241	
Aged Bronze	64533	64534	64535	64537	64538	64539	99243	
Antique Brass	63009	63010	63011	63013	63014	63015	63129	
Antique Pewter	28054	28055	28056	28057	28058	28059	28060	
Architectural White	63352	63353	63354	63355	63357	63358	63359	
Bright Brass	63001	63002	63003	63005	63006	63007	63128	
Bronze Patina	28206	28207	28208	28209	28210			
Brushed Cocoa	64525	64526	64527	64529	64530	64531	99242	
Brushed Nickel	26019	26020	26021	26022	26023	26024	26025	63266
Bullion Black	64612	64613	64614	64616	64617	64618		
Cottage White	99200	99201	99202	99203	99204	99205	99206	
Graphite	62428	62429	62430	62432	62433		62435	
Industrial Rust	99244	99245	99246	99247	99248	99249	99250	
Maiden Bronze	99207	99208	99209	99210	99211	99212	99213	
Matte Black	63025	63026	63027	63029	63030	63031	63131	
New Bronze (alternate for Oil-Rubbed Bronze)	26041	26042	26043	26044	26045	26046	26047	
Oil-Rubbed Bronze	63505	63510	63515	63525	63530	63535	63540	63350
Oil-Rubbed Bronze (Candelier II only)	64684	64685	64686	64688	64689	64690	64691	64692
Onyx Bengal	99221	99222	99223	99224	99225	99226	99227	
Provence Crackle	99228	99229	99230	99231	99232	99233	99234	
Snow White	63049	63050	63051	63053	63054	63055	63133	63156
Tahoe	Use Brushed Cocoa or New Bronze for this finish							
Aged Steel	Use Matte Black for this finish							



Note: For best performance and appearance, an extension downrod should be used with your Casablanca fan when installing on a high or sloped ceiling. Casablanca offers extension downrods in lengths up to 8' (96"). The chart lists the most common ceiling heights and suggested downrod lengths. For safety reasons, the fan blades must be a minimum of 7 feet above the floor. For more information, see your Casablanca dealer.

CEILING FAN SPECIFICATIONS

Series	Model Number (x, xx, or xxx = Finish Code)	Dimensions (in inches)						Blade Pitch
		A	B	C	D	E	F	
19th Century	62063	22.00	28.50	6.75	10.50	5.60	-	14°
Academy (with 99004 blade set)	54083-54085	13.11	10.95	2.75	13.72	6.49	-	13°
Academy Gallery	54080, 54081	13.11	10.95	2.75	13.72	6.49	18.32	13°
Adelaide (with 99004 blade set)	54116-54118	13.11	11.70	2.75	13.99	6.49	-	13°
Ainsworth 54"	54000-54002	13.11	11.73	2.75	12.41	6.49	-	13°
Ainsworth 60"	55000-55002	13.11	11.73	2.75	12.41	6.49	-	13°
Ainsworth Gallery 54"	54005-54007	13.11	11.73	2.75	12.41	6.49	19.56	13°
Ainsworth Gallery 60"	55005-55007	13.11	11.73	2.75	12.41	6.49	18.88	13°
Alessandria	59057	-	11.54	2.75	13.73	6.49	17.15	14°
Areto (with 99004 blade set)	54120-54122	13.11	11.74	2.75	10.50	6.49	-	13°
Aris	59123, 59124	14.69	12.78	2.75	8.74	6.49	-	13°
Atria	64395	23.40	28.80	3.00	17.10	5.60	-	11°
Bel Air	59076-59078	-	9.86	2.75	12.19	6.49	14.29	14°
Brescia Control (with 99004 blade set)	55019, 55020	12.12	10.54	2.75	14.04	6.49	-	13°
Brescia Pullchain (with 99004 blade set)	55015, 55016	12.12	10.54	2.75	14.04	6.49	-	13°
Bullet	59068-59070	-	20.86	2.75	8.08	6.49	24.03	14°
Caledonia	54105, 54106	9.15	7.97	-	12.50	-	15.02	13°
Candelier II	66083	24.37	24.37	4.82	10.93	8.00	-	20°
Caneel Bay	59113, 59114	-	13.04	2.75	10.03	6.49	16.79	13°
Capistrano (with 99004 blade set)	54028-54030	13.12	11.67	2.75	12.50	6.50	-	13°
Capistrano Gallery	54031-54033	13.12	11.67	2.75	12.50	6.50	19.00	13°
Charthouse (with 99004 blade set)	55010-55012	13.13	11.92	2.75	12.50	6.49	-	13°
Coletti (with 99004 blade set)	55054-55056	13.11	11.69	2.75	13.27	6.49	-	13°
Compass Point (with 99004 blade set)	54010, 54011	13.11	11.58	2.75	9.17	6.49	-	13°
Concentra	54019-54021	13.12	11.39	2.75	12.50	6.49	-	13°
Concentra Gallery	54022-54025	13.12	11.39	2.75	12.50	6.49	18.77	13°
Durant 44"	53187, 53188	8.90	7.75	-	12.50	-	14.80	13°
Durant 54"	54101, 54102	8.90	7.81	-	12.50	-	14.80	13°
Durant 54" (no light)	54103	8.90	7.81	-	12.50	-	-	13°




Energy measurements taken with included or exclusive blades unless noted otherwise.  
\* Energy measurements taken with 21" basic blades

Blade Span		Weight (lb.)	Min. Ceiling Height (ft.)	Energy Information (at High Speed)				Motor Size	Technology and Fan Controls
Long	Short			Speed (rpm)	Airflow (cfm)	Electricity Use (watts)	Airflow Efficiency (cfm/watt)		
54"		35	9	169	6,050	108	56.2	XLP-2000 - 28mm	I•T3 W-85
60"	54"	25	8	150	7,156	80.4	89.01	172mm x 20mm	4 speed pullchain
54"		29	8	185	6,546	80	82	172mm x 20mm	4 speed pullchain
60"	54"	15	8	153	6,289	80.4	78.23	172mm x 20mm	4 speed pullchain
54"		23	8	174	6,125	77.8	79	172mm x 20mm	4 speed pullchain
60"		24	8	145	7,093	83	85.5	188mm x 20mm	4 speed pullchain
54"		28	8	174	6,125	78	78.74	172mm x 20mm	4 speed pullchain
60"		29	8	146	7,204	86	83.4	188mm x 20mm	4 speed wall control
54"		27	8	171	6,195	84	74	172mm x 20mm	4 speed wall control
60"	54"	16	8	155	6,200	82	75.4	172mm x 20mm	4 speed pullchain
54"		21	8	121	6,196	82	75.5	172mm x 20mm	4 speed wall control
68"		42	9	156	9,042	93	97.4	XTR200 - 30mm	4-S W-81
56"		23	8	164	7,133	86	83	188mm x 20mm	4 speed wall control
60"	54"	27	8	162	7,282	88	83	188mm x 20mm	4 speed wall control
60"	54"	27	8	162	7,533	86	87.7	188mm x 20mm	4 speed pullchain
54"		22	9	171	6,486	84.5	76.7	172mm x 20mm	4 speed wall control
54"		24	8	162	4,388	78.3	56	172mm x 20mm	4 speed pullchain
30"		150	9	300	2,004	22	90.3	XLP-2000 - 28mm	D•T W-74DL
56"		29	9	177	6,585	87.4	75.35	188mm x 20mm	4 speed wall control
60"	54"	24	8	133	6,496	82.5	78.7	172mm x 20mm	4 speed pullchain
54"		31	8	187	5,965	83.1	71.8	172mm x 20mm	4 speed wall control
60"	54"	24	8	157	7,206	86	83.4	188mm x 20mm	4 speed pullchain
60"	54"	22	8	165	6,626	86	77.1	188mm x 20mm	4 speed pullchain
60"	54"	23	8	146	6,590	83	80	172mm x 20mm	4 speed pullchain
54"		27	8	175	6,129	81.2	75.7	172mm x 20mm	4 speed pullchain
54"		31	8	180	6,129	80.7	76	172mm x 20mm	4 speed pullchain
44"		19	8	246	3,375	61	55.3	172mm x 12mm	4 speed pullchain
54"		22	8	145	4,249	81	53	172mm x 20mm	4 speed pullchain
54"		17	8	143	4,412	82	54	172mm x 20mm	4 speed pullchain

Technology:  
I-T = Intelli-Touch  
4-S = Four Speed  
D-T = Direct-Touch  
DC = DC 6-speed

CEILING FAN SPECIFICATIONS (CONTINUED)

Series	Model Number (x, xx, or xxx = Finish Code)	Dimensions (in inches)						Blade Pitch
		A	B	C	D	E	F	
Fellini	55035, 55036	14.96	12.50	2.75	14.20	6.49	-	13°
Fellini DC	59518	15.13	11.88	2.75	14.20	6.49	-	13°
Fordham	53194, 53195	12.61	10.88	2.75	10.08	6.49	4.57	13°
Heathridge	55051, 55052	13.12	11.76	2.75	15.21	6.49	20.32	13°
Heritage	59527, 59528	13.02	11.97	2.75	15.96	6.49	-	13°
Holliston (with 99004 blade set)	59533-59535	12.47	10.50	2.75	13.94	6.49	-	14°
Holliston Gallery	59536, 59537	12.47	10.50	2.75	13.94	6.49	19.94	14°
Isotope 44"	59018-59020	-	9.59	-	10.20	-	12.76	14°
Isotope 52"	59021-59023	-	9.59	-	10.20	-	12.76	14°
Malibu Star	60334	21.00	23.00	3.00	6.25	5.60	-	15°
Mission	64831	11.00	15.40	3.00	13.90	7.70	-	13°
Panama Control (with 99004 blade set)	55027-55032	11.20	12.40	2.75	12.00	6.50	-	13°
Panama DC	59510-59512	13.29	11.69	2.75	12.00	6.49	-	13°
Panama Gallery	55058-55061	10.86	12.37	2.75	12.00	6.49	19.17	13°
Panama Pullchain (with 99004 blade set)	55021-55026	11.20	12.40	2.75	12.00	6.50	-	13°
Panama XLP Control (with 99004 blade set)	59095-59098	13.07	11.90	2.75	12.00	6.49	-	15°
Riello	59119, 59121	-	11.47	2.75	11.73	6.49	12.40	15°
Stealth	59090-59094	-	11.24	2.75	11.06	6.49	13.98	14°
Stealth DC	59105-59107	-	11.24	2.75	11.06	6.49	13.98	14°
Tercera	59064, 59065	-	11.30	2.75	12.94	6.49	13.71	15°
Tribeca 52"	59500, 59501	17.96	17.27	2.75	7.50	6.49	-	16°
Tribeca 60"	59503-59505	17.96	17.30	2.75	7.50	6.49	-	16°
Trident	59081-59083	-	10.08	2.75	10.20	6.49	14.15	14°
Utopian	54035-54038	12.86	11.64	2.75	11.24	6.49	-	13°
Utopian Gallery	54039-54042	12.86	11.64	2.75	11.24	6.49	18.33	13°
Victorian	61937, 60129	11.50	13.50	3.00	13.00	5.60	-	15°
Wailea	59523-59525	11.34	11.93	3.00	8.50	5.60	-	25°
Whitman	59059-59062	-	11.54	2.75	13.10	6.49	17.00	14°
Zudio	59109, 59110	-	11.96	2.75	9.73	6.49	13.20	13°



Energy measurements taken with included or exclusive blades unless noted otherwise.  
\* Energy measurements taken with 21" basic blades

Blade Span		Weight (lb.)	Min. Ceiling Height (ft.)	Energy Information (at High Speed)				Motor Size	Technology and Fan Controls
Long	Short			Speed (rpm)	Airflow (cfm)	Electricity Use (watts)	Airflow Efficiency (cfm/watt)		
60"		29	8	130	6,351	87	72.9	188mm x 20mm	4 speed wall control
66"		19	8		8,651	34.8	248.6	165 DC	DC 6 speed
44"		15	8	254	4,955	64.2	77.19	172mm x 12mm	4 speed pullchain
60"	34"		8	145	6,191	87.7	70.6	188mm x 20mm	4 speed wall control
60"		27	8	142	6,864	82	84	188mm x 20mm	4 speed pullchain
60"	54"		8	146	7,001	85	82.37	188mm x 20mm	4 speed pullchain
60"		29	8	127	6,369	88	72	188mm x 20mm	4 speed wall control
44"		28	8	265	3,784	68.1	55.6	188mm x 20mm	4 speed wall control
52"		28	8	171	3,859	68.9	55.9	188mm x 20mm	4 speed wall control
84"		19	9	83	5,170	109	47.4	XLP-2000 - 28mm	4-S W-81
56"		36	8	153	6,162	102	60.5	XLP-2100 - 33mm	I-T3 W-85
58"	52"	26	8	168	7,375	84	88	188mm x 20mm	4 speed wall control
54"		19	8	186	6,675	32.4	206	165 DC	DC 6 speed
54"		27	8	214	6,393	89.3	71.59	188mm x 20mm	4 speed wall control
58"	52"	26	8	145	7,264	91	80	188mm x 20mm	4 speed pullchain
58"	52"	18	8	153	6,178	111.3	55.51	XLP-2000 - 28mm	4 speed wall control
60"		18	8	180	6,916	87.2	79.32	188mm x 20mm	4 speed wall control
54"		34	8	184	6,565	90	73	188mm x 20mm	4 speed wall control
54"		31	8	177	6,142	32	190	165 DC	DC 6 speed
52"		30	8	210	6,233	81.4	76.6	172mm x 20mm	4 speed wall control
52"		23	9	183	6,168	75	82.4	172mm x 18mm	4 speed pullchain
60"		25	9	140	6,709	78	86.1	172mm x 18mm	4 speed wall control
54"		19	8	218	7,010	86	82	172mm x 20mm	4 speed wall control
52"		26	8	107	6,424	81	79	172mm x 20mm	4 speed pullchain
52"		30	8	212	6,503	84.5	77	172mm x 20mm	4 speed wall control
54"		23	8	220	6,250	122	51	XLP-2000 - 28mm	I-T3 W-85
31"		16	8	289	3,055	63.5	48.1	172mm x 12mm	4 speed pullchain
54"		26	8	170	6,692	84.4	79.3	172mm x 20mm	4 speed wall control
56"		27	8	185	6,468	85.1	76	188mm x 20mm	4 speed wall control

Technology:  
I-T = Intelli-Touch  
4-S = Four Speed  
D-T = Direct-Touch  
DC = DC 6-speed

MOTOR FINISH REFERENCE CHART

Model	2014 Page #	Acadia	Aged Bronze	Aged Steel	Antique Brass	Antique Pewter	Architectural White	Basque Black	Bright Brass	Bronze Patina	Brushed Cocoa	Brushed Nickel
19th Century	42											
Academy	21											54084
Academy Gallery	45					54081				54080		
Adelaide	17		54117		54116							
Ainsworth 54"	33							54002			54001	
Ainsworth 60"	31										55001	
Ainsworth Gallery 54"	34							54007				
Ainsworth Gallery 60"	32							55007				
Alessandria	30										59057	
Areto	16											54120
Aris	56 and 91										59124	59123
Atria	84		64395 / C18G500F									
Bel Air	48										59078	59076
Brescia Control	19											55019
Brescia Pulchain	20										55015	55016
Bullet	61										59069	59068
Caledonia	72										54105	
Candelier II	77											
Caneel Bay	82			59113								
Capistrano	18 and 88										54030	54029
Capistrano Gallery	40	54031				54032						
Charthouse	22 and 86		55011									
Coletti	15		55054								55055	
Compass Point	26 and 87											
Concentra	35										54020	54021
Concentra Gallery	36	54024			54025							54023
Durant 54"	69											54101
Durant (no light) 54"	70											
Durant 44"	71											53187
Fellini	49										55035	
Fellini DC	50											
Fordham	29										53195	
Heathridge	81			55051								
Heritage	83		59527								59528	
Holliston	14				59535							59534
Holliston Gallery	46									59536		
Isotope 44"	74										59020	59019
Isotope 52"	73										59023	59022
Malibu Star	65											
Mission	78									64831 / 97052Z		
Panama Control	23		55029		55032						55030	55028
Panama DC	39										59512	59511
Panama Gallery	37-38					55059	55058		55061			
Panama Pulchain	24 and 92		55023		55026						55024	55022
Panama XLP Control	25											59098
Riello	57											
Stealth	59-60			59093								59090, 59094
Stealth DC	58											59106
Tercera	62											59064
Tribeca 52"	64											59501
Tribeca 60"	63											59504
Trident	66											59083
Utopian	51 and 89		54036								54035	54038
Utopian Gallery	52 and 90		54040								54039	54042
Victorian	41											
Wailea	85										59525	59524
Whitman	47					59062				59061	59060	59059
Zudio	55											59109

Bullion Black	Burnished Brass	Burnished Creme	Cottage White	Graphite	Industrial Rust	Maiden Bronze	Oil-Rubbed Bronze	Onyx Bengal	Provence Crackle	Snow White	Tahoe	Model
	62063 / 99069Z											19th Century
						54085				54083		Academy
												Academy Gallery
										54118		Adelaide
			54000									Ainsworth 54"
			55000						55002			Ainsworth 60"
			54005					54006				Ainsworth Gallery 54"
			55005					55006				Ainsworth Gallery 60"
					54121					54122		Alessandria
												Areto
												Aris
												Atria
										59077		Bel Air
						55020						Brescia Control
												Brescia Pulchain
										59070		Bullet
		54106										Caledonia
							66083 / C16G73L					Candelier II
						59114						Caneel Bay
											54028	Capistrano
											54033	Capistrano Gallery
							55012					Charthouse
							55056					Coletti
							54010					Compass Point
								54011				Concentra
										54019		Concentra Gallery
										54022		Durant 54"
								54102				Durant (no light) 54"
										54103		Durant 44"
								53188				Fellini
										55036		Fellini DC
										59518		Fordham
						53194						Heathridge
											55052	Heritage
												Holliston
										59533		Holliston Gallery
59537											59018	Isotope 44"
											59021	Isotope 52"
											60334 / 238002	Malibu Star
												Mission
							55031				59510	Panama Control
											59096	Panama DC
											55060	Panama Gallery
							55025				55027	Panama Pulchain
							59095				55021	Panama XLP Control
											59119	Riello
											59092	Stealth
											59107	Stealth DC
												Tercera
											59065	Tribeca 52"
											59500	Tribeca 60"
											59505	Trident
								59081			59082	Utopian
											54037	Utopian Gallery
											54041	Victorian
											60129 / 6373Z	Wailea
												Whitman
											59523	Zudio
											59110	

Note: Further information on the entire line of Casablanca ceiling fans is available from your authorized dealer.

MOTOR FINISHES



Acadia



Aged Bronze



Aged Steel



Antique Brass



Antique Pewter



Architectural White



Basque Black



Bronze Patina



Brushed Cocoa



Brushed Nickel



Bullion Black



Burnished Brass



Burnished Creme



Cottage White



Graphite




Industrial Rust



Maiden Bronze



Oil-Rubbed Bronze



Onyx Bengal



Provence Crackle



Snow White



Tahoe

INDEX IN NUMERICAL ORDER

Model #	Description	Page	Model #	Description	Page
53187, 53188	Durant 44"	71	62063 (99U69Z)	19th Century	42
53194, 53195	Fordham	29	54083-54085	Academy	21
54000-54002	Ainsworth 54"	33	54080, 54081	Academy Gallery	45
54005-54007	Ainsworth Gallery 54"	34	54116-54118	Adelaide	17
54010, 54011	Compass Point	26 and 87	54000-54002	Ainsworth 54"	33
54019-54021	Concentra	35	55000-55002	Ainsworth 60"	31
54022-54025	Concentra Gallery	36	54005-54007	Ainsworth Gallery 54"	34
54028-54030	Capistrano	18 and 88	55005-55007	Ainsworth Gallery 60"	32
54031-54033	Capistrano Gallery	40	59057	Alessandria	30
54035-54037	Utopian	51 and 89	54120-54122	Areto	16
54039-54041	Utopian Gallery	52 and 90	59123, 59124	Aris	56 and 91
54080, 54081	Academy Gallery	45	64395 (C18G500F)	Atria	84
54083-54085	Academy	21	59076-59078	Bel Air	48
54101, 54102	Durant 54" with light kit	69	55019, 55020	Brescia (Control)	19
54103	Durant 54" w/o light kit	70	55015, 55016	Brescia (Pullchain)	20
54105, 54106	Caledonia	72	59068-59070	Bullet	61
54116-54118	Adelaide	17	54105, 54106	Caledonia	72
54120-54122	Areto	16	66083 (C16G73L)	Candelier II	77
55000-55002	Ainsworth 60"	31	59113, 59114	Caneel Bay	82
55005-55007	Ainsworth Gallery 60"	32	54028-54030	Capistrano	18 and 88
55010-55012	Charthouse	22 and 86	54031-54033	Capistrano Gallery	40
55015, 55016	Brescia (Pullchain)	20	55010-55012	Charthouse	22 and 86
55019, 55020	Brescia (Control)	19	55054-55056	Coletti	15
55021-55026	Panama Pullchain	24 and 92	54010, 54011	Compass Point	26 and 87
55027-55032	Panama Control	23	54019-54021	Concentra	35
55035, 55036	Fellini 60"	49	54022-54025	Concentra Gallery	36
55051, 55052	Heathridge	81	54101, 54102	Durant 54" with light kit	69
55054-55056	Coletti	15	54103	Durant 54" w/o light kit	70
55058-55061	Panama Gallery	37	53187, 53188	Durant 44"	71
59018-59020	Isotope 44"	74	55035, 55036	Fellini 60"	49
59021-59023	Isotope 52"	73	59518	Fellini DC	50
59057	Alessandria	30	53194, 53195	Fordham	29
59059-59062	Whitman	47	55051, 55052	Heathridge	81
59064, 59065	Tercera	62	59527	Heritage	83
59068-59070	Bullet	61	59533-59535	Holliston	14
59076-59078	Bel Air	48	59536, 59537	Holliston Gallery	46
59081-59083	Trident	66	59018-59020	Isotope 44"	74
59090-59094	Stealth	59	59021-59023	Isotope 52"	73
59095-59098	Panama XLP Control	25	60334 (23BOO2)	Malibu Star	65
59105-59107	Stealth DC	58	64831 (97052Z)	Mission	78
59109, 59110	Zudio	55	55021-55026	Panama Pullchain	24 and 92
59113, 59114	Caneel Bay	82	55027-55032	Panama Control	23
59119-59121	Riello	57	55058-55061	Panama Gallery	37
59123, 59124	Aris	56 and 91	59095-59098	Panama XLP Control	25
59500, 59501	Tribeca 52"	64	59510-59512	Panama DC	39
59503-59505	Tribeca 60"	63	59119-59121	Riello	57
59510-59512	Panama DC	39	59090-59094	Stealth	59
59518	Fellini DC	50	59105-59107	Stealth DC	58
59523-59525	Wailea	85	59064, 59065	Tercera	62
59527	Heritage	83	59500, 59501	Tribeca 52"	64
59533-59535	Holliston	14	59503-59505	Tribeca 60"	63
59536, 59537	Holliston Gallery	46	59081-59083	Trident	66
60334 (23BOO2)	Malibu Star	65	54035-54038	Utopian	51 and 89
61937 (6344Z), 60129 (6373Z)	Victorian	41	54039-54042	Utopian Gallery	52 and 90
62063 (99U69Z)	19th Century	42	61937 (6344Z), 60129 (6373Z)	Victorian	41
64395 (C18G500F)	Atria	84	59523-59525	Wailea	85
64831 (97052Z)	Mission	78	59059-59062	Whitman	47
66083 (C16G73L)	Candelier II	77	59109, 59110	Zudio	55

INDEX IN ALPHABETICAL ORDER



7130 Goodlett Farms Pkwy., Suite 400

Memphis, TN 38016

1.888.227.2178

[www.casablancafanco.com](http://www.casablancafanco.com)

TWELVE DOLLARS

PRINTED IN THE U.S.A.

©2014 CASABLANCA FAN COMPANY

SR-1342