



TRUE BLUE® BATH WASTE FULL KIT W/TEST

| | |
|----------------------|------------------|
| Job Name _____ | Item # _____ |
| Location _____ | |
| Engineer _____ | Contractor _____ |
| PO # _____ | Tag _____ |
| Representative _____ | |

SPECIFICATIONS

The Dearborn True Blue Bath Waste shall be used in commercial and residential applications requiring a bath waste and overflow drain with integrated test features. Overflow and drain elbow components shall come factory preassembled for added convenience. Overflow gasket shall be made of a high memory foamed rubber. Drain gasket shall be notched and undercut in order to wrap around drain elbow and lock into place. This will prevent gasket from being knocked off during installation and remain secured to drain elbow regardless of orientation. Test plugs shall be quarter turn installation and must be removable and reusable. Overflow test plug shall be used to install the designer trim veneer with a quarter turn and will not require additional tools or sealants for installation. Faceplate installation shall not require additional tools or screws, symmetrical design will eliminate the need for precise alignment.

APPROVALS AND LISTINGS

ASME A112.18.2-2015/CSA B125.2-15

 Uniform Plumbing Code (UPC®)

 National Plumbing Code of Canada

IPC International Plumbing Code (IPC®)

 ASME A112.18.2-2015/CSA B125.2-15

Listed with Massachusetts Board of Plumbing

FEATURES AND MATERIALS


| | |
|-----------------|---|
| Finish Trim | Tool-Free, Screw Free Installation |
| Test Plugs | Reusable, Quarter Turn Tool-Free Installation |
| Drain Gasket | Locking Rubber Gasket |
| Overflow Gasket | High Memory Foamed Rubber |
| Spud | Chrome Plated Brass |

PERFORMANCE SPECIFICATIONS

| | |
|------------------|--------------------|
| Test Plug Rating | 40 FT Head, 17 PSI |
| Flow Rate | 10.95 GPM |

DIMENSIONS

| | | |
|------|---------------------|--------------------|
| [A]: | Drain / Spud Thread | 1-1/2" – 11.5 NPSM |
| [B]: | Drain Length | 7-5/8" |
| [C]: | Pipe Diameter | 1-1/2" |
| [D]: | Overflow Height | 14-1/4" |



Access BIM/Revit content through www.oatey.com



TRUE BLUE® BATH WASTE FULL KIT W/TEST

PRODUCT SELECTOR

| TRUE BLUE® BATH WASTE FULL KIT W/TEST | | | | | | |
|---------------------------------------|----------------|----------|---------------|-------------------|---------------------|--------------------|
| ✓ | Product Number | Material | Stopper Style | Finish | Drain Spud Material | Test Plug Included |
| | A9840CP | ABS | Push & Pull | Chrome | Chrome Plated Brass | Yes |
| | A9840BN | ABS | Push & Pull | Brushed Nickel | Chrome Plated Brass | Yes |
| | A9840RB | ABS | Push & Pull | Oil Rubbed Bronze | Chrome Plated Brass | Yes |
| | A9850CP | ABS | Touch Toe | Chrome | Chrome Plated Brass | Yes |
| | A9850BN | ABS | Touch Toe | Brushed Nickel | Chrome Plated Brass | Yes |
| | A9850RB | ABS | Touch Toe | Oil Rubbed Bronze | Chrome Plated Brass | Yes |
| | A9860CP | ABS | Uni-Lift | Chrome | Chrome Plated Brass | Yes |
| | A9860BN | ABS | Uni-Lift | Brushed Nickel | Chrome Plated Brass | Yes |
| | A9860RB | ABS | Uni-Lift | Oil Rubbed Bronze | Chrome Plated Brass | Yes |
| | P9840CP | PVC | Push & Pull | Chrome | Chrome Plated Brass | Yes |
| | P9840BN | PVC | Push & Pull | Brushed Nickel | Chrome Plated Brass | Yes |
| | P9840RB | PVC | Push & Pull | Oil Rubbed Bronze | Chrome Plated Brass | Yes |
| | P9850CP | PVC | Touch Toe | Chrome | Chrome Plated Brass | Yes |
| | P9850BN | PVC | Touch Toe | Brushed Nickel | Chrome Plated Brass | Yes |
| | P9850RB | PVC | Touch Toe | Oil Rubbed Bronze | Chrome Plated Brass | Yes |
| | P9860CP | PVC | Uni-Lift | Chrome | Chrome Plated Brass | Yes |
| | P9860BN | PVC | Uni-Lift | Brushed Nickel | Chrome Plated Brass | Yes |
| | P9860RB | PVC | Uni-Lift | Oil Rubbed Bronze | Chrome Plated Brass | Yes |

| TRUE BLUE® BATH WASTE TRIM KIT | | | | | | | |
|--------------------------------|----------------|---------------|-------------------|---|----------------|---------------|-------------------|
| ✓ | Product Number | Stopper Style | Finish | ✓ | Product Number | Stopper Style | Finish |
| | K97WH | Touch Toe | White | | K98WH | Uni-Lift | White |
| | K97MB | Touch Toe | Matte Black | | K98MB | Uni-Lift | Matte Black |
| | K97CP | Touch Toe | Chrome | | K99CP | Push & Pull | Chrome |
| | K97BN | Touch Toe | Brushed Nickel | | K99BN | Push & Pull | Brushed Nickel |
| | K97RB | Touch Toe | Oil Rubbed Bronze | | K99RB | Push & Pull | Oil Rubbed Bronze |
| | K98CP | Uni-Lift | Chrome | | K99WH | Push & Pull | White |
| | K98BN | Uni-Lift | Brushed Nickel | | K99MB | Push & Pull | Matte Black |
| | K98RB | Uni-Lift | Oil Rubbed Bronze | | | | |