Ground Rod Clamp, Rod to Conductor, Bronze - CP58












- For use with copper-bonded ground rods
- Parts that are UL Listed are suitable for direct burial in earth or concrete











Part Number	CP58
Torque (TQ)	150 – 300 in lb
Material	Silicon Bronze
Ground Rod Diameter, Nominal	1/2" – 5/8"
Ground Rod Diameter, Actual (Ø)	0.50" – 0.56"
Conductor Size	#10 Solid - #2 Stranded 6 mm² Solid - 25 mm² Stranded
Wrench Size	1/2"
Complies With	IEC® EN 62561-1
Certifications	CSA 46866 cULus Qualifoudre RUS
Standard Packaging Quantity	50 pc
UPC	78285630703
EAN-13	8711893041675

CSA, CSA-US and C-CSA-US are registered trademarks of Canadian Standards Association. IEC is a registered trademark of the International Electrotechnical Commission. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent 's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

 \odot 2019 nVent All rights reserved nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

