



Catalog Number: E2-H


Baci At Home

E2-H



The center of the mirror is 7 1/8" above the center of the outlet box. Since the typical user's eye height is 58 3/4" the outlet box should be centered 51 5/8" above the floor.







E2-H

Installation

 Attach backplate to the outlet box
Connect wires - green to ground, white to neutral and black to line
Slide canopy over the screws protruding from the backplate
Secure with trim nuts





E2-H — Affordable Reversible Wall Mirror

	Product Category	Echo Mirrors
	Special Features	Solid brass construction Optical quality 5X and 1X glass mirror Halo light and fog-free optics Traditional incandescent lighting Easy to replace 15 watt T-6 candelabra base lamp 1 year warrantee
	Lighting	Halo Light - Low Power Incandescent
	Lumens	120
	Color Temperature	2500° K
	Color Rendering Index	98
	Electrical	
	Watts	15
	Volts	120
	Hertz (Frequency)	60
	Amps (Current)	.13
	UL Listing	Portable lamp - suitable for damp locations (US)
	Dimensions	Mirror body 8 1/4" diameter Folds to 9 7/8" wide x 13 3/4" high x 3 1/4" deep Canopy is 4 3/4" diameter Maximum extension 13 1/4"
Other Models in this Family		
E2-LED	Basic Model	E2-H-CHROME
	Body Types	All metal body
	Magnification	5X front/1X back
	Finish Options Standard Standard Standard	Chrome Satin Nickel Bronze
E2-X		



E2-X