

TAPE-ROPE HYBRID



Easy to use, flexible, dimmable lighting in Bright White and Warm White kits. Interconnect to build your own semi-custom c/ETL/us rated solution.

Performance

- Line voltage kits are economical - no drivers needed
- 3528 SMD LEDs emit up to 72 lumens per foot
- Dimmable with most electronic low voltage (ELV) dimmers* for 5-100% light control
- Suitable for indoor and outdoor use

Construction

- Each kit includes removable five foot power cord with 1.6A inverter and fused 120V AC 2-prong plug, removable cap on opposite end and 1 clip per foot of light
- 2/3" LED spacing in white perforated PVC housing with clear PVC jacket

Installation

- Use clips to hold in place for many indirect view installations
- Clear plastic track should be used for direct view installations and when mounting to the underside of a shelf or ledge to prevent sagging
- Easy to install - kits interconnect and plug into standard 120V AC receptacles



Specifications

Series	120-TL60
Input voltage	120V AC, 60Hz
Colors	WH and WW
CRI or nm	82+ CRI
Wattage	See individual product
Lumens	65Lm/ft (WW) / 72Lm/ft (WH)
Kit lengths	See individual product
Maximum run	106 feet
Cuttability	N/A
Beam angle	109°
Dimming	5-100% with ELV dimmers
Material	White PVC housing, clear PVC jacket
Rating	c/ETL/us, suitable for wet locations
Dimensions	3/8"W x 1/4"H
Switching	Wall control
Mounting	Clips or mounting track
Linking	See 120-TL-JUMP accessories
LED type	3528 SMD LEDs (60 per meter)
Rated life	35,000 hrs

*Per the NEC, switched wall outlets cannot be used with wall dimmers



WARM WHITE KITS
3000K • 82CRI • 65Lm/ft

120-TL60-3.3-WW

3.3ft / 4.8W

120-TL60-6.6-WW

6.6ft / 9.6W

120-TL60-13.2-WW

13.2ft / 19.2W

120-TL60-19.7-WW

19.7ft / 28.8W

120-TL60-32.8-WW

32.8ft / 48W

120-TL60-45.9-WW

45.9ft / 67.2W



BRIGHT WHITE KITS
5000K • 82CRI • 72Lm/ft

120-TL60-3.3-WH

3.3ft / 4.8W

120-TL60-6.6-WH

6.6ft / 9.6W

120-TL60-13.2-WH

13.2ft / 19.2W

120-TL60-19.7-WH

19.7ft / 28.8W

120-TL60-32.8-WH

32.8ft / 48W

120-TL60-45.9-WH

45.9ft / 67.2W

Each kit includes clear plastic mounting clips with screws (1 set per foot), (1) 5ft 120V AC removable power cord with 1.6A inverter and (1) removable end cap

Tape-Rope-Hybrid Accessories



Jumper (linking) cables

120-TL-JUMP-3 3ft cable

120-TL-JUMP-6 6ft cable

120-TL-JUMP-15 15ft cable



120-TL-TRACK-4

4ft clear plastic mounting track