

BRADENTON COLLECTION

TWO-PIECE HIGH EFFICIENCY TOILET

Product Codes:

MIRBD250WH - ADA bowl (white), MIRBD250BS - ADA bowl (biscuit),

MIRBD230WH - round-front bowl (white), MIRBD200WH - tank, 12" rough-in (white) MIRBD230BS - round-front bowl (biscuit), MIRBD200BS - tank, 12" rough-in (biscuit) MIRBD240WH - elongated bowl (white), MIRBD210WH - tank, 10" rough-in (white) MIRBD240BS - elongated bowl (biscuit), MIRBD214WH - tank, 14" rough-in (white) MIRBD200UWH - insulated tank, 12" rough-in (white)

MIRBD200RWH - right hand tank, 12" rough-in (white)

- Vitreous china construction
- 1.28 gpf HET, High efficiency toilet
- EPA WaterSense certified
- Uses 20% less water than standard low-consumption toilets
- 2" fully glazed trapway with high performance 3" flush valve
- Includes polished chrome trip lever

- 100% factory flush tested
- Installation, operating, care and maintenance instructions included
- Seat and supply not included
- 1 year limited warranty
- Meets ASME standard: A112.19.2M
- Meets ASME standard: A112.1914-2006
- cUPC/IAMPO listed
- Recommended Accessories MB130969 - Flush lever, CP MB130970 - Flush lever, BN MB130971 - Flush lever, ORB

MIRTSSC100BS - Round, slow-close seat (biscuit) MIRTSSC200WH - Elongated, slow-close seat (white) MIRTSSC200BS - Elongated, slow-close seat (biscuit)







BRADENTON COLLECTION


TWO-PIECE HIGH EFFICIENCY TOILET

Product Codes:

MIRBD230WH - round-front bowl (white), MIRBD200WH - tank, 12" rough-in (white) MIRBD230BS - round-front bowl (biscuit), MIRBD200BS - tank, 12" rough-in (biscuit) MIRBD240WH - elongated bowl (white), MIRBD210WH - tank, 10" rough-in (white)

MIRBD240BS - elongated bowl (biscuit), MIRBD214WH - tank, 14" rough-in (white)

MIRBD250WH - ADA bowl (white), MIRBD200UWH - insulated tank, 12" rough-in (white)
MIRBD250BS - ADA bowl (biscuit) , MIRBD200RWH - right hand tank, 12" rough-in (white)



	MIRBD200/ MIRBD230	MIRBD200/ MIRBD240	MIRBD200/ MIRBD250
А	30-1/8"	30-1/4"	30-7/8"
В	17"	17"	17"
С	16-1/2"	18-1/2"	18-1/2"
D	8-3/8"	8-3/8"	8-3/8"
E	16-1/4"	16-1/4"	17"
F	28"	29-1/2"	29-1/2"
R	12"	12"	12"

	MIRBD210/ MIRBD230	MIRBD210/ MIRBD240	MIRBD210/ MIRBD250
D	6-3/4"	6-3/4"	6-3/4"
F	26-3/8"	28"	28"
R	10"	10"	10"

	MIRBD214/ MIRBD230	MIRBD214/ MIRBD240	MIRBD214/ MIRBD250
D	10"	10"	10"
F	29-1/2"	31-1/2"	31-1/2"
R	14"	14"	14"

