TOOL

ANCHOR









Match your application to the right system

BIT


ACCESSORY

For the Electrical Contractor I System Selection















TAB


TAB is a concept developed specifically for the contractor. It provides the optimum combination of Tools, ICC approved Anchors, Bits and Accessories(+) for a concrete application. Choose the application, then choose the system:







For the Electrical Contractor I System Selection





TAB+

Tools, Anchors, Bits + Accessories

Electrical


Junction Box











Conduit C to Concre	te Block			
	T4 T0	A7	В6	+8,11
System:	T1,T2, T3,T4	A5	B4	+1,11
System.	,	8A	B1	+1,11
	T6	A11	-	+9,11

For the Electrical Contractor I System Selection







DCF880M2



T7

A12

+1.,11



DCF887D2

Anchors

P3500



Bits



+ Accessories



For the Electrical Contractor I Tools I Anchors





DCH273P2DH

Dust Extractor for 1" 20v MAX SDS Rotary Hammer

Product Features

- · Powerful dust extraction system with built in motor
- 2-second power-off delay
- Replaceable dust nozzle & high capacity dust box
- Replaceable HEPA filter
- Fits DEWALT 1" 20V rotary hammers DCH273P2 and DCH273.





D25263K

1" D-Handle Three-Mode SDS Rotary Hammer Kit

Product Features

- 2.8 Joules of impact energy
- 8.0 Amp motor
- · Reverse feature for removal of fasteners
- Variable speed
- Factory-set clutch reduces sudden, high torque reactions if bit jams
- 360° side handle adjusts easily





1" L-Shape SDS Rotary Hammer

Product Features

- SHOCKS Active Vibration Control® reduces
- 9 amp motor: 0-820 RPM, 0-4,700 BPM
- Variable speed trigger
- 4.2 Joules impact energy
- 3-Mode selector
- E-Clutch Anti-rotational technology
- 360° side handle





DCH273P2

20V Max Brushless SDS Rotary Hammer

Product Features

- Brushless motor extends runtime and durability
- SHOCKS Active Vibration Control® significantly reduces vibration
- 2.1 Joules impact energy





D25603K

1-3/4" SDS Max Combination Hammer

Product Features

- Active Vibration Control® shocks reduce vibration
- 2 Stage Clutch & E-Clutch
- 8.0 Joules of impact energy; 13.5 amp highperformance motor
- Electronic variable speed dial, trigger lock-on, electronic soft start





Trak-It® C5 ST

Fuel Injected Cordless Nailer

- Fastens into substrates of concrete, lightweight concrete, hollow & grouted CMU, masonry and steel
- · Lightest and smallest tool in its class; powerful 105 Joules output
- Shoots pins up to 1-1/2" in length
- Shoots .102", .108", .120" and .145" dia. pins
- Accepts Stick-E accessories
- NEW! Trak-It C5 pole tool for overhead attachment

Specifications	
Tool Dimensions	17.24" I x 14.71" h x 4.88" w
Weight	7.90 lbs.
Power / Power to Weight Ratio	105 Joules / 13.04
Pin Length / Shank Diameter	1/2"-1-1/2" I. / .102"145" dia.
Trigger Pull Load	2.5 lbs.
Shots Per Fuel Cell	800

Trak-It C5 Product Offering		
Powers #	Description	
55144-PWR	Short track, for pins up to 1-1/2" length	
Note: Alternate	tracks available in accessory section of this manual,	





.27 Caliber Powder Actuated Tool

- Low velocity, semi-automatic for high speed and repetitive volume applications
- · Accepts ceiling clip assemblies.
- Di-electric 6 or 8' length pole tool for overhead attachment (see accessories section)

Specifications	
Tool Body	Precision Cast Aluminum
Tool Length / Weight	13-5/8" / 5 lbs
Pin Length / Type	1/2" - 3" Total Length Ballistic Point Drive Pin, .300 Head Drive Pin, 8mm Head 1/4"-20 Threaded Stud
Load Type	.27 Caliber in a 10 Load Strip
Power Level	Brown (2), green (3), yellow (4) red (5)

P3500 Product Offering		
Powers #	Description	
52000-PWR	P3500 tool deluxe kit	
52021-PWR	P3500 tool blister pack	





DCF887D2

20V Max XR Brushless 1/4" 3-Speed Impact Driver

- Brushless motor; 0-1000/ 2800/ 3250 rpm, 240/1500/1825 in-lbs
- 3-mode impact selector
- · Drop & load easy grip chuck
- · Compact: 5.3" length





DCF880M2

20V Max Lithium Ion 1/2" Impact Wrench

Product Features

- Compact: 5.70" (front /back), 3.4 lbs
- Three (3) LED lights with 20 second delay
- XR[™] Li-lon batteries with fuel gauge
- · Textured anti-slip comfort grip









Snake+®

Internally Threaded Self-Tapping Anchor

Product Features





ESR-2272 Category 1 Cracked & Uncracked Concrete

Report# 25810 Concrete

Base Material

Normal Weight Concrete, Light Weight Concrete, Concrete Over Metal Deck

Size Range

1/4", 3/8", 1/2" dia. (Cracked & Uncracked Concrete)

Anchor Material

Zinc Plated Carbon Steel

- Internally threaded self-tapping screw anchor
- Consistent performance in cracked or uncracked concrete
- Packed with SDS Wedge-Bit & Snake+ setting tool

Snake+ Product Offering					
Powers #	Size	Min. Hole Depth	Internal Thread Depth	Box	Ctn.
6400SD-PWR	1/4"	2"	22/32"	100	1000
6401SD-PWR	3/8"	1-5/8"	11/16"	50	500
6403SD-PWR	1/2"	2-1/2"	29/32"	50	300





Vertigo®+

Rod Hanger System

Product Features



ESR-2989 Category 1 Cracked & Uncracked Concrete

Base Material

Concrete

Size Range

For rod sizes 1/4", 3/8" and 1/2"

Anchor Material

Carbon Steel, Yellow Dichromate Finish

- Threaded fastening system for suspending steel threaded rod and other assemblies
- · Install with Vertigo Concrete Driver Socket
- · Packed with SDS Wedge-Bit

Vertigo+ Product Offering					
Powers #	Rod Size	Screw Shank & Length	Box	Ctn.	
7180SD-PWR	1/4"	3/8" x 2-1/8""	100	1000	
7181SD-PWR	3/8"	3/8" x 2-1/8""	50	500	
7182SD-PWR	1/2"	3/8" x 2-1/8""	50	300	





Smart DI+® Drop In Anchor

Internally Threaded Expansion Anchor

Product Features





File# Ex1289

Base Material

Concrete

Size Range

1/4" - 3/4"

Anchor Material

Carbon Steel

- · Blue indicator clearly shows anchor is properly set
- Patented plug design yields a higher percentage of the expansion at the bottom of the anchor,
- Set using Smart Tool. Drill hole, slide the tool sleeve over carbide drill and lock into place

Smart DI+ Anchor Product Offering				
Powers #	Size	Box	Ctn.	
6304SD-PWR	1/4"	100	1000	
6306SD-PWR	3/8"	50	500	
6308SD-PWR	1/2"	50	250	

Consider 5/8"-1" Steel Dropin for higher load option.

Carbon Steel Dropin (Smooth Wall) Powers # Size Box Ctn. 6320-PWR 5/8" 25 125 6312-PWR 3/4" 10 50

Type 303 Stainless Steel Dropin				
Powers #	Size	Box	Ctn.	
6210-PWR	5/8"	25	125	
6212-PWR	3/4"	10	50	

Type 316 Stainless Steel Dropin				
Powers #	Size	Box	Ctn.	
6230-PWR	5/8"	25	125	
6232-PWR	3/4"	10	50	

Carbon Steel Coil Thread Dropin				
Powers #	Size	Box	Ctn.	
6332-PWR	3/4"	10	50	

A4

Lok-Bolt AS®

Sleeve Type Expansion Anchor

Base Material

Concrete, Block, Brick

Size Range

1/4" x 5/8" to 3/4" x 7-1/2"

Anchor Material

Carbon Steel & Stainless Steel

- Pre-assembled single unit sleeve anchor, extension sleeves create longer lengths
- Carbon steel and stainless steel



Lok-Bolt Product Offering					
Powers #	Size	Drill Dia.	Box	Ctn.	
05150S-PWR	1/4" x 5/8" Acom Head	1/4"	100	1000	
05010S-PWR	5/16" x 1-3/8" Hex Head	5/16"	50	500	
For additional hea	ad styles, diameters and lengths.	refer to www.	powers.	com	





Nail Anchor

Base Material

Concrete, Block, Brick, Stone

Size Range

1/4" x 1-3/8" and 1/4" x 2-1/2"


Anchor Material

Carbon Steel

- One piece, all steel, nail drive anchor. Just drill a hole and hammer it in.
- Applications include HVAC duct straps, light to medium duty signage, termination bar & flooring
- Box includes a 6mm SDS Carbide drill bit

Safe-T+ Pin Product Offering					
Powers #	Size	Drill Dia.	Box	Ctn.	
2800SD-PWR	6mm (1/4") x 1-3/8"	6mm	100	600	
2801SD-PWR	6mm (1/4") x 2-1/2"	6mm	100	600	





Wedge Expansion Anchors Product Features



ESR-2818



Report# 25864 Masonry







3033795 E

ESR-2966 Masonry Base Material

Category 1 Cracked & Uncracked Concrete

Normal-Weight Concrete, Light Weight Concrete, Concrete Over Metal Deck, Grout Filled Masonry

Size Range

1/4" diameter, 3/8" diameter through 1-1/4" diameter (Cracked & Uncracked Concrete)

Anchor Material

Carbon Steel

- Fully threaded, torque-controlled. Consistent performance in cracked & uncracked concrete
- Zinc plated carbon steel body and expansion clip
- · Packed with nut and washer
- · Patented & additional patents pending
- Consider Power-Stud+ SD2 for seismic usage. Technical and ordering information can be found at www.powers.com/mechanical anchors

Power-Stud+SD1	Product Offering			
Powers #	Size	Thread Length	Box	Ctn.
7400SD1-PWR*	1/4" x 1-3/4"	3/4"	100	600
7402SD1-PWR	1/4" x 2-1/4"	1-1/4"	100	600
7404SD1-PWR	1/4" x 3-1/4"	2-1/4"	100	600
7410SD1-PWR*	3/8" x 2-1/4"	7/8"	50	300
7412SD1-PWR*	3/8" x 2-3/4"	1-3/8"	50	300
7413SD1-PWR*	3/8" x 3"	1-5/8"	50	300
7414SD1-PWR*	3/8" x 3-1/2"	2-3/8"	50	300
7415SD1-PWR*	3/8" x 3-3/4"	3-3/8"	50	300
Table continues on	next page	10000	1.7	

For the Electrical Contractor I Anchors I Bits

Power-Stud+SD1 Product Offering, Continued					
Powers #	Size	Thread Length	Box	Ctn.	
7416SD1-PWR*	3/8" x 5"	3-5/8"	50	300	
7417SD1-PWR*	3/8" x 7"	5-5/8"	50	300	

† Sizes which are less than the minimum standard anchor length for Strength Design. For additional diameters (up to 1-1/4") and lengths (up to 12"), please refer to www.powers.com



Tapper+® / Tapper+X

Concrete Screws



Tapper+ Product Features





ESR-3068 Concrete ESR-3196 Masonry

ESR-3042 Wood ESR-3215 Pressure Treated Lumber

Uncracked Concrete, Block, Brick, Wood, Pressure Treated Lumber

Size Range

3/16" and 1/4" Diameters, 1-1/4" - 6" Lengths

Anchor Material

Carbon Steel, Type 304 & Type 410 Stainless Steel

- One-piece self-tapping concrete screw for light to medium duty applications
- Corrosion resistant Perma-Seal® coating; variety of head styles and colors
- Optimized thread design for lower torque, gimlet drill point for wood base materials (no pre-drilling)

Tapper+ Product Offering				
Powers #	Description	Box	Ctn.	
2720SD-PWR [†]	1/4" x 1-1/4" Hex Washer Head	100	500	
2722SD-PWR [†]	1/4" x 1-3/4" Hex Washer Head	100	500	
2724SD-PWR	1/4" x 2-1/4" Hex Washer Head	100	500	
2726SD-PWR	1/4" x 2-3/4" Hex Washer Head	100	500	

Sizes which are less than the minimum standard anchor length for Strength Design. For additional head styles, 3/16" diameter, lengths & finishes, please refer to www.powers.com







ESR-3068 Concrete NOA 10-0505.05

Base Material

Uncracked Concrete


Size Range

5/16" Diameter, 1-3/4" - 6" Lengths

Anchor Material

Carbon Steel

- 5/16" concrete screw, threaded lengths up to 3-1/4"
- · For light gauge metal attachment to CMU
- Hex Flange Head, Trim Hex Head, Phillips Flat Head and Trim Flat Head
- Silver Perma-Seal® coating standard, white and bronze available by special order



Powers # Description			Ctn.	
2200SD-PWR	5/16" x 1-3/4" Hex Washer Head	100	500	
2202SD-PWR	5/16" x 2-1/4" Hex Washer Head	100	500	
2204SD-PWR	5/16" x 2-3/4" Hex Washer Head	100	500	
2206SD-PWR	5/16" x 3-1/4" Hex Washer Head	100	500	
For additional head styles, lengths & finishes, please refer to www.powers.com				







Zamac Hammer-Screw®

Nail Anchor

Base Material

Concrete, Block, Brick and Stone

1/4" x 3/4" to 1/4" x 3"

Anchor Material

Zamac Alloy with Carbon Steel and Perma-Seal **Drive Screw**

- Unique, one-step drive anchor; #2 Phillips head and internal screw thread
- Corrosion resistant Zamac alloy body, carbon steel drive screw, also offered with an optional Perma-Seal® coated screw
- Removable

Zamac Hammer-Screw Product Offering				
Powers #	Description	Box	Ctn.	
02839-PWR	1/4" x 3/4"	100	500	
02840-PWR	1/4" x 1"	100	500	
02842-PWR	1/4" x 1-1/4"	100	500	
02844-PWR	1/4" x 1-1/2"	100	500	
02846-PWR	1/4" x 2"	100	500	
02848-PWR	1/4" x 2-1/4"	100	500	
02850-PWR	1/4" x 3"	100	500	
02817-PWR	1/4" x 1-1/4" Perma-Seal Screw	100	500	





Hollow-Set Dropin

Internally Threaded Expansion Anchor

Product Features





File# 15219/1952 3/8", 1/2" & 5/8"

3/8", 1/2" & 5/8" diameters

Base Material

Concrete, Block, Brick, Pre-Cast Hollow Core Plank and Stone

Size Range

1/4" to 5/8"

Anchor Material

Zamac Alloy with Carbon Steel or Stainless Steel Cones

- Overcomes the problem of spalling on the back side of hollow base materials
- Can also be used in solid base materials





Wedge-Bolt+

Screw Anchor

Product Features



ESR-2526 Category 1 Cracked & Uncracked Concrete ESR-1678 Masonry

LARR

Report# 25808 Concrete

Normal-Weight Concrete, Light Weight Concrete, Concrete Over Metal Deck, Grouted CMU

Size Range

1/4" diameter, 3/8" diameter through 3/4" diameter (Cracked & Uncracked Concrete)

Zinc plated carbon steel body & finished hex head

- One piece, heavy duty screw anchor with finished hex head
- · Simple to install, easy to identify and removable
- Suited for many applications in a variety of base materials
- Consistent performance in cracked and uncracked
- · Install with matched tolerance Wedge-bit

Powers #	Size	Min. Embed.	Box	Ctn.
7204SD-PWR	1/4" x 1-1/4"†	1"	100	600
7206SD-PWR	1/4" x 1-3/4"†	1"	100	600
7207SD-PWR	1/4" x 2"	1-3/4"	100	600
7208SD-PWR	1/4" x 2-1/4"	1-3/4"	100	600
7210SD-PWR	1/4" x 3"	1-3/4"	100	500
7220SD-PWR	3/8" x 1-3/4"* †	1-1/2"	50	300
7222SD-PWR	3/8" x 2-1/2"	2-1/8"	50	300
7224SD-PWR	3/8" x 3"	2-1/8"	50	250
7226SD-PWR	3/8" x 4"	2-1/8"	50	250
7228SD-PWR	3/8" x 5"	2-1/8"	50	250
7230SD-PWR	3/8" x 6"	2-1/8"	50	150
7240SD-PWR	1/2" x 2"†	1-3/4"	50	150
7242SD-PWR	1/2" x 2-1/2"†	1-3/4"	50	200
7244SD-PWR	1/2" x 3"	2-1/2"	50	150
7248SD-PWR	1/2" x 5"	2-1/2"	25	100
7250SD-PWR	1/2" x 6"	2-1/2"	25	75
7268SD-PWR	1/2" x 6-1/2"	2-1/2"	25	75
7252SD-PWR	1/2" x 8"	2-1/2"	25	75

† Sizes which are less than the minimum standard anchor length for Strength Design. For additional diameters, lengths, mechanically galvanized and 316 stainless steel options, please refer to www.powers.com





Trak-It Drive Pins

For C5 Fuel Injected Cordless Nailer

Product Features





Report# 25920 Concrete

Base Material

Concrete, Lightweight Concrete, Hollow and Grouted CMU, Masonry & Steel

- Zinc plated for corrosion resistance
- · Plastic collation breaks free of during installation
- Wide range of pins at www.powers.com

Standard 0.102" Shank Diameter Pin Product Offering				
Powers #	Length	Plating	Box	Ctn.
55310-PWR	3/4"	Zinc	800	4,000

Specialty Tapered Short Pin Product Offering						
Powers #	Length	Shank	Plating	Box	Ctn.	
55325-PWR	1/2"	0.120	Zinc	800	4.000	



Powder Drive Pins

For The P3500 Powder Actuated Tool

Product Features



ESR-2024 .300 Head Drive Pins ESR-1995 8mm Head Spiral CSI Pins

Concrete, some types of Masonry & A36 Structural Steel

1/2" to 3" shank length, shank diameter 0.145"

- · Permanent fastening
- Knurled shank increases performance in steel
- Plastic flute retains the pin in the fastener guide
- Washered pins provide pullover resistance



50070-PWR	50012-PWR	50026-PWF

.300 Head Drive Pins, .145" Shank Diameter						
Powers #	Description	Length	Box	Ctn.		
50070-PWR	.300 Head Drive Pin, 3/4" Washer	3/4"	100	1000		
50012-PWR	.300 Head Drive Pin, Knurled	1/2"	100	5000		
50022-PWR	.300 Head Drive Pin	3/4"	100	5000		
50026-PWR	.300 Head Drive Pin	1"	100	5000		



50201-PWR

8mm Head Spiral CSI Drive Pins; .157" Shank Diameter					
Powers #	Description	Length	Box	Ctn.	
50197-PWR	Spiral CSI Drive Pin (145")	1/2" (13mm)	100	1000	
50201-PWR	Spiral CSI Drive Pin	5/8" (16mm)	100	1000	
50203-PWR	Spiral CSI Drive Pin	3/4" (19mm)	100	1000	
Collated Spira	I CSI pins available in length	s 5/8" to 2"; 10) pin s	trips	



- · For removability or where shimming is required
- · Plastic cap protects the threads of the fastener during the driving process


1/4"-20 Threaded Stud; .145" Shank Dia; 1/4" Thread Dia., Knurled					
Powers #	Description	Thread Len.	Shank Len.		Ctn.
50330-PWR	1/4"-20 Threaded Stud,	3/4"	1/2"	100	1000



SDS-Plus Carbide Bits

High Impact / Standard





• Use in a rotary hammer equipped with an SDS (slotted drive shaft) type chuck in concrete block brick & soft stone

High Impact SDS-Plus Carbide Bit Product Offering				
DEWALT #	Powers #	Diameter	Usable Length	Overall Length
DW5517	0713-PWR	1/4"	4"	6"
DW5524	0721-PWR	5/16"	4"	6-1/2"
DW5527	0727-PWR	3/8"	4"	6-1/2"
DW5537	0739-PWR	1/2"	4"	6"
DW5471	N/A	5/8"	8"	10
DW5474	N/A	3/4"	8"	10"
DW5479	N/A	1"	8"	10"



Standard SDS-Plus Product Features





SDS-Plus Shank 2-Cutter Tip Conforms ANSI Std. B212.15

 Use in a rotary hammer equipped with an SDS (slotted drive shaft) type chuck in concrete block brick & soft stone

Standard SDS-Plus Carbide Bit Product Offering					
DEWALT #	Powers #	Diameter	Usable Length	Overall Length	
DW5417	0321-PWR	1/4"	4"	6-1/2"	
DW5424	0329-PWR	5/16"	4-1/4"	6-1/4"	
DW5427	0333-PWR	3/8"	4-1/4"	6-1/2"	
DW5429	0334-PWR	3/8"	8-1/4"	10-1/4"	
DW5430	0336-PWR	3/8"	10-1/4"	12-1/4"	
DW5446	0359-PWR	5/8"	6"	7-3/4"	
DW5453	0368-PWR	3/4"	6"	8"	
DW5464	0380-PWR	1"	8"	10"	


Wedge-Bolt Bits

For Wedge-Bolt +, Vertigo+ and Tapper+X

2 Cutter

SDS-Plus Wedge-Bit Product Features

SDS-Plus Shank High Impact Tip



SDS-Plus Wedge-Bit Product Offering						
DEWALT #	Powers #	Diameter	Usable Length	Overall Length		
N/A	1312-PWR	1/4"	2"	4"		
N/A	1314-PWR	1/4" (Tapper+Xtreme)	4"	6"		
N/A	1315-PWR	1/4" (Tapper+Xtreme)	6"	8"		
N/A	1316-PWR	3/8" (Vertigo+)	4"	6"		
N/A	1318-PWR	3/8"	6"	8"		
N/A	1319-PWR	3/8"	16"	18"		
N/A	1332-PWR	3/8"	10"	12"		
N/A	1320-PWR	1/2"	4"	6"		

N/A 1335-PWR 1/2" 18"

1/2"

1/2



1322-PWR

1334-PWR



SDS-Max Shank High Impact Tip

SDS-Max Wedge-Bit Product Offering				
DEWALT #	Powers #	Diameter	Usable Length	Overall Length
N/A	1354-PWR	1/2"	8"	13"



N/A

N/A

SDS-Max Carbide Bits

High Impact

High Impact SDS-Max Product Features





SDS-Max Shank 4-Cutter Tip

8"

10"

16"

10"

12"

 Use in a rotary hammer equipped with an SDS Max type chuck in concrete block brick & soft stone

High Impact SDS-Max Carbide Bit Product Offering				
DEWALT #	Powers #	Diameter	Usable Length	Overall Length
DW5806	8809-PWR	5/8"	8"	13-12"
DW5810	8817-PWR	3/4"	8"	13-1/2"



Standard SDS-Max Product Features



SDS-Max Shank 2-Cutter Tip

- DEWALT carbide tip design maximizes carbide surface contact for longer bit life
- U-Flute cleans out debris, open head design channels dust into flutes

SDS-Max Carbide Bit Product Offering				
DEWALT #	Powers #	Diameter	Usable Length	Overall Length
DW5803	N/A	1/2"	8"	13-1/2"
DW5870	N/A	5/8"	8"	13-1/2"
DW5872	N/A	3/4"	8"	13-1/2"

For the Electrical Contractor | Bits | Accessories



SDS-Plus 6mm



SDS-Plus Shank 2-Cutter Tip

Sale-1+ Fill Carbide Dit Froduct Offering				
DEWALT #	Powers #	Diameter	Usable Length	Overall Length
N/A	2800-PWR	6mm	3-1/4"	13-1/2"



Smart DI+® Bits SDS-Plus

Product Features





SDS-Plus Shank 2-Cutter Tip

• Part of the Smart DI+ System; match with Smart DI+ Anchor and Smart DI+ Setting tool

SDS-Plus A	SDS-Plus Accu-Bits Product Offering				
DEWALT #	Powers #	Size	For Dropin Size		
N/A	00391SD-PWR	3/8" DI+ Drill	Smart DI+ 1/4"		
N/A	00397SD-PWR	1/2" DI+ Drill	Smart DI+ 3/8"		
N/A	00410SD-PWR	5/8" DI+ Drill	Smart DI+ 1/2"		

Tapper+ Bits

For Tapper+ Concrete Anchors

Staight Shank Tapper+ Bit Product Features



Tapper+ Straight Shank Bit Product Uttering				
	DEWALT #	Powers #	Size	Usable Length
į	N/A	2785SD-PWR	3/16" x 3-1/2"	2"
1	N/A	2786SD-PWR	3/16" x 4-1/2"	3"
	N/A	2787SD-PWR	3/16" x 5-1/2"	4"
	N/A	2788SD-PWR	3/16" x 6-1/2"	5"
	N/A	2789SD-PWR	3/16" x 7-1/2"	6"



SDS-Plus Tapper+ Bit Product Features





SDS-Plus Shank 2-Cutter Tip

Tapper+ Hex Shank Bit Product Offering				
DEWALT #	Powers #	Size	Usable Length	
N/A	2796SD-PWR	3/16" x 5"	3"	
N/A	2797SD-PWR	3/16" x 7"	4"	



Sledge Hammer

2.5 lb. Double Faced

PROTO

Made in U.S.A.

- · Designed for striking metal, concrete, and stone
- · Strong fiberglass handle with slip-resistant cushion grip

Specifications	1/	
Head Weight / Overall Weight	2.5 lbs. / 3.28 lbs.	
Face Diameter / Head Length	1-11/16" / 3"	
Handle Length / Overall Length	14" / 15-11/16"	
Specification ASME	ASME B107.54	

Product Offering				
Proto #	Head Weight	Face Diameter	Total Weight	
J1433G	2.5 lbs.	1-11/16"	3.28	



Torque Wrench 3/8" Drive Ratcheting Head

Product Features



PROTO

Made in U.S.A

- Calibrated to +/- 3% in clockwise direction and +/- 6% in counter-clockwise direction
- Manufactured to meet precision/highly accurate applications such as military and aerospace

Specifications	
Drive Size	3/8"
Head Width / Head Depth	1-1/32" / 7/8"
Overall Length / Weight	11-7/8" / 2.60 lbs.
Style	Micrometer
Specification ASME	ASME B107.14
Specification TO	T033K6-4-2193-1

Torque Wrench Product Offering		
Proto #	Description	
J6064CX	3/8" Drive Ratcheting Head Micrometer Torque Wrench 40-200 in-lbs	



Smart DI+® Setting Tool

For The Smart DI+ Anchor System

Part of the Smart DI+ System; match with Smart DI+ Anchor and Smart DI+ Setting tool

Smart DI+ Setting Tool Product Offering				
Powers #	Size	For Smart DI+ Size		
00425SD-PWR	1/4"	1/4"		
00427SD-PWR	3/8"	3/8"		
00429SD-PWR	1/2"	1/2"		



Vertigo® + Accessories

For The Vertigo+ Rod Hanger System

Vertigo+ Driver Socket Product Offering			
Powers #	Size	For Vertigo+ Size	
7198-PWR	1/2"	1/2"	

Vertigo+ Pole	Tool Product Offering
Powers #	Description
7166-PWR	Pole tool telescopes from 6' to 12' to access hard to reach overhead areas. Includes Three Jaw Chuck





Snake+® Driver Socket

For Snake+ Anchors

Snake+ Driver Socket Product Offering			
Powers #	Size	For Snake+ Size	
6402-PWR	1/4"	1/4"	
6407-PWR	3/8"	3/8"	
6404-PWR	1/2"	1/2"	



Impact Ready® Socket

For Wedge-Bolt+


- Recessed corners distribute torque across flats
- Thinner than wrench sockets for tough-toaccess areas
- Easily identifiable
- Suitable for use with corded or cordless impact drivers and wrenches

DEWALT #	Socket Size	Drive Size
DW2281	1/4"	3/8" Drive
DW2282	5/16"	3/8" Drive
DW2283	11/32"	3/8" Drive
DW2284	3/8"	3/8" Drive
DW22842	3/8"	1/2" Drive
DW2285	7/16"	3/8" Drive
DW22852	7/16"	1/2" Drive
DW2286	1/2"	3/8" Drive
DW22862	1/2"	1/2" Drive
DW2287	9/16"	3/8" Drive
DW22872	9/16"	1/2" Drive
DW2288	5/8"	3/8" Drive
DW22882	5/8"	1/2" Drive
DW2289	11/16"	3/8" Drive
DW22892	11/16"	1/2" Drive
DW2290	3/4"	3/8" Drive
DW22902	3/4"	1/2" Drive
DW2291	13/16"	3/8" Drive
DW22912	13/16"	1/2" Drive
DW2292	7/8"	3/8" Drive
DW22922	7/8"	1/2" Drive






6 pt Deep Socket, Continued				
DEWALT #	Socket Size	Drive Size		
DW2293	15/16"	3/8" Drive		
DW22932	15/16"	1/2" Drive		
DW2294	1"	3/8" Drive		
DW22942	1"	1/2" Drive		
DW22952	1-1/16"	1/2" Drive		
DW22962	1-1/8"	1/2" Drive		
DW22972	1-1/4"	1/2" Drive		



Setting Tools For Dropin Anchors

Dropin Setting Tool Product Offering			
Powers #	Description	Box	Ctn.
6305-PWR	1/4" Setting Tool	1	250
6307-PWR	3/8" Setting Tool	1	100
6309-PWR	1/2" Setting Tool	1	100
6311-PWR	5/8" Setting Tool	1	50
6313-PWR	3/4" Setting Tool	1	25



Tionett det Brop				
Hollow-Set Dropin Setting Tool Product Offering				
Powers #	Description	Box	Ctn.	
9323-PWR	1/4"	1	1	
9333-PWR	5/16"	1	1	
9343-PWR	3/8"	1	1	
9353-PWR	1/2"	1	1	
9363-PWR	5/8"	1	1	

Installation Kits

For Tapper+ / Tapper+Xtreme



· Kit includes drill adapter, Phillips driver adapter, drive sleeve, #2 & #3 Phillips bits, 1/4" & 5/16 hex drivers, hex key, plastic carry case

Tapper+ Installation Kit Product Offering					
Powers #	Description	Max. Screw Length	Max. Bit Length	Box	
02791-PWR	Tapper 1000 Tool Kit	4"	5-1/2"	1	
02795-PWR	1000SDS Extension	6"	7-1/2"	1	



• Kit includes magnetic nut driver, #3 Phillips power bit, 1/4" x 8-1/4" and 1/4" x 6" SDS-Plus Wedge Bits, plastic carry case

Tapper+ Xtreme Installation Kit Product Offering		
Powers #	Description	Box
2291SD-PWR	Tapper+ Xtreme Installation Kit	1

Trak-It Accessories

For Use With Trak-It C5 Tool



BX Clip	Minerallac Straps Conduit Clips	Rod H	angers
Powers #	Description	Box	Ctn.
55054-PWR	3/8" Stick-E BX Clip	100	1000
55064-PWR	1/2" Stick-E Mini Conduit Clip	100	1000
55066-PWR	3/4" Stick-E Mini Conduit Clip	100	1000
55068-PWR	1" Stick-E Mini Conduit Clip		1000
55059-PWR	1/2" Stick-E Ribbed Conduit Clip 100		1000
55061-PWR	3/4" Stick-E Ribbed Conduit Clip	100	1000
55063-PWR	1" Stick-E Ribbed Conduit Clip	100	1000
55050-PWR	1/4" Stick-E Rod Hanger	100	1000
55052-PWR	3/8" Stick-E Rod Hanger	100	1000



Fuel Cell			
Powers #	Description	Box	Ctn.
55302-PWR	Trak-It C5 Fuel Cell	20	80
55301-PWR	Trak-lt C5 Fuel Cell / 100 pack	100	-



55583-PWR Extra Battery for Trak-It Tool

NEW pole tool for overhead attachment with Trak-It C5

Pole Tool Product Offering		
Powers #	Description	Box
56347-PWR	C5 Pole Tool Accessory Kit (C5 not included)	1
56348-PWR	C5 Pole Tool 3' Extension	1



Accessory Track Product Offering				
Powers #	Description	Box	Ctn.	
56342-PWR	Accessory deep track; 1-1/4" pin length	1	-	
56344-PWR	Accessory long track; 1-1/2" pin length	- 1	/ -	

Powder Actuated Accessories


For Use With P3500 Tool



Rod Hanger C	Clip Ceiling Clip / w. Post Nut EMT C	onduit	Clips
Powers #	Description	Box	Ctn.
Ceiling clips li	sted below have .145" shank diameter pin	S	
50219-PWR	32mm (1-1/4") pin with 1/4"-20 Rod Hanger; 8mm Head	100	1000
50364-PWR	1" Pin .300 Head Ceiling Clip	100	1000
50376-PWR	1-1/8" Pin / Domed Right Angle Ceiling Cip / Post Nut; .300 Head	100	1000
50382-PWR	1/2" EMT Conduit Clip, 1" Pin; .300 Head	100	1000



.27 Caliber 10-Load Safety Strip Product Offering			
Powers #	Description	Box	Ctn.
50620-PWR	Brown (#2) Power Level	100	1000
50622-PWR	Green (#3) Power Level	100	1000
50626-PWR	Yellow (#4) Power Level	100	1000
50630-PWR	Red (#5) Power Level	100	1000



Pole Tools Product offering			
Powers #	Description	Box	Ctn.
50065-PWR	6' Di-Electric Pole Tool	-	1
50066-PWR	8' Di-Electric Pole Tool	1/-	1



Personal Safety

earing Pi	rotection Product Offering
EWALT #	Description
PG62	Interceptor - Lightweight folding earmuff Noise reduction rating 29 CoolMax headband moves moisture away; cool comfortable fit Adjustable ear cups offer a comfortable fit Padded ear cups fit securely and comfortably

Vision Protection Product Offering

JF 004	Dominator - eye protection	
	Full frame with larger lens	

Rubber accents on temple offers greater comfort

· Compact folding feature for easy storage. Keeps debris

- Integrated rubber nosepiece
- Gradient lens option glare protection
- Meets ANSI Z87.1+ Standards
 99.9% UVA / UVB protection
- Hard coat lens available in clear, smoke, silver mirror, indoor/outdoor, yellow mirror, brown gradient tints

Note: for more personal protection products, go to www.DEWALT.com

More products for the Electrical Contractor



DWM120K

Deep Cut Band Saw

100000000000000000000000000000000000000
10Amps / 100-350fpm
5"
5" x 4-3/4"
Yes
No



DCS373P2

20V Max Lithium Ion Saw

Specifications	
No Load Speed	3,700rpm
Blade Diameter	5-1/2"
Max Watts Out / Voltage	460MW0 / 20V



DCS371P1

20V Max Lithium Ion Band Saw

Specifications	
Blade Length	32-7/8"
Max Capacity (Round)	2-1/2" Rnd. & Sq.
Cutting Speed	740fpm



DCS380P1

20V Max Lithium Ion Reciprocating Saw

Specifications	
Strokes/Min	0-3000spm
Stroke Length	1-1/8"
Variable-Speed Dial.	Kevless, 4-Position Blade Clam



DCD995M2

20V Max XR Lithium Ion Brushless Premium 3-Speed Hammerdrill

Specifications		
No Load Speed	0-430rpm	
Drive	1/4" Hex	



20V Max Lithium Ion Compact Drill /Driver Kit

Specifications		
Max rpm	2,000	
Max Power	350UW0	



E402/DWE402N

4-1/2" Small Angle Grinders

Specifications		
Amps	11.0 Amps	3
rpm	11,000 rpm	Ŧ.
Max Watts Out	1,400 W	ı
Spindle Size, Thread	5/8"-11"	
No Load Speed	11,000 rpm	



18/20V Max Cordless Wet-Dry Vacuum

Specifications	
No Load Speed	7000.0rpm
Spindle Lock	5/8-11
Spindle Thread	5/8-11
Use Wheels rpm Above	10000rpm
Tool Weight	5.1lbs



12V/20V Max USB Power Source

Specifications	
Compatible	12V/20V MAX*



Self Leveling 3 Beam Line Laser

Specifications	71/21
2x Brighter diode	1
Accurate to +/- 1/8" @ 30'	
Built-in magnetic pivot bracket	



DCF681N2/DCF682N1

8V Max Gyroscopic Screwdriver With

Specifications		
No Load Speed	0-430rpm	
Drive	1/4" Hex	



DWV012

Wet / Dry HEPA Dust Extractor

Specifications		
Tank Size	10gal	
Amps	15Amps	Ī
Max CFM	155CFM	Ī
Weight	33.5lbs	Ī
Power Cord	15ft	Ī
Hose	1-1/4" x 15ft	Ī

See dust extractor accessories D25301D, DWH050K and D25303DH listed with corresponding tools on page 8.



DCF681N2/DCF682N1

8V Max Gyroscopic Screwdriver With

OV Wax ayroscopic ocrevvariver vitar		
Specifications		
No Load Speed	0-430rpm	
Drive	1/4" Hex	



AC100+Gold®

Acrylic Adhesive Anchor







For Anchoring, Rebar Doweling, Specified Use, General Use and Cold Weather; (Installation temp. range 14°F to 95°F); or overhead installation, wet concrete and water-filled holes

For rebar & threaded rod 3/8" to 1-1/4"; #3 to #10 10 fl.oz. Quik-Shot; 12 and 28 fl.oz dual cartridges



Pure110+®

Epoxy Adhesive Anchor







For Anchoring, Rebar Doweling, Specified Use, General Use

Installation temp. range 50°F to 110F°; in-use temperatures above 95F°

For rebar & threaded rod 3/8" to 1-1/4"; #3 to #10 9 fl.oz. Quik-Shot; 21 fl.oz. dual cartridges; 3:1 mix ration 12 & 20 fl.oz.



Strap-Toggle™& **Self Drilling Strap-Toggle**

Hollow Wall Anchors

Base Material	Hollow Wallboard or Hollow Block
Size Range	3/16" x 4" to 1/2" x 4
1000	Self-Drilling:
	3/16" x 4" to 1/3" x 4l
Anchor Material	Plastic



Bang-It & Wood-Knocker

Cast-In-Place Anchors



Base Material	Concrete, Lightweight Concrete	
Size Range	1/4" through 3/4" diameter rod; color coded	
	O. L. OL. LO F	

Anchor Material Carbon Steel & Engineered Plastic

Installs through pre-drilled metal composite deck (pan deck) used to support a newly poured concrete floor or roof slab

Wood-Knocker

Installs onto wooden forms used to support newly poured concrete floor slabs, roof slab, or walls



Wall Dog

Universal Light Duty Anchor

Please refer to www.powers.com for a wide range of Wall Dog sizes and head styles.

Packaged Fasteners

Please refer to www.powers.com for a wide range

Hole Saws & Reciprocating Blades

DWA4186	6" 2X™ Premium Metal Cutting Blade; 5 Pk.
DWA4188	8" 2X™ Premium Metal Cutting Blade; 5 Pk.
DWA4176	6" 10TPI 2X™ Recip Blade; 5 Pk.
DWA4179	9" 10TPI 2X™ Recip Blade; 5 Pk.
DWA4101	8pc. 2X Recip Blade Set
DWA1801	2X™ Plumbers Holesaw 9 Pc. Set
DWA1812	2X™ Plumbers Holesaw 3/4"
DWA1814	2X™ Plumbers Holesaw 7/8"
DWA1818	Bi-Metal Hole Saw 1-1/16"
DWA1824	Bi-Metal Hole Saw 1-1/2"
DWA1828	Bi-Metal Hole Saw 1-3/4"
DWA1836	Bi-Metal Hole Saw 2-1/4"

Saw Blades

DWA//4/	14" 66T Heavy Gauge Ferrous Metal Cutting 1" arbor
DWA7770	5-1/2" 30T Ferrous Metal Cutting 2mm arbor
DWA7889	14" 100T Aluminum Cutting 1" arbor

Vacuum Accessories

Accessori	es
DW9315	15' Kink Hose
DW9400	Disposable Plastic Liner, 5 Pk.
DW9402	Fleece Bag, 5 Pk.
DW9316	15' Anti Static Hose
DW9401	Paper Bag, 5 Pk.
DW9314	8' x 2-1/2" Hose
DW9320	Replacemt. HEPA Filter, Typ1; 2 Pk.
DW9330	Replacemt. HEPA Filter, Typ2; 2 Pk.
Attachman	-t-

DWV2759B	Beater Bar Floor Brush Kit Includes: 11" beater bar floor brush, 2 extension wands & storage bag
----------	--

onnectors	
WV9000	Universal Quick Connector
WV9110	Tapered Adapter 1.14" - 1.45"
WV9120	Tapered Adapter 1.37" – 1.54"
WV9130	Tapered Adapter 1.37"
	Tapered Large Diameter Adapter 2.17" – 2.36"

THE CONCRETE SOLUTION DEWALD DRIVER





POWERS FASTENERS BRANCH INFORMATION NATION-WIDE CUSTOMER SERVICE: 1-800-524-3244

ALABAMA + ATLANTA	6115-C Jimmy Carter Blvd. Norcross, GA 30071	678-966-0000
BOSTON	2 Powers Lane Brewster, NY 10509	800-524-3244 877-871-1965
CHARLOTTE	3557-B Wilkinson Blvd. Charlotte, NC 28203	704-375-5012
CHICAGO	2472 Wisconsin Avenue Downers Grove, IL 60515	630-960-3156
DALLAS	1300 I-35 North, Suite #118 Carrollton, TX 75006	972-446-5985
DENVER	700 West Mississippi Ave. Unit B-1 Denver, CO 80223	303-922-9202
DETROIT	21600 Wyoming Avenue Oak Park, MI 48237	248-543-8600 248-543-8601
FLORIDA	2412 Lynx Lane Orlando, FL 32804	813-626-4500 813-626-4545

HOUSTON	13-33 North Promenade Suite 100 Stafford, TX 77477	281-491-0351 281-491-0367
INDIANAPOLIS	15290 Stony Creek Way Noblesville, IN 46060	317-773-1668 317-773-1690
LOS ANGELES	2761 Dow Avenue Tustin, CA 92780	714-731-2500
MARYLAND	3137-B Pennsy Drive Landover, MD 20785	301-773-1722
MILWAUKEE	1650 Miller Parkway Milwaukee, WI 53214	414-645-8821
MINNEAPOLIS	351 Wilson Street, NE Minneapolis, MN 55413	612-644-3047
MISSOURI	3225 Harvester Road Kansas City, KS 66115	816-472-5033 816-472-5040
NASHVILLE	221 Blanton Avenue Nashville, TN 37210	615-248-2667
NEW ORLEANS	102 Sampson Street Houston, TX 77003	713-228-1524 713-228-1528

NEW YORK + PHILADELPHIA	2 Powers Lane Brewster NY 10509	800-524-3244 877-871-1965
PHOENIX	3602 E. Southern Avenue Suite 5, Phoenix, AZ 85040	602-431-8024
PORTLAND	18609 72nd Avenue South Kent, WA 98032-1082	425-251-0312
ROCHESTER	245 Summit Point Drive Suite 2A Rochester, NY 14467	585-334-1423
SALT LAKE CITY	3120 W. California Avenue Suite E Salt Lake City, UT 84104	801-466-9428
SAN FRANCISCO	28970 Hopkins Street Suite D Hayward, CA 94545	510-293-1500
SEATTLE	18609 72nd Avenue South Kent, WA 98032-1082	425-251-0312

DEWALT LOCATIONS

ALABAMA		Birmingham 205-942-0538
		Mobile 251-602-1000
ALASKA	200	Anchorage 907-561-7181
ARKANSAS	-	Little Rock 501-372-3040
ARIZONA		Phoenix 602-437-1200
CALIFORNIA		San Francisco 510-783-3959
		San Diego 858-279-2011
		Anaheim 714-414-0369
		Sacramento 916-344-3520
		Ontario 909-930-1437
COLORADO		Denver 303-922-8325
CONNECTICUT	100	Hartford 860-563-5800
FLORIDA		Ft. Lauderdale 954-321-6635
		Tampa 813-884-0434
		Jacksonville 904-781-2253
		Orlando 407-657-0474
	1910	W. Palm Beach 561-689-3247
GEORGIA		Atlanta 770-246-1710
HAWAII		Honolulu 808-842-9925
IOWA		Des Moines 515-270-1340
ILLINOIS	3234	Chicago South 708-614-1596
		Chicago North 630-521-1097
INDIANA		Indianapolis 317-243-8308
KANSAS		Kansas City 913-495-4330
34		Wichita 316-943-1271
KENTUCKY	13	Louisville 502-380-3748

LOUISIANA	New Orleans 504-832-2187
	Baton Rouge 225-296-3191
	Shreveport 318-688-1553
MARYLAND	Baltimore 410-536-0722
	Capital Heights 301-333-0865
MASSACHUSETTS	Boston 781-329-3407
MICHIGAN	Grand Rapids 616-261-0425
	Detroit 248-597-5000
MINNESOTA	Minneapolis 952-884-9191
MISSOURI	St Louis 314-997-9100
NEVADA	Las Vegas 702-889-6025
NEW JERSEY	Elmwood Park 201-475-3524
NEW MEXICO	Albuquerque 505-884-1002
NEW YORK	Buffalo 716-884-6220
	Queens 718-335-1042
	Rochester 585-334-7071
	Long Island 631-952-2008
	Albany 518-785-1867
NORTH	Charlotte 704-392-0245
CAROLINA	Greensboro 336-852-1300
	Raleigh 919-878-0357
OHIO	Cleveland 440-842-9100
	Cincinnati 513-772-3111
	Columbus 614-895-3112
	Toledo 419-867-8561
OKLAHOMA	Oklahoma City 405-634-8403
	Tulsa 918-249-8641

OREGON		Portland 503-255-6556
PENNSYLVANIA		
TENNSTEVANIA		Philadelphia 215-271-5500
		Pittsburgh 412-642-0204
		Allentown 610-435-9544
		York 717-755-3441
SOUTH CAROLINA		Charleston 843-745-9197
		Greenville 864-299-8662
TENNESSEE		Memphis 901-384-8100
		Nashville 615-242-1633
The state of		Knoxville 865-688-0921
TEXAS		Dallas 972-446-2996
		Houston 713-466-1194
		San Antonio 210-732-1221
		Fort Worth 817-831-3828
		El Paso 915-778-9769
		Mcallen 956-661-1122
		Austin 512-382-3971
UTAH		Salt Lake City 801-486-5828
VIRGINIA		Virginia Beach 757-363-0091
WASHINGTON		Seattle 206-763-2010
	15/	Spokane 509-535-9252
WEST VIRGINIA		Charleston 304-343-0289
WISCONSIN		Milwaukee 414-645-4285















servicenet.dewalt.com or 1-800-4-DEWALT







Powers and DEWALT: two industry leading and trusted construction brands are now a complete solution for your electrical anchoring needs.

Engineered for peak performance and productivity when used together, Powers Fasteners and DEWALT tools and accessories provide complete solutions for professional contractors.

Our fleet of service locations and jobsite representatives complete the package by canvassing the nation and are available for product support and safety training.

For more product information, visit us at:







www.protoindustrial.com

Copyright ©2016 DEWALT. The following are examples of trademarks for one or more DEWALT power tools and accessories: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

Note: The information and data contained within this documentation was current as of February 2016. The information is for marketing purposes only and is subject to change and updates as needed. Powers Fasteners, Inc. reserves the right to change designs and specifications without notice or liability for such changes. Please contact Powers Fasteners for the most current and up to date available information or refer to our website at www.powers.com

Powers Fasteners 701 E. Joppa Road, Towson, MD 21286 P:(800) 524-3244 F:(877) 871-1965 www.powers.com Powers # PWRCONCELECBR 5/16 ©2016 Powers Fasteners, Inc.