

# Welding tools & accessories Electrode holders

#### Electrode holder ESAB 200, 400 & 500

ESAB's CE-approved screw-type electrode holder offers many advantages including:

- Excellent current transfer between electrode and holder ✓ Two hole positions at 45° and 90° for welding in different positions
- ✓ Electrode cable held in place by two Allen screws
- ✓ All electrode holders are fully insulated to provide maximum safety

Ordering information	
ESAB 200, 200 A (35%)	0333 249 001
ESAB 400, 400 A (35%)	0369 849 880
ESAB 500, 500 A (35%)	0369 850 880



#### **EHSK-20, EHSK-40 & EHSK-60**

The economy series, sturdy, tried and tested spring assembly. Closed head design. All electrode holders are fully insulated and approved to EN-60974-11.

EHSK 200 000
EHSK 400 000
EHSK 600 000



## **Eco holder confort**

The Samson (EHSM / confort model) is the "classic" electrode tong with an open design. All EHSM / confort electrode holders are fully insulated and approved to EN-60974-11.

Ordering information	
Confort 300 A (35%), (EHSM300000) Confort 400 A (35%), (EHSM500000)	07000 060 005 07000 060 015
Comort 400 /1 (05/0), (Encline 00000)	07000 000 013



## EHL-30, EHL-40 & EHL-50

The American series L-series, popular heavy duty open design. The electrode holder is made of fibre glass-reinforced plastic. All electrode holders are fully insulated and approved to EN-60974-11.

Ordering information	
EHL 30, 300 A	EHL 300 0000
EHL 40, 400 A	EHL 400 0000
EHL 50, 500 A	EHL 500 0000

