## For Residential and Commercial Applications

Job Name	Engineer / Architect	
Job Location	Wholesaler	
Submittal Date	Contractor	

## PLB200X 1/4 Turn Straight Stop – Compression x Compression


*Use:* For use only in potable water distribution systems, hot and cold, in accessible locations only

Part Listing:

PLB200X B 1/2" nom compression x 3/8" OD compression, chrome plated, bulk
PLB200X P 1/2" nom compression x 3/8" OD compression, chrome plated, bagged




	PART DIMENSIONS (Inches)					
Model	DIM. A	DIM. B	DIM. C	DIM. D	DIM. E	
PLB200X	1.77	1.12	1.64	2.31	.94	



Operating Specifications				
Temperature	Pressure			
Intermittent 40°- 140° F	125 PSI maximum			

MATERIAL SPECIFICATIONS			
Body	Low lead brass, chrome plated		
Stem	Low lead brass		
Ball	Low lead brass, chrome plated		
Seats	PTFE		
O-ring	NBR		
Handle	ABS, chrome plated		
Handle Screw	Stainless steel		
Compression Nut	Brass, chrome plated		
Compression Sleeve	Brass		
Adaptor	Low lead brass, chrome plated		



## **Listings & Certifications:**

- IAPMO listed to ASME A112.18.1 / CSA B125.1 (File #8425)
- IAPMO listed to NSF / ANSI 372 for No-Lead (File #8427)
- IAPMO listed to NSF61 (File #N-8426)



This specification and all information contained herein is the confidential and exclusive property of Brasscraft Manufacturing Co., and shall not be disclosed to others without the written consent of Brasscraft Mfg. Co. This specification must be returned to Brasscraft Mfg. Co. if requested.

