

# Table of Contents

Loading Requirements Cross Reference 4 89

## New England Municipal and Construction Castings

Section	Description	Page
Introduction	New England Municipal and Construction Castings	3
	Loading Requirements, Proof Load Testing, Material Selection, and	4
	State Product Number Nomenclature	
General Overview	We are EJ	5
	A Legacy is Cast	6
	Product Lines	7
	Capabilities	8
Massachusetts		9
Municipal and DOT	Massachusetts Cleanout/Monument Boxes	10
Castings	Massachusetts Municipal Manhole Frames Covers	11
	Massachusetts Municipal Drainage Frames Grates	20
	Traps and Hoods	30
	MassDOT Frames, Covers, and Grates	32
Rhode Island Municipa	al	37
and DOT Castings	Rhode Island Municipal Frames, Covers, and Grates	38
	RIDOT Frames, Covers, and Grates	43
Connecticut Municipal	I	49
and DOT Castings	Connecticuit Municpal Manhole Frames, Covers, and Grates	50
-	Connecticut DOT	59
New Hampshire		61
Municipal Castings	New Hampshire Catch Basins	62
	New Hampshire Manhole Frame and Cover	64
Vermont Municipal		65
Castings	Vermont Standard Frame and Cover	66
	Vermont Drainage Frames and Grates	67
Maine Municipal and		71
DOT Castings	Maine Municipal Frames, Covers, and Grates	72
· ·	MaineDOT Frames, Covers, and Grates	73
Utility and		75
Telecommunication	1802-1825 Frames and Covers	76
Castings	National Grid	77
<b>3</b>	Northeast Utilities	78
	NSTAR	79
Additional Solutions		81
and Information		

Square hole hook lock grate (page 24)



# New England Municipal and Construction Castings



## One Brand. Many Solutions.

Once known as East Jordan Iron Works, EJ is a family-owned company that has grown into a global supplier of infrastructure access solutions. Along the way, EJ acquired the strengths and talents of several reputable companies including LeBaron Foundry Corporation, formerly located in Brockton, Massachusetts.

EJ customers in the New England region can expect a robust portfolio of products and services designed to meet their specific needs—all backed by a legacy built on trust and reliability.

When doing business with EJ, you will receive the personal attention you are accustomed to, backed by an established global brand that delivers quality, value, and exceptional customer focus.

Thank you for considering products and services from EJ. We are eager to assist you with your continuing or future infrastructure needs.



#### **Loading Requirements**

All of our products are designed to meet or exceed the specified loading requirements. They conform to AASHTO and ASTM standards. These standards specify material quality and load requirements.

#### **Proof Load Testing**

All H-20 heavy duty traffic rated construction castings must pass a proof load test conducted in accordance with AASHTO M306 guidelines. The proof load testing procedure calls for the load to be concentrated on a 9" x 9" contact area in the center of the cover or grate and hold 40,000 pounds for one minute. Following the test the casting is carefully inspected. Cracks or permanent deformation are cause for rejection. Frequently, EJ castings are tested far beyond the specified proof load, often to destruction.

#### **Material Selection**

Depending on the model, our construction castings can be manufactured using either gray iron or ductile iron. Gray iron has an unequaled record of success as a material for construction castings. Gray iron is highly resistant to corrosion and maintains compressive strength, abrasion resistance, vibration absorption, and low-notch sensitivity. Additionally, gray iron has a long service life and is very cost effective. Ductile iron combines the advantages of gray iron with greater strength, toughness, higher impact resistance and increased durability without additional weight. Because it has the ability to withstand greater loads without failure, it is often specified for extra-heavy load applications.

#### **State Product Number Nomenclature**

When referencing state specific product numbers listed in this catalog, the following diagram will help you to understand the nomenclature. Note that some state specific products have been adopted for use in states outside of their original designation.



4

Gray and Ductile Iron Load Ratings and Descriptions

Rating	Acceptable Load Weight (lbs)	Description
Airport Extra Heavy Duty	Max. 200,000	Casting has been proof load tested to a minimum 200,000 lbs. This includes an additional safety factor over FAA design loading.
Extra Heavy Duty	Max. 100,000	Casting has been proof load tested to 100,000 - 200,000 lbs. This meets the design loading associated with the FAA wheel loading.
Heavy Duty	Max. 40,000	Casting must meet the requirements of AASHTO M306 to be classified as heavy duty. AASHTO M306 requires that castings bear a minimum of 40,000 lbs on a 9" x 9" area.
Medium Duty	Max. 16,000	Castings designated as medium duty accept loading from 16,000 - 40,000 lbs. These castings can accept standard traffic loading, and are in conformance with H-20/HS-20 (wheel load of 16,000 lbs. on a tire contact area of 8" x 20") or Federal Specification RR-F-621D (25,000 lbs. on a 9" x 9" load contact area).
Light Duty	Max. 2,500	Light duty castings are able to withstand some vehicular loading, but are not designed to accept roadway traffic. Items can accept loading from 2,500-16,000 lbs. These products may be subject to occasional traffic from process maintenance, mowers, etc.
Non-traffic	Under 2,500	Castings designated as non-traffic are intended for use in areas that are not subject to vehicle traffic. Generally nothing over 2,500 lbs. should be placed on these items. Duty rating is 0 - 2,500 lbs.

## **Heavy Duty Rating**

Unless otherwise noted, products in this catalog are Heavy Duty rated. Please refer to product drawings for specific details.

## Made in the USA

All products are Made in the USA and meet Buy America requirements.

## If You Don't See It, Ask Us

Products listed in this catalog are not all inclusive. Visit ejco.com, or contact your EJ sales representative, for our full line of products, information, product drawings, and additional support.

## We are EJ

EJ is the leader in the design, manufacture and distribution of access solutions for water, sewer, drainage, telecommunications and utility networks worldwide.

EJ offers the broadest range of high-quality infrastructure access solutions. Our distribution coverage continues to expand into new markets. As an entrepreneurial family-owned company, we have a long, successful heritage of meeting change with innovation

Since our founding in 1883, we have grown by providing access solutions to meet the demands of the world's growing infrastructure. Fueled by innovation, our design, manufacturing and distribution processes continue to evolve—creating solutions that provide an unparalleled customer experience.

EJ is a family-owned company that has a long history of fostering strong customer relationships. These relationships are supported with personal contact from company representatives, a complete offering of product literature, a comprehensive web site (ejco.com), trade show exhibits, as well as seminars and training opportunities. All these services help to provide customers with the product information required for successful projects.

Wherever you are, EJ provides access solutions that adhere to the local specifications in a timely and competitive manner. We also work with our customers to produce access solutions to meet their specialized requirements. Our sales staff around the world understands the unique needs of your market.

Our people: our core strength. While working together, employees use their expertise, knowledge, and ability to achieve positive results. Core values at EJ include, safety and security, honesty and integrity, environmental responsibility, respect for others, quality and excellence and social responsibility. These core values are imbedded into our culture and are practiced daily throughout the organization.


Our state-of-the-art manufacturing plants employ world class machinery, systems and processes to produce specified products efficiently and on time.

Wherever you are, whatever your specific requirement might be, EJ has the best access solutions for your infrastructure project.



#### **Product Range**

EJ offers a comprehensive portfolio of products and services, including municipal and construction castings, fabricated products, water distribution solutions and other infrastructure access solutions.



#### Quality Manufacturing

Integrating technology, lean processes and over a century of experience in crafting metal castings and fabrications, keeps our facilities performing at peak efficiencies.



#### Distribution Network

Access solution products, including municipal and construction castings, are available worldwide at our internal stocking locations and from our extensive network of distribution partners.



# A Legacy is Cast



William E. Malpass (standing back right, next to window) with employees during the 1920s.

The EJ legacy dates back to 1883 when William E. Malpass and his father-in-law Richard W. Round established a foundry on the shores of Lake Charlevoix, in the town of East Jordan, Michigan, USA. This foundry was called East Jordan Iron Works and originally produced cast parts for the lumber industry, machinery, ships, agricultural equipment and railroads.

In the 1920s, when the lumbering era came to a close, the company expanded into new markets allowing continued success in changing times and shifted to the production of street castings, water works valves, fire hydrants and various industrial castings.

During World War II the foundry produced castings for the war effort.

In the 1950s, semi-automation was introduced into the foundry. During the 60s, the third generation converted the foundry to an automated high-pressure molding line. By integrating automatic sand processing and mechanized casting handling systems, the company was operating the largest

6

automated molding line in the United States and maximized production capabilities.

Since the mid-1980s, the business has been led by the fourth generation descendants of the Malpass family. They have transformed the Midwest business into an international leader of construction castings.

In the 1990s, new acquisitions throughout the United States allowed the company to expand product lines, sales offices, distribution capabilities and customer service across North America. In 2001, a new foundry was built in Oklahoma, providing additional capacity to service the construction castings market.

The 21st century had barely introduced itself when East Jordan Iron Works began turning its attention to expansion in other parts of the world, including Cavanagh Foundry in Ireland (2000), Norinco in France (2004), McCoy Construction Castings in Canada (2006) and HaveStock in Australia (2010).

In 1999, the fifth generation of the Malpass family began joining the company to continue the strong family commitment to its success. Dedicated to maintaining the company's long-established culture and values, they are significantly involved in strategies and priorities, bringing a renewed energy and enthusiasm to the company.

In 2012, East Jordan Iron Works and its affiliated companies began doing business using the same name and brand, EJ. One global name and brand, supported by a single mission, vision and set of values has unified the company. This action leverages all company resources to improve internal operations, as well as provide superior product offerings and services to its valued customers. EJ has supplied products to infrastructure projects in over 140 countries around the world.

EJ continues to be 100% owned and operated by the Malpass family with corporate headquarters located in East Jordan, Michigan.



## **Product Lines**

## **Street Castings**

- · Manhole Frames and Covers
- · Curb Inlets and Frames
- · Utility Castings
- · Airport and Port Authority Castings
- ·Tree Grates
- Trench Grates
- · Drainage Grates
- · DURALAST® Detectable Warning Plates

## **Fabricated Products**

- Grating
- · Riser Rings
- · INFRA-RISER® Adjustment Risers
- · Aluminum Access Hatches
- · Custom Fabrications

#### **Water Products**

- ·WaterMaster® Fire Hydrants
- · FlowMaster® RW Gate Valves
- · Valve Boxes
- · Meter Boxes

## **Innovative Access Solutions**

- · Captive Hinge Grates/Covers
- · ERGO® and ERGO® XL Access Assemblies
- · Ductile Hinged Hatch Access Assemblies
- · 5624 Heavy Duty Hinged Grates
- · SELFLEVEL® Access Assemblies
- · REVOLUTION® Access Assemblies
- · ERMATIC® Modular Covers
- · Multi-Leaf® Hinged Covers
- · CAMPRESSION® Access Assemblies
- · Composite Access Covers

#### **Innovative Features**

- · LOCKEO® Security Feature
- · Mechanical Strut Lift Assist
- · Cam Lock
- · EON LOCK® Designs
- · EPIC® Pick Bar
- · MPIC® Multi-tool Pick Bar

















# Capabilities

#### Service

- · Employees with localized knowledge throughout the world
- · On-site assistance
- $\cdot \text{Seminars and technical presentations}$
- · Communicate new product innovations
- · Assistance with specification process

#### **Innovative Use of Technology**

- · Electronic invoicing
- · EDI transactions
- · ejco.com—comprehensive product database with advanced search and browsing capabilities
- · Electronic certification of materials provided upon request
- · CAD and PDF drawings available electronically

## **Quality Manufacturing**

- · Product research and development
- · Commitment to reinvestment
- · North America ISO 9001 certified facilities
- · Europe ISO 9001, ISO 14001, OHSAS 18001 certified facilities
- · Australia ISO 9001 certified facilities

## **Foundry Facilities**

- · East Jordan, Michigan
- · Ardmore, Oklahoma
- · Picardie/St. Crepin, France

## **Fabrication Facilities**

- · Birr, Ireland
- · Youngstown, Ohio
- · Cicero, New York
- ·Tooele, Utah
- · Ardennes/Bogny sur Meuse, France
- · Geebung/Queensland, Australia

## **Water Products Manufacturing**

· East Jordan, Michigan

#### Distribution

- · Delivering products quickly and smoothly worldwide
- · Stocking branch locations throughout U.S., Canada, Europe, and Australia
- Distribution centers located in Michigan, Oklahoma, Ireland, France, and Australia



















# Massachusetts Municipal and DOT Castings





## **CLEANOUT/MONUMENT BOXES**

Features Heavy duty

Options Custom badging/lettering Security bolting 7", 8", or 10" frame height





0MA157000006 frame and cover

Frame	Options
-------	---------

Frame Height	Product Number	
9	0MA157000001	

Note: all dimensions are in inches.

## 9" Cover Options

Cover Type	Lettering	<b>Product Number</b>
Solid*	Plain	0MA157000002
Solid*	Sewer	0MA157000003
Solid*	Drain	0MA157000004
Solid*	Cleanout	0MA157000005

<sup>\*</sup> Bolted cover available

## Additional Assembly Options

Frame Height	Cover Size	Flange Size	Product Number
7	8	13 1/4	00296520C03
8	12	18	0DE156400001
8	10 1/4	15 (across flats) 16 (outside)	00156621C02
10	9	13 3/4	0MA157000006

Note: all dimensions are in inches.

## 24" MANHOLE FRAMES, COVERS, AND GRATES


Features

Heavy duty

Options

Solid, flat grate, or ADA grate Custom badging/lettering Gasket seal covers 4", 6", or 8" frame height EPIC® pick bar





0MA124000014 frame and cover

Frame Options	
Frame Height	Product Number
4	0MA124000021
6	0MA124000022
8	0MA124000023

Note: all dimensions are in inches.

24" Cover Options		
Cover Type	Lettering	Product Number
Solid*	Plain	0MA124000024
Solid*	Sewer	0MA124000025
Solid*	Drain	0MA124000026
Solid, gasket seal	Plain	0MA124000027
Solid, gasket seal	Sewer	0MA124000028
Flat grate	Dump No Waste!	0MA124000029
ADA grate	Dump No Waste!	0MA112000001

<sup>\*</sup>Bolted cover available

## **Cover Options**







ADA grate



Gasket cover



Watertite assembly





## 26" MANHOLE FRAMES, COVERS, AND GRATES


Features

Heavy duty

Options

Solid, flat grate, or ADA grate Custom badging/lettering Gasket seal covers 4", 6", or 8" frame height EPIC® pick bar





0MA211000024 frame and cover

0MA211000024 dimensions shown

Frame Options	
Frame	
Height	Product Number
4	0MA226000001
6	0MA226000002
8	0MA211000038

Note: all dimensions are in inches.

26" Cover Options		
Cover Type	Lettering	Product Number
Solid*	Plain	0MA211000039
Solid*	Sewer	0MA211000040
Solid*	Drain	0MA211000041
Solid, gasket seal	Plain	0MA211000042
Solid, gasket seal	Sewer	0MA211000043
ADA grate	Dump No Waste!	0MA211000045
Flate grate	Dump No Waste!	0MA211000044

<sup>\*</sup>Bolted cover available.

## **Cover Options**







Solid plain open pick hole

ADA grate

Flate grate





Gasket cover

Watertite assembly


800 626 4653 12 ejco.com

## 32" MANHOLE FRAMES AND COVERS

Features Heavy duty

Options Solid, flat grate, or ADA grate Custom badging/lettering Gasket seal covers 4", 6", or 8" frame height EPIC® pick bar Security bolting





0MA200000008 frame and cover

0MA200000008 dimensions shown

Frame Options	
Frame Height	Product Number
4	0MA200000022
6	0MA200000023
8	0MA200000024

Note: all dimensions are in inches.

Cover Options		
Cover Type	Lettering	Product Number
Solid*	Plain	0MA200000025
Solid*	Sewer	0MA200000026
Solid*	Drain	0MA200000027
Solid, gasket seal	Plain	0MA200000028
Solid, gasket seal	Sewer	0MA200000029

<sup>\*</sup> Bolted cover available



0MA200000020 32 x 6 watertite assembly plain



0MA200000030 gasket seal CATV




00200656 Pembroke cover



ejco.com

## **WORCESTER 23" FRAMES, COVERS, AND GRATES**





0MA105000010 frame and cover

0MA105000010 dimensions shown

Frame Options	
Frame Height	Product Number
4	0MA105000014
9 standard	0MA105000004
9 bolted	00105613

Note: all dimensions are in inches.

Cover Options		
Cover Type	Lettering	Product Number
Solid	Worcester A Town Since June 14, 1722 A City Since Feby 29, 1848	0MA105000005
Solid, gasket seal	Worcester A Town Since June 14, 1722 A City Since Feby 29, 1848	0MA105000008
Flat grate	Plain	0MA105000009

<sup>\*</sup>Bolted cover available

## **Cover Options**



Worcester logo cover



Watertite assembly



Gasket seal




Flat grate


800 626 4653 14 ejco.com



## BOSTON WATER AND SEWER COMMISSION (BWSC) FRAMES AND COVERS







Frame Options


Frame Height	Product Number
8	0MA211000046

Note: all dimensions are in inches.

Lettering	Product Number			
Boston Sewer	0MA211000047			
Boston Drain	0MA211000048			



00191711 frame and 00191723 cover



Frame Options

Frame Height	Product Number
8 1/8	00191711

Note: all dimensions are in inches.

Cover	Options
00101	Options


Lettering	Product Number
Boston Sewer	00191721
Boston Drain	00191723



800 626 4653 ejco.com

## FROST PROOF MANHOLE FRAME AND COVER





800 626 4653

1123 series frost proof manhole assembly


Frost Proof Manhole Assembly Options

1103t 1100t Walliote As	Treat Froot Mannote Assembly Options						
Α	В	С	E	F			
Cover Diagram	Cover Thickness	Clear Open	Flange Dia.	Frame Height	Series Number		
24	1 1/2	19 7/8	33 7/8	7	1123		
26	1 1/2	22	39	7	1041		
25 3/5	1 1/4	22 1/16	43 1/4	11 1/2	1706		
26	1 1/2	22 1/8	38 3/4	7	1044		
28 3/4	1 3/8	24 1/2	37 1/2	7	1893		
31 3/4	1 3/8	28	40	7	1233		
32	1 1/2	28	40	6 1/2	1323		
38 1/2	1 1/2	34	45	10 1/8	1583		

Note: all dimensions are in inches.

## HAND HOLE/PULL BOX FRAMES AND COVERS







00811812 frame and 00811825 BSWC cover



0MA801000003 frame and 0MA801000012 electric cover



0MA801300001 frame and 0MA801300014 CATV cover

Hand Hole/Pull Box Assembly Options

Hand Hole/Full Box Assembly Options							
Cover Size	Lettering	Cover Thickness	Clear Opening	Frame Height	Flange Dim.	Product Number	
12 x 12	Plain	1	10 3/4 SQ	3 1/2	17 1/4 SQ	0MA801200002 / 00801221	
16 x 18	BWSC	1 3/8	15 7/8 x 13 15/16	6 1/2	25 5/8 x 23 5/8	00811812 / 00811825	
23 3/4 × 23 3/4	Electric	15/16	21 7/8 SQ	3	30 SQ	0MA801000003 / 0MA801000012*	
12 3/4 × 24 3/4	CATV	1 1/2	24 x 12	3	29 3/4 x 17 3/4	0MA801300001 / 0MA801300014	

<sup>\*</sup> Medium duty rated


Note: all dimensions are in inches.



800 626 4653 ejco.com

## V-1600/V-1800 FRAMES AND COVERS





V-1600-4 assembly

Features Heavy duty Reversible frame (BF = V-1600, TF = V-1800)

Options Solid or vented covers Special lettered covers Custom logo covers Bolted assemblies Grates (see V-3600/V-3800) Hinged unit available in select sizes

V-1660/V-1800 Frame and Cover Options


Catalog	A Cover	B Cover	C Clear	D Frame	E Flange	F
Number	Diameter	Thickness	Opening	Opening	Diameter	Height
V-1600-1	19 1/4	1 1/2	18 1/4	19 1/2	24	4
V-1600-2	23 1/2	1 1/2	22	23 3/4	28 1/2	4
V-1600-3	25 3/8	1 1/2	24	25 5/8	32 1/8	4
V-1600-4	31 3/4	1 3/8	30	32 1/8	38	4
V-1600-5	38	2	36	38 1/4	46	6
V-1600-6	50 1/4	2	48	50 1/2	56 1/2	6
V-1800-1	19 1/4	1 1/2	18 1/4	20 1/2	24	4
V-1800-2	23 1/2	1 1/2	22	24 3/4	28 1/2	4
V-1800-3	25 3/8	1 1/2	24	26 5/8	32 1/8	4
V-1800-4	31 15/16	1 3/8	30	33 1/8	38	4
V-1800-5	38	2	36	40	46	6
V-1800-6	50 1/4	2	48	52	56 1/2	6

Note: all dimensions are in inches.



## V-1610/V-1810 FRAMES AND COVERS





V-1610-4 assembly

Features Heavy duty Reversible frame

Options Special lettered covers Logo covers Bolted assembly Grates (see V-3610)

V-1610/V-1810 Frame and Cover Options

v-1010/ v-1010 i laille ai		l .	<b>D</b>		l <b>n</b>	<b>-</b>	l <b>-</b>
Catalog Number	Pipe Size	A Cover Dia.	B Cover Thikness	C Clear Opening	D Frame Opening	E Flange Dia.	F Height
V-1610-1	12	10 1/4	1 1/2	8 1/2	10 1/2	14 1/2	4
V-1610-2	15	13 1/4	1 1/2	11 1/2	14 1/2	17 5/8	4
V-1610-3	18	16 1/4	1 1/2	14 3/8	17 1/2	20 1/2	4
V-1610-4	24	21 7/8	1 1/2	20 1/4	23 5/8	26 5/8	4
V-1610-5	30	27 7/8	1 1/2	26 3/8	29 3/8	32 1/2	4 1/8
V-1610-6	36	33 7/8	1 1/2	32	35 1/2	38 1/2	4 1/8
V-1610-7	42	39 5/8	1 1/2	38 1/4	41 1/2	44 1/2	4
V-1610-8	48	45 3/4	1 1/2	43 3/4	47 3/4	50 1/2	4
V-1810-1	12	10 1/4	1 1/2	8 1/2	10 1/2	14 1/2	4
V-1810-2	15	13 1/4	1 1/2	11 1/2	14 1/2	17 5/8	4
V-1810-3	18	16 1/4	1 1/2	14 1/2	17 1/2	20 1/2	4
V-1810-4	24	21 7/8	1 1/2	20 1/4	23 5/8	26 5/8	4
V-1810-5	30	27 7/8	1 1/2	26 3/8	29 1/8	32 1/2	4
V-1810-6	36	33 7/8	1 1/2	32	35 5/8	38 1/2	4
V-1810-7	42	39 5/8	1 1/2	38 1/4	41 1/2	44 1/2	4
V-1810-8	48	45 3/4	1 1/2	44 1/2	47 3/4	50 1/2	4

Note: all dimensions are in inches.




800 626 4653 ejco.com 19

## **24" X 24" CATCH BASINS**




23 7/8" SQ-



0MA552000028 3 flange frame and square grate

3 flange dimensions shown





23 7/8" SQ

See page 21 for grate and assembly options

0MA554000006 4 flange frame

Frame Options


4 flange dimensions shown

F Frame Height	Flange	W Flange Dimension	Product Number		
Standard	Frame				
4	3 flange	32 x 29 1/8	0MA554000001		
4	4 flange	32 x 32	0MA554000002		
6	3 flange	33 x 29 7/8	0MA554000003		
6	4 flange	33 x 33	0MA554000004		
8	3 flange	33 x 29 11/16	0MA554000005		
8	4 flange	33 x 33	0MA554000006		
Drop Inlet	t				
4	3 flange	32 x 29	0MA552000016		
4	4 flange	32 SQ	0MA552000015		
Heavy Frame					
8	3 flange	34 x 30 5/16	0MA552000081		
8	4 flange	34 SQ	0MA552000082		

Note: all dimensions are in inches.


## **Grates Options**





24" x 24" Grate Options				
Conta Torra	Product			
Grate Type	Number			
Standard grate	0MA552000074			
Square hole grate	0MA552000075			
Cascade grate (left)	0MA552000076			
Cascade grate (right)	0MA552000077			
ADA grate	0MA552000078			





24"	v 2	7/1"	Catch	Racin	Assembly	Ontions

rrame				
Height Flanges		Product Number		
Standard	Grate			
4	3 flange	0MA552000018		
4	4 flange	0MA552000019		
6	3 flange	0MA552000020		
6	4 flange	0MA552000021		
8	3 flange	0MA552000022		
8	4 flange	0MA552000023		
<b>Square H</b>	ole Grate			
4	3 flange	0MA552000024		
4	4 flange	0MA552000025		
6	3 flange	0MA552000026		
6	4 flange	0MA552000027		
8	3 flange	0MA552000028		
8	4 flange	0MA552000029		
ADA Grate				

0MA552000042

0MA552000043

0MA552000044

0MA552000045

0MA552000046

0MA552000047

Note: all	dimensions	aro	in	inches	

3 flange

4 flange

3 flange

4 flange

3 flange

4 flange

24" v	24"	Catch	Rasin	Assembly	Ontions

Frame Height	Flanges	Direction	Product Number
Cascade (	Grate		
4	3 flange	Left	0MA552000030
4	3 flange	Right	0MA552000032
4	4 flange	Left	0MA552000031
4	4 flange	Right	0MA552000033
6	3 flange	Left	0MA554600001
6	3 flange	Right	0MA554600002
6	4 flange	Left	0MA552000035
6	4 flange	Right	0MA552000037
8	3 flange	Left	0MA552000038
8	3 flange	Right	0MA552000040
8	4 flange	Left	0MA552000039
8	4 flange	Right	0MA552000041

Note: all dimensions are in inches.



4

4

6

6

8


8




## **24" X 48" CATCH BASINS**




0MA544400012 frame Note: 4 flange shown. 3 flange available with long side deleted or short flange deleted



4 flange dimensions shown



0MA544000002 frame Note: 4 flange shown. 3 flange available with long side deleted or short flange deleted



4 flange dimensions shown

Frame	Options
Tanno	Options

Traine Opti	UIIS		
		w	
Frame	Flange	Flange Dimension	Product Number
4	3 flange (long flange deleted)	56 3/8 x 29 5/16	0MA544400011
4	3 flange (short flange deleted)	53 3/8 x 32 1/4	0MA544400106
4	4 flange	56 3/8 x 32 1/4	0MA544400012
8*	3 flange (long flange deleted)	58 1/2 x 30 3/16	0MA544000001
8*	3 flange (short flange deleted)	54 15/16 x 33 3/4	0MA544400107
8*	4 flange	58 1/2 x 33 3/4	0MA544000002


\*8" frames feature center support bar Note: all dimensions are in inches.


See page 2 for grate and assembly options



## **Grates Options**











Note: 2 grates required per frame

24" x 48" Grate Options

24" x 48" Cato	h Basin Assembl	y Options
----------------	-----------------	-----------

Frame Height	Flanges	Product Number
Standard	d Grate	
4	3 flange (long flange deleted)	0MA544400001
4	3 flange (short flange deleted)	0MA544400100
4	4 flange	0MA544400001
8	3 flange (long flange deleted)	0MA552000064
8	3 flange (short flange deleted)	0MA552000202
8	4 flange	0MA552000065
Square H	lole Grate	
4	3 flange (long flange deleted)	0MA544400003
4	3 flange (short flange deleted)	0MA544400101
4	4 flange	0MA544400004
8	3 flange (long flange deleted)	0MA552000066
8	3 flange (short flange deleted)	0MA552000203
8	4 flange	0MA552000067
ADA Gra	te	
4	3 flange (long flange deleted)	0MA544400009
4	3 flange (short flange deleted)	0MA544400105
4	4 flange	0MA544400010
8	3 flange (long flange deleted)	0MA552000072
8	3 flange (short flange deleted)	0MA552000206
8	4 flange	0MA552000073

24" x 48" Catch Basin Assembly Options

Frame Height	Flanges	Direction	Product Number
Cascade	Grate		
4	3 flange (short flange deleted)	Left	0MA544400102
4	3 flange (long flange deleted)	Left	0MA544400005
4	3 flange (short flange deleted)	Right	0MA544400103
4	3 flange (long flange deleted)	Right	0MA544400007
4	4 flange	Left	0MA544400006
4	4 flange	Right	0MA544400008
8	3 flange (short flange deleted)	Left	0MA552000204
8	3 flange (long flange deleted)	Left	0MA552000068
8	3 flange (short flange deleted)	Right	0MA552000205
8	3 flange (long flange deleted)	Right	0MA552000070
8	4 flange	Left	0MA552000069
8	4 flange	Right	0MA552000071

23

Note: all dimensions are in inches.


Note: all dimensions are in inches.






## CITY OF BOSTON 28" X 28" FRAMES, COVERS, AND GRATES







0MA728800018 3 flange frame with grate

3 flange frame with BSD cover

4 flange dimensions shown

Frame Options		
F		
Frame Height	Flanges	Product Number
4	3 flange	0MA728800022
4	4 flange	0MA728800023
8	3 flange	0MA728800012
8	4 flange	0MA728800013


28" x 28" Grate and Cover Options

Cover Type	Product Number
Solid, BSD	00728825
Grate	0MA728800014

Note: all dimensions are in inches.



00726725 Charles River catch basin sign



Catch Basin Sig	n Options
Product Number	Lattoring
Number	Lettering
00726722	Don't Dump Drains to Boston Harbor
00726724	Don't Dump Drains to Neponset River
00726728	Don't Dump Drains to Charles River


## **SQUARE HOLE HOOK LOCK GRATE**



24" square hole hook lock grate

Grate Options	
Grate Type	Product Number
Hook lock square	00552064A01
hole grate	

Note: grate fits all frames listed on page 20.



Underside view






## **WORCESTER 28" X 28" FRAMES AND GRATES**



0MA728800018 Worcester 3 flange frame and grate



0MA728800019 Worcester 4 flange frame and grate



4 flange dimensions shown

Frame	Options

Frame Height	Flanges	Product Number
8	3 flange	0MA728800015
8	4 flange	0MA728800016

Note: all dimensions are in inches.


## 28" x 28" Grate Options

Cover Type	Product Number
Grate	0MA728800017

## "D" FRAMES AND GRATES



00726811 / 00726831 frame and grate



00727833 grate

## "D" Frame Options

F Frame Height	C Clear Opening	D Flange Opening	E Flange Size	Product Number
8	24	27 1/8	35 13/16	00726811
8 1/16	23 15/16	27 13/16	35 3/8	00727811

Note: all dimensions are in inches.

## "D" Grate Options

Α	В	
Cover Width	Cover Thk.	Product Number
26	2	00726831
26 1/2	2	00727831
26 1/2	2	00727833*

<sup>\*</sup> Features lock lug

Note: all dimensions are in inches.






Hook lug

## V-5600 REVERSIBLE FRAMES AND GRATES





V-5622-80 ADA compliant‡



Heavy duty Reversible unit Special lettered grates

Options ADA compliant grates Extra heavy duty grates Vane grates

26



V-5660-80 ADA compliant‡ with "DUMP NO WASTE!"

See page 27 for V-5600 series frame and grate options




V-5600 Revers	V-5600 Reversible Frame and Grate Options								
Series Number	Grate Number	Cover Number	A Grate Size	B Grate Thk.	C Clear Opening	D Frame Opening	E Flange Dim.	F Frame Ht.	Open Area Sq. In.
Square	'					,			
V-5613	V-5713	V-6713	13 3/8	1 9/16	11 5/8	13 5/8	19 1/8	4	55
V-5620	V-5720	V-6720	19 3/4	1 1/2	18	20	25 1/2	4	175
V-5622 V-5622-1	V-5622 V-5622** V-5622-2† V-5622-80‡ V-5622-5§	V-6622	23 3/4 23 3/4 23 3/4 23 3/4 23 3/4	1 1/2 1 1/2 1 1/2 1 1/2 1 1/2	22 22 22 22 22 22 22	24 24 24 24 24 24 26 1/4	29 1/4 29 1/4 29 1/4 29 1/4 29 1/4 32	4 4 4 4 4 5	266 266 200 156 269
V-5624	V-5624 V-5624-80 V-5624	V-6624	25 3/4 25 3/4 25 3/4	1 1/2 1 1/2 1 1/2	24 24 24	26 26 26	31 3/8 31 3/8 31 3/8	4 4 4	295 194 295
V-5626-1 V5626-2	V-5626 V-5726** V-5726-80‡	V-6726	25 3/4 25 3/4 25 3/4 25 3/4	2 2 2 2	24 24 24 24	26 26 26 26	32 32 32 32 32	5 5 5 6	321 321 194
V-5630	V-5630 V-5630** V5630-80‡	V-6630	31 3/4 31 3/4 31 7/8	1 1/2 1 1/2 1 1/2	30 1/8 30 1/8 30 1/8	32 32 32	37 1/2 37 1/2 37 1/2	4 4 4	474 472 283
V-5632	V-5732 V-5732** V-5732‡	V-6732	31 7/8 31 7/8 31 7/8	2 2 2	30 30 30	32 1/8 32 1/8 32 1/8	38 1/8 38 1/8 38 1/8	5 5 5	490 490 283
V-5636	V-5636 V-5636** V-5636‡	V-6636	37 1/2 37 1/2 37 1/2	1 1/2 1 1/2 1 1/2	36 36 36	37 3/4 37 3/4 37 3/4	43 1/4 43 1/4 43 1/1	4 4 4	651 651 305
V-5642 (2P)	V-5742 (2P) V-5742 (2P)**	V-6642 (2P)	43 7/8 43 7/8	2 2	42 42	44 1/4 44 1/4	49 3/4 49 3/4	5 5	868 868
V-5648 (2P)	V-5648 (2P)	V-6648 (2P)	50 5/8	1 5/8	48 5/8	51	58 3/4	4 3/8	820
Rectangula	r								
V-5660	V-5660 V-5660‡	V-6660	23 3/4 x 35 3/4 23 3/4 x 35 3/4	1 1/2 1 1/2	22 x 34 22 x 34	34 x 36 34 x 36	29 1/2 x 41 1/2 29 1/2 x 41 1/2	4 4	390 260
V-5662	V-5662	No cover	25 5/8 x 31 3/4	1 1/2	24 x 30	26 x 32	31 3/8 x 37 3/8	4	390
V-5665	V-5665	V-6665	25 3/4 × 37 3/4	1 1/2	24 1/8 x 36 1/8	26 x 38	31 1/2 x 43 1/2	4	463
V5667	V-5667 (2P)	V-6667 (2P)	25 3/4 × 49 3/4	1 1/2	24 x 48	26 x 50	31 1/2 x 55 1/2	4	598
V-5668	V-5668	V-6668	31 3/4 x 37 3/4	2	30 x 36	32 1/8 x 38	38 1/4 x 44 1/4	5	562
V-5669	V-5669 (2P)	No cover	31 3/4 × 49 3/4	1 1/2	30 1/8 x 48 1/8	32 x 50	37 1/2 x 55 1/2	4	724
V-5670	V-5670 (2P)	V-6670 (2P)	37 3/4 × 49 3/4	1 1/2	36 1/8 x 48 1/8	38 x 50	43 1/2 x 55 1/2	4	708

Note: all dimensions are in inches.



800 626 4653 ejco.com

## V-5700 FRAME AND GRATE SERIES



Heavy duty ADA compliant grates available

See page 29 for V-5700 series frame and grate options



800 626 4653 28 ejco.com

Series		Cover	Α	В	С	E	F	Open Area	
Number	Grate Number	Number	Grate Size	Grate Thk.	Clear Opening	Frame Size	Frame Ht.	Sq. In	
Square									
V-5708	V-5708	No cover	9 3/8	1	7 3/4	11	1 1/2	33	
V-5712	V-5712 V-5712‡	V-6712	12 12	7/8 7/8	10 1/2 10 1/2	13 7/8 13 7/8	1 1/4 1 1/4	66 43.33	
V-5713	V-5713	V-6713	13 3/8	1 9/16	11 5/8	15 3/8	2 1/8	55	
V-5714	V-5714	V-6714	14 1/2	1	13 1/4	16	1 9/16	76	
No frame	V-5715‡	No cover	14 3/4	1 3/16				58	
V-5716	V-5716	No cover	15 7/8	1 1/8	14 1/4	17 1/2	1 3/4	90	
V-5718	V-5718	V-6718	18	1 1/2	16 3/8	19 1/2	2	152	
V-5720	V-5720 V-5720‡	V-6720	19 3/4	1 1/2	18 1/4	21 1/4	2	175	
	V-5720‡		19 3/4	1 1/2	18 1/4	21 1/4	2	105	
V-5724	V-5724-1 V-5724-2 V-5724-4** V-5724-80‡ V-4896 (beehive)	V-6724	24 24 24 24 24	1 7/8 1 7/8 1 7/8 1 7/8 1 7/8	22 1/4 22 1/4 22 1/4 22 1/4 22 1/4	25 7/8 25 7/8 25 7/8 25 7/8 25 7/8	2 5/8 2 5/8 2 5/8 2 5/8 2 5/8	268 212 336 164 446	
V-5724-1 (w/flange)			24	1 7/8	22 1/8	30	2 5/8		
V-5726-1	V-5726 V-5726** V-5726-80‡	V-6726	25 3/4 25 3/4 25 3/4	2 2 2	22 1/4 22 1/4 22 1/4	27 7/8 27 7/8 27 7/8	2 3/4 2 3/4 2 3/4	321 321 194	
V-5728	V-5728	No cover	28	2	25 7/8	30 1/8	2 3/4	370	
V-5732	V-5732 V-5732-80‡	V-6732	31 7/8 31 7/8	2 2	30 1/4 30 1/4	33 3/4 33 3/4	2 3/4 2 3/4	490 283	
V-5736	V-5736 V-5736** V-5736-80‡	V-6736	38 1/4 38 1/4 38 1/4	2 2 2	36 1/2 36 1/2 36 1/2	40 3/8 40 3/8 40 3/8	2 3/4 2 3/4 2 3/4	652 652 356	
V-5742	V-5742 (2P) V-5742 (2P)**	V-6642 (2P)	43 7/8	2	42 1/8 42 1/8	45 7/8 45 7/8	2 3/4 2 3/4	868	
V-5748 (non-traffic) (steel angle frame)	V-5648 (2P)	V-6648	50 9/16	1 1/2	48	51 1/2		820	
Rectangular									
V-5751	V-5751	V-6751	13 7/8 x 25 7/8	1	12 × 24	15 5/16 x 27 3/8	1 1/2	158	
V-5752	V-5752	No cover	18 x 23 3/4	1 3/8	16 1/4 x 22	19 3/8 x 25 1/8	2	188	
V-5754	V-5754-1 (1" slots)	No cover	17 7/8 x 35 7/8	2	15 5/8 x 33 5/8	20 1/4 x 38 1/4	2 3/4	245	
V-5760	V-5760 7510 M3† 7510 M4 7510 M1 (DG)	No cover	24 x 36 23 7/8 x 35 3/4 23 7/8 x 35 3/4 23 5/8 x 35 5/8	2 2 2 2	21 1/2 x 33 1/2 21 1/2 x 33 1/2 21 1/2 x 33 1/2 21 1/2 x 33 1/2	28 × 40 1/4 28 × 40 1/4 28 × 40 1/4 28 × 40 1/4	2 3/4 2 3/4 2 3/4 2 3/4	413 446 324 410	
V-5763	V-5763	No cover	25 7/8 x 31 7/8	1 3/4	24 5/8 × 30 3/8	27 7/8 x 33 7/8	2 3/8	402	
V-5766	V-5666	V-6666	25 7/8 x 37 7/8	2	24 3/8 × 36 3/8	28 x 40	3	397	
V-5770	V-5670 (2P)	V-6670 (2P)	37 3/4 × 49 3/4	1 1/2	36 x 48	39 3/4 x 51 3/4	2 1/4	708	

29



800 626 4653 ejco.com

## **BEEHIVE FRAMES AND GRATES**



0MA801300020 22" x 6" frame and beehive grate


Beehive Assembly Options							
Frame Height	Flange Size	Grate Size	Grate Height	Product Number			
Beehive Grate							
6	28 1/4	22	7	0MA801300020			
7	35 7/16	26	6	0MN120500025			

Note: all dimensions are in inches.


## **TRAPS AND HOODS**



0MAL20200001 catch basin hood












0MAL20200005 catch basin hood








## TRAPS AND HOODS (CONTINUED)



0MALB2100008 catch basin trap





00595469 pipe catch basin trap

5954 Series	Assembly	Options
-------------	----------	---------

Pipe Size	Α	В	С	Product Number
6	16	12	6 1/2	00595466
8	18	12	6 1/2	00595467
10	20	12	6 1/2	00595468
12	22	16 3/8	6 1/2	00595470
12 (24" radius)	22	16 1/2	6 1/2	00595469
15	25	20 1/2	6 1/2	00595475

Note: all dimensions are in inches.



800 626 4653 31 ejco.com

## **MASSDOT FRAMES AND COVERS**

## Standard 26" Manhole



MassDOT Type B manhole frame and cover 0MA211000101




MassDOT Type A manhole frame and cover 0MA211000100


26" DIA




MassDOT bolted manhole frame and cover assembly 0MA211000054

26" DIA







Frame Options
---------------

32

Frame Type	Product Number
Туре В	0MA211000002
Type A	0MA211000001

Note: all dimensions are in inches.

Cover	Options

Cover Type	Lettering	Product Number
Solid*	Plain	0MA211000003
Solid	Sewer	0MA211000004
Solid	Drain	0MA211000005

1 1/8"

<sup>\*</sup> Bolted cover available

## **MASSDOT FRAMES AND GRATES**


## **Cascade Grates**



MassDOT 8" 3 flange frame and left flow cascade grate 0MA552000103



MassDOT 8" 4 flange frame and right flow cascade grate 0MA552000106



4 flange dimensions shown

F	ra	me	0	pti	ons

Flange	Product Number
3 flange	0MA552000010
4 flange	0MA552000011

Grate Options

Grate Type	<b>Product Number</b>
Cascade (left)	0MA552000076
Cascade (right)	0MA552000077


## **Hook Lock Cascade Grates**



MassDOT B-1 hook lock 3 flange frame and left flow cascade grate 0MA552000004



MassDOT B-2 hook lock 4 flange frame and left flow



4 flange dimensions shown

Frame Options

Flange	Product Number
3 flange	0MA552000003
4 flange	0MA552000002

Note: all dimensions are in inches.



Hook lock 0MA555000005 cascade (left)





Hook lock cascade (left) 0MA555000004


## **MASSDOT FRAMES AND GRATES**

## **Bar Grate**



MassDOT 3 flange frame and A-1 bar grate 0MA552000100

MassDOT 4 flange frame and A-1 bar grate 0MA552000101



4 flange dimensions shown

Frame	Options
-------	---------

Flange	<b>Product Number</b>
3 flange	0MA552000010
4 flange	0MA552000011

Note: all dimensions are in inches.

## Grate Options

Grate Type	Product Number			
Bar grate	0MA552000014			


## **Hook Lock Bar Grate**



MassDOT 3 flange frame and A-4 bar grate 0MA552000008



MassDOT 4 flange frame and A-4 bar grate 0MA552000009



4 flange dimensions shown

F	0-4:
Frame	Options

Flange	Product Number			
3 flange	0MA552000003			
4 flange	0MA552000002			

Note: all dimensions are in inches.

Grate Options


Grate Type	Product Number			
Hook lock bar grate	0MA552000001			


800 626 4653

## **MASSDOT FRAMES AND GRATES**

## **Drop Inlet Bar Grate**







Available in 2, 3 or 4 flange design



MassDOT 3 flange frame and A-1 bar grate 0MA552000115

Frame	Options

Flange	w	Product Number
2 flange	26	0MA552500001
3 flange	29	0MA552500016
4 flange	32	0MA552500015

Note: all dimensions are in inches.



MassDOT 4 flange frame and A-1 bar grate 0MA552000117

Grate Options

Grate Type	Product Number			
Bar grate	0MA552000014			



## **MASSDOT FRAMES AND COVERS**

## **Electrical**



MassDOT  $12 \times 12 \times 3-1/2$  pull box frame and cover



 $24 \times 24 \times 3$  reversible frame and DOT logo cover



MassDOT  $8 \times 23 \times 2$ -1/2 pull box frame and cover



 $13 \times 25 \times 3$  pull box frame and cover



00211056A01 MassDOT 6" frame and 27 1/2" cover



00124837A01 MassDOT 6" manhole assembly



00227045A01 MassDOT 6" manhole assembly with transitional manhole frame with 42" square base flange

MassDOT Assembly Options							
Cover Size	Cover Thickness	Clear Opening	Flange Size	Flange	Frame Height	Load Rating	Product Number
Rectangular / Square							
12 x 12	1	10 3/4	17 1/4	4 flange	3 1/2	Heavy Duty	0MA801200001
23 3/4 × 23 3/4	15/16	21 7/8	30	4 flange	3	Medium Duty	0MA805300001
22 7/8 x 7 15/16	1	21 1/2 x 6 1/2	28 1/2 x 13 3/4	4 flange	2 1/2	Heavy Duty	0MA801100003
24 3/4 × 12 3/4	1-1/2	24 x 12	29 3/4 x 17 3/4	4 flange	3	Heavy Duty	0MA801300003
Round							
26 DIA	1 1/8	24 DIA	34 DIA	N/A	8 1/8	Heavy Duty	00211056A01
23 3/4 DIA	1 1/4	22 DIA	34 DIA	N/A	6	Heavy Duty	00124837A01
27 1/2 DIA	1	26 DIA	42 SQ	N/A	6	Heavy Duty	00227045A01

Note: all dimensions are in inches.

# Rhode Island Municipal and DOT Castings






ejco.com 800 626 4653

# **CRANSTON**







00200677A01 Cranston Sewer frame and cover

002006002W01 Cranston watertite assembly

Frame Option	ns
Frame	
Height	Product Number

00200611

Note: all dimensions are in inches.

Cover Options		
Cover Type	Lettering	Product Number
Solid*	Cranston Sewer	00200677
	[current year]	

<sup>\*</sup> Watertite bolted assembly available



#### **PROVIDENCE**



00240834B01 Providence frame and 4 bolt cover assembly

22 1/8" DIA 34 1/16" DIA


23 7/8" DIA

Frame Options	ı
Frame Height	Product Nun

Frame Height	Product Number
8	00242019

Note: all dimensions are in inches.





001040081A02 Providence frame and cam lock cover assembly

	<b>◄</b> 25 7/8" DIA	
į.		
N		
	\ \	4"
	24" DIA	1
-	35 1/8"	

Frame Options

Frame Height	Product Number
4	00225311

Note: all dimensions are in inches.

C	0-4:
L.over	Options

Cover Type	Lettering	Product Number
Solid, gasketed with cam locks	City of Providence	001040081A01



00801144B01 Providence chute frame and 2 bolt cover assembly

22 7/8" 1"	7 15/16"
2 1/2"	6 1/2"

Frame Options

Frame	
Height	<b>Product Number</b>
2 1/2	00801111

Note: all dimensions are in inches.







800 626 4653 ejco.com


# **PROVIDENCE (CONTINUED)**



005520001C01 3 flange frame and cascade grate



005520001C02 4 flange frame and cascade grate






005520002C01 3 flange frame and square hole grate



005520002C02 4 flange frame and square hole grate



Frame Options


Flange	Product Number
3 flange	00554813
4 flange	00554811

Note: all dimensions are in inches.

#### Grate Options

Grate Type	<b>Product Number</b>
Square hole	005520002
Cascade	005520001





45660040 4" tall reversible frame and grate

Frame	Options

40

Frame Height	Product Number
4	45660010

Note: all dimensions are in inches.


Grate	Option

Product Number
45660033



#### **WARWICK**





00211147C05 Warwick frame and cover

Frame	Options
-------	---------


Frame	Product
Height	Number
6	00226611

Note: all dimensions are in inches.

26" Cover Options

		Product
Cover Type	Lettering	Number
Solid	City of Warwick	00211147





00200687A01 Warwick frame and sewer cover

Frame Options

Frame	
Height	Product Number
6	00200611

Note: all dimensions are in inches.

32" Cover Options

_		Product
Cover Type	Lettering	Number
Solid, vented	seWer	00200687



800 626 4653 ejco.com

#### WOONSOCKET



00125851A01 1256Z 1258C Woonsocket sewer undipped 6" assembly

1 1/4" 6" 26 3/4" DIA 34 1/8" DIA -



00125850 Woonsocket drain cover

Frame Opti	ons
------------	-----

Frame	
Height	Product Number
6	00125611

Note: all dimensions are in inches.


Cover	Options

Cover Type	Lettering	Product Number
Solid	Woonsocket Drain	00125850
Solid	Woonsocket Sewer	00125851



#### **RIDOT FRAMES AND GRATES**





0RI547000003 RIDOT 6.3.3 5 bar cascade frame and grate

RIDOT Frame

Clear	Flange	Flange	Frame	RIDOT	Product
Opening	Size		Height	Standard	Number
22 x 24 1/2	29 1/2 x 30 1/2	4 flange	6 1/4	6.3.3	0RI547000001


Note: all dimensions are in inches.

RIDOT Grate

Grate Type	Cover Size	Grate Thickness	RIDOT Standard	Product Number
5 bar cascade	23 1/2 x 19	5	6.3.3	0RI547000002

Note: all dimensions are in inches.





0RILK2840003 RIDOT 6.4.1 26 x 4 frame and grate

Frame Option

	RIDOT	Product Number
4	6.4.1	00120513

Grate RII	OT	Product	
Grate Option			

Grate	RIDOT	Product
Dia.	Standard	Number
25 3/8	6.4.1	00120533


Note: all dimensions are in inches.



800 626 4653 ejco.com

# **RIDOT FRAMES AND COVERS**





0RI225000009 RIDOT 6.2.1 26" x 9" frame & "RIDOT" cover

0RI225000009 dimensions shown

Frame Options

Frame Height	Frame Type	RIDOT Standard	Product Number
4	Square	6.1.0 and 6.1.1	0RI225000001
6	Round	6.2.0	0RI223000001
9	Round	6.2.1	0RI225000003

Note: all dimensions are in inches.

26"	Cover	Options
20	Cover	Options

Lettering	RIDOT Standard	Product Number
RIDOT	6.1.0	0RI225000011
RIDOT	6.1.1	0RI225000006
RIDOT	6.2.0	0RI223000002
RIDOT	6.2.1	0RI225000010






800 626 4653

ORI225000001 6.1.0/6.1.1 26" x 6" square flange frame ORI223000001 6.2.0 26" x 6" frame









0RI290000004 RIDOT 18.2.0 16 x 3 1/2 frame & electric cover

0RI290000004 dimensions shown

0RI225615000 18.2.2 26 x 9 frame and electric cover

Frame	Ontione*

Frame Height	Cover Dia.	RIDOT Standard	Product Number
3 1/2	16	18.2.0	0RI290400001
6	20	18.2.1	0RI106100008
9	26	18.2.2	0RI225615002

<sup>\*</sup> Drilled and tapped for electrical grounding Note: all dimensions are in inches.

#### Cover Options\*

Cover Dia.	Cover Type	Lettering	RIDOT Standard	Product Number
16	Solid	Electric	18.2.0	0RI290400002
16	Solid	Signal	18.2.0	0RI290400003
20	Solid	Electric	18.2.1	0RI106100009
20	Solid	Signal	18.2.1	0RI106100003
26	Solid	Electric	18.2.2	0RI225615003
26	Solid	Signal	18.2.2	0RI225615004

<sup>\*</sup> Drilled and tapped for electrical grounding Note: all dimensions are in inches.



0RI290400003 RIDOT 18.2.0 16" signal cover drilled and tapped for electrical grounding




0RI225615004 RIDOT 18.2.2 26" signal cover drilled and tapped for electrical grounding




#### **RIDOT FRAMES AND GRATES**

#### **Frames**



0RI552000003 RIDOT 24" x 24" x 8" 4 flange frame 6.3.0 / 6.3.1 / 6.3.2 / 6.3.4



0RI544000004 RIDOT 4 flange double frame 3.3.4/3.3.5


Rhode Island DOT Frame					
Opening Type	W Flange Dimension	Flange	F Frame Height	RIDOT Standard	Product Number
Single	34 x 30 5/16	3 flange	8	6.3.0, 6.3.1, 6.3.2, 6.3.4	0RI552000001
Single	34 x 34	4 flange	8	6.3.0, 6.3.1, 6.3.2, 6.3.4	0RI552000003
Double	58 1/2 x 30 3/16	3 flange	8	3.3.4, 3.3.5	0RI544000001
Double	58 1/2 x 33 3/4	4 flange	8	3.3.4, 3.3.5	0RI544000004

800 626 4653

Note: all dimensions are in inches.

#### **Grates**







0RI552000006 RIDOT 24" x 24" slotted grate 6.3.1



0RI552000010 RIDOT 24" x 24" bike safe grate 6.3.2



0RI552000014 RIDOT 24" x 24" cascade left grate



0RI552000015 RIDOT 24" x 24" cascade right grate


24" x 24" Rhode Island DOT Grate

Cover Type	Cover Thk.	RIDOT Standard	Product Number
Square hole	2	6.3.0	0RI552000002
Slotted bar	2	6.3.1	0RI552000006
Bike safe	2	6.3.2	0RI552000010
Cascade grate (left)	2	6.3.4	0RI552000014
Cascade grate (right)	2	6.3.4	0RI552000015

Note: all dimensions are in inches.



# Notes



# Connecticut Municipal and DOT Castings






#### 24" MANHOLE FRAMES AND COVERS

# **Eighth District Sewer, Greater New Haven Water Pollution Control Authority,** Hamden, Manchester, Milford, Southington, Stafford, and Wallingford

Features Heavy duty

Options Solid, flat grate, or ADA grate Custom badging/lettering Gasket seal covers 4", 6", or 8" frame height EPIC® pick bar





8" frame and cover

Frame (	Options
---------	---------

Frame	
Height	Product Number
4	00124411
6	00124611
8	00124811

Note: all dimensions are in inches.

#### 24" Cover Options

Municipality	Cover Type	Lettering	Product Number
Eighth District Sewer	Solid	Sewer	00133856
GNHWPCA	Solid	GNHWPCA logo	00124677
GNHWPCA	Solid, watertite assembly	GNHWPCA logo	0CT124800004
Hamden	Solid	Hamden Storm	00124879
Manchester	Solid	Town of Manchester Drain	00133871
Manchester	Solid	Town of Manchester Sewer	00133872
Milford	Solid	Milford Sewer	00124865
Southington	Solid	Sewer	00124825
Southington	Solid	Storm	00124827
Stafford	Solid	Stafford Sewer	00124869
Wallingford	Solid	Wallingford Storm	00124844

#### **Cover Options**



00133856 Eighth District sewer cover



00133871 Town of Manchester drain cover




00124677 GNHWPCA logo cover

#### **BRIDGEPORT**



0CT211100001 8" frame and solid cover



0CT211100001 frame and cover dimensions shown

Frame	
Height	Product Number
4	00226411
6	00226611
8	00211111

Note: all dimensions are in inches.


26"	Carror
20	Cover

Cover Type	Lettering	Product Number
Solid	WPCA Bridgeport Sewer	00211157

#### **BRISTOL**



0CT224000001 frame and cover



0CT224000001 frame and cover dimensions shown

22 1/4" DIA-- 36 1/2" DIA-

Frame Options

Frame Height	Product Number
4	00241015S01
6	00124615S01
8	00124815S01
10	00224011

Note: all dimensions are in inches.




Cover Type	<b>Product Number</b>
Solid	00224021



#### **DANBURY**





00126823 / 00126811 frame and cover

Frame	Options
-------	---------


Frame Height	Product Number	
8	00126811	

Note: all dimensions are in inches.

Cover Type	Lettering	Product Number
Solid	City of Danbury Sanitary Sewer	00126823
Solid	City of Danbury Storm Sewer	00126829

#### **EAST LYME**





00132213 / 00132257 frame and cover

Frame Options

Frame Height	Product Number
6.5	00132213

Note: all dimensions are in inches.

32"	Cover
-	00.0.

Cover Type	Lettering	<b>Product Number</b>
Solid	Plain	00132221
Solid	Sewer	00132257


#### **HARTFORD MDC**





00220523C02 frame and sewer cover





00124819 frame

Frame Options
---------------

Frame Height	Flange Diameter	Product Number
8	48	00220513
8	34	00124819

Note: all dimensions are in inches.

24" Cove	

Cover Type	Additional Cover Description	Lettering	Product Number
Solid		Sewer	00220521
Solid	Vented 1 hole	Sewer	00220523
Solid	Vented 1 hole, Gasket	Sewer	00220546
Solid*	Gasket	Sewer	00220548
Solid		Water	00220525
Solid	Vented 1 hole	Water	00220549
Solid	Vented 1 hole	Storm Drain	00220527
Solid		Storm Drain	00220528
Grate		Dump no pollutants outfall to streams	00244031

 $<sup>\</sup>hbox{*Watertite bolted assembly available, product number } \hbox{00220548W03}$ 




00244031 grate



800 626 4653 ejco.com

#### **MERIDEN**





00124878A02 wide base frame and Meriden sewer cover.





00124811 top hat frame

Frame Options
---------------

Frame Type	Frame Height	Product Number
Wide Base*	8	00220515
Top Hat*	8	00124811

<sup>\*</sup> Bolted frame available Note: all dimensions are in inches.

24" Cover

Cover Type	Lettering	Standard Number
Solid*	Meriden Sewer	00124878
Solid	Meriden Storm	00124875

<sup>\*</sup> Bolted cover available.

Additional Top Hat Frame Options

Frame Height	Product Number
4	00124411
6	00124611


Note: all dimensions are in inches.



#### **MIDDLETOWN**



00220515 / 00124862 8" standard frame and solid cover



00220515 / 00124862 8" standard frame and solid cover dimensions shown

Frame Options		
Frame Height	Standard Number	Watertite Number
4	00124411	00124413
6	00124611	00124613
8	00220515	00220517


Note: all dimensions are in inches.

24" Cover			
Cover Type	Lettering	Product Number	
Solid	Middletown	00124862	
Solid, watertite	Middletown	00124863	
Solid, vent holes	Middletown	00124862D01	

#### **NEW BRITAIN**



00224020A01 frame and cover



00224020A01 dimensions shown

24" Cover

Frame Options		
Frame Height	Product Number	
4	00241015S01	
6	00124615S01	
8	00124815S01	
10	00224011	

Note: all dimensions are in inches.


	<u>                                     </u>
22 1/4" DIA	10 1/4"

**Cover Type** Lettering **Product Number** Solid, vent holes 00224020 Plain Solid, vent holes SW 00224022



#### **NEW HAVEN**





9" frame and New Haven cover

Frame Options

Frame Height	Product Number
9	00224211


Note: all dimensions are in inches.

24" Cover

Cover Type	Lettering	Product Number
Solid, vented	New Haven	00224221
Solid, vented	New Haven Storm	00224223







00774017 / 00774031 3 flange Type A frame and grate 00774017 / 00774031 3 flange Type A frame and grate dimensions shown

Frame Options

Frame Height	Flanges	Product Number
5	3	00774017
5	4	00774015

16" x 33" Grate

Grate Style	Standard Product Number	Bolted Product Number
Туре А	00774031	00774033
Type B	00774041	00774043

Note: all dimensions are in inches.




00774041 Type B grate

56



#### **NORTH HAVEN**





00126811 / 00126822 frame and cover

Frame	
Frame	Product
Height	Number
8	00126811


Note: all dimensions are in inches.

26" Cover		
Cover Type	Lettering	Product Number
Solid	Sewer	00126822
Solid	Drain	00126824


#### **TRUMBULL**



00126811 / 00126822 frame and cover



00126811 / 00126822 frame and cover dimensions



		26 1/4" DIA	-	1 7/8"
k				10"
	-	- 24" DIA - 35" DIA		
-		– 43" DIA		_

00226011 frame dimensions

Frame Options		
Frame Height	Product Number	
8	00126811	
10	00226011	

Note: all dimensions are in inches.

26" Cover		
Cover Type	Lettering	Product Number
Solid	Sewer	00126822
Solid	Drain	00126824
Solid, gasket seal	Sewer	00126827

57




00226011 frame



#### **WATERBURY**



City of Waterbury logo sewer



00124725 / 00124725 dimensions shown

Frame	Options
-------	---------

Frame	
Height	Product Number
4	00241015
6	00124615
8	00124815


Note: all dimensions are in inches.

24"	COVO

Cover Type	Lettering	Product Number
Solid	Waterbury Sanitary Sewer	00124725
Solid	City of Waterbury Logo Storm Drain	00124670
Solid	City of Waterbury Logo Sewer	00124671



00759107 curb inlet assembly



Frame Option

58


Frame	
Height	Product Number
4	00759113

Note: all dimensions are in inches.

Grate Option		Hood Option	
Lettering	Product Number	Lettering	Product Number
Dump No	00759039	Dump No	00759062
Waste Drains to		Waste Drains to	
Waterways		Waterways	

# **CONNECTICUT DOT**





0CT121000006 CDOT 8" frame and cover

0CT121000006 dimensions shown


Frame	
Frame	
Height	Product Number
4	00121411
8	0CT121000003

Note: all dimensions are in inches.

25" Cover		
Cover		
Туре	Lettering	Product Number
Solid	CDOT	0CT121000005



# Notes





# New Hampshire Municipal Castings






ejco.com 800 626 4653

# **CATCH BASINS**









0NH532000007 NH DOT Type B 4" 4 flange frame



0NH532000003 NH DOT Type B 8" 4 flange frame







0NH547000001 Type E frame

Frame	Options

·	F		w	
Frame Type	Frame Height	Flange	Flange Dimensions	Product Number
Type A & F	8	3 flange	34 x 30 5/16	0NH552000001
Type A & F	8	4 flange	34 x 34	0NH552000003
Type B	4	3 flange	28 3/16 x 29	0NH532000005
Type B	4	4 flange	31 3/16 x 29	0NH532000007
Type B	8	3 flange	28 3/16 x 29	0NH532000001
Type B	8	4 flange	31 3/16 x 29	0NH532000003
Type E	6 1/4	4 flange	30 1/2 x 29 1/2	0NH547000001

Note: all dimensions are in inches.

#### **Grates**



0NH552000002 NH DOT Type A slotted grate



0NH532000008 NH DOT Type B grate



0NH547000002 NH DOT Type E 5-bar cascade grate



0NH552000012 NH DOT Type F cascade grate left



0NH552000010 NH DOT Type F cascade grate right



0NH552000016 square hole grate

New Hampshire Grate Options

New Hamperine drate options			
Grate Type	Grate Size	Product Number	
Type A slotted	23 7/8 x 23 7/8	0NH552000002	
Туре В	23 1/4 x 21	0NH532000008	
Type E 5-bar cascade	23 1/2 x 19 3/8	0NH547000002	
Type F cascade (left)	23 7/8 x 23 7/8	0NH552000012	
Type F cascade (right)	23 7/8 x 23 7/8	0NH552000010	
Square hole	23 7/8 x 23 7/8	0NH552000016	


Note: all dimensions are in inches.



# **MANHOLE FRAME AND COVER**



0NH200600003 NH 32" x 6" standard manhole frame and cover plain



0NH200600003 dimensions shown

Frame Options		
Frame		
Height	Product Number	
4	0MA200000022	
6	0NH200000001	

Note: all dimensions are in inches.

Cover Options			
Lettering	Product Number		
Plain	0NH200000002		
Sewer	0NH200600001		
Drain	0NH200600002		










# **VERMONT STANDARD FRAME AND COVER**





0VT124000003 Vermont standard frame and cover

Frame	
Frame	
Height	Product Number
•	

Note: all dimensions are in inches.

24" Cover		
Cover		Product
Type	Lettering	Number
rype	Lettering	Number




# **DROP INLET**





0VT554600002 4 flange drop inlet frame

0VT554600001 3 flange drop inlet frame






Frame Options			
Frame		W	
Height	Flange	Flange Dimensions	<b>Product Number</b>
6	3	29 7/8 x 33	0VT554600001
6	4	33 x 33	0VT554600002

Note: all dimensions are in inches.







0VT552000015 Type D square hole grate

Grate Options	
Grate Type	Product Number
Type A	
Slotted bar	0VT552000002
Type D	
Square hole	0VT552000015
Type E	
Cascade (left)	0VT552000007
Cascade (right)	0VT552000008



0VT552000007 Type E cascade (left)



0VT552000008 Type E cascade (right)




# **TYPE A, D AND E FRAMES**






0VT552000003 3 flange frame

0VT552000001 4 flange frame





Frame Options			
Frame Height	Flange	W Flange Dimension	Product Number
Type A, D and E			
8	3 flange	30 5/16 x 34	0VT552000003
8	4 flange	34 x 34	0VT552000001

Note: all dimensions are in inches.

#### **DOUBLE TYPE A FRAMES**





Frame Options			
Frame Height	Flange	W Flange Dimension	Product Number
Double Type A			
8	3 flange	30 3/16 x 58 1/2	0VT544000002
8	4 flange	33 3/4 x 58 1/2	0VT544000001

Note: all dimensions are in inches.

0VT544000002 Double Type A 3 flange frame







0VT544000001 Double Type A 4 flange frame


# **TYPE A, D AND E GRATES**



0VT552000002 Type A slotted bar grate



0VT552000015 Type D square hole grate





0VT552000007 Type E cascade (left)




0VT552000008 Type E cascade (right)



# **TYPE** B







Frame Options			
Frame			
Height	Flange	Product Number	
6 1/4	4 flange	0VT547000001	

Note: all dimensions are in inches.

Grate Type	Product Number
5 bar cascade	0VT547000002



# Maine Municipal and DOT Castings







ejco.com 800 626 4653

#### **CITY OF PORTLAND**







0ME552000018 frame and grate

Frame Height	Product Number
5	0ME552000019


Note: all dimensions are in inches.


24" Grate

Grate Type	Lettering	Product Number
Flat Grate	Dump No Pollutants Outfall to Streams	0ME552000020



00836023A01 frame and cover





46713021A01 frame and cover

Note: frame is reversible

Frame Options

Frame Height	Product Number
4	46713021
10	00836011

Note: all dimensions are in inches.

Portland	Survey	Monument	Cove
rortianu	Survey	Monument	Cove

Cover Type	Cover Size	Lettering	Product Number
Solid	8 x 8	Portland DPS Survey Monument	00836023
Solid	13 3/8 x 13 3/8	Portland DPS Survey Monument	45613010



## **MAINE DOT FRAME AND COVER**



0ME126000005 Maine DOT frame and cover

– 24" DIA-1 1/8" 8 3/8" 22" DIA 33 1/2" DIA

Frame (	Options
---------	---------

Frame Height	Product Number
8	0ME126000002

Note: all dimensions are in inches.


ove

Cover Type	Lettering	Product Number
Solid	Plain	0ME126000003



800 626 4653 73 ejco.com

## **MAINE DOT CATCH BASIN FRAMES AND GRATES**



0ME552000012 Maine DOT 24" x 24" x 8" 4 flange frame

Frame Options

F Frame Height	Flange	W Flange Dimension	MaineDOT	Product Number
8	3 flange	34 x 30 5/16	Type A	0ME552000001
8	4 flange	34 x 34	Type B	0ME552000003

Note: all dimensions are in inches.



0ME552000002 24" x 24" bar grate



0ME552000016 24" x 24" cascade grate with corner

800 626 4653

Note: this product ships with no cut corner

24" x 24" Grate Options

74

Grate Type	Product Number
Bar grate	0ME552000002
Cascade type grate	0ME552000016
-no cut corners	







75

#### **1802—1825 FRAME AND COVER**







1825 Type A2

#### Features

Vertical and horizontal machined surfaces Stackable frames

#### Options

Custom logo covers TYPE E 1810 outer cover Special lettered covers Gasket seal covers Two bolt assembly Two pent bolt assembly Cam lock assembly Pick bars, drop handles, closed pick holes Adjusting risers



Type Aa hex design

Type E outer cover with 1040 26" diameter inner cover Use with the 1820 & 1825 frames



Type A3 hex design with pick bars

Frame supplied with 4 - 1" diameter base flange holes on 43 1/2" bolt circle \*Available with 49" base flange

All units can be secured

1802—1825 Frame and Cover Assembly Options

		Α	С	D	E	F
Series		Cover	Clear	Frame	Flange	Frame
Number	Reference	Diameter	Opening	Opening	Diameter	Height
1802	SB-27	28 15/16	27	34	46	5 5/8
1805	B-27	28 15/16	27	34	46	10
1820	SB-30	31 15/16	30	37	46	5 5/8
1825	B-30	31 15/16	30	38	46	10

Many of the covers in this series are manufactured with corporate names and their respective logos. These names and images are the protected property of our customers. EJ maintains custom covers for dozens of electrical, telecommunication, and other utility companies. Please contact your nearest EJ office for information regarding new or existing designs.


Note: all dimensions are in inches.

800 626 4653 76 ejco.com

### **NATIONAL GRID**










0MA228600000 frame, 0MA22760002 adaptor, and 0MA227600001 cover



0MA290400001 frame with 0MA290400002 cover







. ramo optio	Traine options				
Frame			Product Number		
Height	Frame Type	Flange Dim.			
3 1/2	Top flange	21 dia.	0MA290400001		
6	Bottom flange	42 x 42	0MA228600000		
6	Bottom flange	48 x 48	0MA227600004		

Note: all dimensions are in inches.

Cover and Grate Options			
<b>Cover Diameter</b>	Cover Type	Lettering	Product Number
16	Solid, vent holes	Electric Service	0MA290400002
27 7/8	Solid, vent holes	Electric Service	0MA227600001
37 7/16 outside dia. (for 27 7/8 cover)	Solid, adaptor	N/A	0MA227600002


Note: all dimensions are in inches.



800 626 4653 77 ejco.com

### **NORTHEAST UTILITIES**





38

0MA380000001 Northeast Utilities frame and 38" cover

Frame Options					
Α	С	E	F		
Cover	Clear	Flange	Frame		
Dia.	Opening	Dia.	Height	Product Number	
32	30	49	5 5/8	0MA320000002	
38	36	50	6	0MA380000005	
38	36	50	10	0MA380000002	

Cover Options Α Cover Dia. **Product Number Cover Type** Lettering 32 Solid, vent holes 0MA320000003 Electric

Electric

0MA380000003

Note: all dimensions are in inches.

Solid, vent holes


Note: all dimensions are in inches.





### **NSTAR**





0MA227000002 NSTAR Electric No. 1 frame and No. 1C cover

Frame Options

NSTAR Frame Type	NSTAR Cat. ID No.	A Cover Diameter	C Clear Opening	E Flange Diameter	F Frame Height	Product Number
No. 0-L shallow frame	24055	37 7/16	36	48 x 48	6	00228612
No. 1-L frame	1385	27 9/16	26	48 x 48	6	0MA227400000
No. 0 frame	1382	37 7/16	36	48 x 48	10	0MA228000000
No. 1 frame	1384	27 9/16	26	48 x 48	10	0MA227000001

Note: all dimensions are in inches.

#### **Grates/Vented Covers**









79

0MA227200014 NSTAR Electric No. 1V grate

00158035 NSTAR Electric No. 0 ventilated cover

0MA228000001 NSTAR No. 0 adaptor

Cover and Grate Options


Cover Diameter	NSTAR Cover Type	NSTAR Cat. ID No.	Product Number
27 9/16	No. 1 cover	1347	0MA227200001
27 9/16	No. 1V grate	1348	0MA227200014
37 7/16	No. 0 ventilated	19483	00158035
37 7/16 outside (for 27 9/16 cover)	No. 0 adaptor	1097	0MA228000001

Note: all dimensions are in inches.



800 626 4653 ejco.com

## **NSTAR (CONTINUED)**



0MA227200020 NSTAR No. 00 frame, No. 00 solid cover adaptor and No. 1 cover

Frame Options							
	NSTAR Frame Type	NSTAR Cat. ID Number	Product Number				
10	No. 00 frame	1383	0MA227300000				

Note: all dimensions are in inches.

Cover Size	NSTAR Cover Type	NSTAR Cat. ID Number	Product Number
53 x 41 outside dim.	No. 00 adaptor	1098	0MA227300001
53 x 41 outside dim.	No. 00 vented adaptor	19700	00227335

Note: all dimensions are in inches.

Cover Options



00227335 NSTAR No. 00 vented adaptor



800 626 4653 80 ejco.com





## MANHOLE FRAMES AND COVERS



EJ produces street castings to meet ASTM and AASHTO criteria. In addition, our castings meet federal and state DOT specifications, and that of individual customers. Non-traffic, light, medium, heavy, extra heavy-duty, and extra heavy-duty airport are the load designations assigned, which indicate where (on which application) a product should be used.

As a result of continued research and development—the product line is increasingly expanding—and has become more complex and diverse than ever. New features such as ergonomic lift-assist devices; new configurations that are more modular and scalable; new advanced security attributes help prevent theft or mitigate explosions; and applied technology provides capabilities like remote sensing with wireless telemetry.

#### **DRAINAGE CASTINGS**



Drainage castings or grates are designed to accept water and can be round, square, or rectangular. They are typically sold with a frame, curb inlet frame, monument box, or bridge drain. Some markets call these slotted covers.

Specifying the appropriate drainage solution is an important part of a storm water management plan. EJ offers a wide array of products designed for storm water drainage including ditch grates, pipe grates, curb and gutter inlets, and catch basins. Drainage castings are available as an assembly or set. EJ also offers bridge drains, scuppers, and ADA grates.

Optional "Dump No Waste! Drains To Waterways" and other permanent cast-in lettering is an effective, low cost, and long-term means to support local environmental initiatives.

#### TRENCH GRATES




From pedestrian areas to airport loading ramps, EJ has the trench drainage solution to fit your application. With a grate that is designed to be supported on two sides, it is expandable and available in numerous widths.

Grating options include parallel grates, perpendicular cross-street drainage, and ADA styles - available in 24" lengths, and widths from 8" to 51". Frames available in standard 24", 36", and 48" lengths.

Standard heavy duty grates and covers are suitable for general traffic service and AASHTO H-20 loading conditions. Our ADA style trench grating and solid trench covers are available for either general traffic loading or non-traffic applications. Extra heavy duty (EXA) airport trench grating is made with ductile iron and is proof load tested to 200,000 pounds.

For that artistic touch, EJ offers designer trench grates that can be stand alone architectural enhancements, or can accompany matching tree grate designs.

## AIRPORT AND PORT AUTHORITY



Environments that undergo excessive load conditions require construction castings specifically designed to meet or exceed heavy duty load rating standards. EJ telecommunication offers many solutions for these types of applications.

From round or square manhole frames and covers, catch basins, drainage inlets, trench grating, and mooring eyes, EJ has you covered.

All extra heavy duty construction castings are manufactured with gray iron conforming to ASTMA 48 Class 35B and ductile iron conforming to ASTM A536. Many of our airport castings can be made-to-order with custom logos and messaging, in most languages, to meet your project specifications.

## UTILITY AND TELECOMM CASTINGS



EJ offers a comprehensive line of high quality utility construction casting solutions for specialized applications such as telecommunication, electric, gas, traffic signals, and street lighting.

Utilities are the lifeblood of any facility, and uninterrupted service is crucial. Our product designs offer superior access and unparalleled security for critical infrastructure —available in a variety of sizes, shapes, materials, and load ratings to fit the needs of any project.

EJ is the world leader in telecommunication and utility solutions, offering features and attributes to meet your unique requirements:

- · Ergonomic and safety
- · Vented covers
- · Composite materials
- · Wireless monitoring
- · Specialty and custom
- $\cdot \, \mathsf{Explosion} \, \mathsf{mitigation} \,$

## INNOVATIVE ACCESS SOLUTIONS



Innovative access solutions are a classification of products that address issues beyond standard manhole frames and covers. This product series includes ergonomic solutions, advanced locking mechanisms, and products that prolong your infrastructure.

For example, the SELFLEVEL® manhole assembly allows the upper frame cover to adjust with the surface of the roadway; keeping the cover level at all times. This product is ideal for extreme freeze/thaw (frost heave) environments.

INFRA-RISER® adjustment risers prolong structure life by dissipating traffic vibrations.

The mechanical strut on our ductile iron hatch line reduces the lifting force of covers weighing up to 560 pounds to less than 35 pounds.

EJ has taken generations of knowledge and experience and fine-tuned designs to offer you the best innovative access solutions.

83



## ERMATIC RANGE AND OTHER MODULAR SOLUTIONS



## HINGED HATCH ACCESS ASSEMBLIES



## COMPOSITE COVERS AND FRAMES



Worldwide, the ERMATIC® modular system is one of the most adaptable product ranges in the industry. This comprehensive and highly engineered range of access covers can be customized to fit any underground vault dimension or cover configuration. Some of the world's most prestigious infrastructure prjoects have selected the ERMATIC range as their preferred solution: from airports, docks and tunnels to sewage, telecommunications and other utility networks.

Specifiers, contractors, and end users choose this product because it is reliable, durable and serviced by the most professional technical support teams. EJ provides solutions that lead the industry, act as best-in-class benchmarks, and satisfy the most demanding customer expectation.

Features and options include security locking, various load ratings and standard sizes between 2' x 2' to 10' x 17'. Custom sizes are available to fit your needs. Cover options include solid or recessed for concrete infill or brick pavers. This product is manufactured at our regional facility in France.

Hinged access assemblies offer ergonomic benefits with the strength of ductile iron. The 8190 and 8210 series of hinged hatch access assemblies are typically installed in traffic areas, airports, and ports.

This hatch provides a secure and easy access point to underground utility structures, and the mechanical strut reduces the lifting force of the cover to less than 35 pounds. The pre-assembled unit saves time and money on the job site; just "drop and pour." The cover opens to 105 degrees and removes at 90 degrees, and features a self-engaging safety bar.

Field performance has proven that composite manhole covers are ideal for the most challenging environment. Safety for pedestrian traffic and utility workers has driven EJ to develop an advanced solution offering the highest level of safety and performance. Composite manhole covers will conduct neither stray voltage nor high heat, thus shielding pedestrians from the underground environment. The advanced ergonomic aspects of composite manhole covers and frames help to safeguard the municipal workforce from injuries.

Contact your local Sales Representative for the solution that best fits your unique needs: stray voltage, heat transfer, steam covers, ergonomics, radio frequency and cellular transmissions, theft (no scrap value), corrosion, identification (color options), and noise abatement.

Patented design features and advanced fiber reinforced polymer (FRP) material technology make our composite products strong, lightweight, and safe for everyone.

## ALUMINUM ACCESS HATCHES



EJ has a broad offering of access hatch products available in aluminum, steel, and ductile iron.

Our hatches are designed to provide easy and secure access to below ground, and below floor installations. The aluminum SAFE HATCH® safety grate system is available in all hatch series. This additional fall through protection and controlled confined space entry enhances worker safety. Heavy duty stainless steel hinges are standard on all units.

Access hatches are used in areas such as sewer pump stations, water treatment plants, gas valve vaults, water meter pits, water valve vaults, telephone and electric vaults, industrial plant pits, fuel storage pits, de-icing control facilities, storm drains, monitoring wells, and collection pits.

EJ also has a complete line of fabricated steel reticuline and welded type drainage grates.

Our modern manufacturing facilities are capable of producing custom fabrications. Contact our expert design team next time you need a custom solution for your project.

#### RISER RINGS



Riser rings are an adjustable solution to bring a manhole or catch basin to grade on your resurfacing projects. They are used in conjunction with a frame to increase its overall height. A typical application would be during pavement overlays.

Avoid unnecessary project costs by eliminating extra labor, equipment and materials. There are reduced traffic disruptions—when the street is paved the job is done and the manhole cover is finished to grade.

- · Solid or adjustable styles
- · Steel and cast iron risers available to fit all your grade adjustments
- · Load tested to ensure dependable strength and long lasting durability
- · Large inventory ready for delivery nationwide
- $\cdot$  Made to order sizes for custom application
- · Sloped risers available
- · DOT approved in many states

#### **ADJUSTMENT RISERS**



Maintain the integrity of your infrastructure by reducing traffic vibration damage. Adjust any manhole or catch basin to grade on your resurfacing projects, new installations, or rehabilitation work with INFRA-RISER® rubber composite adjustment risers.

Below ground, the rubber composite adjustment riser reduces traffic vibration damage—prolonging the life of manhole structures and surrounding pavement:

- · Protects against load concentration stress
- $\cdot \mbox{Dramatically reduces water infiltration}$
- · Perfect grade adjustment in moments with uniform precision
- ·Will not break, split, rot, crack, or chip
- · Made of 92% recycled raw materials
- Round, square, and rectangular designs; flat and tapered risers, select bolt hole patterns
- · Custom sizes available

INFRA-RISER adjustment riser is a simple, economic, efficient, and long-lasting solution. It dissipates the energy transferred between the casting and the manhole structure.

85

ej

#### **FIRE HYDRANTS**



WaterMaster® Fire Hydrants have set the standard for reliability and ease of maintenance. With 2 and 3-nozzle hydrant designs, along with multiple shoe connection options, WaterMaster hydrants offer the right options to meet your standard specifications. All hydrants are compliant with the Reduction of Lead in Drinking Water Act 2011. Computer aided design and analysis, along with ductile iron construction, ensures superior performance. All cast components are made and assembled in the USA.

Each hydrant is pressure tested to twice the rated working pressure. WaterMaster 5CD250 and 5BR250 fire hydrants meet or exceed the requirements of ANSI/AWWA C502 Standard for Dry-Barrel Fire Hydrants, Underwriters Laboratories Standard UL246, and Factory Mutual 1510.

Options include individual hydrants being assembled to your (municipal) specification. Additionally, EJ offers hydrant accessories, including the snow barrel for BR models to keep hydrants accessible for areas with high snowfall, and Storz nozzle connections for quick pumper nozzle attachment.

#### **GATE VALVES**



FlowMaster® Resilient Wedge Gate Valves are designed to control the flow of water in fire hydrant applications—but can also be utilized for other water distribution or sewer system applications. All valves are compliant with the Reduction of Lead in Drinking Water Act 2011.

The valves incorporate quality parts and a simple design. All-ductile iron construction delivers superior strength, impact resistance and reduced weight ensuring long service life. All valve parts are manufactured and assembled in the USA.

Available in 2" through 24" sizes, with multiple end connections, and bevel or spur gear operators for 20" and 24" valves. The valves are available as either an assembly or set.

FlowMaster valves meet or exceed the performance requirements of AWWA C515 and Underwriters Laboratories Standards UL262. The valve body and other ductile iron components are manufactured from material conforming to ASTM A536. The wedge is fully rubber encapsulated to meet ASTM D429 requirements.

#### **VALVE BOXES**



Valve boxes are used to access an underground valve and can be adjustable using multiple pieces with either a screw type or slip type arrangement.

Valve boxes are available to accommodate 4" through 20" valves.

- · Natural gray iron or water-based asphaltic coating
- · Covers with special lettering and custom logos
- · Locking lids
- · Valve box risers—raise valve box lid to adapt to a new grade
- · Made in the USA

The slip type has interchangeable pieces that allow for overall height adjustment with parts sliding past each other, while the screw type has interchangeable pieces that allow for overall height adjustment with parts threaded into each other. Valve boxes are available as either an assembly or set.

#### **METER BOXES**



The meter box product is specifically intended to cover a water meter. It is typically large enough to allow for inspection and limited access, and is often intended for non-traffic situations.

EJ offers an assortment of meter boxes, covers, and rings to fit your application. Our broad meter box product offering includes customized logo covers to help promote your identity, special lettered covers that clearly identify the access point, and touch read covers.

- · Oval meter boxes
- · Round meter boxes
- · Rectangular meter boxes
- · Meter pits
- · Meter lids
- Meter box cover accessories including security locking

Meter boxes are available as either an assembly or set.

#### TREE GRATES



Style your surroundings with timeless and appealing streetscape products manufactured by EJ. Tree grates are durable, functional, and architecturally appealing, and promote healthy tree growth. Designed for pedestrian traffic; our full line of tree grates provide natural drainage and enhance any urban, campus, or park setting.

The slotted design allows for efficient watering and is ADA compliant for pedestrian safety. The narrow slot of an ADA grate also prohibits litter from collecting in the tree well and minimizes the growth of weeds.

Optional expandable tree openings consist of removable center rings, which are a convenient way to adjust diameter of the grate opening as the tree trunk grows in width. Other options include security bolting features, and light port options.

Cast iron grating is strong and stands up to harsh environmental conditions. As an added value, the tree grates can carry community logos and mottos and are made in the USA.

## DETECTABLE WARNING PLATES



DURALAST® Detectable Warning Plates help warn visually impaired pedestrians of the approaching street. Engineered to outlast the sidewalk, this cast iron plate is a long-lasting streetscape product that can withstand rigorous urban conditions, such as snow plows, street cleaning machines, and vehicular traffic.

Lower your maintenance and product life cycle costs by using DURALAST detectable warnings—your ADA compliant and environmentally friendly solution.

- · Long-wearing cast iron (over 500 times more wear resistant than composites\*)
- · Withstands vehicular and snow plow traffic
- · Corrosion resistant
- $\cdot \, \text{Permanently embedded into concrete} \,$
- · Comply with the latest ADA guidelines regarding pedestrian and vehicular traffic

\*An independent third party laboratory test was conducted to determine the wear index values of DURALAST® Detectable Warning Plates versus a competing composite surface. Test results indicate that DURALAST plates are over 500 times more wear resistant than composites.

## ejco.com

Featuring a comprehensive product database with advanced search and browsing capabilities

#### Information for Registered Users

- · Quick and easy registration
- · PDF sales drawings for download
- · Specification information
- · Customizable project lists
- · Detailed product info

#### **Up-to-date Product Resources**

- ·Literature
- ·Videos
- · Installation instructions

#### The Video Tour

· Collection of online videos providing an overview of key features and functions

#### Finding your Solution


- · Search by Product Line
- · Search by Project Type
- · Search Bar
- · Narrow Search by Product Attributes
- · Search by Regional Specification

#### **Product Specifications**

- · Available only to registered users
- · National and international specifications
- · Local Standards—City, County, State

#### Project Lists

- · Simple to create
- · Quick access to frequently used products
- · Helps manage complex projects
- · Feature—request a quote with a click of a button
- · Feature—print project list
- · Feature—e-mail project list
- · No limit to the number of lists









The search results can be narrowed by using the facets and attributes on the left



# Cross Reference





89

### **MASSACHUSETTS**

LeBaron No.	EJ Product No.	Description	Page No.	LeBaron No.	EJ Product No.	Description	Page No.
9" x 10" Frame a	nd Covers	i -	1	L32C22	0MA200000027	32 X 1-3/4 COVER DRAIN	13
LA0910	0MA157000001	9 X 10 FRAME	10	L32C22ST	0MA200000028	32 X 1-3/4 SEALTITE PLAIN	13
L09C3	0MA157000002	9 X 3/4 COVER PLAIN	10	LOGGOGT	014400000000	COVER	10
L09C3	0MA157000003	9 X 3/4 COVER SEWER	10	L32C22ST SEWER	0MA200000029	32 X 1-3/4 SEALTITE SEWER COVER	13
L09C3	0MA157000004	9 X 3/4 COVER DRAIN	10	City of Worceste	r Frames and Cove	rs	
L09C3	0MA157000005	9 X 3/4 COVER CLEANOUT	10	N/A	0MA105000014	WORCESTER 23 X 4 FRAME	14
24" Frames	'			LC239	0MA105000004	WORCESTER 23 X 9 FRAME	14
LA244	0MA124000021	24 X 4 FRAME	11	LC239	00105613	1056ZPT 9" TALL FRAME FOR	14
LA246	0MA124000022	24 X 6 FRAME	11	1.0001	0144105000005	BOLTING WITH EON FEATURE	14
LA248	0MA124000023	24 X 8 FRAME	11	L23C1	0MA105000005	WORCESTER PLAIN COVER	14
24" Covers	'			L23C1ST	0MA105000008	WORCESTER SEALTITE COVER	14
L24C32	0MA124000024	24 X 1-1/4 COVER PLAIN	11	L23G1	0MA105000009	WORCESTER GRATE	14
L24C32	0MA124000025	24 X 1-1/4 COVER SEWER	11			on Frame and Covers	
L24C32	0MA124000026	24 X 1-1/4 COVER DRAIN	11	LJ101A FRAME	0MA211000046	BWSC 26 X 8 FRAME	15
L24C32ST PLAIN	0MA124000027	24 X 1-1/4 SEALTITE PLAIN COVER	11	L26C08 COVER	0MA211000047	COVER - "BOSTON SEWER"	15
L24C32ST SEWER	0MA124000028	24 X 1-1/4 SEALTITE SEWER COVER	11	L26C08 COVER	0MA211000048	COVER - "BOSTON DRAIN"	15
24" Grates				LJ115	00191711	1917Z FRAME 8-1/8"	15
L24G6	0MA124000029	24 X 1-1/4 GRATE	11	L30C5	00191721	1917 VENTED COVER BOSTON	15
L24G7 ADA	0MA112000001	24 X 1 1/4 GRATE "ADA"	11	L30C5	00191723	SEWER L30C5  1917 VENTED COVER BOSTON	15
26" Frames				L30C3	00131723	DRAIN L30C5	13
LA264-2	0MA226000001	26 X 4 FRAME	12	Hand Hole / Pull	Box Frames and Co	vers	
LA266	0MA226000002	26 X 6 FRAME	12	S612F	0MA801200002	MASSDOT 12X12X3-1/2 PULL	17
LA268-4	0MA211000038	26 X 8 FRAME	12	C212C	00801221	BOX FRAME	17
26" Covers				S212C	00801221	8012A SOLID JUNCTION BOX COVER	17
L26C26	0MA211000039	26 X 1-1/8 COVER	12	LV1618	00811812	8118Z 4 FLG FR	17
L26C26	0MA211000040	26 X 1-1/8 SEWER COVER	12	LV1618C	00811825	8118A BWSC DIAMOND TOP CV	17
L26C26	0MA211000041	26 X 1-1/8 DRAIN COVER	12	S324F	0MA801000003	MASSDOT 24X24X3	17
L26C26ST	0MA211000042	26 X 1-1/8 SEALTITE PLAIN COVER	12	S224C	0MA801000012	REVERSIBLE FRAME  24 X 24 COVER - "ELECTRIC"	17
L26C26ST SEWER	0MA211000043	26 X 1-1/8 SEALTITE SEWER COVER	12	LV1325	0MA801300001	MASSDOT 13X25X3 PULL BOX FRAME	17
26" Grates	I			LV1325C	0MA801300014	COVER - "CATV"	17
L26G5 GRATE	0MA211000044	26 X 1-1/8 GRATE	12	24" x 24" Frames			
L26G13 ADA GRATE	0MA211000045	26 X 1-1/8 ADA GRATE	12	LF 244-2 3FLG	0MA554000001	24 X 4 3-FLANGE FRAME	20
32" Frames	1			LF 244-2 4FLG	0MA554000002	24 X 4 4-FLANGE FRAME	20
LA324-5	0MA200000022	32 X 4 FRAME	13	LF 246-2 3FLG	0MA554000003	24 X 6 3-FLANGE FRAME	20
LA326-5	0MA200000023	32 X 6 FRAME	13	LF 246-2 4FLG	0MA554000004	24 X 6 4-FLANGE FRAME	20
LA328-5	0MA200000024	32 X 8 FRAME	13	LF 248-5 3FLG	0MA554000005	24 X 8 3-FLANGE FRAME	20
32" Covers	I		1	LF 248-5 4FLG	0MA554000006	24 X 8 4-FLANGE FRAME	20
L32C22	0MA200000025	32 X 1-3/4 COVER PLAIN	13	LK125 3FLG	0MA552000016	24X24X4 3-FLANGE HEAVY	20
L32C22	0MA200000026	32 X 1-3/4 COVER SEWER	13			FRAME	

Products listed in cross reference section are not all inclusive of products available. Contact your local EJ representative for more information.

## **MASSACHUSETTS (CONTINUED)**

LeBaron No.	EJ Product No.	Description	Page No.	LeBaron No.	EJ Product No.	Description	Page No.
LK125 4FLG	0MA552000015	24X24X4 4-FLANGE HEAVY	20	L27DG1 GR	00727831	7278 GRATE	25
EK120 20	0.00.0000000000000000000000000000000000	FRAME		L27DG3	00727833	7278 GRATE WITH LOCK LUG	25
LK123 3 FLG	0MA552000081	24X24X8 3-FLANGE HEAVY FRAME	20	Beehive Frame a		7270 010 112 771111 20 01 20 0	20
LK124 4 FLG	0MA552000082	24X24X8 4-FLANGE HEAVY FRAME	20	LCG226-2	0MA801300020	22 X 6 BEEHIVE FRAME & GRATE ASSEMBLY	30
24" x 24" Grates	!		'	N/A	0MN120500025	MN 1205Z 7" FR & 1205 02	30
L24SG17	0MA552000074	24 X 24 STANDARD GRATE	21			BEEHIVE GR	
L24SG01	0MA552000075	24 X 24 SQUARE HOLE GRATE	21	Traps and Hoods		CATCLI DACIALLICOD ACCEMBLY	1 00
L24SG1	00552064A01	5520M5 UND DNW CAM HORN GR	24	L202 L202	0MAL20200001 0MAL20200002	CATCH BASIN HOOD ASSEMBLY L202 HOOD	30
L24SG18L	0MA552000076	24 X 24 CASCADE LEFT GRATE	21	L202H	0MAL20200003	L202H HANGER	30
L24SG18R	0MA552000077	24 X 24 CASCADE RIGHT GRATE	21	L202SH	0MAL20200005	CATCH BASIN HOOD ASSEMBLY	30
L24SG20	0MA552000077	24 X 24 ADA GRATE	21	L218	0MALB2100008	CATCH BASIN TRAP	31
24" x 48" Frames		24 A 24 ADA GNATE	21	N/A	00595466	5954 UND 6" TRAP	31
LV2448-1	0MA544400011	24X48X4 3-FLANGE DOUBLE	22	N/A	00595467	5954 UND 8" TRAP	31
3FLG LSD	0101A544400011	FRAME	22	N/A	00595468	5954 UND 10" TRAP	31
LV2448 3FLG	0MA544400106	24X48X4 3-FLANGE DOUBLE	22	N/A	00595470	5954 UND 12" TRAP STRAIGHT	31
SSD	0044544400010	FRAME	00	N/A	00595469	5954 UND 12" TRAP 24" RADIUS	31
LV2448-1 4FLG	0MA544400012	24X48X4 4-FLANGE DOUBLE FRAME	22			5954 UND 15" TRAP STRAIGHT	
LV2448-2 3FLG LSD	0MA544000001	24X48X8 3-FLANGE DOUBLE FRAME	22	N/A MassDOT	00595475	9994 UND 19 TRAF STRAIGHT	31
LV2448-2 3FLG SSD	0MA544400107	24X48X8 3-FLANGE DOUBLE FRAME	22	LK110A	0MA211000002	MASSDOT TYPE B MANHOLE FRAME	32
LV2448-2	0MA544000002	24X48X8 4-FLANGE DOUBLE	22	L26C2	0MA211000003	26 X 1-1/8 COVER	32
4FLG		FRAME		L26C02	0MA211000004	26 X 1-1/8 SEWER COVER	32
•	3" x 28" x 8" Frames	I		L26C02	0MA211000005	26 X 1-1/8 DRAIN COVER	32
LF284 3 FLG	0MA728800022	28 X 28 X 4 FRAME 3 FLANGE	24	LK110	0MA211000001	MASSDOT TYPE A MANHOLE	32
LF284 4 FLG	0MA728800023	28 X 28 X 4 FRAME 4 FLANGE	24	1.144.00	0144550000040	FRAME	
LF288 3 FLG	0MA728800012	28 X 28 X 8 3-FLANGE FRAME	24	LK120	0MA552000010	MA 24X24X8 3 FLANGE FRAME	33
LF288 4 FLG	0MA728800013	28 X 28 X 8 4-FLANGE FRAME	24	L24SG7	0MA552000014	MA 24 X 24 A-1 BAR GRATE	35
L28SC1	00728825	7288A VENTED 1 HOLE COVER BSD	24	LK121	0MA552000011	MA 24X24X8 4 FLANGE FRAME	33
L28SG1	0MA728800014	28 X 28 GRATE	24	L24SG7	0MA552000014	MA 24 X 24 A-1 BAR GRATE	34
L0814C01	00726721	7267PL BOSTON HARBOR UND	24	LK120	0MA552000010	MA 24X24X8 3 FLANGE FRAME	34
L0814C02	00726723	7267PL NEPONSET RIVER UND	24	LK120-M	0MA552000003	MASSDOT 24X24X8 3 FLG FRM FOR H&L	34
L0814C03	00726725	7267PL CHARLES RIVER UND	24	LK121-M	0MA552000002	MASSDOT 24X24X8 4 FLG FRM	34
City of Worceste	 r 28" x 28" x 8" Frai	nes and Grate				FOR H&L	
LF288 3 FLG	0MA728800015	28 X 28 X 8 FRAME 3FLG	25	L24SG24	0MA552000001	MASSDOT A-4 HOOK & LOCK BAR GRATE	34
LF288 4 FLG	0MA728800016	28 X 28 X 8 FRAME 4FLG	25	L24SG18-L	0MA552000076	MA 24X24 CASCADE LEFT GR	21
L28SG1	0MA728800017	28 X 28 GRATE	25	L24SG18-R	0MA552000077	MA 24X24 CASCADE RIGHT GR	21
"D" Frames and	Grates			L24SG23-L	0MA555000004	MASSDOT B-1 HOOK & LOCK	33
LD-268-1	00726811	7268Z "D" STYLE UND	25	1.040000.5	014455500000	CSCADE GR L	00
LD278-2 FR	00727811	7278 8" TALL CATCH BASIN FRAME	25	L24SG23-R	0MA555000005	MASSDOT B-2 HOOK & LOCK CSCADE GR R	33
L26DG1	00726831	7268M1 "D" STYLE UND	25	LK125-2FLG	0MA552500001	MA 24X24X4 DROP INLET 2 FLANGE FRM	35



## **MASSACHUSETTS (CONTINUED)**

LeBaron No.	EJ Product No.	Description	Page No.	LeBaron No.	EJ Product No.	Description	Page No.
LK125-3FLG	0MA552000016	MA 24X24X4 DROP INLET 3	35	5 Bar Cascade Fr	ame and Grate		1
LK125-4FLG	0MA552000015	FLANGE FRM  MA 24X24X4 DROP INLET 4	35	LK450	0RI547000001	RI 6.3.3 24 X 22 X 5 4 FLANGE FRAME	43
L24SG7	0MA552000014	FLANGE FRM  MA 24 X 24 A-1 BAR GRATE	35	L2422G1	0RI547000002	RI 6.3.3 24 X 22 5-BAR CASCADE GRATE	43
S612F	0MA801200002	MASSDOT 12X12X3-1/2 PULL	17	Circular Drain Fra	ame and Grate	OTATE	
		BOX FRAME		LK284	00120513	1205Z1 4" TALL FRAME	43
S324F	0MA801000003	MASSDOT 24X24X3 REVERSIBLE FRAME	17	L424G1	00120533	1205M2 CIRCULAR VANE GRATE	43
LV1325	0MA801300001	MASSDOT 13X25X3 PULL BOX	17	26" Manhole Fra	mes and Covers		
		FRAME		LK253-3	0RI225000001	RI 26 X 4 LIGHT DUTY SQ FLG FRAME	44
RHODE IS	I AND			LK237A	0RI223000001	RI 6.2.0 26 X 6 FRAME	44
Municipal Frame				LK256-2	0RI225000003	RI 6.2.1 26 X 9 FRAME	44
LA326-5	00200611	2006Z 6" TALL FRAME	38	L26C10	0RI225000011	RI 26" 'RIDOT COVER W/ HOLES	44
L32C22	00200677	2006C UND CRANS SW YR HL1 L32C22	38	L26C2 (84)	0RI225000006	RI 26" RIDOT HEAVY DUTY COVER	44
LJP10	00242019	2420Z1PT UND FRAME	39	L26C14	0RI223000002	RI 6.2.0 26" RIDOT COVER	44
		STACKABLE		L26C10	0RI225000010	RI 6.2.1 26" RIDOT COVER	44
L24C8	00240834	2408CPT UND EPIC CITY OF PROVIDENCE	39	Handhole Frame	s and Covers		
LK253	00225311	2253Z UND FR FLG3	39	LJ104	0RI290400001	RI 18.2.0 16X3-1/2 FR D&T ONLY	45
N/A	001040081A01	1040AGS CAM SPC MCH 1" DP CV ASY	39	L16C1 "ELECTRIC" D&T	0RI290400002	RI 18.2.0 16" ELECTRIC D&T ONLY	45
LV0823	00801111	8011Z 2-1/2" TALL JUNCTION BOX FRAME	39	L16C1 "SIGNAL" D&T	0RI290400003	RI 18.2.0 16" SIGNAL COVER	45
L0823C	00801144	8011A UND CITY OF PROVIDENCE CV	39	LA206	0RI106100008	RI 18.2.1 20 X 6 FR D&T ONLY	45
LF248-5 3 FLG	00554813	5548Z 8" TALL CATCH BASIN FRAME WITH 3 FLANGES	40	L20C1 "ELECTRIC" D&T	0RI106100009	RI 18.2.1 20" ELECTRIC D&T ONLY	45
LF248-5 4 FLG	00554811	5548Z 8" TALL CATCH BASIN FRAME WITH 4 FLANGES	40	L20C1	0RI106100003	RI 18.2.1 20" SIGNAL COVER	45
L24SG1	005520002	5520M5 DI UND DNW	40	"SIGNAL" LK256-2	0RI225615002	RI 18.2.1 26 X 9 FR D&T ONLY	45
L24SG1	005520001	PROVIDENCE GR 5520M4 DI UND DNW PROVIDENCE GR	40	L26C6A	0RI225615003	RI 18.2.2 26" ELECTRIC COVER D&T ONLY	45
LJP15	45660010	V5660 4" TALL REVERSIBLE FRAME	40	L26C6A	0RI225615004	RI 18.2.2 26" SIGNAL COVER D&T ONLY	45
L2436G1/G2	45660033	V5660 GRATE DUMP	40	24" x 24" Single l	 Frames	Dai onei	
2240001/02	4000000	NO WASTE! DRAINS TO WATERWAYS	10	LK120	0RI552000001	RI 24 X 24 X 8 3 FLANGE FRAME	46
LA/LC266	00226611	2266Z 6" TALL FRAME	41	LK121	0RI552000003	RI 24 X 24 X 8 4 FLANGE FRAME	46
L26C26	00211147	2111A UND EPIC WARWICK CV	41	24" x 48" Single	Frames		
LA326-5	00200611	2006Z 6" TALL FRAME	41	LV2448-2	0RI544000001	RI 3 FLANGE DOUBLE FRAME	46
L32C22-	00200687	2006C1 HL1 UND W SW LO	41	LV2448-2	0RI544000004	RI 4 FLANGE DOUBLE FRAME	46
WARWICK	00105011	L32C22	40	24" x 24" Grates			
LC256-2	00125611	1256Z 6" TALL FRAME	42	L24SG1	0RI552000002	RI 24 X 24 SQUARE HOLE GRATE	47
L25C8-WD	00125850	1258A WOONSOCKET DRN HL2 UND CV	42	L24SG7	0RI552000006	RI 24 X 24 SLOTTED GRATE	47
L25C8-WS	00125851	1258C WOONSOCKET SW HL2	42	L24SG15	0RI552000010	RI 24 X 24 BIKE SAFE GRATE	47
		UND CV		L24SG18-L	0RI552000014	RI 24 X 24 CASCADE GRATE L	47

Products listed in cross reference section are not all inclusive of products available. Contact your local EJ representative for more information.

## **RHODE ISLAND (CONTINUED)**

LeBaron No.	EJ Product No.	Description	Page No.	LeBaron No.	EJ Product No.	Description	Page No.
L24SG18-R	0RI552000015	RI 24 X 24 CASCADE GRATE R	47	East Lyme			
				LC327-2	00132213	1322Z UND FR NYTY	52
CONNECT	TICLIT			L32C20	00132221	1322A UND OPH2 COVER NYTY	52
	mes and Covers			L32C20	00132257	1322A SOLID COVER SEWER	52
LA244	00124411	1244Z UND FRAME	50	Hartford MDC			
LA244 LA246	00124411	1246Z UND FRAME	50	LJ105	00220513	2205Z UND PH1 FRAME	53
LA248	00124011	1248Z UND FRAME	50	N/A	00124819	1248Z2 DI UND PH1 FRAME	53
L24C32	00124811	1338A UND EIGHTH DISTRICT	50	L24C21	00220521	2205A UND SEWER COVER	53
L24C32	00133630	SEW COVER	30	L24C21	00220523	2205C UND HL1 SEWER COVER	53
L24C32	00124677	1246C UND GNHWPCA LO HL2 OPH2 COVER	50	L24C21	00220546	2205CGS UND SEWER COVER	53
L24C32	0CT124800004	GNHWPCA 8" WATERTITE ASSEMBLY	50	L24C21	00220548	2205AGS UND SEWER COVER	53
L24C32	00124879	1248B UND EP HL8 DRL	50	L24C21	00220525	2205A UND WTR COVER	53
		HAMDEN STM COVER	=0	L24C21	00220549	2205C UND HL1 WTR COVER	53
L24C32	00133871	1338A UND TOWN MANCHESTER DRN COVER	50	L24C21	00220527	2205C UND STM DRN HL1 COVER	53
L24C32	00133872	1338A UND TOWN MANCHESTER SEWER COVER	50	L24C21	00220528	2205A UND STM DRN COVER	53
L24C32A	00124865	1248A UND EPIC MILFORD SEWER	50	L24G1-SP	00244031	2440M UND DNP TROUT LO GRATE	53
L24C32A	00124825	1248A UND EPIC SEWER COVER	50	Meriden			
L24C32A	00124827	1248A UND EPIC STM COVER	50	LJ116	00220515	2205Z1 UND 1 1/4" SEAT FR	54
L24C32	00124869	1248AGS UND EPIC STAFFORD	50	LC248-8	00124811	1248Z UND FRAME	54
L24C32A	00124844	SEWER COVER 1248A UND EPIC WALLINGFORD	50	L24C32-SW	00124878	1248A UND EPIC MERIDEN SEWER	54
Bridgeport				L24C36-ST	00124875	1248A UND EPIC MERIDEN STM	54
LA264-2	00226411	2264Z UND FRAME	51	LA244	00124411	1244Z UND FRAME	54
LA266	00226611	2266Z UND FRAME	51	LA246	00124611	1246Z UND FRAME	54
LC268-2	00211111	2111Z UND FRAME	51	Middletown			
L26C17	00211157	2111A UND BRIDGEPORT WPCA	51	LA244	00124411	1244Z 4" TALL FRAME	55
		SEWER EPIC		LA246	00124611	1246Z 6" TALL FRAME	55
Bristol				LJ105	00220515	2205Z1 8" TALL FRAME WITH	55
LC244-SP	00241015S01	2410Z1 UND FRAME SPC MACH 24 3/8"	51	LA244	00124413	1-1/4" SEAT DEPTH  1244ZPT 4" TALL FRAME FOR	55
LC246-2SP	00124615S01	1246Z1 UND FR HVY SPC MACH 24 3/8"	51	LA246	00124613	BOLTING WITH EON FEATURE  1246ZPT 6" TALL FRAME FOR	55
LC248-1SP	00124815S01	1248Z1 UND FR HVY SPC MACH 24 3/8"	51	LA248	00220517	BOLTING WITH EON FEATURE  1248ZPT 8" TALL FRAME FOR	55
LC240	00224011	2240Z UND FRAME	51			BOLTING WITH EON FEATURE	
L24C23-ST	00224021	2240A SOLID COVER WITH GASKET	51	L24C32	00124862	1248A UND EPIC MIDDLETOWN COVER	55
Danbury				L24C32B	00124863	1248APT UND EPIC MIDDLETOWN CV	55
LA268-3	00126811	1268Z UND FRAME	52	L24C32	00124862D01	1248C UND EPIC MIDDLETOWN	55
L26C27-DAN-	00126823	1268A SOLID COVER DANBURY	52			HL4 COVER	
SS L 26C27 DAN	00126920	SANITARY SEWER	52	New Britain			
L26C27-DAN- ST	00126829	1268A UND DANBURY STM SW CV	52	LC244-SP	00241015S01	2410Z1 UND FRAME SPC MACH 24 3/8"	55



800 626 4653 ejco.com 93

## **CONNECTICUT (CONTINUED)**

LeBaron No.	EJ Product No.	Description	Page No.	LeBaron
LC246-2SP	00124615S01	1246Z1 UND FR HVY SPC MACH	55	Connecti
LC248-1SP	00124815S01	24 3/8" 1248Z1 UND FR HVY SPC MACH	55	LK310
1.0040	00004044	24 3/8"		LA254-S
LC240	00224011	2240Z UND FRAME	55	1.0500
L24C23	00224020	2240C UND HL4 COVER	55	L25C3
L24C23	00224022	2240C UND SEWER HL4 COVER	55	
New Haven	L	L	1 = 0	NEW
LC240-2	00224211	2242Z UND FR	56	Catch Ba
L24C33	00224221	2242B UND NEW HAVEN COVER	56	LK120-30
L24C33	00224223	2242B UND NEW HAVEN STM COVER	56	
N/A	00774017	7740Z2PT UND FLG3 FR	56	LK121-40
N/A	00774015	7740Z1PT UND FLG4 FR	56	LK424
N/A	00774031	7740M1 DI UND DNW TR LO GR TYPE A	56	LK424
N/A	00774041	7740M2 DI UND DNW TR LO GR TYPE B	56	LK420
N/A	00774033	7740M1 DI UND BLT4 DNW TR LO TYPE A	56	LK420
N/A	00774043	7740M2 DI UND BLT4 DNW TR LO TYPE B	56	LK450
North Haven				L24SG7
LA268-3	00126811	1268Z UND FRAME	57	L2123G1
L26C1S	00126822	1268A UND SEWER COVER	57	L2422G1
L26C1S	00126824	1268A UND DRN COVER	57	L242201
Trumbull				L24SG18
LA268-3	00126811	1268Z UND FRAME	57	L24SG18
LE260	00226011	2260Z UND FRAME	57	L24SG1
L26C1S	00126822	1268A UND SEWER COVER	57	Manhole
L26C1S	00126824	1268A UND DRN COVER	57	LA324-5
L26C1S	00126827	1268AGS UND SEWER COVER	57	LA326-5
Waterbury				L32C22
LC244	00241015	2410Z1 UND FRAME W/O MUD	58	L32C22
		RG 4"		L32C22
LC246-2	00124615	1246Z1 UND FRAME HVY	58	1 00000
LC248-1	00124815	1248Z1 UND FRAME HVY	58	L32C22
L24C32-WSS	00124725	1247A UND WATERBURY SAN SEWER	58	
L24C32-WST	00124670	1246C UND HL1 WATERBURY STM DRN LO	58	VERI\ Standard
L24C32 WS	00124671	1246A UND WATERBURY	58	
LOGO LV2248-5	00759113	SEWER LO COVER 7591Z1 UND FRAME	58	LC248
		759121 UND FRAME 7590M3 UND DNW GR		L24C01
L2248G7	00759039		58	Drop Inle
LV2248CU5	00759062	7590T1 6" UND TYNS DNW DTW TRO LO	58	LF246-30

			Page
LeBaron No.	EJ Product No.	Description	No.
Connecticut DOT	Frame and Covers		
LK310	0CT121000003	CONNDOT STANDARD MANHOLE FRAME	59
LA254-SP	00121411	1214Z 4" TALL FRAME WITH SLOTTED BASE FLANGE HOLES	59
L25C3	0CT121000005	CONNDOT MANHOLE COVER - OPEN PICKHOLE	59

### **HAMPSHIRE**

LK120-300	0NH552000001	NH DOT TYPE A, E, & F 3-FLANGE FRAME	62		
LK121-400	0NH552000003	NH DOT TYPE A, E, & F 4-FLANGE FRAME	62		
LK424	0NH532000005	NH TYPE B 3 FLANGE 4" TALL FRAME	62		
LK424	0NH532000007	NH TYPE B 4 FLANGE 4" TALL FRAME	62		
LK420	0NH532000001	NH TYPE B 3 FLG 8" TALL FRAME	62		
LK420	0NH532000003	NH TYPE B 4 FLG 8" TALL FRAME	62		
LK450	0NH547000001	NH TYPE E FRAME	62		
L24SG7	0NH552000002	NH TYPE A SLOTTED GRATE	63		
L2123G1	0NH532000008	NH TYPE B GRATE	63		
L2422G1	0NH547000002	NH OLD TYPE E 5 BAR CASCADE GRATE	63		
L24SG18	0NH552000012	NH TYPE F CASCADE GRATE L	63		
L24SG18	0NH552000010	NH TYPE F CASCADE GRATE R	63		
L24SG1	0NH552000016	NH SQUARE HOLE GRATE	63		
Manhole Frames and Covers					
LA324-5	0MA200000022	32 X 4 FRAME	64		

Mannoie i rames	una oovers		
LA324-5	0MA200000022	32 X 4 FRAME	64
LA326-5	0NH200000001	NH 32 X 6 STANDARD MANHOLE FRAME	64
L32C22	0NH200000002	NH 32" STANDARD MANHOLE COVER PLAIN	64
L32C22	0NH200600001	NH 32" STANDARD MANHOLE COVER SEWER	64
L32C22	0NH200600002	NH 32" STANDARD MANHOLE COVER DRAIN	64

### MONT

Standard	Eramo	and	Covo
Jianuaru	Traine	anu	COVE

LC248	0VT124000001	VT STANDARD FRAME	66				
L24C01	0VT124000002	VT STANDARD COVER	66				
Drop Inlet Frames							

FRAME

VT 3 FLANGE DROP INLET

0VT554600001

Products listed in cross reference section are not all inclusive of products available. Contact your local EJ representative for more information.

94 800 626 4653 ejco.com





## **VERMONT (CONTINUED)**


LeBaron No.	EJ Product No.	Description	Page No.	LeBaron No.	EJ Product No.	Description	Page No.
LF246-400	0VT554600002	VT 4 FLANGE DROP INLET FRAME	67	L28C11	0MA227600001	NATIONAL GRID 28" ELECTRIC SERVICE COVER	77
24" x 24" Grates			LE2836X1	0MA227600002	NATIONAL GRID 38" ADAPTOR	77	
L24SG07-000	0VT552000002	VT TYPE A SLOTTED BAR GRATE	67	LE276-3	0MA227600004	NATIONAL GRID 28 X 6 FRAME	77
L24SG01-000	0VT552000015	VT TYPE D SQUARE HOLE GRATE	67	LJ104	0MA290400001	NATIONAL GRID 16 X 3 1/2 FRAME	77
L24SG18	0VT552000007	VT TYPE E CASCADE GRATE LEFT	67	L16C01	0MA290400002	NATIONAL GRID 16" ELECTRIC SERVICE COVER	77
L24SG18	0VT552000008	VT TYPE E CASCADE GRATE RIGHT	67	Northeast Utilities			
Type A, D, & E and Double Type A Frames				LE380-2	0MA380000002	NORTHEAST UTILITIES 38 X 10 FRAME	78
LK123-300	0VT552000003	VT TYPE A, D, & E 3 FLANGE FRAME	68	L38C05	0MA380000003	NORTHEAST UTILITIES 38 COVER 5 HOLE ELECTRIC	78
LK124-400	0VT552000001	VT TYPE A, D, & E 4 FLANGE FRAME	68	LE3265	0MA320000002	NORTHEAST UTILITIES 32 FRAME	78
LV2448-2-300	0VT544000002	VT TYPE A DOUBLE 3 FLANGE FRAME	68	LE32C18	0MA320000003	NORTHEAST UTILITIES 32 COVER 5 HOLE ELECTRIC	78
LV2448-2-400	0VT544000001	VT TYPE A DOUBLE 4 FLANGE FRAME	68	LE386-2	0MA380000005	NORTHEAST UTILITIES 38 X 6	78
Type B Frame and Cover			L38C05	0MA380000003	NORTHEAST UTILITIES 38	78	
LK450-000	0VT547000001	VT TYPE B FRAME	70	COVER 5 HOLE ELECTRIC			
L2422G01-000	0VT547000002	VT TYPE B 5 BAR CASCADE GRATE	70	LE270-2	0MA227000001	NSTAR #1384 NO. 1 MANHOLE	79
MAINE			L28C06	0MA227200001	NSTAR #20453 NO. 1 MANHOLE COVER	79	
City of Portland			LE276-4	0MA227400000	NSTAR #1385 NO. 1-L MANHOLE FRAME	79	
N/A	0ME552000019	PORTLAND STANDARD DR5 24 X 5 FRAME	72	L28C06	0MA227200001	NSTAR #20453 NO. 1 MANHOLE COVER	79
L24C12	0ME126000003	ME 24" PLAIN SOLID COVER 604(7)	72	LE380	0MA228000000	NSTAR #1382 NO. 0 MANHOLE FRAME	79
Main DOT Frame and Cover				LE2836X3	0MA228000001	NSTAR #1097 NO. 0 MANHOLE	79
LK610	0ME126000002	ME 24 X 8 FRAME 604(16)	73	L28G4	0MA227200014	ADAPTOR  NSTAR #1348 NO. 1301 GRATE	79
L24C12	0ME552000020	ME 24" PLAIN SOLID COVER 604(7)	73		0MA227200014		
Maine DOT Catc	 h Basin Frames and			L28G5	UIVIAZZ/ZUUU15	28" NSTAR VENTED COVER	79
LK126			74	Verizon LE296	0MA180200000	VEDIZONI EDAME MANILIOLE	NI/A
LK127	0ME552000002	GRATE ME 24 Y 24 Y 8 EB 4 EL G 604(5)	74	LEZU	UIVIATOUZUUUUU	VERIZON FRAME, MANHOLE SB27 542303	N/A
	0ME552000003	ME 24 X 24 X 8 FR 4 FLG 604(5) TY B	74	L29C02	0MA180500000	VERIZON COVER, MANHOLE B27 87028647	N/A
L24SG7 L24SG18	0ME552000002 0ME552000016	ME 24 X 24 BAR GRATE 604(5)  ME 24X24 GR NO CUT CORNERS	74	LE290	0MA180500001	VERIZON FRAME, MANHOLE B27 11048273	N/A
		604(4)		LE326	0MA182000000	VERIZON FRAME, MANHOLE SB30 11000169	N/A
UTILITY AND TELECOMMUNICATION				L32C13	0MA181000000	VERIZON COVER, MANHOLE B30 87028646	N/A
National Grid				LE320	0MA182500000	VERIZON FRAME, MANHOLE	N/A
LE386	0MA228600000	NATIONAL GRID 38 X 6 SQUARE BASE FRAME	77			B30 87028675	

Products listed in cross reference section are not all inclusive of products available. Contact your local EJ representative for more information.





# Notes











## Americas

**800 626 4653** 231 536 2261

231 330 2201

#### EMEA

Europe, Middle East and Africa

+33 (0)344 08 28 00

#### Asia-Pacific

+61 (0)7 3216 5000

East Jordan Iron Works, Inc., East Jordan, Michigan, USA, and its affiliated companies including Norinco in France, Cavanagh in Ireland, McCoy Construction Castings in Canada, and HaveStock in Australia, have been conducting business under one brand, EJ, since 2012.

One global name and brand unifies the company and supports our vision to be the global leader in infrastructure access solutions.

#### EJ

1125 Pearl Street Brockton, MA 02301 508 586 3130 tel 508 580 2740 fax us.sales@ejco.com Registered Mark(s)

