




ZEMS6000AV-HET



Accessories

□-FM12 Floor Mount 12" Rough In
□-YJ Split Ring Pipe Support
□-YK Solid Ring Pipe Support
□-YO Bumper on Angle Stop
□-____ Other

Power Supply Choices (Sold Separately)

□-ACA-BA 6VDC Plug-in Power Converter (Up to 6 valves)
□-HW6 Hardwired Power Converter (Up to 8 Valves)

□ -MJ Mini Junction Box

Architectural/Engineering Approval

The information contained in this document is subject to change without notice.

Please contact Zurn for most up to date information.

NOTE: MUST USE EITHER ZURN P6000-HW6 HARDWIRE POWER CONVERTER OR ZURN P6900-ACA-BA PLUG-IN POWER CONVERTER TO ENSURE PROPER OPERATION. USING A POWER CONVERTER OTHER THAN ZURN MAY RESULT IN OPERATION MALFUNCTION OR UNIT FAILURE.

ZURN INDUSTRIES, LLC. ♦ COMMERCIAL BRASS OPERATION 5900 ELWIN BUCHANAN DRIVE ♦ SANFORD NC 27330

Phone: 1-800-997-3876 ♦ Fax: 919-775-3541

www.zurn.com

In Canada: ZURN INDUSTRIES LIMITED

3544 Nashua Drive ♦ Mississauga, Ontario L4V1L2

Phone: 905-405-8272 Fax: 905-405-1292

ENGINEERING SPECIFICATIONS

Exposed, quiet diaphragm-type, chrome plated flushometer valve with a polished exterior.

Zurn's AquaVantage® TPE diaphragm

Clog Resistant by-pass Chloramine resistant Dual seal

- Proprietary DR resistant low lead brass alloy
- Actuator

ZEMS 6 VDC Motorized Actuator

Automatic Sensor

Fully configurable sensor range adjustment 48 or 168 hour trap seal flush Capacitive sensing push button override

Control Stop

Internal siphon-guard protection Vandal resistant stop cap Sweat solder kit Cast wall flange with set screw

- Vacuum Breaker
 - High back pressure

One piece hex coupling nut

Internal seals

Chloramine resistant

- Adjustable tailpiece
- Spud coupling and flange for top spud connection