PFSH303G Low Flow 1.5 gpm Shower Head



Product Features

- Solid brass swivel connection
- Max. flow rate: 1.5 gpm (5.7 L/min) at 80 psi
- Easy clean rubber nozzles
- cUPC/IAPMO listed
- Uses 40% less water than conventional 2.5 gpm shower heads
- WaterSense® certified



Product Specifications


PFSH303G

Product Numbers

	Gallons Per Minute			
PFSH303G	20 psi	40 psi	60 psi	80 psi
	1.20	1.23	1.35	1.47

Model Numbers

PFSH303GCP	Chrome
PFSH303GBN	Brushed nickel
PFSH303GNORB	Oil rubbed bronze



Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications.

