

Thermostatic Mixing Valve Kit for Eye, Face, and Eye/Face Washes

VALVE FEATURES:

- Includes STW-370, (2) nipple, (1) elbow, (1) mounting bracket and (1) hose
- 9.7 GPM (36.8 L/min) capacity supports most single eyewash and eye/face wash stations @ 30 PSI differential pressure
- 5.2 GPM (19.7 L/min) cold water bypass in case of hot water failure @ 30 PSI differential pressure
- Automatic spring check stops at inlets with flat filter screens
- Maximum working pressure: 125 PSI
- 1/2" NPT female inlets and 1/2" NPT female outlet connections

TEMPERATURE FEATURES:

- Adjustable set point, factory set to 85 °F
- Valve holds to +/- 3 °F
- Valve holds positive shut-off when cold water supply is lost
- Hot water inlet temperature range: 120 °F to 180 °F
- Cold water inlet temperature range: 40 °F to 70 °F
- Outlet water temperature range: 65 °F to 95 °F
- Minimum temperature differential: 10 °F (cold water supply to valve set point)



STANDARDS:

- ASSE 1071 certified (STW-370 only)
- CSA B125.3 certified (STW-370 only)
- NSF 372 certified (STW-370 only)
- cUPC certified (STW-370 only)

WARRANTY:

Visit www.speakman.com for full product warranty information

- 3 Year Limited Warranty (commercial)



1. All dimensions are in inches (millimeters) unless otherwise specified and are subject to change without notice. 2. Before mounting, verify the supply hose will reach the connection.

Architect/Engineer Approval Space:

SPEAKMAN
400 ANCHOR MILL ROAD
NEW CASTLE, DE 19720

P: 800-537-2107
F: 800-977-2747
W: WWW.SPEAKMAN.COM
R: 01-AUGUST 2018