



Blackburn®

Ground Rod Clamps
T&B Catalog Number:

UPC Number: G6
Status: 78378680068
Description: Active

Ground Rod Clamps Type G - Budget-Line, Rod Size 3/4, Wire Range 10 Sol. - 2 Str.

Features

Cast of high-strength corrosion-resistant copper alloy. UL listed for direct burial.

Furnished with hex head bolts. Simplified, compact design makes lasting, trouble-free connection.

General

Style	Type G - Budget-Line
Material	Copper
Wire Range	10 Sol. - 2 Str.
Thread Size	3/8 - 16 UNC-2A
Ground Rod	3/4

Dimension Information

B (inches)	1 1/16
C (inches)	3/8
D (inches)	13/16
E (inches)	1/2

Packaging

T&B Inner Pack	50
Package in Units	400
T&B Sold in UOM	Each
T&B Weight Per UOM	11 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000478
Overview	Available on Website

Notes

Add suffix P to Catalog number for tin-plated clamp.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321

