GMLighting

XENON UNDERCABINET ACCENT LIGHTING - 12V XENON

Project:	
•	
Fixture Type: ——	
Location:	
Contact Phone:	

PRODUCT DESCRIPTION

GM Lighting's Xenon Undercabinet Accent Lighting puck is a 2-7/8" diameter surface or recessed mounted luminaire available in white, black, chrome, brushed nickel and bronze.

PRODUCT SPECIFICATIONS

Fixture Construction: Two-piece, low profile (1" height) steel surface mount ring with matching lens holder that allows for either surface mount or recessed mounting. Frosted lens included.

Electrical: Single puck comes with 48" stripped leads. Select transformer from remote transformer page of catalog. Catalog is available for download at www.gmlighting.net

Lens: Tempered frosted glass lens affixed to lens holder.


Installation: See installation diagram below. NOTE: For recessed, cut 2-3/8" hole.

Lamp: G4 12V Xenon.


Label: UL listed. File E180625

3-light kit available. See www.gmlighting.net






Surface mount diagram



Recessed mount diagram



ORDERING INFORMATION

Cat. No.	Watts	Color	Dimensions
XP20-W	20W	White	2-7/8" x 1"
XP20-B	20W	Black	2-7/8" x 1"
XP20-C	20W	Chrome	2-7/8" x 1"
XP20-BNK	20W	Brushed Nickel	2-7/8" x 1"
XP20-BZ	20W	Bronze	2-7/8" x 1"





9830 W. 190th Street • Unit F • Mokena, IL 60448 • www.gmlighting.net Toll-Free: (866) 671-0811 FAX: (708) 478-2640

e-mail: gmlightingllc@sbcglobal.net • Specifications subject to change without notice. 12Vxenonpuck_112712