Retail Catalog

NEBO

IGLany PRO

ILLUMINATE YOUR WORLD



FEATURING THE RECHARGEABLE BIG LARRY PRO

See page 2-3

NEW from NEBO

the leader in lighting innovation

We are pleased to present to you the latest in innovative lighting from NEBO. These new items represent a broad cross section of lighting types – all featuring the most advanced design and engineering created by NEBO's product development & design team. This season's new product line-up includes a total of eight new lights, each with unique features that meet the needs of today's varied and active lifestyles.





PoPPY

300 lumen lantern and 120 lumen spot light, all in one tough compact design. Perfect for indoors or outdoors, the Poppy features an adjustable handle for easy mobility.

BIG Larry PRO

500 lumens, *FULLY RECHARGEABLE* and equipped with 2 magnetic charging stations, the BIG Larry[™] PRO is ready to handle any task at any time.

Our new lights include the versatile *PoPPY Lantern & Spot Light*, the bug-zapping *Z-Bug Lantern + Light*, the flickering *Old Red Lantern*, the rechargeable *BIG Larry PRO*, and the powerful *REDLINE V* flashlight. Also, the new line-up includes the *Contemporary Flipit* (a new version of the popular original Flipit), our newest pocket light called the *POPLITE* and the rechargeable *ARC500 Pro Bike Light*. With so many new lights, NEBO has a light for every one of your customers.

Z-Bug Lantern + Light

90

REDLINE V

Redefining the REDLINE series, the REDLINE

V features 5 light modes, 500 lumens and

a powerful magnetic base for convenient

hands-free lighting.

The next line of bug defense is Z-Bug Lantern + Light. Equipped with bug-attracting UV LEDs and a 360° bug-zapping electric grid, this lantern & spot light combo will keep your outdoor excursions enjoyable and bug free!



OBUG

10

POPLITE This personal sized light features an expandable design, which allows the POPLITE to easily change from spot light to

lantern.



pg, 1 C

Old Red Lantern

Traditional oil lantern style with realistic flickering flame, the Old Red is a 100 lumen LED lantern that brings classic charm and warm, inviting light.



ARC500 Pro Bike Light

This **RECHARGEABLE** 500 lumen bike light features signature ARCUS technology that allows you to see and be seen.







@NEBOTOOLS









The BRIGHTEST Larry yet...The BIG Larry[®] PRO features a high-power, **500 lumen** C·O·B work light and red hazard flasher. **Fully rechargeable** and equipped with 2 magnetic charging stations, the BIG Larry[®] PRO is ready to handle any task at any time. The PRO also has a powerful magnetic base and adjustable steel clip for convenient hands-free lighting. When there is work to be done...bring a PRO!



EBO **3 LIGHT MODES** • HIGH (500 lumens) - 4.5 hours / 37 meters • Red (45 lumens) - 8 hours / 13 meters • Red hazard flasher - 24 hours / 13 meters BIG Anny P DESIGN • Fully dimmable • Direct-to-Red • Anodized aircraft-grade aluminum; water and impact-resistant Adjustable clip • Powerful magnetic base OPERATION • Top-positioned, ON/OFF button ACCESSORIES • Two magnetic charging stations and cables BATTERIES • Powered by 1 Li-ion rechargeable battery (included) (Recharge time: 5 - 6 hours) SPECS • 0.8 lbs. JUST • (H) 7.75" x (W) 1.1875" x (D) 1.375" DOCK TO EIG CHARGE 2 Magnetic PA ways to charge! When there is work to be done....Bring a PRO! HIP TECH A new innovation in LED technology, C+O+B features smaller, easier clustered LED chips that work together as one lighting module. Because of this design, C·O·B outperforms traditional lighting with







UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397931959	6640	BIG Larry® PRO Power Work Light	34.99	12 PIECES

- Display holds 6 pieces in gift boxes front display gift box is open for TRY ME.
- Each BIG Larry[®] Pro comes with a gift box.

Display Dimensions (H) 15.5" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions (H) 7.75" x (W) 1.5625" x (D) 1.325"





The REDLINE® V is a powerful, 500 lumen flashlight, featuring OC[™] optics. The REDLINE® V is completely waterproof (IPX7) and is also equipped with a steel clip, powerful magnetic base, 4x zoom and 5 light modes (high, medium, low, defensive strobe & S.O.S.).



5 LIGHT MODES

- High (500 lumens) 2.5 hours / 170 meters
- Medium (200 lumens) 6 hours / 110 meters
- Low (50 lumens) 22 hours / 50 meters
- Strobe (500 lumens) 6 hours
- S.O.S. (500 lumens) 48 hours

DESIGN

- Convex lens
- Tactical edge
- 4x adjustable zoom • Signature Red Ring®
- Anodized aircraft-grade aluminum; waterproof (IPX7) and impact-resistant
- Steel belt/pocket clip
- Powerful magnetic base

OPERATION

• Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

• Powered by 3 AAA batteries (included)

SPECS

• 0.35 lbs.

- Length: Compacted: 5" / Extended: 5.5"
 Diameter: (Head) 1.375" / (Barrel) 1.25"

U.S. PATENT

• 659,869 S



The OC[™] (Optimized Clarity) Technology creates a perfectly dispersed beam of intense, pristine light that is as bright on the edge as it is in the center when used in flood mode.









UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397931942	6639	REDLINE® V 500 Lumen Flashlight	24.99	16 PIECES

NEBO° SLÝDE+

The SLYDE[™]+ is equipped with programmable memory settings for each light mode, a new C·O·B red light function, a 4x adjustable zoom and instant slide on. And best of all? With all these new great features, the new SLYDE™+ is still the same price!

NEBO[®] SLÝDE KING

of all...it's **rechargeable!**

NEBO

SUNDE



- Convex lens
- Tactical edge
- 4x adjustable zoom
- Fully dimmable
- Direct-to-Red Feature (hold button and slide open)
- Memory Power Setting
- Powerful magnetic base
- Anodized aircraft-grade aluminum; weather-proof (IPX4) and impact-resistant

OPERATION

- Side-positioned, ON/OFF button; hold to dim • C•O•B Work Light automatically turns ON when opened and OFF when closed
- BATTERIES
- Powered by 4 AAA batteries (included)

SPECS • 0.7 lbs

- Length: Compacted: 7.25" / Extended: 9.5" • Diameter: (Head) 1.625" / (Barrel) 1.375"
- U.S. PATENT • D 786,466 S



Display Dimensions
(H) 11.75" x (W) 7.25" x (D) 7.75"

Gift Box Dimensions (H) 6.825" x (W) 1.75" x (D) 1.75"









NEBO



• Fully rechargeable Tactical edge Convex lens • 4x adjustable zoom • Fully dimmable

DESIGN

- water and impact-resistant
- Powerful magnetic base

OPERATION

BATTERIES

ACCESSORIES

SPECS • 0.8 lbs.

U.S. PATENT • D 786,466 S

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397931249	6525	SLYDE™+ with Display	29.99	16 PIECES	645397930884	6434	SLYDE™ KING with Display	39.99	12 PIECES
645397931935	6618	SLYDE™+ - Bulk Camo	29.99	8 PIECES	645397931973	6643	SLYDE™ KING - Bulk Camo	39.99	8 PIECES



With all of the features that you would expect from a SLYDE...and more! The SLYDE™ KING is equipped with programmable memory settings for each light mode, a new C·O·B red light function, a 4x adjustable zoom and best

4 LIGHT MODES

• Flashlight (330 lumens) - 2 hours / 123 meters • C·O·B work light (250 lumens) - 4.25 hours / 22 meters • Red light (40 lumens) - 4.75 hours / 7 meters • Red flash - 24 hours

- Memory Power Setting Anodized aircraft-grade aluminum;

• Side-positioned ON/OFF button • Work light automatically turns ON when opened

• Powered by 1 Li-ion rechargeable battery included (3-4 hour recharge time)

• Micro USB to USB cable included

• Length: Compacted: 6.875" / Extended: 9" • Diameter: (Head) 1.75" / (Barrel) 1.25"











NEBO° **POP**LITE

The new NEBO POPLITE is a versatile, compact light and lantern. Its expandable design allows the POPLITE to easily change from flood light, to spot light, to lantern, by sliding the body of the light. Small enough to fit on a key ring, the POPLITE also features a magnetic base and a detachable carabiner clip. To activate the light, just pop the carabiner clip from the light body and the POPLITE is ready to light the way!



Poppy is a combination 300 lumen C·O·B LED lantern and bright LED spot light. Poppy is the perfect light for indoor or outdoor use when versatility and powerful lighting are critical. With a rubberized impact-resistant body, Poppy is both rugged and soft to the touch. Poppy easily changes from spot light to lantern with just a slide of its top, revealing a full 360° C·O·B lantern. The handle is designed to easily adjust to conveniently serve both light modes.







ON	MSRP	CASE PACK
	16.99	24 PIECES
	16.99	6 PIECES
	16.99	6 PIECES
	16.99	6 PIECES
	16.99	6 PIECES
lay	FREE with 12 piece order	1 PIECE



The next line of bug defense is Z-Bug Lantern + Light. Equipped with bug-attracting NUV LEDs and a 360° bug-zapping electric grid, this lantern & spot light combo will keep your outdoor excursions enjoyable and bug free! The handle easily adjusts to conveniently serve both light modes. Z-Bug[™] Lantern + Light includes Z-Bug Bulb[™] Sweeper to remove insect remains from the grid housing.

NEBO°

For use indoors or outdoors, Z-Bug Bulb[™] provides bright white, ambient lighting to any space with its 600 lumen LED. The 4 NUV LEDs emit a 395nm near ultraviolet glow, which mosquitoes and other flying insects find very attractive. Surrounding the NUV LEDs is a 1,000 - 1,200V high-voltage grid that kills the allured insects on contact. Z-Bug Bulb™ includes Z-Bug Bulb[™] Sweeper to remove insect remains from the grid housing.









The Larry[®] BOSS, the essential 3-in-1 power work light, features a high-power flashlight, work light and red light. Taking charge of keeping your work space clean, the BOSS is equipped with a recessed 13.5" telescopic magnetic grabber, great for picking up lose screws, nails, nuts and bolts. The Larry[®] BOSS also has a powerful magnetic base for hands-free lighting.

6431 Larry[®] BOSS Power C•O•B Work Light



Equipped with a 120 lumen C·O·B LED work light and a 50 lumen flashlight, The Larry[®] TILT is adaptable for any work environment. The TILT provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. This new design features an **easy-to-activate push button**. Whether you are under the hood, under the sink or just out in the dark, the Larry[®] TILT is the perfect directional pocket work light!



34.99

12 PIECES

645397931300

645397930860

2 LIGHT MODES • Top Light (50 lumens) - 3.5 hours / 27 meters

• Work Light (120 lumens) - 3 hours / 19 meters

DESIGN

- Weather-proof (IPX4) and impact-resistant
- Fully dimmable
- Non-slip compact body design
- Steel belt/pocket clip
- 200° pivoting stand
- Collapsible, hanging hook
- Powerful magnetic base

OPERATION

• NEW rear-positioned ON/OFF button

BATTERIES

• Powered by 2 AAA batteries (included)

SPECS

- 0.15 lbs.
- (H) 6.375" x (W) 1" x (D) 0.75"









ITEM	DESCRIPTION	MSRP	CASE PACK
6539-В	Larry® TILT Directional Pocket Work Light	11.99	24 PIECES



The BIG Larry knows how to light up a room! Equipped with new C·O·B LED technology, the BIG Larry outputs 400 lumens of intense light. Secondary light modes include Low (160 lumens) and the Emergency Red Flash mode. This intense red light is perfect for distress signaling or roadside emergencies. The anodized aluminum body and recessed LED housing ensures that the BIG Larry can handle any situation.



Don't let the name fool you, LiL Larry[®] packs enough power to take its rightful place in the Larry[®] family. Equipped with a 250 lumen C·O·B work light, LiL Larry features 3 light modes: high, low and emergency red flash. The anodized aluminum body and recessed LED housing ensure that LiL Larry is ready for any task. Flex-Fuel[™] allows the LiL Larry to condense in size and operate with 2 AAA batteries instead of 3 AAA.



UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK					
645397930365	6306	BIG Larry® with Display	24.99	14 PIECES	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397930648	6382	BIG Larry® - Bulk Camo	24.99	7 PIECES	645397930570	6373	LiL Larry® with Display	19.99	18 PIECES
645397930679	6384	BIG Larry® - Bulk Black	24.99	7 PIECES	645397931027	6463	LiL Larry® - Bulk Red	19.99	9 PIECES
645397930686	6385	BIG Larry® - Bulk Silver	24.99	7 PIECES	645397931034	6464	LiL Larry® - Bulk Black	19.99	9 PIECES
645397930792	6413	BIG Larry® - Bulk Red	24.99	7 PIECES	645397931041	6465	LiL Larry® - Bulk Silver	19.99	9 PIECES
645397931157	6493	BIG Larry [®] - Bulk Patriotic	24.99	7 PIECES	645397931058	6466	LiL Larry® - Bulk Camo	19.99	9 PIECES
645397930761	6393	BIG Larry [®] Work Light Holster	4.99	7 PIECES	645397931140	6492	LiL Larry® - Bulk Patriotic	19.99	9 PIECES

- **3 LIGHT MODES**
- High (250 lumens) 3 hours / 29 meters
- Low (95 lumens) 10 hours / 17 meters
- Red Flash 10 hours

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Steel clip
- Powerful magnetic base

OPERATION

• Top-positioned, ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)
- Flex-Fuel allows operation with just 2 AAA

SPECS

- 0.2 lbs.
- (H) 6.0625" x (W) 0.625" x (D) 1"

U.S. PATENT

• 8,628,210



#6373 Color Assortment: 4 Red, 4 Silver & 10 Black









NEBO[®] Larryo

The Larry[®] and Lucy[®] are now **BRIGHTER THAN EVER!** Now, equipped with new C+O+B LED technology, the Larry[®]C and Lucy[®]C output **170 lumens** of intense light. The rotating magnetic clip gives you convenient hands-free lighting by attaching to virtually anything. The reinforced plastic body design is water and impact-resistant, making this light basically indestructible.



The brightest flashlight ever created by NEBO is here – the REDLINE BLAST. With 1,400 lumens of high intensity light, this must-have flashlight can throw a spectacularly bright beam over 260 meters. The BLAST is **completely waterproof** and ready for any weather condition. Want more? How about a 4x zoom and 5 light modes (high, medium, low, defensive strobe & flashing beacon).



8.99

8.99

8.99

12 PIECES

12 PIECES

12 PIECES

UPC CODE

645397931331

ITEM

6542 REDLINE® BLAST 1400 Lun

645397930495

645397930501

645397930518

6353 Larry®C - Bulk Yellow

6354 Larry®C - Bulk Camo

6355 Lucy®C - Bulk Pink

5 LIGHT MODES

- High (1400 lumens) 2.5 hours / 260 meters
- Medium (560 lumens) 7 hours / 180 meters
- Low (140 lumens) 30 hours / 90 meters
- Strobe (1400 lumens) 6 hours
- Beacon (200 lumens) 120 hours

- Convex lens
- Tactical edge
- 4x adjustable zoom
- Signature Red Ring®
- Anodized aircraft-grade aluminum;
- waterproof (IPX7) and impact-resistant

• Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

Lanyard (included)

• Powered by 6 AA batteries (included)

- Length: Compacted: 7.25" / Extended: 7.75"
- Diameter: (Head) 1.875" / (Barrel) 1.375"











Gift Box Dimensions (H) 7" x (W) 2" x (D) 1.95"



DESCRIPTION	MSRP	CASE PACK
1400 Lumen Flashlight	39.99	12 PIECES







Don't let the micro size fool you...the Micro REDLINE® OC[™] packs enough power to carry the REDLINE® name. This light is small enough to fit in the palm of your hand, but bright enough for any situation. Equipped with OC[™] Technology the Micro has a perfectly dispersed beam of light while in flood mode. The Micro REDLINE® OC[™]...small never shined so big!

The REDLINE[®] RC[™] with MagDock features a **MagDock magnetic charging station** that docks and charges your REDLINE[®]. Small enough to fit in the palm of your hand, the RC[™] is fully equipped with all of the features that make the REDLINE[®] series so popular.



4 LIGHT MODES

- High (320 lumens) 1 hour / 110 meters
- Medium (125 lumens) 2 hours / 70 meters
- Low (32 lumens) 9 hours / 35 meters
- Strobe (320 lumens) 2 hours / 110 meters

DESIGN

- 4x adjustable zoom Anodized aircraft-grade aluminum;
- water and impact-resistant
- OC[™] Technology
- Convex lens
- Signature Red Ring®
- Steel belt/pocket clip
- Magnetic base
- Protective LED housing
- Charging indicator light




• Side-positioned, ON/OFF button

- ACCESSORIES
- USB to Micro USB cable included
 Lanyard included

BATTERIES

• Internal, rechargeable lithium-ion battery (Recharge time - up to 2 hours)



SPECS0.25 lbs.

Length: Compacted: 3.5625" / Extended: 3.875"
Diameter: 1.25"





Display Dimensions (H) 11.125" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions (H) 4.2" x (W) 2.95" x (D) 2.35"





UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397930754	6392	REDLINE® RC™ with MagDock	39.99	10 PIECES	645397930167	6272-A	Micro REDLINE® OC™ Flashlight	14.99	16 PIECES

- **4 LIGHT MODES**
- High (360 LUX) 6 hours / 76 meters
- Medium (183 LUX) 12 hours / 54 meters
- Low (39 LUX) 15 hours / 25 meters
- Strobe (360 LUX) 12 hours / 76 meters

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- OC[™] Technology
- Convex lens
- Signature Red Ring[®]
- 6x adjustable beam
- Steel belt/pocket clip
- Magnetic base

OPERATION

Rear-positioned, glow-in-the-dark ON/OFF
 button with Soft Touch Technology

BATTERIES

• Powered by 1 CR123A battery (included)

SPECS

- 0.1 lbs.
- Length: Compacted: 2.625" / Extended: 3.15"
- Diameter: (Head) 0.875" / (Barrel) 0.8125"

U.S. PATENT

• 659,869 S













More features...more brightness...same great quality. The SE REDLINE® has 5 lighting modes, separated into two categories, primary and secondary. Turning the flashlight on and off gives you the primary lighting mode, which is 2800 LUX of intense white light. The secondary lighting modes (Medium, Low, S.O.S. and Defensive Strobe) can be activated by holding down the power button for 3 seconds.



the maximum power of this flashlight with 2185 LUX of blinding bright light.



659,869 S









#5557 Display Dimensions (H) 7.25" x (W) 13.1875" x (D) 5" (H) 9.375" x (W) 6.25" x (D) 1.625'

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397312116	5615	SE REDLINE® Flashlight with Display	39.99	14 PIECES	645397401100	5557	REDLINE [®] Flashlight with Display	34.99	14 PIECES
645397914112	5616	SE REDLINE® Flashlight in Clamshell - Gray	39.99	12 PIECES	645397531111	5581	REDLINE [®] Flashlight in Clamshell - Gray	34.99	12 PIECES
645397015123	5638	SE REDLINE® Flashlight - Bulk Black	39.99	18 PIECES	645397122111	5599	REDLINE® Flashlight - Bulk Gray	34.99	18 PIECES
645397067122	5956	SE REDLINE® Flashlight - Bulk Gray	39.99	18 PIECES	645397111115	5610	REDLINE® Flashlight - Bulk Black	34.99	18 PIECES







(H) 9.375" x (W) 6.25" x (D) 1.625"



The ability to bring high-end technology to a compact, fully redesigned, extremely powerful light source is finally here. In an automobile, red-lining means reaching the peak of it's performance; with NEBO® REDLINE® we are harnessing

5 LIGHT MODES

- High (2185 LUX) 4 hours / 187 meters
- Medium (1025 LUX) 8 hours / 128 meters
- Low (225 LUX) 15 hours / 60 meters
- S.O.S. (2185 LUX) 72 hours / 187 meters
 Strobe (2185 LUX) 72 hours / 187 meters

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Convex lens
- Signature Red Ring®
- Tactical edge
- 4x adjustable beam
- Magnetic base

OPERATION

• Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

• Powered by 3 AAA batteries (included)

SPECS

- 0.428 lbs.
- Length: Compacted: 4.34" / Extended: 4.7"
- Diameter: (Head) 1.5" / (Barrel) 1"

U.S. PATENT

• 659,869 S











#5581 Clamshell Dimensions







This fully rechargeable flashlight offers a Smart Select Dial to control the 5 unique light modes, a 4x adjustable beam and a steel clip. The REDLINE Select RC also acts as a **power bank for your USB powered device**.

To improve functionality of the 5 light modes, the REDLINE® Select features a Smart Select Dial to quickly and conveniently choose your light mode while the light is on or off.







Display Dimensions (H) 13.75" x (W) 8.5" x (D) 9"

Acrylic Box Dimensions (H) 9.25" x (W) 3" x (D) 3"

					UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	645397111276	5620	REDLINE® Select Flashlight - Black	49.99	9 PIECES
645397930013	6189	REDLINE [®] Select RC [™] Flashlight	69.99	6 PIECES	645397066125	5955	REDLINE® Select Flashlight - Titanium	49.99	9 PIECES

AVAILABLE COLORS

Black

Titanium

5 LIGHT MODES

- High (2950 LUX) 2 hours / 198 meters
 Medium (1230 LUX) 5 hours / 96 meters
- Low (305 LUX) 12 hours / 37 meters
- S.O.S. (2950 LUX) 60 hours / 198 meters • Strobe (2950 LUX) - 60 hours / 198 meters

DESIGN

- Anodized aircraft-grade aluminum;
- water and impact-resistant
- Convex lens • Signature Red Ring®
- Tactical edge
- 4x adjustable beam
- Steel belt/pocket clip
- Magnetic base
- Low battery indicator

OPERATION

• Rear-positioned, glow-in-the-dark ON/OFF button with Smart Select Dial

ACCESSORIES

Lanyard included

BATTERIES

• Powered by 3 AAA batteries (included)

SPECS

- 0.7 lbs.
- Length: Compacted: 4.6875" / Extended: 5"
 Diameter: (Head) 1.5" / (Barrel) 1"

U.S. PATENT

• 659,869 S













The REDLINE® OC[™] outputs 600 LUX of pristine white light. 600 LUX is bright, but what makes the OC[™] so special is the OC[™] (Optimized Clarity) Technology that creates a perfectly dispersed beam of light while in flood mode.



Another addition to the REDLINE® OC[™] lineup is the Classic REDLINE® OC[™]. Maintaining some of the key features as it's predecessor, the Classic also features an intense power upgrade...2640 LUX to be exact.



2 LIGHT MODES

- Steady ON (600 LUX) 2 hours / 92 meters • Strobe (600 LUX) - 4.5 hours / 92 meters

DESIGN

- Anodized aircraft-grade aluminum;
- water and impact-resistant
- OC[™] Technology Convex lens
- Signature Red Ring®
- Tactical edge
- 6x adjustable beam

OPERATION

• Dual-direction belt/pocket clip • Magnetic base

with Soft Touch Technology









• Length: Compacted: 4.1825" / Extended: 4.75" • Diameter: (Head) 1.375" / (Barrel) 1"

• Rear-positioned, glow-in-the-dark ON/OFF button

U.S. PATENT • 659,869 S



Display Dimensions (H) 8" x (W) 7.5" x (D) 8.25"

		D
(H) 7.	12

UPC CODE	ITEM DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397929499	6092 REDLINE® OC™ Flashlight	19.99	16 PIECES	645397930174	6273	Classic REDLINE® OC™ Flashlight	29.99	12 PIECES

5 LIGHT MODES

- High (2640 LUX) 2.5 hours / 206 meters
 Medium (1226 LUX) 6.5 hours / 140 meters
- Low (476 LUX) 20 hours / 87 meters
- Strobe (2640 LUX) 24 hours / 206 meters
- S.O.S. (2640 LUX) 24 hours / 206 meters

DESIGN

- Anodized aircraft-grade aluminum;
- water and impact-resistant
- OC[™] Technology
- Convex lens
- Signature Red Ring®
- Tactical edge
- 6x adjustable beam • Dual-direction belt/pocket clip
- Magnetic base

OPERATION

• Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

• Powered by 3 AAA batteries (included)

SPECS

- 0.32 lbs.
- Length: Compacted: 4.5" / Extended: 4.75"
 Diameter: (Head) 1.5" / (Barrel) 1"

U.S. PATENT

• 659,869 S











NEBO° TWYSTZ

The TWYST®Z is a a high-power work light, lantern and flashlight, all in one! The TWYST®Z features a 4x adjustable zoom and a powerful magnetic base that provides convenient hands-free lighting. TWYST®Z...shaping light like never before!

NEBO° CRYKET

The NEBO® CRYKET[™] is a versatile 3-in-1 LED light, featuring a 240 lumen C·O·B work light, a bright 250 lumen spot light and an intense red or areen light. Its unique swivel design allows the light's head to rotate into a forward-facing light, perfect for various working conditions. The magnetic base and steel clip provide convenient hands-free lighting.



3 LIGHT MODES

• C·O·B Work Light (75 lumens) - 10 hours / 11 meters • C·O·B Lantern (200 lumens) - 2 hours / 13 meters



• Flashlight (200 lumens) - 2 hours / 107 meters



- DESIGN • 4x adjustable zoom
- ARCUS C·O·B LED Technology
- Tactical edge
- Fully dimmable beam
- Anodized aircraft-grade aluminum;
- water and impact-resistant Powerful magnetic base



OPERATION • Side-positioned ON/OFF button

BATTERIES • Powered by 4 AAA batteries (included)

SPECS

• 0.55 lbs. • Length: Compacted: 6.3125" / Extended: 6.75" • Diameter: (Head) 1.75" / (Barrel) 1"







Display Dimensions (H) 8.5" x (W) 9.25" x (D) 7"

Gift Box Dimensions (H) 6.5" x (W) 1.875" x (D) 1.875"





Smoke Gray Camo

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397930563	6372	TWYST®Z with Display	29.99	16 PIECES	645397930914	6437	CRYKET™ with Display	24.99	16 PIECES
645397930907	6436	TWYST®Z - Bulk Black	29.99	12 PIECES	645397931393	6549	CRYKET [™] - Bulk Camo	24.99	12 PIECES

3 LIGHT MODES

• Spot Light (250 lumens) - 3.5 hours / 113 meters • C·O·B Flood Light (240 lumens) - 2.75 hours / 21 meters • Red (15 lumens) - 6.5 hours / 6 meters Green (30 lumens) - 3 hours / 8 meters [#6549 Camo]

DESIGN

- Fully dimmable
- Anodized aircraft-grade aluminum; water and impact-resistant
- 90° swivel head
- Power memory setting
- Direct-to-red feature
- Steel belt/pocket clip
- Powerful magnetic base
- Rubberized non-slip grip

OPERATION

• Top-positioned, ON/OFF button

BATTERIES

• Powered by 4 AAA batteries (included)


SPECS

- 0.3 lbs.
- (H) 4.825" x (W) 1.625"

PATENT PENDING











NEBO **WORK**BRITE®

The WORKBRITE 2[™] adapts to your work environment, making it the handiest of work lights. Equipped with a 200 lumen C·O·B LED work light, the WORKBRITE 2[™] also features a 100 lumen flashlight and a rear, emergency red flasher LED. The WORKBRITE 2[™] provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. Whether you are under the hood, under the sink or just out in the dark, the WORKBRITE 2[™] works great for any application.

NEBO THE**rechargeable WORK**BRITE®

Never worry about replacing batteries again, with The **RECHARGEABLE** WORKBRITE 2[™]. This work light is equipped with a 220 lumen C·O·B LED work light, a 120 lumen flashlight and a rear, emergency red flasher LED. The WORKBRITE 2[™] provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. Whether you are under the hood, under the sink or just out in the dark, the WORKBRITE 2^{M} works great for any application.



UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397930341	6304	WORKBRITE 2 [™] C•O•B LED Work Light	19.99	12 PIECES	645397930358	6305	The Rechargeable WORKBRITE 2™	29.99	12 PIECES

















The NEBO® Contemporary Flipit is a 240 lumen C·O·B LED light that operates like a standard household light rocker switch. Flipit includes hook & loop double-sided tape and 2 magnets for two easy mounting options, as well as a drywall screw hole for permanent mounting. The Flipit is powered by 3 AAA batteries (included). Each package contains 2 Contemporary Flipit portable LED lights.



UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	_	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397931539	6558 C	Contemporary Flipit™ Portable Work Light	14.99	24 PIECES	_	645397931225	6523	Flipit™ Portable Work Light	14.99	24 PIECES

NEBO°

Flipit Bright light where you need it.

package contains 2 Flipit portable LED lights.



NEBO Flipit is a 215 lumen C·O·B LED that operates like a standard household light switch. No wires, no tools and no fuss! There are 3 ways to attach it: 2 hook and loop tabs, 2 magnets or 2 screw holes (for permanent mounting). Each





NEBO



Designed for iPhone 6/6S, 6/6S Plus, 7 & 7 Plus





The NEBO® CaseBrite[™] offers more than just protection for your mobile device. The CaseBrite[™] features a high-power, 200 lumen C+O+B flashlight that is up to 400% brighter than a standard smart phone light. Designed specifically to not draw from your phone's battery, each CaseBrite[™] is independently powered by an internal, rechargeable lithium-ion battery.

The NEBO® CaseBrite[™] offers more than just protection for your mobile device. The CaseBrite[™] features a high-power, 200 lumen C·O·B flashlight that is up to 12x brighter than a standard smart phone light. Designed specifically to not draw from your phone's battery, each CaseBrite[™] is independently powered by an internal, rechargeable lithium-ion battery.




3 LIGHT MODES

- High (200 lumens) 3 hours / 30 meters
- Low (20 lumens) 24 hours
- Strobe (200 lumens) 7 hours



DESIGN

- Impact-resistant, non-slip rubber case • Screen protection lip
- Fully dimmable
- Slim 15mm profile
- Battery life indicator
- Fits iPhone 6/6S, 6/6S Plus, 7 & 7 Plus



- ACCESSORIES • USB to Micro USB charging cable (included)

BATTERIES

• Internal, rechargeable lithium-ion battery (Recharge time - up to 3 hours)



• 0.2 lbs

• **6/6S** - (H) 5.5" x (W) 2.75" x (D) 0.6" • 6/6S Plus - (H) 6.3125" x (W) 3.125" x (D) 0.6"







#6349 Display Dimensions	
(H) 12.5" x (Ŵ) 10" x (D) 9.25"	

Box Dimensions (6/6S/7) (H) 6.75" x (W) 4.375" x (D) 1"

Box Dimensions (6, 65 & 7 Plus) (H) 7.5" x (W) 4.375" x (D) 1"

*7 & 7 Plus Available September 2017

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397930433	6347	CaseBrite™ iPhone 6/6S - Black	39.99	4 PIECES
645397930440	6348	CaseBrite™ iPhone 6/6S Plus - Black	39.99	4 PIECES
645397930693	6386	CaseBrite™ iPhone 6/6S - White	39.99	4 PIECES
645397930709	6387	CaseBrite™ iPhone 6/6S Plus - White	39.99	4 PIECES
645397931997	6647	CaseBrite™ iPhone 7 - Black	39.99	4 PIECES
645397932000	6648	CaseBrite™ iPhone 7 Plus - Black	39.99	4 PIECES
645397932017	6649	CaseBrite™ iPhone 7 - White	39.99	4 PIECES
645397932024	6650	CaseBrite™ iPhone 7 Plus - White	39.99	4 PIECES
645397930457	6349	CaseBrite™ Countertop Display	FREE with 12 piece order	1 PIECE

(H)	12
#65	

UPC CODE	ITEM	DESCRIPTION
645397931201	6513	CaseBrite™ Samsung Galaxy S7
645397930457	6349	CaseBrite [™] Countertop Display

Designed for Samsung Galaxy S7



- **3 LIGHT MODES**
- 100% (200 lumens) 2.25 hours
- 10% (20 lumens) 20 hours
- Strobe (200 lumens) 6 hours

DESIGN

- Impact-resistant, non-slip rubber case
- Screen protection lip
- Fully dimmable
- Slim 15mm profile
- Battery life indicator
- Fits Samsung Galaxy S7

OPERATION

• Rear-positioned, ON/OFF button

ACCESSORIES

• USB to Micro USB charging cable (included)

BATTERIES

• Internal, rechargeable lithium-ion battery (Recharge time - up to 3 hours)

SPECS

- 0.2 lbs.
- Galaxy S7 (H) 5.75" x (W) 2.875" x (D) 0.59"











MSRP 39.99 FREE with 12 piece order

CASE PACK 4 PIECES 1 PIECE







The ARC500 Rechargeable Bike Light features 2 independently controlled light sources - a 500 lumen spot light and a 120 lumen C+O+B flood light. The C+O+B flood light covers 250° using **ARCUS LED Technology**, which allows the user to be visible from multiple angles, enhancing the user's safety.

multiple angles, enhancing the user's safety.







2 LIGHT MODES - SPOT LIGHT • High (500 lumens) - 2.5 hours / 188 meters

- Low (170 lumens) 3.25 hours / 105 meters
- 4 LIGHT MODES C·O·B FLOOD LIGHT
- High (120 lumens) 4.5 hours / 18 meters
 Low (60 lumens) 7.5 hours / 13 meters
- Day Flash 30 hours / 7 meters
- Night Flash 6 hours / 14 meters



DESIGN

- Fully rechargeable • Water and impact-resistant
- Mount allows light to swivel 90°
- Tool-free universal mounting system
- Quick-release mount design
- Battery / power indicator

OPERATION

• Top-positioned, independently controlled ON/OFF buttons for spot and flood light

ACCESSORIES • USB to Micro USB charging cable (included)

BATTERIES


• Internal, rechargeable lithium-ion battery (Recharge time: 2 - 4 hours)

SPECS

• 0.4 lbs. • (H) 4.825" x (W) 1.625"







and comes with an instruction manual



ARCUS is a new proprietary C.O.B LED technology that shapes light like never before with 250° of intense light coverage for maximum safety.





Dimensions

Available August 2017

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION
645397931966	6641	ARC500 Rechargeable Bike Light	39.99	6 PIECES	 645397931218	6514	ARC250 Pro Bike Light

The ARC250 Pro Bike Light features 2 independently controlled light sources, a 250 lumen spot light and a 115 lumen C•O•B flood light. The C•O•B flood light covers 250° using **ARCUS LED Technology**, which allows the user to be visible from

2 LIGHT MODES - SPOT LIGHT • High (250 lumens) - 9 hours / 133 meters • Low (120 lumens) - 15 hours / 86 meters

4 LIGHT MODES - C·O·B FLOOD LIGHT • High (115 lumens) - 14 hours / 15 meters • Low (60 lumens) - 23 hours / 11 meters • Day Flash (15 lumens) - 24 hours / 15 meters • Night Flash (15 lumens) - 15 hours / 15 meters

DESIGN

- Water and impact-resistant
- Mount allows light to swivel 90°
- Tool-free universal mounting system
- Quick-release mount design
- Battery / power indicator

OPERATION

• Top-positioned, independently controlled ON/OFF buttons for spot and flood light

BATTERIES

• Powered by 3 AA batteries (included)

SPECS

- 0.4 lbs.
- (H) 4.825" x (W) 1.625"











NEBO[®] DUO ²⁵⁰⁺ LUMEN HEADLAMP

The NEBO® DUO Headlamp is an all-powerful, hands-free lighting solution. The push button on/off button allows you to easily cycle through the FOUR light modes: one white LED (250 Lumens), 2 C·O·B strips (80 Lumens) or 2 RED C·O·B strips in steady or beacon mode. The red LED is a low-signature light, which ensures stealth in the dark, enhances night vision and makes reading in little to no light possible. Its signature 2 strip C·O·B design fully illuminates your immediate area with its wide flood beam. The DUO Headlamp is tough, reliable, lightweight and completely shock-proof.



The NEBO® 90 Lumen Head Lamp is a powerful and convenient hands-free lighting solution. The head tilts 90° to direct light exactly where you need it and the adjustable strap provides a sure fit for any size.



Red C·O·B (10 lumens) - 8 hours / 4 meters Red Beacon - 48 hours / visible over 1 mile

4 LIGHT MODES

DESIGN




Fully dimmable

• Water and impact-resistant durable housing

Spot Light (250 lumens) - 3.5 hours / 122 meters
C·O·B Flood Light (80 lumens) - 7 hours / 13 meters

- 90° tilt
 Power memory setting
- Direct-to-red feature
- OPERATION
- Top-positioned, ON/OFF button



- BATTERIES
- Powered by 3 AAA batteries (included)

SPECS • 0.2 lbs.







Display Dimensions (H) 12.5" x (W) 6.625" x (D) 10"

Clamshell Dimensions (H) 6.125" x (W) 5.25" x (D) 3"

 UPC CODE
 ITEM
 DESCRIPTION
 MSRP
 CASE PACK
 UPC CODE
 ITEM
 DESCRIPTION

 645397930983
 6444
 DUO 250+ Lumen Headlamp
 24.99
 12 PIECES
 645397929215
 6003
 90 Lumen Head Lamp

3 LIGHT MODES • White (90 lumens) - 9 hours / 100 meters • Red (8 lumens) - 150 hours / 3 meters • Red Flash (8 lumens) - 250 hours / 3 meters

DESIGN

- Reinforced plastic;
- water and impact-resistant
- 90° tilt
- Adjustable head strap

OPERATION

• Top-positioned ON/OFF button

BATTERIES

• Powered by 3 AAA batteries (included)

SPECS

0.225 lbs.One size fits all; adjustable fit









Clamshell Dimensions (H) 7.25" x (W) 4.45" x (D) 2.875"


ON	MSRP	CASE PACK	
	16.99	6 PIECES	

LUMO

Compact, handy and bright...the LUMO® Clip Light is the perfect "whatever you need it to be" light. Key chain light, purse light, backpack light, book light...the possibilities are endless. This compact 25 lumen light comes with a carabiner attachment to clip anywhere you need. The white top of the LUMO® is a diffuser dome that helps spread the light evenly to create a more omnidirectional light source. LUMO® Clip Light... the brilliant clip light!

LUMORE

Introducing the latest in ultimate versatile lighting...the LUMORE[™]. This brilliant clip light features a 25 lumen LED. Surrounding the LED is a dome, which doubles the features of the light output. The dome acts as a diffuser to create ambient light, while a small hole allows light to shine through for standard flashlight use. The LUMORE[™] is equipped with a flat base and a rotating clip to provide convenient hands-free lighting in two different ways.



UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397929529	6095	LUMO [®] 25 Lumen Clip Light	5.99	48 PIECES	645397930426	6329	LUMORE™ Dome Light and Flashlight	5.99	48 PIECES
645397929864	6157	LUMO [®] 25 Lumen Clip Light - Bulk Red	5.99	12 PIECES	645397930525	6357	LUMORE [™] - Bulk White	5.99	12 PIECES
645397929871	6158	LUMO [®] 25 Lumen Clip Light - Bulk Silver	5.99	12 PIECES	645397930532	6358	LUMORE [™] - Bulk Red	5.99	12 PIECES
645397929888	6159	LUMO [®] 25 Lumen Clip Light - Bulk Blue	5.99	12 PIECES	645397930549	6359	LUMORE™ - Bulk Blue	5.99	12 PIECES
645397929895	6160	LUMO [®] 25 Lumen Clip Light - Bulk Black	5.99	12 PIECES	645397930556	6360	LUMORE [™] - Bulk Green	5.99	12 PIECES

- **3 LIGHT MODES**
- High (25 lumens) 1 hour / 9 meters
- Low (10 lumens) 3.5 hours / 6 meters
- Strobe 4.5 hours / 9 meters

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Carabiner clip
- Glow-in-the-dark button
- Diffuser dome
- · Dinoser donie

OPERATION

• Rear-positioned ON/OFF button

BATTERIES

• Powered by 3 LR44 batteries (included)

SPECS

- 0.2 lbs.
- (H) 3.625" x (W) 0.75"









#6329 Color Assortment: 12 of each color

NEBO[®] **TWIN PUCKS**

Twin Pucks features a task light and an emergency beacon all-in-one. Both lights attach magnetically to each other, but can also operate independently and are separately powered. The task light provides hands-free lighting in three different ways: 180° adjustable stand, hanging hole or the magnetic base. The emergency beacon works perfectly for roadside hazard lighting, and each puck has a magnet to adhere to metal surfaces...PERFECT FOR ANY CAR!

NEBO[®] TEMPRA

Not just for the professional, the TEMPRA[™] can help save time and money at work, around the house or in the car.



UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397930747	6391 Twi	n Pucks Task Light & Emergency Beacon	19.99	12 PIECES	645397930877	6433	TEMPRA [™] IR Surface Thermometer & Light	49.99	8 PIECES

Use the laser-guided infrared thermometer to make sure your car engine is firing on all cylinders. Check your HVAC to ensure your home is cooling and heating efficiently. The TEMPRA[™], just one more way NEBO® helps get the job done.

2 LIGHT MODES • High (1340 LUX/130 lumens) - 3.5 hours / 146 meters Low (650 LUX/65 lumens) - 7 hours / 102 meters

• 4x adjustable zoom • Infrared lens • Red laser guide for accurate temperature reading Backlit LCD Adjustable emissivity for different surface materials • Fahrenheit/Celsius conversion • Ergonomic handle · Low battery indicator Data hold function

TEMPERATURE RANGE

• -4°F - 716°F (-20°C - 380°C)

OPERATION

• Back-positioned ON/OFF button for spot light • Trigger for laser and temperature scan

• Powered by 4 AA batteries (included)

• (H) 7.625" x (W) 2" x (D) 4.25"









EMP



Display Dimensions (H) 13.2" x (W) 7" x (D) 7.75"

Gift Box Dimensions (H) 9.3" x (W) 5.55" x (D) 2.25"

NEBO° TRANSPØRT



The TRANSPORT[™] is a compact, *rechargeable* flashlight that provides powerful bright light at your fingertips! The TRANSPORT[™] is compatible with any DC 12V socket. Just plug directly into your car, truck, boat or any other 12V outlet. Ideal for travel, the TRANSPORT[™] conveniently fits in your pocket, purse or briefcase.

NEBO[®] BENDBRITE

bright light right where you need it!



									9
UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK					
645397930396	6311	TRANSPORT™ with Display	19.99	18 PIECES					
645397931065	6467	TRANSPORT™ - Bulk Black	19.99	6 PIECES	UPC CODE	ITEM	DESCRIPTION	MSRP	
645397931072	6468	TRANSPORT [™] - Bulk Silver	19.99	6 PIECES	645397900306	5423	BENDBRITE™ Hands-Free Flex Light	9.99	

The BENDBRITE[™] Hands-Free Flex-Light is a unique and innovative source of no-hassle lighting, perfect for any situation. The BENDBRITE[™] is equipped with a magnetic clip base, giving it the ability to attach to virtually any surface. BENDBRITE[™],







Some of the first tactical flashlights in the NEBO® line up, the EDGE series. Equipped with tactical edges, rear-positioned ON/OFF buttons and strong, compact body designs, the EDGE[™] series is all that you need in a tactical flashlight.

NEBO° OOM JOINT STOLUX

Let's admit it, everyone has that cheap-o plastic flashlight in the drawer that barely holds a candle to...well, a candle. Here's to the new and more reliable solution for your flashlight drawer...the NEBO® ZOOM[™].









water and impact-resistant Removable tactical edge

#5872 EDGE 90[™]

Dual-direction steel belt/pocket clip
Rear-positioned ON/OFF button

water and impact-resistant

Rear-positioned ON/OFF button

• Powered by 1 AA battery (included)

• Anodized aircraft-grade aluminum;

• Powered by 1 AA battery (included)

water and impact-resistant Removable tactical edge Steel belt/pocket clip

Rear-positioned ON/OFF button

• High-power 90 lumen LED with Defensive Strobe

• Powered by 1 AA battery (included)

SPECS

• (#5519/#5872) 0.179 lbs. / (#6085) 0.2lbs. • (#5519/#5872) 3.75" x 0.75" / (#6085) 4.56" x 0.875"







#5519/#5872 Display Dimensions (H) 7" x (W) 7" x (D) 5.375'

#5519 Color Assortment: 12 gray / 12 black

#6085 Display Dimensions (H) 8" x (W) 7.5" x (D) 8.25"

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	
645397900702	5519	EDGE™ 50 Lumen Flashlight	9.99	24 PIECES	
645397107125	5872	EDGE™ 90 Lumen Flashlight	12.99	24 PIECES	UPC CODE
645397929475	6085	EDGE™ 200 Lumen Flashlight	15.99	20 PIECES	645397058120

ITEM DESCRIPTIO 5947 ZOOM[™] 370 LUX Flashligh

ON	MSRP	CASE PACK	
ht	11.99	16 PIECES	

NEBO° CSILUMA50

NEBO **IN/IFRF**

The CSI LUMA50[™] is a compact high-intensity tactical flashlight. Small enough to fit in the palm of your hand, the LUMA50[™] shows off its tough side with the agaressive self-defense face.

tough side with the aggressive self-defense face.



The LUMIÈRE[™] is a compact high-intensity tactical flashlight with a feminine twist. Small enough to fit in the palm of your hand, the LUMIÈRE[™] has a jeweled grip for stylish non-slip grip. Don't let the jewels fool you, the LUMIÈRE[™] shows off its

ON	MSRP	CASE PACK
shlight	9.99	24 PIECES
shlight	9.99	24 PIECES

NEBO **FLASHLIGHT/LASER** 8 LEDS+LASER+FLASHER

NEBO[®] **Flashlight Holsters**

Each NEBO® flashlight holster has a pouch made to securely fit an assortment of NEBO flashlights and most other brands as well. The holsters are designed for protection, durability and structural strength.

The CSI Tactical Flashlight is the original NEBO® tactical light. Constructed of anodized aircraft grade aluminum, this flashlight's design is completely water and impact-resistant. Adding to the toughness of this light is the tactical edge and anti roll body design. This flashlight features 8 White LED's and a red laser pointer.



4 LIGHT MODES

- 8 LEDs (24 lumens) 8 hours / 30 meters • Red Laser (<5mW) - 72 hours / 412 meters
- 8 LEDs Flashing 16 hours / 30 meters
- S.O.S. (LEDs & laser)



DESIGN

Anodized aircraft-grade aluminum; water and impact-resistant • Tactical edge

OPERATION Rear-positioned ON/OFF button

BATTERIES • Powered by 3 AAA batteries (included)











UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397010128	5633	CSI Tactical Flashlight with Display	9.99	18 PIECES
645397128007	5077	CSI Tactical Flashlight in Clamshell	12.99	12 PIECES





#5089 CSI Flashlight Holster Leather covered steel belt/pocket clip, carabiner clip, reinforced holster backing

#6032 Flashlight Holster

belt loop



#6274 Flashlight Holster Designed specifically for #5620/#5955 REDLINE Select, hook and loop closure oelt/pocket clip

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397850892	5089	CSI Flashlight Holster	3.99	10 PIECES
645397035121	5922	Leather Flashlight Holster	16.99	6 PIECES
645397069126	5958	Flashlight Holster	6.99	10 PIECES
645397929284	6032	Flashlight Holster	6.99	10 PIECES
645397930181	6274	Flashlight Holster	6.99	16 PIECES
645397930761	6393	BIG Larry Flashlight Holster	4.99	7 PIECES
645397931560	6561	Flashlight Holster	6.99	16 PIECES

#5922 Leather Flashlight Holster Snap cover with hook and loop closure, steel belt/pocket clip



Designed specifically for #6156/#6383 SLYDE™ & #6525/#6618 SLYDE™+, steel



#5958 Flashlight Holster Snap cover, steel belt/pocket clip



#6393 BIG Larry Flashlight Holster Designed specifically for BIG Larry, belt/ bocket clip, magnetic base and flashlight lin



#6561 Flashlight Holster Hook and loop / snap closure, snap belt

NEBO° 14-in-1 Ultra[®] Socket

The NEBO® 14-in-1 Ultra[™] Socket comes with 7 screwdriver bits and 5 sockets conveniently stored inside the handle. The head of the Ultra[™] Socket tilts a full 180° and locks at 0°, 45°, and 90°, working perfectly as a nut driver for those hard to reach places. The handle is ergonomically designed to add comfort and grip to improve performance. The Ultra™ Socket features a reversible ratchet mechanism making it easier to loosen or tighten any bolt. The 14-in-1 Ultra™ Socket meets and exceeds ANSI standards and is created to withstand more than the normal wear and tear.



an ergonomic rubber handle to add comfort and grip.



UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	 UPC CODE	ITEM	DESCRIPTION
645397610113	5606	Ultra™ 14-in-1 Socket and Screwdriver	16.99	12 PIECES	 645397130406	4327	Ultra [™] Socket Combination

The NEBO® Ultra[™] Socket Combination Kit comes with 19 sockets conveniently stored in SAE and Metric trays. The head of the Ultra[™] Socket tilts and locks at 0°, 45°, and 90°, working perfectly as a nut driver for those hard to reach places. The Ultra[™] Socket features a reversible ratchet mechanism making it easier to loosen or tighten any bolt and









NEBO° Folding LOCK-BLADE Utility Knife

The Folding Lock-Blade Utility Knife uses a quick change feature making it easier to change the blade without any tools. The utility knife accepts all standard utility blades and incorporates a blade lock system which makes this a safe, strong and secure knife that can be unlocked with one hand.







- Anodized aluminum handle with rubber grip • Quick change blade feature; no tools required
- Thumb studs for one-handed opening
- Carabiner • Lock release button to unfold
- SPECS • 0.5 lbs.
- Length: (Open) 8" / (Closed) 4.25" (W) 1.5" x (D) 0.75"





Display Dimensions (H) 8.75" x (W) 14" x (D) 10.5"

Clamshell Dimensions (H) 8.25" x (W) 4.25" x (D) 1.25"

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
645397900504	5517	Folding Lock-Blade Utility Knife Assorted	6.99	18 PIECES





Whether cruising around the city streets or mountain biking in the middle of nowhere, NEBO® Sports has the essentials you need for your ride.



The REDLINE[®] Bright Light features a quick release bar mount that easily attaches to any bar, no tools necessary. The REDLINE[®] can detach from the bar mount to be used as a handheld flashlight.



3 LIGHT MODES

• High (2185 LUX) - 4 hours / 187 meters

- Low (225 LUX) 8 hours / 60 meters
- Strobe (2185 LUX) 72 hours / 187 meters

• Self locking, universal bar mount; no tools required



DESIGN • Tactical edge

MOUNT STYLE

- Convex lens
- 4x adjustable beam
- Anodized aircraft-grade aluminum;
- water and impact-resistant
- Magnetic base
- Quick-release tab quickly detaches flashlight
 Mount allows light to swivel 180°



 Rear-positioned Glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES • 3 AAA batteries included

• (L) 4.5" x (W) 1.325" x (D) 3"

SPECS

• 0.5 lbs.


U.S. PATENT

• 659,869 S





L	
1	Clamshell Dimensions
11	(H) 8.375" x (W) 6.25" x (D) 2.75"





The 6 LED Bike Light by NEBO® offers 18 lumens of bright white light. The Bike Light has 2 lighting modes: 100% On and Strobe. The Bike Light has a convenient quick-release mount to turn the Bike Light into a flashlight. A lanyard wrist strap is also included to keep this light handy. The bike mount rotates a full 360° to direct light wherever you need it. Water and impact-resistant, this 6 White LED Bike Light is an essential add-on to your bicycle. This Bike Light is easy to install, no tools required.

2 LIGHT MODES

On (18 lumens) - 15 hours / 22 meters
 Strobe (18 lumens) - 28 hours / 22 meters

MOUNT STYLE

Self locking, universal bar mount; no tools required

DESIGN

Water and impact-resistant
Quick-release tab quickly detaches light
Mount allows light to swivel 180°

OPERATION

• Top-positioned ON/OFF button

ACCESSORIES • Lanyard included

Larryara incloada

BATTERIES

• 3 AAA batteries included

SPECS

• 0.25 lbs. • (L) 3.5" x (W) 1.25" x (D) 3"









ON	MSRP	CASE PACK	
	13.99	6 PIECES	


NEBO° 75 Lumen 5 LED Red Bike Light / Tail Light COMBO

The Bike Light Combo by NEBO® is designed to provide maximum visibility and safety while you are riding. Each light features a bar mount that secures to the bike with no tools needed. Lights also have a quick release feature that allows the lights to be easily removed from the bar mount.



4 LIGHT MODES - HEAD LIGHT • High (75 lumens) - 3 hours / 65 meters

- Low (37.5 lumens) 4.7 hours / 32 meters
- Strobe (75 lumens) 5.3 hours / 65 meters • S.O.S. (75 lumens) - 3.5 hours / 65 meters



7 LIGHT MODES - TAIL LIGHT • On (3.5 lumens) - 55 hours / 1.6 KM

• Flash, Slow flash, Cascading, Rising, Rapid cascade, Random flash (120 hours / 1.6 KM)



MOUNT STYLE

• Self locking, universal bar mount; no tools required

DESIGN

- Water and impact-resistant
- Quick-release tab quickly detaches light
 Mount allows head light to swivel 180°
- Tail light features strong clip

OPERATION

- ON/OFF button
- ACCESSORIES
- Lanyard included

BATTERIES

• 3 AAA batteries included for head light • 2 AAA batteries included for tail light



SPECS

- #5952: 0.15 lbs. / #5953: 0.2 lbs. • #5952: (H) 2.75" x (W) 1.25" x (D) 3.5"
- #5953: (L) 3.875" x (W) 1.25" x (D) 3"





(H) 6.625" x (W) 5.5" x (D) 2"

5953 Bike Light Combo 24.99 6 PIECES UPC CODE ITEM DESCRIPTION	ITEM DESCRIPTION MSRP CASE PACK
· · · · · · · · · · · · · · · · · · ·	TEM DESCRIPTION MSRP CASE PACK
	Bike Light Combo 24.99 6 PIECES UPC CODE ITEM DESCRIPTION
	952 5 Red LED Tail Light 9.99 6 PIECES 645397812111 5611 250 PSI Air Compressor




The 250 PSI Air Compressor by NEBO® Sports is a 12V portable air compressor that can inflate a standard size bicycle tire in less than a minute! While designed for bicycle tires, this Air Compressor has the power to use on your vehicle as well. This compact, portable Air Compressor is a perfect addition to your trunk for when those inconvenient, vet inevitable flat tires occur.





WEATHERRITE **OLD RED**

The Old Red is a 15 LED, 100 lumen lantern that brings classic charm and warm, inviting light to any space. Blending rustic design with modern technology, the Old Red features a realistic flickering flame and a control to adjust the amount of light that is generated. No smoke and no fire...the Old Red operates for hours on end with 4 AA batteries, which are included.



Your next camping excursion will not be complete without your WeatherRite® products. Whether at home or in the great outdoors, WeatherRite® specializes in creating recreational and emergency preparedness consumer products, ideal for any situation.

UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
044435917779	6642	Old Red Lantern	19.99	4 PIECES



Available

August 2017







OIL LANTERN

The Oil Lantern captures a classic design and technology that has been around since 1850. This 12" high metal lantern has a wire-guard to protect the glass globe. The fuel tank is 12 oz., which provides 35 hours of burn time on a full tank. The Oil Lantern has a control to adjust the wick height and light output (2 wicks included.) This lantern can be used indoors to provide light during power outages, or to just add a warm glow to any room. Also perfect for outdoor use as well for camping, hunting or any outdoor recreational activity.

15 LED LANTERN

This 15 LED Lantern is the perfect blend between classic design and modern technology. This 9" high metal lantern has a wire-guard to protect the glass globe. No kerosene, no lamp oil and no citronella...this 15 LED is completely battery operated (batteries not included.) To maintain the functionality of a traditional kerosene lantern, this 15 LED Lantern has a control to adjust the amount of light that is generated. A reflector is positioned above the LEDs to cast the light evenly in every direction. Perfect for indoor or outdoor use, this lantern generates over 96 hours of continuous bright light. The 15 LED Lantern, the traditional lantern look with efficient LED lighting!



UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK	UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
044435915393	6048 Oil Lantern		8.99	4 PIECES	044435627104	5572	15 LED Lantern	12.99	4 PIECES

ADJUSTABLE LIGHT OUTPUT • High (25 lumens) - 96 hours / 5 meters

DESIGN

- Metal construction with wire-guarded glass globe
- Hanging hook
- 25 lumens
- 96 hours of continuous light
- Adjustable light output
- Powered by 2 D batteries (not included)

SPECS

- 0.9 lbs.
- (H) 9" x (D) 4.5" x (W) 4.5"





WEATHERRITE **LED** LANTERNS

WeatherRite® LED Lanterns are portable, reliable lanterns that are perfect for camping, fishing, hunting, boating, road trips, RVing, power outages, at-home use or any emergency situation.


WEATHERRITE **ECOLANTERN**[™]

The ECO LANTERN[™] is a portable, reliable energy-saving lantern with 24 super bright energy efficient white LEDs that guarantee continuous supreme illumination. *Requiring no batteries*, the ECO LANTERN[™] charges with AC, DC, solar or wind up making it perfect for camping, fishing, hunting, boating, road trips, RVing, power outages, at home use, or any emergency situation.





UPC CODE 645397060123	ITEM	DESCRIPTION 600 Lumen LED Lantern	MSRP 39.99	CASE PACK 4 PIECES					~	¥- 1
044435915904		130 Lumen LED Lantern	21.99	6 PIECES		UPC CODE	ITEM	DESCRIPTION	MSRP	CASE PACK
044435916420	6005	300 Lumen LED Lantern	29.99	4 PIECES	_	645397070122	5959	ECO LANTERN™	49.99	4 PIECES







1 LIGHT MODE

• 24 high-power LEDs output 157 lumens

DESIGN

- Water and impact-resistant
- Uses 4 methods of recharging:
- AC, DC, solar & wind up
- Charging indicator changes from red to green when fully charged
- Folding carry handle
- Top and bottom reflectors
- Wire guard protects LED housing
- Crank handle for wind up

OPERATION


• Front-positioned ON/OFF button

ACCESSORIES

• AC and DC adaptors included

SPECS

- 3.678 lbs.
- (H) 9.125" x (D) 6" x (W) 5.5"











Who is Alliance Sports Group?

Alliance Sports Group is the parent company of NEBO®, iPROTEC[™] Firearm Accessories, Bollinger® Fitness, WeatherRite® Outdoor, Quarrow® Fishing and True Utility®.

What does NEBO® mean?

NEBO is mentioned in the Bible as the burial site of Moses. There is an excellent view of "The Promised Land" from Mt. NEBO. NEBO is also a mountain in Utah near where NEBO originated.

Can I order online?

Yes. Go to nebotools.com to purchase products at retail or sign up to become a dealer. Credit card orders only.

Can I order less than a case pack?

Yes. Go to nebotools.com to purchase products in any quantity that you like at retail price.

Why does NEBO offer countertop displays?

NEBO products sell much faster in display packaging when it's placed on counters and end-caps because this allows customers to try the product before buying it.

Are lasers safe and legal?

Lasers of all types are regulated by the FDA. All lasers used in NEBO flashlights meet the required standards and have the appropriate warnings to avoid direct eye contact with any laser.

Are NEBO products waterproof?

Some NEBO products are waterproof, however most are water-resistant. Please see product details for further information.

Does NEBO offer a warranty for its products?

Yes, NEBO stands behind its products with a 1 year limited manufacturer's warranty. Any item that does not perform properly due to a manufacturer's defect can be returned for a warranty replacement. Warranty does not cover normal wear and tear or batteries.

How do I get free freight?

First time orders receive free freight (not valid for online orders). Secondary orders exceeding \$600 (\$300 in Texas, Arkansas, Louisiana and Oklahoma) also receive free freight*. Alaska* and Hawaii* customers: ASG will pay freight to the furthest point within the 48 states, then customer is PPA from that point to final ship to location.

Do you accept credit card payments?

Yes. Visa, Mastercard, American Express and Discover

What are my payment terms?

Cash in Advance, NET 30 with approved ASG credit application

Where do I send my payment?

Alliance Sports Group, PO Box 203246, Dallas, TX 75320-3246

Who do I make the check payable to?

Alliance Sports Group

Do you send out monthly statements?

Yes, we send them out at the end of each month.

Can I get my invoices and statements emailed to me?

Yes. Just email a request to accounting@nebotools.net and your invoice/statement will be emailed back to you.

How will my order be shipped (UPS, FedEx, USPS)? How Long will it take to receive my order?

We use UPS, FedEx and USPS. After being processed,* all orders, unless otherwise specified, are shipped standard or ground service which takes approximately 3-5 business days. *Please allow 48-72 hours for order to be processed.

Will I be notified when my product ships?

Yes, a confirmation email will be sent to you when you place your order online. An email with tracking information gets sent out with all orders when they ship.

If an item is out of stock, do you back order the item or wait and ship the order complete?

We back order any items that are out of stock rather than waiting for the remaining items to come in stock.

What is your address for returns? Do you pay the return freight?

Alliance Sports Group, 3025 N. Great Southwest Parkway, Grand Prairie, TX 75050. ASG pays return freight when a Return Authorization has been issued by ASG.

How can I get a call tag/return an item?

Contact your sales rep or corporate office warranty@ nebotools.net or 800.255.6061

What is NEBO's MAP (Minimum Advertised Price) Policy?

The advertised price PLUS any shipping charges paid by the consumer must be within 10% of the Suggested Retail Price. We reserve the right to stop providing product to all sellers that do not comply. A full download-able version of the MAP Policy can be found at our website, www.nebotools. com.

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.NEBOTOOLS.COM

For more information or to place an order, contact your NEBO® Tools sales manager.

CUSTOM PRINTING & ENGRAVING

OUR LO

What's better than a NEBO product?...

One with your name on it!

NEBO° offers custom screen printing and laser engraving services on most all products. Utilize NEBO° products to advertise your company or event!



ADVERTISE YOUR COMPANY WITH OUR PRODUCTS!

Screen Printing Prices

- 100 499 pieces = Dealer price + \$2.00 per unit
- 500 999 pieces = Dealer price + \$1.50 per unit
- 1000+ pieces = Dealer price + \$1.00 per unit

Laser Engraving Prices

- 100 499 pieces = Dealer price + \$2.50 per unit
- 500 999 pieces = Dealer price + \$2.00 per unit
- 1000+ pieces = Dealer price + \$1.50 per unit

*There is a one-time \$35 fee (per custom print/engrave order), which includes the setup for either screen printing or laser engraving. This setup fee covers the logo/text printed in a single location on the product, using a single color. There is an additional charge for printing or laser engraving on multiple locations or printing in more than one color.

FAQs

QUANTITY REQUIREMENTS Custom printing orders must be a minimum of 100 pieces.

LEAD TIME Allow 15-20 business days for production time.

SHIPPING

All orders ship FOB Grand Prairie, TX. Prepaid DOES NOT apply for custom print orders.

PAYMENT Orders will not be released for printing until payment has been received in full, via credit card or CIA.

Contact Your Sales Manager for Additional Information! 800-255-6061

The next best thing to NEBO lights NEBO GEAR



NEBO Cap (Brown) - Two tone mesh back trucker hat. Embroidered. One size fits all.



NEBO Cap (Blue) - Two tone mesh back trucker hat. Embroidered. One size fits all.



NEBO T-Shirt - 50/50 cotton blend. Screen printed. Check for available colors. (M, L, XL & XXL)



NEBO Socks - Cotton socks with embroidered NEBO logo. Set equals 1 pair of each

NEBO GEAR

ITEM	DESCRIPTION	MSRP
#5115	NEBO T-Shirt (M)	14.95
#5116	NEBO T-Shirt (L)	14.95
#5117	NEBO T-Shirt (XL)	14.95
#5118	NEBO T-Shirt (XXL)	14.95
#6289	NEBO Socks	5.95
#6462	NEBO Cap - Red	14.95
#6551	NEBO 30 oz. Tumbler	19.95
#6552	NEBO Cap - Brown	14.95
#6553	NEBO Cap - Blue	14.95
#6554	NEBO Cap - Camo	14.95

*Styles and colors may vary for caps and t-shirts.



NEBO Cap (Camo) - Two tone mesh back trucker hat. Embroidered. One size fits all.



NEBO Cap (Red) - 5 panel cotton Chino cap. Embroidered. Adjustable for all sizes.



NEBO Tumbler - Double wall 30 oz. 18/8 stainless steel. Keeps drinks super cold or hot. No leak cap.


LIGHTING 101

GAUGING LED PERFORMANCE

Measuring the brightness of light is not a very straight-forward task. Currently, the most common measure of brightness is the lumen rating. Lumens replaced the old wattage-rating system because modern lights consume far less power and are much brighter.

A single lumen is the measure of energy that's released from a light. Imagine putting a transparent bubble around a light bulb and being able to measure all of the energy that flows through the bubble -this is how lumens are measured.

At NEBO[®], we don't live in a bubble and we know that as lighting technology advances, so must the tools used to gauge



RATING PERFORMANCE BY PRODUCT TYPE:

LANTERNS & WORK LIGHTS

These lighting products are designed to illuminate the area around — just like a household light bulb. Since light bulbs are rated in lumens, lantern output is rated using lumens.

CLASSIC FLASHLIGHTS





TECHNOLOGY:



Eliminating inconsistencies in light, the OC[™] (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.



A new innovation in LED technology. C·O·B (Chip On Board) features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C·O·B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.

the performance. Thus, many of our flashlights are now gauged by lux instead of lumens. Lux isn't a measurement of the amount of energy released — it's a measure of how much light is actually hitting your target.

We've recently introduced flashlights that have advanced optics designed to maximize energy efficiency by tightly focusing the beam of light. So you can light up the mystery across the field without wasting energy by lighting the ground at your feet.

At NEBO® we make flashlights that are designed to meet real-life applications and we use advanced engineering to create lighting products that conserve energy yet blast a powerful beam of light.

Classic flashlights illuminate the area directly in front of us - mimicking a light-post fixture, so it's appropriate to also rate these products using lumens.



LONG-RANGE FLASHLIGHTS

These flashlights feature specialized optics with zoom capabilities that are designed to project an intense beam of light at a distance. Lumen ratings ignore the use of specialized optics and fail to provide a clear representation of beam distance or brightness. Lux on the other hand, measures the amount of light actually hitting the target.



ARCUS is a new proprietary C·O·B LED technology that shapes light like never before with 250° of intense light coverage for maximum safety.

UPC CODE	ITEM	NEBO [®] Tools	DISPLAY	MSRP	CASE PACK	PAGE #
Flashlights and Lig			Clauseda ell	¢10.00		40
645397128007	5077	CSI Tactical 8 LED Flashlight with Laser CSI LUMA 50™ Flashlight		\$12.99	12 PIECES	48
645397900108 645397900306	5112 5423	BENDBRITE™Hands-Free Flex Light	Display Display	\$9.99 \$9.99	24 PIECES 16 PIECES	46 43
645397900306	5519	EDGE™ 50 Lumen Flashlight	Display	\$9.99 \$9.99	24 PIECES	43
645397401100	5557	REDLINE® Flashlight	Display	\$34.99	14 PIECES	21
645397531111	5581	REDLINE® Flashlight	Clamshell	\$34.99	12 PIECES	21
645397122111	5599	REDLINE® Flashlight (Gray)	Bulk	\$34.99	18 PIECES	21
645397421115	5604	LUMIÈRE™ Flashlight	Display	\$9.99	24 PIECES	47
645397111115	5610	REDLINE® Flashlight (Black)	Bulk	\$34.99	18 PIECES	21
645397929116	5614	LUMIÈRE™ Flashlight	Clamshell	\$9.99	24 PIECES	47
645397312116	5615	SE REDLINE® Flashlight	Display	\$39.99	14 PIECES	20
645397914112	5616	SE REDLINE® Flashlight	Clamshell	\$39.99	12 PIECES	20
645397111276	5620	REDLINE® Select Flashlight (Black)	Display	\$49.99	9 PIECES	23
645397010128	5633	CSI Tactical 8 LED Flashlight with Laser	Display	\$9.99	18 PIECES	48
645397015123	5638	SE REDLINE® (Black)	Bulk	\$39.99	18 PIECES	20
645397107125	5872	CSI EDGE™ 90 Flashlight	Display	\$12.99	24 PIECES	44
645397058120	5947	ZOOM™ 370 LUX Flashlight	Display	\$12.77	16 PIECES	44
645397066125	5955		Display		9 PIECES	23
645397066125		REDLINE® Select Flashlight (Titanium)	Bulk	\$49.99	18 PIECES	23
	5956	SE REDLINE® Flashlight (Gray)		\$39.99		
645397929215	6003	90 Lumen Headlamp	Clamshell	\$16.99	6 PIECES	37
645397929475	6085	EDGE 200 [™] Flashlight	Display	\$15.99	20 PIECES	44
645397929499	6092	REDLINE® OC [™] Flashlight	Display	\$19.99	16 PIECES	24
645397929529	6095	LUMO® Clip Light	Display	\$5.99	48 PIECES	38
645397929864	6157	LUMO® Clip Light (Red)	Bulk	\$5.99	12 PIECES	38
645397929871	6158	LUMO® Clip Light (Silver)	Bulk	\$5.99	12 PIECES	38
645397929888	6159	LUMO® Clip Light (Blue)	Bulk	\$5.99	12 PIECES	38
645397929895	6160	LUMO® Clip Light (Black)	Bulk	\$5.99	12 PIECES	38
645397930013	6189	REDLINE® Select RC Flashlight	Display	\$69.99	6 PIECES	22
645397930167	6272-A	Micro REDLINE® OC™ Flashlight	Display	\$14.99	16 PIECES	19
645397930174	6273	Classic REDLINE® OC™ Flashlight	Display	\$29.99	12 PIECES	25
645397930341	6304	WORKBRITE 2 [™] C•O•B LED Work Light	Display	\$19.99	12 PIECES	28
645397930358	6305	The Rechargeable WORKBRITE 2™	Display	\$29.99	12 PIECES	29
645397930365	6306	BIG Larry® Power C·O·B LED Work Light	Display	\$24.99	14 PIECES	14
645397930396	6311	TRANSPORT® 12V DC Rechargeable Flashlight	Display	\$19.99	18 PIECES	42
645397930402	6327	Larry®C C•O•B LED Work Light	Display	\$8.99	24 PIECES	16
645397930426	6329	LuMORE™ Clip Light	Display	\$5.99	48 PIECES	39
645397930433	6347	CaseBrite™ iPhone 6/6S Case + Light (Black)	Bulk	\$39.99	4 PIECES	32
645397930440	6348	CaseBrite™ iPhone 6/6S Plus Case + Light (Black)	Bulk	\$39.99	4 PIECES	32
645397930457	6349	CaseBrite™ Countertop Display	Display	FREE with 12 piece order	1 PIECE	32-33
645397930464	6350	Larry®C C•O•B LED Work Light - Bulk Red	Bulk	\$8.99	12 PIECES	16
645397930471	6351	Larry®C C•O•B LED Work Light - Bulk Blue	Bulk	\$8.99	12 PIECES	16
645397930488	6352	Larry®C C•O•B LED Work Light - Bulk Gray	Bulk	\$8.99	12 PIECES	16
645397930495	6353	Larry®C C•O•B LED Work Light - Bulk Yellow	Bulk	\$8.99	12 PIECES	16
645397930501	6354	Larry®C C•O•B LED Work Light - Bulk Camo	Bulk	\$8.99	12 PIECES	16
645397930518	6355	Lucy®C C·O·B LED Work Light - Bulk Pink	Bulk	\$8.99	12 PIECES	16
645397930525	6357	LuMORE™ Clip Light - Bulk White	Bulk	\$5.99	12 PIECES	39
645397930532	6358	LuMORE [™] Clip Light - Bulk Red	Bulk	\$5.99	12 PIECES	39
645397930549	6359	LuMORE™ Clip Light - Bulk Blue	Bulk	\$5.99	12 PIECES	39
645397930556	6360	LuMORE™ Clip Light - Bulk Green	Bulk	\$5.99	12 PIECES	39
645397930563	6372	TWYST®Z Work Light, Lantern & Flashlight	Display	\$29.99	16 PIECES	26
645397930402	6373	LiL Larry® C•O•B LED Work Light	Display	\$19.99	18 PIECES	15
645397930648	6382	BIG Larry® C•O•B LED Work Light - Bulk Camo	Bulk	\$24.99	7 PIECES	14
645397930679	6384	BIG Larry® C+O+B LED Work Light - Bulk Black	Bulk	\$24.99	7 PIECES	14
645397930686	6385	BIG Larry® C+O+B LED Work Light - Bulk Black	Bulk	\$24.99 \$24.99	7 PIECES 7 PIECES	14
645397930686						32
	6386	CaseBrite [™] iPhone 6/6S Case + Light (White)	Bulk	\$39.99	4 PIECES	
645397930709	6387	CaseBrite™ iPhone 6/6S Plus Case + Light (White)	Bulk	\$39.99	4 PIECES	32
645397930747	6391	Twin Pucks Task Light & Emergency Beacon	Display	\$19.99	12 PIECES	40
645397930754	6392	REDLINE® RC™ with MagDock	Display	\$39.99	10 PIECES	18
645397930792	6413	BIG Larry® C•O•B LED Work Light - Bulk Red	Bulk	\$24.99	7 PIECES	14
645397930860	6431	Larry® BOSS Power C+O+B Work Light	Display	\$34.99	12 PIECES	12
645397930877	6433	TEMPRA™ IR Surface Thermometer & Spot Light	Display	\$49.99	8 PIECES	41
645397930884	6434	SLYDE™ KING Flashlight and Work Light	Display	\$39.99	12 PIECES	7

645397930907	(42)	TW/VCT@7.W/ork Light Leptorn & Flexblight Dull Plack	Dulla	¢00.00	12 PIECES	26
	6436	TWYST®Z Work Light, Lantern & Flashlight - Bulk Black	Bulk	\$29.99		26
645397930914 645397930983	6437 6444	CRYKET [™] C•O•B Work Light & Spot Light DUO 250+ Lumen Headlamp	Display Display	\$24.99 \$24.99	16 PIECES	36
645397930990	6458	Z-Bug™ Bulb	Display	\$19.99	16 PIECES	11
645397931027	6463	LiL Larry® - Bulk Red	Bulk	\$17.77	9 PIECES	15
645397931034	6463	LiL Larry® - Bulk Black	Bulk	\$19.99	9 PIECES	15
645397931041	6465	LiL Larry® - Bulk Silver	Bulk	\$17.77	9 PIECES	15
645397931058	6466	LiL Larry® - Bulk Camo	Bulk	\$19.99	9 PIECES	15
645397931065	6467	TRANSPORT® 12V DC Rechargeable Flashlight - Bulk Black	Bulk	\$19.99	6 PIECES	42
645397931072	6468	TRANSPORT® 12V DC Rechargeable Flashlight - Bulk Silver	Bulk	\$19.99	6 PIECES	42
645397931140	6492	LiL Larry® - Bulk Patriotic	Bulk	\$19.99	9 PIECES	15
645397931157	6493	BIG Larry® C•O•B LED Work Light - Bulk Patriotic	Bulk	\$24.99	7 PIECES	14
645397931201	6513	CaseBrite [™] Samsung Galaxy S7 Case + Light	Display	\$39.99	4 PIECES	33
645397931225	6523	Flipit Portable LED Lights	Display / Clam	\$14.99	24 PIECES	31
645397931249	6525	SLYDE™+ Work Light & Flashlight	Display / Claim Display	\$29.99	16 PIECES	6
645397931300	6539-B	Larry® TILT Directional Pocket Work Light	Display	\$11.99	24 PIECES	13
645397931331	6542	REDLINE® BLAST 1400 Lumen Flashlight	Display	\$39.99	12 PIECES	17
645397931393	6549	CRYKET™ Camo	Bulk	\$24.99	12 PIECES	27
645397931942	6555	Poppy Lantern & Spot Light	Display	\$16.99	24 PIECES	9
645397931522	6557	POPLITE	Display	\$5.99	48 PIECES	8
645397931539	6558	Contemporary Flipit	Display / Clam	\$14.99	24 PIECES	30
645397931706	6587	Z-Bug™ Lantern + Light	Display	\$24.99	12 PIECES	10
645397931713	6594	Poppy Lantern & Spot Light - Bulk Red	Bulk	\$16.99	6 PIECES	9
645397931720	6595	Poppy Lantern & Spot Light - Bulk Dark Gray	Bulk	\$16.99	6 PIECES	9
645397931737	6596	Poppy Lantern & Spot Light - Bulk Yellow	Bulk	\$16.99	6 PIECES	9
645397931744	6597	Poppy Lantern & Spot Light - Bulk Green	Bulk	\$16.99	6 PIECES	9
645397931935	6618	SLYDE [™] + Work Light & Flashlight - Camo	Bulk	\$29.99	8 PIECES	6
645397931942	6639	REDLINE® V 500 Lumen Flashlight	Display	\$24.99	16 PIECES	4-5
645397931959	6640	BIG Larry® PRO Power Work Light	Display	\$34.99	12 PIECES	2-3
645397931973	6643	SLYDE™ KING Flashlight and Work Light - Camo	Bulk	\$39.99	8 PIECES	7
645397931997	6647	CaseBrite™ iPhone 7 Case + Light (Black)	Bulk	\$39.99	4 PIECES	32
645397932000	6648	CaseBrite™ iPhone 7 Plus Case + Light (Black)	Bulk	\$39.99	4 PIECES	32
645397932017	6649	CaseBrite™ iPhone 7 Case + Light (White)	Bulk	\$39.99	4 PIECES	32
645397932024	6650	CaseBrite [™] iPhone 7 Plus Case + Light (White)	Bulk	\$39.99	4 PIECES	32
645397932031	6651	Poppy Countertop Display	Display	FREE with 12 piece order	1 PIECE	9
Tools					1	
645397130406	4327	Ultra™ Socket Combination Kit	Box	\$24.99	12 PIECES	51
645397850892	5089	CSI Flashlight Holster	Display	\$3.99	10 PIECES	49
645397900504	5517	Folding Lock-Blade Utility Knife with Carabiner	Display/Clam	\$6.99	18 PIECES	52
645397610113	5606	14-in-1 Ultra™ Socket	Display	\$16.99	12 PIECES	50
645397035121	5922	Leather Flashlight Holster	Hang Tag	\$16.99	6 PIECES	49
645397069126	5958	Flashlight Holster	Hang Tag	\$6.99	10 PIECES	49
645397929284	6032	Flashlight Holster with Belt Loop	Display	\$6.99	10 PIECES	49
645397930181	6274	Flashlight Holster	Hang Tag	\$6.99	16 PIECES	49
645397930761	6393	BIG Larry® Flashlight Holster	Bulk	\$4.99	7 PIECES	13,49
645397931560	6561	Flashlight Holster	Hang Tag	\$6.99	16 PIECES	49
UPC CODE	ITEM	NEBO® Sports	DISPLAY	MSRP	CASE PACK	PAGE #
	+					

UPC CODE	ITEM	NEBO [®] Sports	DISPLAY	MSRP	CASE PACK	PAGE #
645397819103	5576	6 White LED Bike Light	Clamshell	\$13.99	6 PIECES	55
645397812111	5611	250 PSI Air Compressor	Clamshell	\$19.99	12 PIECES	57
645397120018	5624	REDLINE® with Universal Bar Mount	Clamshell	\$39.99	6 PIECES	54
645397063124	5952	5 Red LED Rear Bike Light	Clamshell	\$9.99	6 PIECES	56
645397064121	5953	Bike Light Combo	Clamshell	\$24.99	6 PIECES	56
645397931218	6514	ARC250 Pro Bike Light	Clamshell	\$29.99	6 PIECES	35
645397931966	6641	ARC500 Rechargeable Bike Light	Clamshell	\$39.99	6 PIECES	34

UPC CODE	ITEM	WEATHERRITE® Outdoor	DISPLAY	MSRP	CASE PACK	PAGE #
044435627104	5572	15 LED Lantern	Hang Tag	\$12.99	4 PIECES	61
645397060123	5949	600 Lumen Lantern	Box	\$39.99	4 PIECES	62
645397070122	5959	ECO-Lantern [™]	Box	\$49.99	4 PIECES	63
044435915904	6004	130 Lumen Lantern	Box	\$21.99	6 PIECES	62
044435916420	6005	300 Lumen Lantern	Box	\$29.99	4 PIECES	62
044435915393	6048	Oil Lanterns (Red & Black)	Hang Tag	\$8.99	4 PIECES	60
044435917779	6642	Old Red Lantern	Hang Tag	\$19.99	4 PIECES	59



RET0717

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.NEBOTOOLS.COM

For more information or to place an order, contact your NEBO® Tools sales manager.