



Filter Housings & Cartridges

Product Index	Page
Nelsen Filtration Housings/Main Line Filters/Wrenches	165
Nelsen Taste & Odor Cartridges	166
Nelsen Melt-Blown Sediment Cartridges	166
Nelsen Pleated Sediment Cartridges	167
Nelsen Wound Poly Cord Sediment Cartridges	167
Pentek Filter Housings - Slimline, Standard, Double Duty	168
Pentek Whole House Main Line Filter Housings, "Big Blue", "Big Clear"	169
Pentek Spanner Wrenches, Mounting Brackets, O-Rings	169
Pentek Sediment Cartridges	170 – 171
Autotrol Sediment Cartridges	171
Pentek Pleated Sediment Cartridges	171
Pentek Taste and Odor Cartridges	172 – 173
Pentek Specialty Cartridges	174
Matrikx Cartridges	174 – 175
Aries AF-Series Specialty Cartridges	175
Inline Filters, Refillable Cartridge Canisters, Cartridge Couplers	176
Nelsen Filtration Cartridge Systems	177
Nelsen Filtration Cartridge System Replacement Cartridges	177 – 178
Jumbo Stainless Steel Filter Housings	179
In-Line Stainless Steel Screen Strainers	179
Rusco Spin-Out Sand Separators	179
Rusco Inline "T" Sand Separators, Replacement Filter Screens	180

NOTES

Part Number

Description

Suggested Retail

Nelsen Filter Housings Less Cartridges and Carton

Nelsen filter housings are manufactured from the highest quality NSF-listed, FDA-grade polypropylene. EPDM o-rings, pressure relief and mounting cap are standard. These housings are rated for temperatures to 125°F (52°C), pressures to 125 psi and burst-tested at 500 psi and 150,000 cycles. Prices are listed as each. Case quantities have been provided for easy ordering.

NELSEN THIN-LINE HOUSINGS

Nelsen Thin-Line housings are best utilized for use in a variety of low-flow applications including under-sink and counter top residential filtration, pre and post reverse osmosis filtration, recreational vehicle filtration, food service and humidifying systems. These are the housings used in the Aqua Classic and Aqua Elite RO's and do not include a pressure relief button.

NF-TL-02B	1/4" Thin-Line, Blue (12/Case)	\$22.25
NF-TL02W	1/4" Thin-Line, White (12/Case)	\$25.00

NELSEN 3/4" HEAVY-DUTY HOUSINGS

Nelsen 3/4" Heavy-Duty housings are best utilized for "whole house" water filtration on the main water line after the pressure tank or water meter.

NF10-07C-PR	3/4" #10, Clear (12/Case)	\$36.50
-------------	---------------------------	---------

NELSEN 3/4" DOUBLE-DUTY HOUSINGS

Designed for large homes, restaurants and light commercial use. Accepts two standard sediment or taste/odor/sediment cartridges. Use with standard (9-3/4") cartridges and a cartridge coupler or long (20") cartridge.

NF20-07B-PR	3/4" #20, Blue (6/Case)	\$51.25
NF20-07BLK-PR	3/4" #20, Black (6/Case)	\$51.25

NELSEN 3/4" DOUBLE-DUTY HOUSINGS

Designed for large homes, restaurants and light commercial use. Accepts two standard sediment or taste/odor/sediment cartridges. Use with standard (9-3/4") cartridges and a cartridge coupler or long (20") cartridge.

NF20-07B-PR	3/4" #20, Blue (6/Case)	\$51.25
NF20-07BLK-PR	3/4" #20, Black (6/Case)	\$51.25

Nelsen Countertop Water Filter

Includes a white sump, a white 1/4" threaded cap/base, chrome faucet with plastic fittings and a 1/4" supply line. Uses 9-3/4" cartridges.

AA10CT-02W	Counter top Filter Housing	\$94.00
------------	----------------------------	---------

Spanner Wrenches

Used to loosen the sump when changing cartridges.

NF-RO-WRENCH	RO Wrench	\$7.95
NF-STD-WRENCH	Standard Wrench	\$7.40

Mounting Bracket Kits And O-Rings**NELSEN BRACKETS**

L-shaped brackets for 3/4" & Big Blue filters. Mounting screws included.

NF-STD-BKT	Bracket for standard 10" & 20" housings	\$19.60
NF-WB-BKT	Bracket for Wide Body housings	\$32.60

NELSEN O-RINGS

Please note that these o-rings DO NOT fit Pentek housings.

NF-RO-ORING	O-Ring for NRO System, pack of 2, 1-Top & 1-Bottom	\$2.35
NF-STD-ORING	O-Rings for Standard 10" & 20" Housings	\$1.20
NF-WB-ORING	O-Ring for Wide Body Housings	\$2.35
NF-CLWB-ORING	O-Ring for Wide Body Clear Housings	\$1.95



NF-TL-02B



NF-TL02W



N20-07B-PR



NF10-07C-PR



AA10CT-02W



NF-STD-WRENCH



NF-WB-BKT



NF-STD-BKT

* Non-Stock Items. See "Terms and Conditions" for details.

Taste and Odor Cartridges**NELSEN GAC GRANULAR ACTIVATED CARBON**

Designed for reduction of unwanted tastes and odors, such as chlorine. Water enters the bottom and filters thru the entire bed before exiting at the top. This ensures maximum contact time which ensures maximum adsorption. A built-in 20 micron post filter reduces fines.

NFGAC-10	9-3/4", 2.5 gpm (50/Case)	\$9.80
NFGAC-WH	9-3/4", 4.0 gpm (25/Case)	\$43.20
NFGAC-20	20", 2.5 gpm (18/Case)	\$20.20
NFGAC-20WH	20", 4.0 gpm (9/Case)	\$71.80

Nelsen Melt-Blown Sediment Cartridges**NSF NELSEN MELT-BLOWN SPUN POLYPROPYLENE**

Nelsen melt-blown sediment filters feature a graded density that uses the entire depth of the filter to trap sediment, translating into high dirt-holding capacity. Other features include: thermally bonded fibers will not migrate into water, filters available from 1 to 25 microns, broad chemical compatibility. Melt blown polypropylene cartridges offer a self-supporting, thermally fused filter media that requires no separate center support tube. No adhesives, binding agents or anti-static agents are used.

NP1	9-3/4" 1 Micron (50/Case)	\$3.50
NP5	9-3/4" 5 Micron (50/Case)	\$3.50
NP5-GROOVED	9-3/4" 5 Micron (50/Case)	\$3.00
NP10	9-3/4" 10 Micron (50/Case)	\$3.00
NP20	9-3/4" 20 Micron (50/Case)	\$3.00
NP50	9-3/4" 20 Micron (50/Case)	\$3.10
NP1-20	20" 1 Micron (25/Case)	\$7.90
NP5-20	20" 5 Micron (25/Case)	\$6.50
NP20-20	20" 20 Micron (25/Case)	\$5.80

NSF NELSEN MELT-BLOWN SPUN POLYPROPYLENE FOR WIDE BODY HOUSINGS

Nelsen Big-Blue Melt-Blown Poly Sediment filters are constructed with 4-layers of different micron ratings. The graded densities of layers capture particles throughout the entire cross section of the cartridge reducing surface binding or buildup.

That sediment buildup results in greater pressure drops and quicker replacement of the cartridge. The finer the particle the deeper through the surface of the cartridge it travels. Example: a 5 micron rated cartridge has these four layer densities - Inside Layer - 5 micron, 2nd Layer - 10 micron, 3rd Layer - 25 micron, Outer Layer - 50 micron.

The Nelsen Big-Blue Sediment filters are made from 100% high purity polypropylene, have good chemical resistance are not prone to bacteria attack. They are available in 1, 5, 10 & 25 micron rates and come in 10 and 20 inch lengths.

NP1-BB-10	9-3/4" 1 Micron, BB, (12/Case)	\$16.50
NP5-BB-10	9-3/4" 5 Micron, BB, (12/Case)	\$16.50
NP10-BB-10	9-3/4" 10 Micron, BB, (12/Case)	\$16.50
NP20-BB-10	9-3/4" 25 Micron, BB, (12/Case)	\$16.50
NP1-BB-20	20" 1 Micron, BB, (6/Case)	\$33.00
NP5-BB-20	20" 5 Micron, BB, (6/Case)	\$33.00
* NP10-BB-20	20" 10 Micron, BB, (6/Case)	\$30.50
NP20-BB-20	20" 20 Micron, BB, (6/Case)	\$32.20

NELSEN ECONOMY MELT-BLOWN SPUN POLYPROPYLENE CARTRIDGES

An economical alternative filter to the NSF approved. These filters are made from 100% high purity polypropylene, have good chemical resistance are not prone to bacteria attack.

MB-5	9-3/4" 5 Micron (50/Case)	\$2.20
MB-5-20	20" 5 Micron (25/Case)	\$4.30
MB-5-BB	9-3/4" 5 Micron, BB, (12/Case)	\$8.40
MB-5-BB-20	20" 5 Micron, BB, (6/Case)	\$16.90



NFGAC-10



MELT-BLOWN CARTRIDGES

DEPTH FILTER SHOWING THE
FOUR LAYER DENSITIES

* Non-Stock Items. See "Terms and Conditions" for details.

Part Number

Description

Suggested Retail

Wound Poly Cord Sediment Cartridges**NELSEN SPUN POLYPROPYLENE CORD**

These cartridges are manufactured from a durable polypropylene cord that is wound around a rigid polypropylene core. Ideal for fine sediment removal including sand, silt, scale, unseen sludge and rust particles. Compatible with most acids, alkalis, corrosive fluids and gases. An ideal, yet inexpensive choice for agricultural, photographic and residential applications.



NELSEN SPUN POLY CORD CARTRIDGES

N1PP10	9-7/8", 1 Micron Dirt Cartridge (24/Cs)	\$5.20
N5PP10	9-7/8", 5 Micron Dirt Cartridge (24/Cs)	\$5.20
N10PP10	9-7/8", 10 Micron Dirt Cartridge (24/Cs)	\$5.00
N30PP10	9-7/8", 30 Micron Dirt Cartridge (24/Cs)	\$5.00
N20PP10	9-7/8", 20 Micron Dirt Cartridge (24/Cs)	\$5.20
N50PP10	9-7/8", 50 Micron Dirt Cartridge (30/Cs)	\$4.20
N5BB10	9-7/8" BB, 5 Micron Dirt Cartridge (9/Cs)	\$15.30
N10BB10	9-7/8" BB, 10 Micron Dirt Cartridge (9/Cs)	\$15.30
N30BB10	9-7/8" BB, 30 Micron Dirt Cartridge (9/Cs)	\$15.80
N5BB20	20" BB, 5 Micron Dirt Cartridge (9/Cs)	\$30.70

Pleated Sediment Cartridges**NELSEN PLEATED CARTRIDGES**

The chemical and bacterial resistance of the polyester media makes these cartridges suitable for potable water, light industrial applications, swimming pool and spa, and well water applications. The durable non-woven polyester fabric is reusable, while being pleated to maximize its dirt holding capacity and extending the time period between changes.



PLEATED CARTRIDGE FAMILY

NPF-0.35-975	9-3/4" .35 Micron Pleated (25/Case)	\$19.65
NPF-1-975-ABS	9-3/4" 1 Micron Absolute Pltd (25/Case)	\$19.80
NPF-1-975	9-3/4" 1 Micron Pleated (25/Case)	\$12.85
NPF-5-975	9-3/4" 5 Micron (25/Case)	\$12.55
NPF-20-975	9-3/4" 20 Micron (25/Case)	\$12.55
NPF-30-975	9-3/4" 30 Micron (25/Case)	\$11.45
NPF-50-975	9-3/4" 50 Micron (25/Case)	\$12.95
NPF-5-20	20" 5 Micron (20/Case)	\$22.55
NPF-20-20	20" 20 Micron (20/Case)	\$22.30
NPF-30-20	20" 30 Micron (20/Case)	\$20.90

NELSEN PLEATED CARTRIDGES FOR WIDE BODY HOUSINGS

NPF-BB-10-0.35	9-3/4" 0.35 Micron, BB, (8/Case)	\$43.30
NPF-BB-10-1	9-3/4" 1 Micron, BB, (8/Case)	\$32.85
NPF-BB-10-5	9-3/4" 5 Micron, BB, (8/Case)	\$31.00
NPF-BB-10-20	9-3/4" 20 Micron, BB, (8/Case)	\$29.80
NPF-BB-10-50	9-3/4" 50 Micron, BB, (8/Case)	\$29.80
NPF-BB-20-0.35	20" 0.35 Micron, BB, (6/Case)	\$72.20
NPF-BB-20-1	20" 1 Micron, BB, (6/Case)	\$63.60
NPF-BB-20-5	20" 5 Micron, BB, (6/Case)	\$51.30
NPF-BB-20-20	20" 20 Micron, BB, (6/Case)	\$49.70
NPF-BB-20-30	20" 30 Micron, BB, (6/Case)	\$49.70
NPF-BB-20-50	20" 50 Micron, BB, (6/Case)	\$49.70

* Non-Stock Items. See "Terms and Conditions" for details.

Call Nelsen Toll-Free — OHIO - 800.362.9686, ARIZONA - 866.445.4299, TEXAS - 855.674.0357 or FLORIDA - 866.712.6796

All prices and products subject to change without notice. ©2014 Nelsen Corporation



PENTEK
Pentair Water



SL03B-PR-IB



INTEGRAL BRACKET



10-07B-PR



10-07C-PR



VIH10-07C-PR



10-07HW



20-07B-PR

VIH10-07B-PR

Pentek Filter Housings Less Cartridges and Carton

Prices are listed as each. Case quantities have been provided for easy ordering.

IB - Indicates "Integral Bracket". Third generation design features a integral bracket molded into cap of the housing alleviating the need for separate mounting bracket.

PENTEK 3/8" SLIMLINE HOUSINGS

The 3/8" Slim Line Housings are designed for quick, easy under-sink installation on the cold water line where the space is too tight for standard models. Includes pressure relief in head.

SL03B-PR	3/8" Slimline, Blue (12/Case)	\$19.00
SL03C-PR	3/8" Slimline, Clear (12/Case)	\$28.50
SL03B-PR-IB	3/8" Slimline, Blue w/Integral Bracket	\$30.50
SL03C-PR-IB	3/8" Slimline, Clear w/Integral Bracket	\$43.25

PENTEK 3/4" STANDARD HOUSINGS

Pentek 3/4" housings are best utilized with sediment cartridges for "whole house" water filtration on the main water line after the pressure tank or water meter. Includes pressure relief and mounting bracket cap.

10-07C	3/4" #10, Clear (12/Case), No Pres Relief	\$55.75
10-07B-PR	3/4" #10, Blue (12/Case)	\$44.00
10-07C-PR	3/4" #10, Clear (12/Case)	\$56.25
10-07B-PR-IB	3/4" #10, Blue w/Integral Bracket	\$49.00
10-07C-PR-IB	3/4" #10, Clear w/Integral Bracket	\$61.25

PENTEK 3/4" DOUBLE DUTY HOUSINGS W/PRESSURE RELIEF

Designed for large homes, restaurants and light commercial use. Accepts two standard sediment or taste/odor/sediment cartridges. Use with standard (9-3/4") cartridges and a cartridge coupler or long (20") cartridge. Mounting bracket cap. Built-in pressure relief.

20-07B-PR	3/4" #20, Blue (8/Case)	\$75.25
20-07B-PR-IB	3/4" #20, Blue w/Integral Bracket	\$80.75
20-07C-PR-IB	3/4" #20, Clear w/Integral Bracket	\$112.75

PENTEK 3/4" DOUBLE DUTY HOUSINGS

20-07B	3/4" #20, Blue (8/Case)	\$74.75
--------	-------------------------	---------

PENTEK 3/4" VALVE-IN-HEAD HOUSINGS

Eliminates need for other valves to change cartridges. The unique (patented) Valve-In-Head design allows water to be shut off with a half turn of the handle. Automatic pressure relief.

VIH10-07B-PR	3/4" #10 Blue (12/Case)	\$79.25
VIH10-07C-PR	3/4" #10 Clear (12/Case)	\$95.50
VIH20-07B-PR	3/4" #20 Blue (8/Case)	\$110.50

PENTEK 3/4" HOT WATER HOUSINGS

Made of red glass reinforced nylon for use on water up to 160 degrees F. No pressure relief or mounting bracket cap is available.

10-07HW	3/4" #10 Hot Water (8/Case)	\$208.50
---------	-----------------------------	----------

* Non-Stock Items. See "Terms and Conditions" for details.



HD10-PR



HD10-CL-PR



SW-2



AM150060



AM158011



AM151011



AM150061

Pentek Whole House Main Line Filters

PENTEK "BIG BLUE" HOUSINGS

Available with both 1" and 1-1/2" NPT. Excellent whole house filters or wherever larger flow rates are necessary. Mounting bracket head. Uses 4-1/2" diameter cartridges. Prices are listed as each. Case quantities have been provided for easy ordering.

HD10	1" #10, Blue w/o PR, (6/Case)	\$56.75
HD10-PR	1" #10 Blue w/Pres. Release, (6/Case)	\$60.00
HD15-PR	1-1/2" #10 Blue w/PR, (6/Case)	\$64.75

20" HOUSINGS

HD10-20	1" #20 Blue w/o PR, (4/Case)	\$86.00
HD15-20	1-1/2" #20 Blue w/o PR, (4/Case)	\$80.00
HD10-20-PR	1" #20 Blue w/PR, (4/Case)	\$87.50
HD15-20-PR	1-1/2" #20 Blue w/PR, (4/Case)	\$93.00

PENTEK "BIG CLEAR" HOUSINGS

These housings feature a 1" Inlet/Outlet Blue Cap and are available in 10" and 20" length. The benefit of the clear housing lies in the visibility of the cartridge as it becomes loaded with sediment. Includes pressure release.

NOTE: The clear sumps are not interchangeable with the cap for the opaque "Big Blue" filter housings.

HD10-CL-PR	1", #10 Clear w/PR, (6/Case)	\$204.00
------------	------------------------------	----------

Pentek Spanner Wrenches

PENTEK WRENCHES

SW-1	Slimline Housing	\$6.50
SW-2	Standard Housing	\$6.50
SW-3	10" Big Blue Housing	\$6.95
SW-4	20" Big Blue Housing	\$6.95
SW-BB-CL	Big Clear Housing	\$10.60

Mounting Bracket Kits And O-Rings

PENTEK BRACKETS

For mounting filters with 3/4" caps with bosses.

AM150060	3/4" Housings with Screws	\$12.00
----------	---------------------------	---------

For mounting filters with 1/2", 3/8" and 1/4" caps (Slimline housings) with bosses.

AM158011	1/2", 3/8" and 1/4" Housings	\$7.90
----------	------------------------------	--------

U-shaped bracket for 3/4" housings without mounting bracket caps.

AM151011	3/4" Housings (U-Shape)	\$12.35
----------	-------------------------	---------

Mounting Kit for Big Blue housings.

AM150061	Galvanized Steel	\$64.50
----------	------------------	---------

PENTEK O-RINGS, REPAIR KIT

AM151117	O-Ring, #10 Hot Water, #241 Viton	\$32.70
AM151120	O-Ring, #10, #12 and #20 Housings	\$5.80
AM151121	O-Ring, Slimline Housings	\$5.80
AM151122	O-Ring, Big Blue	\$19.00
AM151254	O-Ring, Big Clear Housing	\$19.00
AM151039	Pressure Relief Button Kit	\$9.15
AM154077	1" Black Cap w/o PR for BB Housings	\$84.00

* Non-Stock Items. See "Terms and Conditions" for details.



PENTEK
Pentair Water



P5

POLYDEPTH
FILTER

DUAL GRADIENT FILTER



WP5BB97P



WP5BB97P

Pentek Sediment Cartridges

PENTEK POLYPROPYLENE FIBER

100% pure polypropylene fibers spun together to form a true gradient density from outer to inner surfaces. Designed for home, commercial and industrial use. Prices are listed as each. Carton quantities have been listed for easy ordering.

P1	9-7/8" 1 Micron, 10 gpm (24/Case)	\$7.15
P5	9-7/8" 5 Micron, 10 gpm (24/Case)	\$6.60
P25	9-7/8" 25 Micron, 10 gpm (24/Case)	\$6.40
P1-20	20" 1 Micron, 20 gpm (20/Case)	\$14.75
P5-20	20" 5 Micron, 20 gpm (20/Case)	\$13.80
P25-20	20" 25 Micron, 20 gpm (20/Case)	\$13.40

POLYDEPTH® SERIES POLYPROPYLENE CARTRIDGE

The Polydepth® filtration cartridge is constructed of thermally-bonded polypropylene micro fibers to ensure high efficiency. The filter incorporates a rigid polypropylene center core for increased collapse strength and durability. This thermal bonded micro-fiber construction has minimal fiber release, consistent flow rate and superior filtration performance. It also is not brittle or prone to breakage problems like resin-bonded cartridges.

PD-5-934	Pentek Polydepth Filter, 9-3/4", 5 mic	\$9.85
PD-25-934	Pentek Polydepth Filter, 9-3/4", 25 mic	\$9.65
PD-5-20	Pentek Polydepth Cartridge, 20", 5 mic	\$17.90

PENTEK DUAL GRADIENT POLYPROPYLENE

DGD Series cartridges are manufactured from 100% pure polypropylene and are sized for use in Big Blue® filter housings. These cartridges are designed for purity and will not impart taste, odor or color to the liquid being filtered. Additionally, the polypropylene construction provides superior chemical resistance and is not prone to bacterial attack.

The DGD Series advanced design combines selective "final filtration" with appropriate "pre-filtration" to achieve up to three times the dirt holding capacity of similar size sediment cartridges and many more times that of standard spun or string-wound cartridges. This performance enhancement is achieved by combining two separate gradient layers in one filter.

The larger diameter of the pre-filter reduces the particle load to the post filter, allowing it to operate at higher velocities. The effective filter depth is increased to a full 233% of standard spun-polypropylene or string-wound filters. This increased depth provides for very high particulate reduction efficiencies and added loading capacity.

The unique design and performance characteristics of the DGD Series cartridges make them an excellent choice for all residential, rural, municipal and commercial applications.

DGD-2501-10-BB	10" 25/1 Micron, 10 gpm (8/Case)	\$25.50
DGD-5005-10-BB	10" 50/5 Micron, 10 gpm (8/Case)	\$23.90
DGD-2501-20-BB	20" 25/1 Micron, 20 gpm (6/Case)	\$45.90
DGD-5005-20-BB	20" 50/5 Micron, 20 gpm (6/Case)	\$44.00
DGD-7525-20-BB	20" 75/25 Micron, 20 gpm (6/Case)	\$43.80

PENTEK SPUN POLYPROPYLENE FIBER

Offers a wide chemical resistance and is compatible with most acids, alkalis, corrosive fluids and gases. Polypropylene cord is wound around a polypropylene core in a precise pattern ensuring a high efficiency rating as well as a high dirt loading capacity.

WP5	9-7/8" 5 Micron, 7 gpm (24/Case)	\$11.60
* WP30	9-7/8" 30 Micron, 10 gpm (24/Case)	\$11.30
WP5BB97P	10" 5 Micron, 7 gpm (8/Case)	\$36.25
WP5BB20P	20" 5 Micron, 10 gpm (6/Case)	\$82.50

PENTEK SPUN POLYPROPYLENE CORD

Ideal for fine sediment removal including sand, silt, scale, unseen sludge and rust particles. Compatible with most acids, alkalis, corrosive fluids and gases. An ideal, yet inexpensive choice for agricultural, photographic and residential applications.

CW-F	9-7/8" 10 Micron, 7 gpm (24/Case)	\$7.35
CW-MF	9-7/8" 30 Micron, 10 gpm (24/Case)	\$6.75
CW-50	9-7/8" 50 Micron, 10 gpm (24/Case)	\$6.85

* Non-Stock Items. See "Terms and Conditions" for details.

Part Number

Description

Suggested Retail

Autotrol Sediment Cartridges**AUTOTROL POLYPROPYLENE FIBER**

AUTOTROL POLYPROPYLENE FIBER

Melt-blown polypropylene cartridges offer a self-supporting, thermally fused media that requires no separate center core. Thermally-bonded fibers will not migrate or contaminate the filtered water.

OP1	9-7/8" 1 Micron, 10 gpm	\$4.85
OP5	9-7/8" 5 Micron, 10 gpm	\$4.70
OP25	9-7/8" 25 Micron, 10 gpm	\$4.45
* OP1-20	20" 1 Micron, 20 gpm	\$9.40
OP5-20	20" 5 Micron, 20 gpm	\$9.20
OP25-20	20" 25 Micron, 20 gpm	\$16.35



PENTEK
Pentair Water

Pentek Pleated Sediment Cartridges

Flow rates shown are nominal for new cartridges. Usage and dirt load will effect capacity. Cartridges with the suffix "BB" are 4-1/2" in diameter and fit "Big Blue" housings.

Prices are listed as each. Case quantities have been provided for easy ordering.

PENTEK ALL CELLULOSE

Designed for general water filtration purposes. Highly-effective, yet economical, these cartridges remove sediment particles down to nominal 20 microns in size. Not reusable.

S1	9-3/4", 12 gpm (24/Case)	\$7.15
S1-20	20", 15 gpm (14/Case)	\$16.30
S1-BB	9-3/4", Big Blue, 25 gpm (8/Case)	\$20.30
S1-20BB	20", Big Blue, 35 gpm (6/Case)	\$36.25

PENTEK POLYESTER

Made of a durable non-woven reusable polyester fabric which allows for several uses. Their synthetic construction makes them ideal for well water applications since they cannot be attacked by bacteria.

R30	9-3/4" 30 Micron, 10 gpm (24/Case)	\$14.95
R50	9-3/4" 50 Micron, 10 gpm (24/Case)	\$14.45
R30-BB	9-3/4" 30 Micron, 10 gpm (8/Case)	\$30.60
R50-BB	9-3/4" 50 Micron, 10 gpm (8/Case)	\$24.30
R30-20BB	20" 30 Micron, 20 gpm (6/Case)	\$60.80

ECP SERIES PLEATED CELLULOSE POLYESTER

ECP Series cartridges are manufactured from a special formulation of resin-impregnated cellulose and polyester fibers.

This unique blend of materials provides a higher wet strength than regular cellulose cartridges. It also provides high flow rates and dirt-holding capacity, while maintaining extremely low pressure drop.

ECP1-10	9-3/4" 1 Micron, 10 gpm (24/Case)	\$11.40
ECP5-10	9-3/4" 5 Micron, 10 gpm (24/Case)	\$10.65
* ECP5-20	20" 5 Micron, 10 gpm (24/Case)	\$20.90
* ECP1-BB	9-3/4" BB, 1 Micron, 10 gpm (24/Case)	\$26.70
ECP5-BB	9-3/4" BB, 5 Micron, 10 gpm (24/Case)	\$26.20
ECP5-20BB	20" BB, 5 Micron, 20 gpm (6/Case)	\$49.10



S1

R-SERIES

ECP5-10

* Non-Stock Items. See "Terms and Conditions" for details.

Taste and Odor Cartridges**PENTEK DUAL PURPOSE POWDERED CARBON**

C Series cartridges offer an economical solution for all of your general-purpose water filtration needs. Constructed of a carbon impregnated cellulose media, these dual-purpose cartridges filter out fine sediment particles and reduce unwanted taste, odor and chlorine taste and odor from your tap water.* A polyester reinforcement backing and external netting provide additional strength and dirt-loading capacity.

C Series cartridges are available in three different sizes and two (2) different micron ratings. Both the C1 and C2 are nominally rated at 5-microns, the C8 is nominally rated at 1-micron.

These dual-purpose cartridges are well suited for a wide range of residential applications, and make excellent polishing filters when used in process or closed-loop streams.

C2	2-1/2" x 4-7/8", 8 gpm (24/Case)	\$11.65
C1	2-1/2" x 9-3/4", 5 gpm, (24/Case)	\$11.65
* C8	2-5/8" x 9-3/4", 5 gpm, (24/Case)	\$19.80
C1-20	2-1/2" x 20", 8 gpm (14/Case)	\$25.30
* C1-20BB	4-1/2" x 20", 8 gpm (6/Case)	\$68.35

PENTEK NCP SERIES NON-CELLULOSE CARBON-IMPREGNATED PLEATED CARTRIDGES

NCP Series cartridges are constructed from a carbon-impregnated non-cellulose media. They offer sediment-filtration, as well as taste, odor and chlorine taste and odor reduction in one cartridge. Unlike cellulose cartridges, NCP Series cartridges are resistant to bacterial attack allowing them to be used for municipal and non-chlorinated water applications.

Pleats provide additional surface area for high dirt-loading capacity, while maintaining minimal pressure drop. This combination of a pleated polyester media and carbon filtration produces an outstanding filter cartridge with extended service life.

NCP Series cartridges are excellent polishing filters, closed loop streams and are ideal for post reverse osmosis and well water applications.

NCP-10	9-3/4", 3 gpm (24/Case)	\$16.00
NCP-BB	9-3/4", 8 gpm (8/Case)	\$40.50
NCP-20BB	20", 10 gpm (6/Case)	\$79.00

GAC GRANULAR ACTIVATED CARBON

Designed for reduction of unwanted tastes and odors such as chlorine. Water enters the bottom and filters thru the entire bed before exiting at the top. This insures maximum contact time ensuring maximum absorption. A built-in 20 micron post filter reduces fines.

GAC10	9-3/4", 2.5 gpm (12/Case)	\$18.00
GAC20	20", 2.0 gpm (6/Case)	\$36.60
GAC-BB	9-3/4", 4.0 gpm (8/Case)	\$46.80
GAC20-BB	20", 5 gpm (6/Case)	\$101.75

PENTEK COCONUT SHELL GRANULAR ACTIVATED CARBON

These cartridges contain coconut shell-based activated carbon which is highly effective at reducing certain organic chemicals, such as, EDB, TCE and THMs in addition to reducing chlorine. Used in the CCF-201 system.

CC-10	9-3/4", 2.5 gpm (12/Case)	\$20.40
-------	---------------------------	---------

PENTEK RFC GRANULAR ACTIVATED CARBON

Designed for liquid and gas filtration. For liquids, they are designed primarily for reducing organics and particulate contaminants from plating, acid, alkaline and hydrocarbon solutions. They can also be used for chlorine removal at low flow rates.

RFC-93	9-3/4", 1 gpm (24/Case)	\$45.30
RFC-20	20", 2 gpm (6/Case)	\$66.50
RFC-BB	9-3/4", 3 gpm (8/Case)	\$71.50
RFC20-BB	20", 6 gpm (6/Case)	\$141.00



C2

C1



NCP-10



GAC10



CC-10



RFC-93

* Non-Stock Items. See "Terms and Conditions" for details.

Part Number

Description

Suggested Retail

PENTEK CARBON BRIQUETTE

Designed to reduce VOC's, chlorine, color bodies as well as fine sediment from residential, commercial and industrial liquids. Provides high chemical adsorption while filtering down to .5 microns. They make excellent polishing or pre-filters on many applications.

CBC-5	4-7/8", 1.0 gpm (24/Case)	\$10.50
CBC-10	9-3/4", 2.0 gpm (12/Case)	\$27.30
* CBC-20	20", 2.0 gpm (6/Case)	\$52.90
CBC-BB	9-3/4", 2.0 gpm (4/Case)	\$85.00
CBC20-BB	20", 4.0 gpm (9/Case)	\$184.00

PENTEK CARBON BLOCK W/LEAD REDUCTION

The CBR2-10 "Multi-Media" Cartridge is designed for multipurpose filtration of liquids. It contains a powdered activated carbon (PAC) briquette, which is more effective at reducing levels of certain organics than granular activated carbon. In addition, the carbon briquette reduces levels of chlorine, sediment down to .5 microns and Giardia and Cryptosporidium cysts.

CBR2-10	Carbon Briquette/Resin (12/Case)	\$33.40
---------	----------------------------------	---------

PENTEK EP SERIES CARBON BLOCK

EP Series cartridges are versatile and combine the long life of carbon block filtration with the dirt-loading tolerance of wound, carbon-impregnated paper cartridges like our C1. EP Series cartridges are manufactured using a patented process that yields a cartridge with a nominal 5-micron filtration rating, high porosity and greater chlorine removal capacity than competitive 10-micron carbon blocks. The high-porosity design helps prevent the cartridge from plugging before its adsorption capability is exhausted, maximizing the utilization of the carbon while maintaining low pressure drop. EP Series cartridges are manufactured entirely from FDA-approved material making them an ideal choice for a wide range of residential, food service, commercial and industrial applications.

EP-10	9-3/4", 4 gpm (12/Case)	\$14.75
* EP-20	2-7/8" x 20", 10 Micron (6/Case)	\$29.55
EP-BB	9-3/4", 4 gpm (4/Case)	\$53.10
EP-20BB	4" x 20", BB, 5 gpm (4/Case)	\$103.25

PENTEK EPM MODIFIED EPSILON CARBON BRIQUETTE CARTRIDGE

EPM Series cartridges are a modified version of the EP Series cartridge. An economical price makes this cartridge suitable for taste, odor and chlorine taste & odor reduction, as well as sediment filtration.*

EPM Series cartridges are manufactured using a patented process that yields a cartridge with a nominal 10-micron filtration rating, high porosity and chlorine taste & odor reduction. The high porosity design helps prevent the cartridge from plugging before its adsorption capability is exhausted, maximizing the utilization of the carbon while maintaining low pressure drop.

These cartridges are protected by Endurawrap®, a uniquely formulated polyolefin bilaminate pre-filter, designed to significantly increase the useful life of the cartridge by trapping sediment that typically plugs carbon block cartridges.

EPM Series cartridges are manufactured entirely from FDA-compliant materials making them an ideal choice for a wide range of residential, food service, commercial and industrial applications.

* EPM-10	2-7/8" x 9-3/4", 10 Micron (12/Case)	\$10.35
* EPM-20	2-7/8" x 20", 10 Micron (6/Case)	\$24.70
* EPM-BB	9-3/4", 4 gpm (4/Case)	\$51.30
EPM-20BB	4" x 20", BB, 5 gpm (4/Case)	\$94.00

Nelsen Specialty Cartridges
PYROLOX CARTRIDGE

Point of use cartridge for iron, manganese and hydrogen sulfide removal. Will not remove orange iron, tannins or sulphur bacteria.

NRC-10-PYRO	#10 Pyrolox Cartridge	\$27.95
-------------	-----------------------	---------



CBC-10



CBR2-10



EP-10



EPM-10



NRC-10-PYRO

* Non-Stock Items. See "Terms and Conditions" for details.

Pentek Specialty Cartridges**PHOSPHATE CRYSTALS**

Contains a pure food grade phosphate that dissolves in water at a slow, controlled rate. The phosphate is highly effective at controlling rust and corrosion by forming a protective coating on the inside surface of piping and water heaters. Also, a small amount of soluble iron in a water supply may be treated, minimizing red water and iron staining.

PCC-1	9-3/4", 5 gpm (6/Case)	\$85.50
* PCC212	9-3/4" 12 oz. (6/Case)	\$44.90
* PCC218	9-3/4" 18 oz. (6/Case)	\$53.60

ACTIVATED CARBON/PHOSPHATE CRYSTALS

Combines activated carbon with phosphate crystals for taste and odor removal and corrosion control.

* TSGAC-10	9-3/4" (12/Case)	\$43.10
------------	------------------	---------

CERAMIC ELEMENT

This micro-straining ceramic element cartridge has been specifically tested for the removal of Cryptosporidium and Giardia cysts. The fine ceramic media will effectively trap dirt, sediment and cysts down to one micron in diameter. May be cleaned by scrubbing with a stiff brush until the outside diameter at the smallest point is 1-1/2".

CRE-1	Ceramic Element (6/Case)	\$59.40
-------	--------------------------	---------

MIX BED DI CARTRIDGE

PCF Series cartridges have been developed in response to the requirements for deionized water in many industries. They are manufactured using an FDA-compliant resin that has been subjected to additional post-production steps to minimize the total organic carbon (TOC) level. This high-capacity, semi-conductor-grade resin cartridges are ideal for use in pharmaceutical and medical laboratories, cosmetics and circuit board printing applications. PCF Series cartridges are available in three sizes, flow rates and capacities.

PCF1-10MB	Mixed Bed DI, .25 gpm (6/Case)	\$61.50
PCF1-20MB	Mixed Bed DI, .5 gpm (6/Case)	\$107.75
BBF1-20MB	Mixed Bed DI, Big Blue, 1.25 gpm (4/Case)	\$245.00

RADIAL FLOW IRON REDUCTION CARTRIDGE

The RFFE20-BB cartridge is designed to provide an easy and effective method of reducing iron from water, which greatly improves the taste. This cartridge helps to eliminate the orange and brown stains often found in sinks, toilets, tubs and other plumbing fixtures.

RFFE20-BB reduces the possibility of damage to pipes and water heaters and reduces up to 3 ppm dissolved iron. It adds no harmful chemicals to the water, making it completely safe for drinking water applications.

The RFFE20-BB cartridge should be installed on the main cold water line after the pressure tank or water meter. For best results, pre-sediment and post-carbon treatment is recommended."

RFFE20-BB	Iron Reduction Cartridge	\$186.00
-----------	--------------------------	----------

MATRIKX® Extruded Carbon Filters

All MATRIKX® Extruded Carbon Filters are manufactured using FDA-compliant materials. Specific models are designed to meet NSF/ANSI Standards 42 and 53. Extruded carbon filter elements can be used in potable water applications, as well as for industrial, food service and commercial applications.

MATRIKX® +CTO/2 CHLORINE TASTE & ODOR REDUCTION FILTER

The MATRIKX + CTO®/2 is manufactured from high purity acid-washed activated carbon. Its dirt-holding capacity and the absence of carbon fines makes the MATRIKX + CTO®/2 the filter of choice. +CTO®/2 filters simultaneously remove free chlorine and organic chemicals that contribute to taste and odor while providing the particulate filtration and dirt-holding capacity of an efficient five-micron nominal sediment filter.

32-250-125-975	2-1/2" x 9-3/4", (20/Case)	\$10.40
32-250-125-20	2-1/2" x 20", (20/Case)	\$39.50
32-425-125-975	4-1/4" x 9-3/4", (9/Case)	\$50.90
32-425-125-20	4-1/4" x 20", (9/Case)	\$100.00

* Non-Stock Items. See "Terms and Conditions" for details.



Part Number

Description

Suggested Retail



06-250-125-975

MATRIKX® +PB 1 LEAD, CYST, CHLORINE TASTE & ODOR REDUCTION FILTER

MATRIKX® + Pb1 extruded activated carbon filters reduce soluble lead using an ion-exchange filter medium with high specificity for soluble lead. Particulate filtration is used to intercept insoluble lead-containing particles. Standard 2.50" O.D. x 9.75" L filters will reduce lead, meeting the performance requirements of NSF/ANSI Standard 53 protocol for over 2,500 gallons when operating at a flow of 0.75 GPM.

Manufactured with KX®'s proprietary extrusion process, MATRIKX® + Pb1 filters offer high levels of chemical reduction in potable drinking water, including chlorine taste and odor.

MATRIKX® + Pb1 filters meet NSF/ANSI Standard 53, Turbidity and Cyst Reduction, including Cryptosporidium, Giardia, Entamoeba and Toxoplasma. Graded-density filtration combined with high dirt capacity extruded activated carbon provide several times greater life than molded filters."

06-250-125-975

2-1/2" x 9-3/4", (20/Case)

\$26.20

Aries AF-Series Specialty Filter Cartridges

Aries Filterworks products are manufactured in the USA using the latest technologies. A variety of welding, filling and molding machinery ensure complete control over the manufacturing process. Aries Filterworks products are solid from the ground up. Each filter is built around ResinTech premium medias. Cartridges are filled fresh from the manufacturing facility giving maximum shelf life.



REDUCTION



CARBON/KDF

NITRATE
REDUCTION**ARSENIC REDUCTION**

The AF Series provides effective Arsenic reduction by utilizing advanced media technology of ResinTech's ASM-10-HP Arsenic selective media has unsurpassed capacity and is effective over the entire pH range of potable water. In cartridge form, the AF Arsenic Reduction Series is an ideal choice for POU applications requiring EPA compliance of less than 10 ppb of arsenic. These cartridges are double-open end cartridges that fit standard residential and industrial housings.

AF-10-3695	Arsenic Reduction Cartridge, 2.5"x 10", Blue	\$104.75
AF-20-3695	Arsenic Reduction Cartridges, 2.5"x 20", Blue	\$219.00
* AF-10-3695-BB	Arsenic Reduction Cartridges, 4.5"x 10", Blue	\$233.00
* AF-20-3695-BB	Arsenic Reduction Cartridges, 4.5"x 20", Blue	\$496.00

CARBON/KDF®

Used in combination with an Acid Washed Coconut Shell Activated Carbon, KDF can significantly extend the life of filter cartridges. KDF is an oxidation-reduction (redox) media that removes chlorine, hydrogen sulfide and many other contaminants. KDF is available in several varieties for specific applications.

KDF-55 removes chlorine and reduces heavy metals. KDF-85 removes hydrogen sulfide and reduces iron. Both KDF redox medias are bacteriostatic and control the growth of micro-organisms in filters. KDF allows Activated Carbon to do a better job at removing taste and odor."

AF-10-2010	KDF-55 & Coconut Shell Cartridges, 2.5" x 10"	\$29.70
* AF-10-2012-BB	KDF-55 & Coconut Shell Cartridges, 4.5" x 10"	\$100.75
AF-10-2210	KDF-85 & Coconut Shell Cartridges, 2.5" x 10"	\$32.00
* AF-10-2212-BB	KDF-85 & Coconut Shell Cartridges, 4.5" x 10"	\$107.75

NITRATE REDUCTION

Nitrate are reduced by using SIR-100-HP, a strong base anion exchange resin. It is especially useful in nitrate removal applications due to its ability to remove nitrates preferentially in the presence of sulfates.

AF-10-3610	Nitrate Removal Filter Cartridges, 2.5" x 10", Blue	\$56.30
* AF-10-3610-BB	Nitrate Removal Filter Cartridges, 4.5" x 10", Blue	\$132.25

* Non-Stock Items. See "Terms and Conditions" for details.

Part Number

Description

Suggested Retail

Nelsen Refillable Filter Cartridge Canisters

Plastic, refillable canisters for activated carbon and other filter media. Low-cost, reuseable and ideal for a wide variety of filter media.

NRC-10	Refillable Canister, 9-3/4" x 2-1/2" Clear	\$6.45
NRC-20	Refillable Canister, 20" x 2-1/2" Clear	\$11.75
NRC-BB10	Refillable Canister, 9-3/4" x 4-1/2" Clear	\$19.60
NRC-BB20	Refillable Canister, 20" x 4-1/2" Clear	\$29.00

Pentek Cartridge Couplers

AMPCC	Coupler for standard cartridges	\$3.40
CC1020	Coupler for Big Blue cartridges	\$4.85

In-Line Filters**CARBON**

Designed for a wide variety of point-of-use applications including: reverse osmosis (RO), distillation units, ice cube makers, water coolers, beverage dispensers, motor homes and boats. 1/4" inlet and outlet. Granulated activated carbon: 6" - 10.5 cu. in., 10" - 20 cu. in.

NINCF-6	6" Filter	\$9.90
NINCF-10	10" Filter	\$10.55
NINCF-10-QC	10" In-Line Carbon Filter w/1/4" Insert Fitting	\$11.95

STOCKED ONLY IN ARIZONA

NINCF-10-QC-3/8	10" In-Line Carbon Filter w/3/8" Insert Fitting	\$16.10
-----------------	---	---------

SEDIMENT

Compact, in-line sediment filter. Five micron filtration. Disposable.

NINSF-10	10" Filter	\$7.50
----------	------------	--------

Omnipure GAC In-Line Cartridge

In-line filter for taste and odor reduction. Specifically designed for RO or distillation units. Granular activated carbon. 1/4" FNPT connections.

CL10R01/4T33	Omnipure 2" x 10" In-Line	\$22.70
--------------	---------------------------	---------

REFILLABLE CARTRIDGES



AMPCC



CC1020



NINCF-6



NINCF-10



NINSF-10

QUICK
CONNECT

1/4" NPT

* Non-Stock Items. See "Terms and Conditions" for details.



Nelsen Filtration Cartridge Systems

The unique design of the Nelsen Filtration Cartridge Systems is truly revolutionary featuring One™ Water Filtration Simplified cartridge tank. Engineered to replace smaller cartridge style housings, the System yields higher flow rates and longer cartridge life than conventional systems.

The Nelsen Filtration Cartridge System can be used to filter a variety of contaminants, from taste and odor issues to sediment and fine particulate reduction requirements. Available for both Residential and Commercial applications, the System boasts the following unique features:

- Higher flow rates and longer cartridge life than conventional cartridge style housings virtually eliminates the need to replace cartridges on a weekly or monthly basis.
- No tools needed! Unique, snap-ring design simplifies assembly and installation.
- 100% plastic design! Completely plastic, non-corrosive design is the ideal replacement for expensive stainless steel cartridge systems.
- Ideal pre-treatment or post-treatment system provides for high flow rates and particulate loading while minimizing pressure drop.
- Repeat filter sales for system installers of equipment.

RESIDENTIAL/LIGHT COMMERCIAL SYSTEM

The Residential System features the complete cartridge tank system with a black 8x40 inch pressure vessel, pressure relief cap and 1-1/4" plumbing connections configured at the bottom of the housing.

NFS-HF

Residential/Lt. Comm. Cartridge Tank System

\$374.00

COMMERCIAL PLUS SYSTEM

The Commercial Plus System features the complete cartridge tank system with a black 8x40 inch pressure vessel, pressure relief cap and 2" plumbing connections are configured for the bottom of the housing.

NFS-HF-PLUS

Commercial Cartridge Tank System

\$402.00

Nelsen Filtration Cartridge Systems Replacement Cartridges

The Nelsen Filtration Cartridge Systems offer a variety of cartridge options to suit your filtration needs. Cartridges are priced each, case quantities for the residential filter cartridges are 6 per case and commercial plus cartridges a 1 per case.

DOUBLE PLEATED CARTRIDGES - (ORANGE SERIES)

The Orange Filtration Series are dual gradient double pleated filtration solutions for extended life and use, with filtration levels of 5, 10 and 20 microns. The filters are designed with a larger pre-filtration layer externally and the smaller internally, extending filtration level contamination and service life, while achieving high flow and low pressure drop.

The filters will outperform competitive filtration solutions in all turbidity applications including silt, rust, and other particle filtration. The Orange Series also provides lower shear water velocity as the raw water passes through the filter, allowing for more contact time and interaction with the extensive surface area of the filters. This results in higher water quality and longer life of the filtration system.

* NFS-PL10/5-HF	Pleated Filter, 10/5 Micron,	\$249.00
* NFS-PL20/10-HF	Pleated Filter, 20/10 Micron,	\$215.00
* NFS-PL50/20-HF	Pleated Filter, 50/20 Micron,	\$195.00

NANOAI DOUBLE PLEATED CARTRIDGES - (GREEN SERIES)

The Green Filtration Series are electro-positively charged dual gradient double pleated filtration solutions that successfully remove contaminants from 1 to 0.2 microns, featuring ENPRESS NanoAI™ media. The filters are designed with a larger 20 micron pre-filtration layer externally and the charged media internally, extending filtration level contamination and service life, while achieving high flow and low pressure drop.

The filters will outperform competitive filtration solutions in all turbidity applications including insoluble scale, Fe3, bacterial iron slime, colloidal solids, silt, rust, and other particle filtration, resulting in higher water quality and longer life of the filtration system.

* NFS-20NANO-AG-HF	NanoAI™ with Agion® Biostat	\$423.00
* NFS-20NANO-PAC-AG-HF	PAC version of NanoAI™ w/Agion® Biostat	\$583.00

* Non-Stock Items. See "Terms and Conditions" for details.

STRING/MELT-BLOWN COMBINATION CARTRIDGE - (YELLOW SERIES)

The Yellow Filtration Series are dual gradient double pleated filtration solutions for extended life and use, with filtration levels of 5 and 20 microns. This Series offers a combination filter composed of an outer layer of Polypropylene String with a Melt blown Polypropylene core. The precise wound pattern provides greater surface area, higher dirt-loading capacity and greater efficiency than standard wound filter cartridges. As a dual media filter, they provide a cost effective, extended-life product capable of capturing a broad range of particulates with high service flow rates greater than 30+gpm with less than 15 Delta P.

NFS-2005-SWMB-HF	20x5 Micron String w/Melt-blown PP Core	\$210.00
* NFS-5020-SWMB-HF	50x20 Micron String w/Melt-blown PP Core	\$191.00

CARBON BLOCK CARTRIDGE - (BLUE SERIES)

The Blue Filtration Series incorporates surface modified carbon block filter technology that is highly effective reducing bad taste, odor, and the reduction of chlorine and chloramines from potable drinking water. The filters are made using high performance coconut shell carbon, which has more micro-pores compared to other types of carbon. Coupled with a unique binder system, these carbon block filters deliver a product with superior adsorption capacity and kinetic dynamics. The unique high capacity filters provide cost effective water filtration solutions in a size and configuration that offer ease-of-use, extended service life and high capacity, with a low pressure loss.

* NFS-03-CB-HF	3 Micron Carbon Block High Capacity	\$359.00
* NFS-20-CB-HF	20 Micron, High Porosity/Low Pres Drop	\$333.00
* NFS-03-CB-HF-MINE	3 Mic. Carbon Block High Cap, Chloramine Reduction	\$730.00

REUSEABLE/DISPOSABLE 1/2 CUBIC FT MEDIA CARTRIDGE - (WHITE SERIES)

The White Filtration Series is a unique and high capacity granular media bottle that allows incorporation of multiple media options and solutions to be used with the series. This filter series is a 0.5 ft³ empty bottle for filling of granular filtration media. This filter series is ideal for a wide range of Residential, Food Service, Commercial, and Industrial applications, and can be used for multiple applications from Service DI, POE for city or well-water installations, Rental Programs, Exchange systems, high-purity pre- or post-filtration applications, etc...

The design also incorporates the patented Vortech® full distributor plate technology, providing uniform distribution and utilization of the media bed along with maximum efficiencies and service flow rates, giving system design maximum flexibility whether installed in up-flow or down-flow service. A removable Top Cap has a locking feature that can be used for limiting access to the internal medias by the end-user, and special Rings on the bottom of the bottle allow for ease of hanging of the cartridge for easy change-out of medias in applications like Service DI Exchange.

NFS-MEDIA05	1/2 Cubic Foot Reuseable Media Cartridge	\$87.00
NFS-MEDIA-MID	1/2 Cubic Foot 2 Chamber Reuseable Media Cartridge	\$108.00

MIDPLATE MEDIA CARTRIDGE PLUG - (WHITE SERIES)

NFS-MEDIA-MID PLUG	2 Chamber Reuseable Media Cartridge Plug	\$8.00
--------------------	--	--------

PLEATED POLYPROPYLENE - COMMERCIAL PLUS SYSTEMS - (RED SERIES)

The Red Series features Pleated Polypropylene cartridges with multiple levels of filtration flexibility.

The pleated cartridges are for service flow rates up to 150gpm, with low pressure drop of less than 15psi, are 100% cellulose free media, and cleanable 5 micron and up.

The PAC cartridge is for a service flow rate of 15gpm with a removal capacity of 140,000 gallons, with a 90% chlorine reduction. This dramatically improves the quality of water by reducing chlorine, bad tastes, foul odors and sediment.

* NFS-P1A-PLUS	1 Micron Absolute Pleated PP	\$341.00
* NFS-P05-PLUS	5 Micron Absolute Pleated PP	\$273.00
* NFS-P10-PLUS	20 Micron Absolute Pleated PP	\$263.00
* NFS-ACP-PLUS	Pleated Activated Carbon	\$479.00

MELT-BLOWN POLYPROPYLENE DEPTH - COMMERCIAL PLUS SYSTEMS - (PURPLE SERIES)

Higher water quality and longer life of the filtration system, due to a lower shear water velocity as the raw water passes through the filter, to allow for more contact time and more interaction with the extensive surface area of the filters.

Ideal for reduction of soft particulate and high service flow rates up to 100gpm.

* NFS-MB05-HF-PLUS	Melt-blown Poly Depth, 5 Micron	\$141.00
NFS-MB20-HF-PLUS	Melt-blown Poly Depth, 20 Micron	\$136.00

* Non-Stock Items. See "Terms and Conditions" for details.



YELLOW SERIES



WHITE SERIES



PURPLE SERIES



BLUE SERIES



RED SERIES



Jumbo Stainless Steel Filter Housings

The ideal filter housings for convenience and savings, in 304L or 316L stainless steel. Single cartridge is easy to install, easy to remove and they are washable and reusable, 20 micron and up! Housings come with band clamp lid closure, mounting legs, pressure gauges installed on inlet and outlet fittings and compression cap for superior sealing. Housings are rated for pressures to 150 psi. Standard cartridges are rated for temperatures to 140° F. Two-inch NPT fittings and 1/2" FNPT drain fitting.

* SJCH-40	Jumbo 50 gpm, 9-5/8" Cartridges	\$1,797.00
* SJCH-90	Jumbo 100 gpm, 19-1/2" Cartridges	\$2,549.00
* SJCH-170	Jumbo 150 gpm, 30-3/4" Cartridges	\$3,451.00



NS1.5-50

NS1.0-50

In-Line Stainless Steel Screen Strainers

These in-line strainers have been the industry standard for cost effective straining and filtering since they were introduced over thirty years ago. Applications are wide ranging and include: agricultural sprayers, pressure washers, floor scrubbers, drinking water pre-filters, medical devices and car washes.

- Materials include 20% glass filled polypropylene and clear nylon (for bowls) pressure rated 150 psi @ 70°F & 100 psi @ 125°F
- Bowls are resistant to solvents, alkalis and salt solutions. Not for use with alcohol
- Elements 50 mesh T304 stainless steel screens

NS1.0-50	1", 50 Mesh, 480 Micron (Nominal)	\$45.75
NS1.5-50	1-1/2", 50 Mesh, 480 Micron (Nominal)	\$49.50



2-50-60P

"Spin-Out" Sand Separator

Head design creates centrifugal force to separate particulate matter from water. Screen "After-Filter" prevents small particles from re-entering product water.

2-50-60P	2" 5-90 gpm, 60 Mesh	\$255.00
----------	----------------------	----------

REPLACEMENT FILTER SCREENS FOR "SPIN-OUT" SEPARATORS

* FS2-50-60	60 Mesh (254 Micron)	\$104.50
* FS2-50-100	100 Mesh (152 Micron)	\$104.50
* FS2-50-250	250 Mesh (61 Micron)	\$108.50

* Non-Stock Items. See "Terms and Conditions" for details.



NT100-60



FS150-60



NT30C



NT30S

Part Number	Description	Suggested Retail
Inline "T" Profile Sand Separator		
NT100-60	1" 20 gpm, 60 Mesh	\$102.50
NT100-100	1" 20 gpm, 100 Mesh	\$102.50
NT150-60	1-1/2" 50 gpm, 60 Mesh	\$139.25
NT150-100	1-1/2" 50 gpm, 100 Mesh	\$139.25
NT200-60	2" 100 gpm, 60 Mesh	\$224.00
NT200-100	2" 100 gpm, 100 Mesh	\$224.00

REPLACEMENT FILTER SCREENS FOR "T" LINE FILTERS

FS100-60	60 Mesh (254 Micron)	\$26.10
FS100-100	100 Mesh (152 Micron)	\$26.10
FS100-140	140 Mesh (104 Micron)	\$26.10
FS100-250	250 Mesh (61 Micron)	\$29.50
FS100-500	500 Mesh (30 Micron)	\$29.50
FS100-1000	1000 Mesh (15 Micron)	\$29.50
FS150-60	60 Mesh (254 Micron)	\$45.90
FS150-100	100 Mesh (152 Micron)	\$45.90
* FS150-140	140 Mesh (104 Micron)	\$45.90
FS150-250	250 Mesh (61 Micron)	\$51.20
FS150-500	500 Mesh (30 Micron)	\$51.20
* FS150-1000	1000 Mesh (15 Micron)	\$51.20
FS200-60	60 Mesh (254 Micron)	\$75.70
FS200-100	100 Mesh (152 Micron)	\$75.70
* FS200-140	140 Mesh (104 Micron)	\$75.70
* FS200-250	250 Mesh (61 Micron)	\$83.70
FS200-500	500 Mesh (30 Micron)	\$83.70
FS200-1000	1000 Mesh (15 Micron)	\$83.70

SUMPS

NT30C	3/4" and 1" Clear	\$53.90
NT60C	1-1/2"	\$80.90
NT120C	2" Clear	\$97.00

O-RING KITS

NT30S	1"	\$10.55
NT60S	1-1/2"	\$12.45
NT120S	2"	\$13.60

* Non-Stock Items. See "Terms and Conditions" for details.