


aquatherm blue pipe* WYE (LATERAL 45)


For low pressure piping and gravity fed systems. SDR 11 is approved for pressures up to 60 psi, SDR 17.6 is approved for pressures up to 35 psi. Additional sizes available upon request.



SDR	Part no.	Dimension (ND — OD)	d	l	z	a	Weight
			[in]	[in]	[in] ± 1/8"	[°]	[lb]
11	2503126	4" — 125 mm	4.92	26.2	18.7	45.0	10.4
	2503130	6" — 160 mm	6.30	30.8	21.7	45.0	19.8
	2503134	8" — 200 mm	7.87	36.4	25.6	45.0	36.4
	2503138	10" — 250 mm	9.84	43.5	30.7	45.0	68.0
17.6	2403126	4" — 125 mm	4.92	26.2	18.7	45.0	7.18
	2403130	6" — 160 mm	6.30	30.8	21.7	45.0	12.8
	2403134	8" — 200 mm	7.87	36.4	25.6	45.0	23.6
	2403138	10" — 250 mm	9.84	43.5	30.7	45.0	43.9

aquatherm green pipe* TEE (SOCKET)

The length of some fittings may not accommodate all butt-fusion equipment. Verify the equipment to be used is compatible with the fittings when ordering.



Part no.	Dimension (ND — OD)	d	z	l	D	Weight
		[in]	[in]	[in]	[in]	[lb]
0113108	½" — 20 mm	0.79	0.43	1.00	1.16	0.05
0113110	¾" — 25 mm	0.98	0.59	1.22	1.34	0.07
0113112	1" — 32 mm	1.26	0.67	1.38	1.69	0.12
0113114	1 ¼" — 40 mm	1.57	0.79	1.59	2.05	0.22
0113116	1 ½" — 50 mm	1.97	1.02	1.95	2.68	0.39
0113118	2" — 63 mm	2.48	1.28	2.36	3.31	0.81
0113120	2 ½" — 75 mm	2.95	1.52	2.70	3.94	1.19
0113122	3" — 90 mm	3.54	1.81	3.11	4.72	2.03
0113124	3 ½" — 110 mm	4.33	2.20	3.66	5.79	3.52
0113126	4" — 125 mm	4.92	3.01	4.59	6.57	5.89