



HUBBARDTON FORGE.

## PRODUCT SPECIFICATIONS

\*Image shown may not reflect your configured options



### Collage LED Sconce

HUBBARDTON FORGE

**Base Item #205432**  
**Configured Item #205432-1001**  
 205432-LED-05-84

**FINISH**  
 Bronze - 05

**ACCENT**  
 Soft Gold - 84

**LAMPING**  
 LED

### OPTIONS

#### FINISH

Mahogany - 03  
 Bronze - 05  
 Dark Smoke - 07  
 Burnished Steel - 08  
 Black - 10  
 Natural Iron - 20  
 Gold - 25  
 Vintage Platinum - 82  
 Soft Gold - 84

#### ACCENT

Vintage Platinum - 82  
 Soft Gold - 84

#### LAMPING

LED

### SPECIFICATIONS

#### Collage LED Sconce

Base Item #: 205432  
 Configured Item #: 205432-1001  
 205432-LED-05-84

Direct wire interior LED wall sconce. Choose a finish option for the backplate and light source housing and an accent option for the decorative metal accent.

- Handcrafted to order by skilled artisans in Vermont, USA
- Lifetime Limited Warranty when installed in residential setting

#### Dimensions

Height	27.10"
Width	9.50"
Projection	3.70"
Product Weight	11.20 lbs
Backplate	4.90" x 4.90"
Vertical Mounting Height	24.70"
Packed Weight	15.00 lbs
Shipping (DIM) Weight	44.00 lbs

#### LED Lamping Dedicated

LED: 16 w att  
 CCT: 3000K  
 CRI: 90  
 Input: 120-277vac  
 Dimming: Line Voltage, ELV  
 Delivered Lumens: 700\*  
 LED Source Lumens: 975  
 IES Files Available: N  
 \* *Not photometric tested, calculated from similar product*

#### Location Rating

Indoor Damp

#### Safety Rating

UL, CUL listed