



# Low Profile LED Cloud

LC Series

## Features:

- Alternative to 32W T8 cloud
- LED modules producing 3000, 4100 or 5000 source lumens
- 3000K or 4000K color temperature
- 120V TRIAC dimming
- Clean appearance
- Surface mounted
- Wide distribution of light
- Frosted white lens



2345 N. Ernie Krueger Circle  
Waukegan, IL 60087  
847.249.5970  
AFXinc.com



## LED Cloud LC Series

### Features

This clean appearance, surface mounted cloud provides a wide distribution of light with a white diffuser. It can be used in various applications including offices, corridors, garages, kitchens and public spaces. Fixture mounts to standard junction box (not included).

### Construction

Housing is die-formed of 22-gauge steel. Standard mounting holes are included. Power supply connections can be made inside the fixture wire way or in a junction box (not included).

### Finish

Housing is finished in lighting grade white baked gloss enamel paint.

### Diffuser

White acrylic diffuser.

### Electrical

Direct wired with a constant current low voltage electronic LED driver rated at 120 VAC. The driver is dimmable with a 2-wire (Triac) or electronic low voltage (ELV) dimmer switch.

### Lamping

50,000 hr. long life replaceable LEDs produce 3000, 4100 or 5000 source lumens. 3000K or 4000K color temperature, 90 CRI.

### Certification


cETLus listed for damp locations.  
ENERGY STAR® - Pending

### Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date of purchase.

Specifications and dimensions subject to change without notice.

LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		



## Ordering Information:

Warm White (3000K)	LED	Source Lumens	L	W	D	MC
LC3000L30D1	36W	3000	50-3/4"	10-1/2"	4-7/8"	43-3/4"
LC4100L30D1	50W	4100	50-3/4"	10-1/2"	4-7/8"	43-3/4"
LC5000L30D1	60W	5000	50-3/4"	10-1/2"	4-7/8"	43-3/4"

Cool White (4000K)	LED	Source Lumens	L	W	D	MC
LC3000L40D1	36W	3000	50-3/4"	10-1/2"	4-7/8"	43-3/4"
LC4100L40D1	50W	4100	50-3/4"	10-1/2"	4-7/8"	43-3/4"
LC5000L40D1	60W	5000	50-3/4"	10-1/2"	4-7/8"	43-3/4"