



CPV2-486GL-N

# 48" Professional Cooktop: 6 burners with grill

This DCS professional cooktop provide as much cooking area as you'll ever need with its 6 burners plus grill. DCS cooktops have unique, patented Dual Flow Burners™ that let you fire up a fierce heat in an instant — and just as quickly turn it down to a precise full surface simmer with the gentlest of flames. Cooktop burner powers reach up to an extraordinary 23,500 BTU with total surface output reaching up to 128,000 BTU. The grill allows you to grill indoors year-round.

Stainless Steel

A PEACE OF MIND SALE  
24 Hours 7 Days a Week Customer Support  
T 1.888.936.7872 W dcsappliances.com

## Dimensions

Depth	28"
Height	A 8 5/16"
Width	B 47 7/8"

## Features & Benefits

**Perfect Heat**  
Sealed Dual Flow Burners™ deliver cooktop power up to 23,500 BTU (NG model) for seriously fast boiling right down to a precise 140°F full surface simmer with the gentlest of flames.

**Total Control**  
From the highest to the lowest temperatures you get precise control with halo-illuminated cooktop dials. A precise full surface simmer is delivered across all burners.

**Easy to Clean**  
DCS Cooktops have sealed burners and a single sheet cooking surface which, coupled with a commercial-style stainless steel finish and dishwasher-safe grates allow easy cleaning.

**Information at a Glance**  
LED halo control dials provide information at a glance and assist in alerting you if any burners are left on.

**Grill**  
The grill has the DCS Grease Management System™ grease channeling technology with double sided cast 304 grade stainless steel grates that drain fat during cooking and help reduce smoke output.

**Cooking Flexibility**  
The cooktops continuous surface grates are designed for pots and pans to move safely across the cooktop, so you can boil, fry or simmer anywhere on the cooktop. Full coverage, deep-platform style grates are designed to sit at the perfect distance from the high powered burners so the heat goes directly onto the pot rather than the grates themselves, for a faster boil and energy efficiency.

**Kitchen Family Match**  
Designed to match the DCS professional kitchen appliance family.

## Specifications

Accessories sold separately	
Pro Hood	VS48

<b>Burner ratings</b>	
Max burner power	23500 BTU
Power back centre	18500 BTU
Power back left	18500 BTU
Power back right	18500 BTU
Power front centre	18500 BTU
Power front left	23500 BTU
Power front right	18500 BTU
Power grill	12000 BTU
Simmer on all burners	140 °F

<b>Burners</b>	
Dual Flow Burners™	6

<b>Cleaning</b>	
Dishwasher proof trivets	•

<b>Controls</b>		Other product downloads available at <a href="http://dcsappliances.com">dcsappliances.com</a>	
Metal illuminated dials		•	
<b>Gas Requirements</b>			
1/2 NPT		•	
Minimum 5/8 inch diameter flex line		•	
Pressure	6" to 9" W.C		
<b>Performance</b>			
Grease Management System™ grease			
channelling technology; (Healthier Cooking)		•	
Natural Gas		•	
Sealed cooking surface		•	
Total cooktop power BTU	128000		
<b>Power requirements</b>			
Circuit Supply Voltage	15 A		
Supply Frequency	60 Hz		
Supply Voltage	120 V		
Wire	3		
<b>Warranty</b>			
Warranty	Limited 2 Years Parts & Labor		
SKU	71240		

The product dimensions and specifications in this page apply to the specific product and model. Under our policy of continuous improvement, these dimensions and specifications may change at any time. You should therefore check with Fisher & Paykel's Customer Care Centre to ensure this page correctly describes the model currently available. © 2016 DCS by Fisher & Paykel Appliances Limited