

## Pipette support rack

03



For orderly, space saving pipette storage, these sturdy racks hold 50 pipettes in a vertical 5 x 10 arrangement. Top and middle decks have 16mm dia. holes; bottom deck holes are tapered from 16mm to 6mm dia. Pipette tips will not contact table surface. The end plates have handles for easy carrying. Autoclavable at 121°C.

Catalogue No	Alt. No	Width, mm	Depth, mm	Height, mm
PMR-750-010L	F18953-0000	213	114	222



## Pipette stand, polypropylene, vertical

02

**Kartell**

Accommodates 18 pipettes with diameters up to 10mm, plus 10 pipettes with diameters up to 15mm. Small holes allow drainage onto dished base. Boss head (supplied) allows for the holder to be raised or lowered on supporting rod. Can be used with other supporting rods - olives supplied for 8mm to 14mm rods.

Catalogue No	Alt. No	Diameter, mm	Size, mm
PMR-520-F	265X	10(18) and 15(10)	168 (between plates)



## Pipette jar, polypropylene

02

**Kartell**

For storing pipettes, with tight fitting cover.

Autoclavable to 120°C (cover not autoclavable).

Welded flanged base gives excellent stability. Can be easily cut down to suit shorter length pipettes. Can be used as a mini soak jar or canted on side for drainage with pipettes in-situ.

Catalogue No	Alt. No	Diameter, mm	Height, mm	Height, internal, mm
PMR-555-010U	592	83	420	410



## Pipette washers, automatic, HDPE, Thermo Scientific Nalgene®

55

**Thermo SCIENTIFIC**

Available in two sizes a set comprises one each of the following: - pipette jar, basket and washer-rinser. All components manufactured from HDPE. Parts can be purchased separately or as part of a set.

Catalogue No	Alt. No	Depth, mm	Length, mm	Height, mm
PMR-580-010G	5250-0040	155	406 (pipette max.)	775
PMR-580-020D	5250-0050	155	150 (pipette max.)	965

### Washer/rinser only

Operates with water input from 1.5 to 12L per minute without 'siphon stall'. An inlet at the top eliminates back siphoning of contaminated water into the water line. With tubing for inlet/outlet connections

Catalogue No	Alt. No	Depth, mm	Length, mm	Height, mm
PMR-580-035N	5245-0040	155	406	775
PMR-580-060X	5245-0050	155	610	965

### Soaking jar

Catalogue No	Alt. No	Depth, mm	Length, mm	Height, mm
PMR-584-533T	5242-0020	165	203	229
PMR-584-534R	5242-0030	127	350	457
PMR-584-535P	5242-0040	165	406	514
PMR-584-536N	5242-0050	165	610	686
PMR-584-560Q	5242-0060	175	813	914

### Pipette baskets

Rugged baskets to cushion pipettes. Perforated screen is recessed in the base 20mm for complete drainage. Basket O.D. 133mm

Catalogue No	Alt. No	Height, mm
PMR-584-570N	DS5241-0020	375
PMR-584-575D	DS5241-0040	578
PMR-584-580K	DS5241-0050	781
PMR-584-585A	DS5241-0060	978

