

T1400


6" WIDE, PRESLOPED POLYPROPYLENE TRENCH DRAIN BODY. STEEL FRAME AND GRATE SYSTEM

Specification: MIFAB® Series T1400, 6" wide, 39.40" long, pre-sloped (0.5%) or neutral trench drain system. Body is manufactured from polypropylene. Each body has four tabs, 20" apart, for #3 rebar tie down and leveling. Bodies have interlocking ends, a radiused bottom for efficient liquid drainage and have staggered, semi-circular cutouts on each side at the bottom to enable concrete flow underneath the body. End and bottom outlets are available in 3" and 4" no hub outlet connections. Grate options include ductile iron, galvanized steel, stainless steel, and plastic, along with grate lockdown hardware for each grate to secure to the body. These grates are available in Class A, B, C, D and E along with ADA compliance (see pages 33-35). Catch basins are also available.

Function: Used in airports, car washes, malls, gas stations, parking lots, golf courses, factories and any other facilities that require large areas of surface drainage. The lightweight and chemical resistant polypropylene body provides for long life. Polypropylene support board prevents debris from entering the trench body during construction. Water resistant sealant recommended between sections for indoor installations. An infinite number of body sections can be assembled together to serve any requirement. 45 and 90 degree body sections are available.



Assembled T1400 Trench Drain



CALIFORNIA PROPOSITION 65 WARNING. This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

Job Name:	Page No:
Section No:	Contractor:
Schedule No:	Purchase Order No:



T1400

6" WIDE, PRESLOPED POLYPROPYLENE TRENCH DRAIN BODY, STEEL FRAME AND GRATE SYSTEM

Body Part Number		Body Su	mp Depth		Overall Body	Max. Flow Rate			Weight (Less Grate)	
	E1 (Min.)		E2 (Max.)		Depth	GPM Gallons per	LPS Litres per	CFS Cubic Feet per		
	Inches	mm	Inches	mm	Inches	Minute	Second	Second	Lbs.	Kg.
T1400N	5.90"	150	5.90"	150	9.84"	130	8.39	0.289	5.00	2.20
T1401	5.90"	150	6.10"	155	9.84"	130	8.39	0.289	5.00	2.20
T1402	6.10"	155	6.29"	160	9.84"	145	9.35	0.323	5.00	2.20
T1403	6.29"	160	6.49"	165	9.84"	160	10.32	0.356	5.00	2.20
T1404	6.49"	165	6.69"	170	9.84"	175	11.29	0.389	5.00	2.20
T1405	6.69"	170	6.89"	175	9.84"	190	12.26	0.423	5.00	2.20
T1405N	6.89"	175	6.89"	175	9.84"	190	12.26	0.423	5.00	2.20
T1406	6.89"	175	7.08"	180	9.84"	215	13.87	0.478	5.00	2.20
T1407	7.08"	180	7.28"	185	9.84"	230	14.84	0.512	5.00	2.20
T1408	7.28"	185	7.48"	190	9.84"	245	15.80	0.545	5.00	2.20
T1409	7.48"	190	7.67"	195	9.84"	260	16.77	0.579	5.00	2.20
T1410	7.67"	195	7.87"	200	9.84"	275	17.74	0.612	5.00	2.20
T1410N	7.87"	200	7.87"	200	9.84"	275	17.74	0612	5.00	2.20
T1411	7.87"	200	8.07"	205	9.84"	290	18.71	0.645	5.00	2.20
T1412	8.07"	205	8.26"	210	9.84"	305	19.67	0.679	5.00	2.20
T1413	8.26"	210	8.46"	215	9.84"	320	20.64	0.712	5.00	2.20
T1414	8.46"	215	8.66"	220	9.84"	335	21.61	0.745	5.00	2.20
T1415	8.66"	220	8.85"	225	9.84"	350	22.58	0.788	5.00	2.20
T1415N	8.85"	225	8.85"	225	9.84"	365	23.54	0.812	5.00	2.20

	Ductile Iron Grates (all 20" long. Two grates required per body section)
Suffix	(Must use frame with grates - Load Class C and greater) Description
-BA	Buy American Act compliant product
-HP-4	Ductile Iron, Heel Proof Longitudinal Slotted Grate, Special Duty - Class E
-HP-4-13	Ductile Iron, Galvanized, Heel Proof Longitudinal Slotted Grate, Special Duty - Class
-LG-4	Ductile Iron, Extra Heavy Duty, Longitudinal Slotted grate - Class E
-LG-4-13	Ductile Iron, Galvanized, Extra Heavy Duty, Longitudinal Slotted grate - Class E
-LG-4-13	
-PA	Pennsylvania Steel Act compliant product
-4	Ductile Iron, Extra Heavy Duty, Slotted grate - Class E MI-GARD trap seal protection device (available for 1-1/2", 2", 3", 3-1/2", 4" and 6" out
-7MG	connections)
-4-13	Ductile Iron, Galvanized, Extra Heavy Duty, Slotted grate - Class E
-4-3	Ductile Iron, Extra Heavy Duty Slotted grate with Stainless Steel Veneer - Class E (morder together with Steel frame with Stainless Steel veneer.
	Part # for assembly is T1400-PFO-TA-3 with open frame. (39.40" long steel frame wiveneer and two D.I. grates with S.S. veneer)
-LG-4-3	Ductile Iron, Extra Heavy Duty Longitudinal Slotted grate with Stainless Steel veneer order together with Steel frame with Stainless Steel Veneer - Class E)
	Part # for assembly is T1400-LG-PFO-TA-3 with open frame. (39.40" long steel frame S.S. veneer and two D.I. grates with S.S. veneer)
	Fabricated Grates (Must use frame with grates - Load Class C and greater)
Suffix	Description
-AWG	Aluminum wire grate - Class A, 40" long
-CDA	Stainless Steel, Circular Decorative grate - Class A, 40" long
-DDA	Stainless Steel, Diagonal Decorative grate - Class A, 40" long
-SSDA	Stainless Steel, Decorative grate - Class A, 40" long
-DSG	Steel, Diagonal Decorative grate - Class A, 40" long
-DWG	Steel, Decorative wave grate - Class A, 40" long
-FSGA	Galvanized Steel, Fabricated Slotted grate - Class A, 40" long
-FS	Stainless Steel, Fabricated Slotted grate - Class A, 40" long
-HPSS	Stainless Steel, Fabricated Heel Proof Slotted grate - Class A, 40" long
-HPP	Polypropylene, Heel Proof Slotted grate - Class A, 20" long (grate is a black color)
-HPP-TAN	Polypropylene, Heel Proof Slotted grate - Class A, 20" long (grate is a tan color)
-HPP-GREY	Polypropylene, Heel Proof Slotted grate - Class A, 20" long (grate is a grey color)
-PGG	Galvanized Steel, Fabricated Perforated grate - Class A, 40" long
	Fabricated Grates (Must use frame with grates - Load Class C and greater) (See pages 33-35 for additional grate information)
Suffix	Description
-PS	Stainless Steel, Fabricated Perforated grate -Class A, 40" long
-PHPP	Heel Proof Polypropylene, Perforated, Light Duty - Class A, 20" long (grate is a black
-SSWG	Stainless Steel, Fabricated Wire grate -Class A, 40" long
-SDG	Steel, Fabricated Decorative grate -Class B, 40" long
-LGHP	Steel, Fabricated Heel Proof Longitudinal grate -Class B, 40" long

365		23.54	0.812	5.00	2.20		
-FSB	Galv	anized Steel, Fabricated	d Reinforced Slotted grate - Cla	ass B, 40" long			
-CDB	_	Stainless Steel, Circular Decorative grate - Class B, 40" long					
-DDB Stainless Steel, Diagonal Decorative grate - Class B, 40" long							
-SSDB	Stainless Steel, Decorative grate - Class B, 40" long						
-RFS	_	Stainless Steel, Fabricated Reinforced Slotted grate - Class B, 40" long					
-RG	Galv	Galvanized Steel, Reinforced Perforated grate - Class B, 40" long					
-RPS	The state of the s						
-SBGGS Galvanized Steel, Fabricated Slotted Bar grate - Class C, 40" long							
-SBGST	Stee	I, Fabricated Slotted Ba	r grate - Class C, 40" long				
-CDC	Stee	I, Fabricated Circular De	ecorative grate - Class C, 40" le	ong			
-sc	Stee	I, Fabricated Solid Cove	er - Class E, 40" long				
-SBG	Stair	nless Steel, Fabricated E	Bar grate - Class E, 40" long				
			Frames				
Suffix	1 11						
-HD	Extra H.D. 1 meter long angle iron steel frame assembly with anchor studs						
-HD-13	Extra	a H.D. 1 meter long galv	anized angle iron steel frame a	assembly with an	chor studs		
-HD-3	Extra	Extra H.D. 1 meter long angle iron steel frame assembly with S.S. veneer and anchor studs					
-SVF	Type 304 stainless steel plastic body veneer, 2 pieces, 1 meter long Stainless Steel frame veneers, open frame for pedestrian traffic only. Load Class A. To be placed over top edges of T1400 body.						
End caps / Outlets / Accessories							
Suffix	_	cription					
-PEC	Includes the T1400-PEC-30 end cap, two pieces of body clips (T1400-CLIP) and one finish cap (T1400-PEFC)						
-PEFC	-PEFC Top Finishing cap (always included with the T1400-PEC-30 Closed end cap))		
-PE4	-PE4 Includes the T1400-PE04-30 end outlet, two pieces of body clips (T1400-CLIP) and one finish cap (T1400-PEFC)				_IP) and one		
-PB4	Com	bination 3" or 4" Polypro	pylene No Hub bottom outlet				
Standard	Supp	oort board (one per body	/ always included)				
-PBDS	-PBDS Bottom dome strainer						
Standard	tandard Connecting Clips (to connect bodies together)						
Standard	3 1/2" long grate lockdown hardware						
-	- 3 1/2" long Stainless Steel grate lockdown hardware (per grate)						
-PGLVP 3 1/2" long vandal resistant grate lockdown hardware (per grate)							
Fabrications							
Suffix	+	cription					
-CUT	_	ng / per cut - Net Price		T4440N TEE	LT4445N TEE		
-TEE	mod	els)	in T1400N-TEE, T1405N-TEE				
-45	_	`	, T1405N-45, T1410N-45 and				
-90	90s	(available in T1400N-90	, T1405N-90, T1410N-90 and	T1415N-90 mode	els)		
-SOF	OF Side Outlet Fabrication						
CE	0	- Fabrication					

CALIFORNIA PROPOSITION 65 WARNING. This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

Job Name:	Page No:
Section No:	Contractor:
Schedule No:	Purchase Order No: