Location:




## ENCASED NON FREEZE LOW LEAD WALL HYDRANT

**Specification:** MIFAB<sup>®</sup> Series MHY-26 \_\_\_\_\_ (specify length) A.S.S.E. 1019-B certified exposed type, self draining, non freeze low lead wall hydrant with A.S.S.E. 1011 approved anti-siphon and vandal resistant integral vacuum breaker with 3/4" (19) male hose connection. Hydrant assembly complete with neoprene plunger to control both the flow and drain functions, hardened bronze operating stem, drain port under the hexagon nut, heavy duty brass casing, 360 degree swivel inlet connection, heavy duty chrome plated bronze head casting, polished chrome plated face plate, and satin finished nickel bronze box with hinged locking cover. Operating key to be furnished with each hydrant.

**MHY-26** 

Function: Designed to blend in with commercial applications such as office buildings, apartment complexes, malls and shopping centers, schools, churches and industrial buildings.



The wetted surface contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight.

MODEL NO.	WALL THICKNESS		OVER LENGTH		APPROXIMATE WEIGHT		SWIVEL INLET CONNECTION
MODEL NO.	IN	MM	IN	MM	Lbs.	Kgs.	IN
MHY-26-6	6	152	10	254	7.0	3.18	3/4" SWT., 1" Male IPS combination
MHY-26-8	8	203	12	305	7.5	3.41	3/4" SWT., 1" Male IPS combination
MHY-26-10	10	254	14	356	8.0	3.64	3/4" SWT., 1" Male IPS combination
MHY-26-12	12	305	16	406	8.5	3.86	3/4" SWT., 1" Male IPS combination
MHY-26-14	14	356	18	457	9.0	4.09	3/4" SWT., 1" Male IPS combination
MHY-26-16	16	406	20	508	9.5	4.32	3/4" SWT., 1" Male IPS combination
MHY-26-18	18	457	22	559	10.0	4.54	3/4" SWT., 1" Male IPS combination
MHY-26-20	20	508	24	610	10.5	4.77	3/4" SWT., 1" Male IPS combination
MHY-26-22	22	559	26	660	11.0	5.00	3/4" SWT., 1" Male IPS combination
MHY-26-24	24	610	28	711	11.5	5.22	3/4" SWT., 1" Male IPS combination

## SUFFIX OPTIONAL VARIATIONS

-BA	Buy American Act	compliant	produ
0,1	buy / inchount / iot	oompnant	produc

-DVB Chrome Plated Double Check Vacuum Breaker (MHY-9006-CP) (tested and certified to the ASSE 1052 Standard)

-K Cylinder key lock

-PA Pennsylvania Steel Act compliant product

-RB Fabricated stainless steel hydrant box with round back for tilt up construction (MHY-3-RB- 5 7/8"round back with 2" x 3.81" rectangular opening to receive hydrant).

## SUFFIX OPTIONAL VARIATIONS

-S Four 1" x 1 1/4" (25 x 6) slots on top and two sides of box to receive mounting brackets

- -0 1" (25) Hose connection
  - Cast stainless steel hydrant box
- -49 Polished chrome plated nickel bronze box

CALIFORNIA PROPOSITION 65 WARNING. This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

-3

Section No:    Contractor:	Schedule No:	Purchase Order No:
Job Name:         Page No:		
	Job Name:	Page No:

<sup>-</sup>WC Wall clamp