



R1200-SO

LARGE SUMP DUAL OUTLET ROOF DRAIN

Specification: MIFAB® Series R1200-SO lacquered fabricated deep sump roof drain with No Hub side and bottom outlet, 15" diameter anchor flange, large cast iron waterproofing membrane clamp ring with integral gravel stop, and standard selflocking low profile aluminum dome strainer.

Function: Used in any type of flat roofs. Large free area dome provides for efficient drainage of rainwater and prevents debris from entering the drain line. Extra wide anchor flange and membrane clamp with tongue in groove design provides for secure grip of membrane and roof flashing materials.





	BODY HEIGHT			
PART NUMBER	"A" PIPE SIZE (NO HUB CONNECTION)	OVERFLOW PIPE SIZE	"B" DIMENSION SIDE OUTLET DEPTH	
R1203-SO	3" (76)	3" (76)	5 9/16" (141)	
R1204-SO	4" (102)	4" (102)	5 9/16" (141)	
R1206-SO	6" (152)	6" (152)	5" (127)	

SUFFIX -6	OPTIONAL VARIATIONS Vandal proof dome	SUFFIX -DU6	OPTIONAL VARIATIONS Fabricated, powder epoxy coated steel dome on overflow pipe 6"
-11	Acid resistant epoxy coating	-G	Stainless steel ballast quard
-12	Galvanized metal dome		ŭ
-12A	Galvanized body and membrane clamp	-M	Metal dome
-12B	Galvanized metal dome and membrane clamp	-MS	Stainless steel mesh screen on overflow pipe
-13	Galvanized body, membrane clamp and dome	-OP	2" high overflow pipe
-45	45 Degree sewer line connection outlet	-SS	Secondary Strainer (Overflow)
-81	Rough bronze dome	-U	Underdeck clamp
-83	Stainless steel mesh screen over dome	-V	Fixed Static Extension 2", 3", 4"
-B	Sump receiver	-VG	Galvanized fixed extension (2",3",4")
-BA	Buy America Act compliant product	-W-1	Water proofing flange
-DU	Fabricated, powder epoxy coated steel dome on overflow pipe 3", 4"		

CALIFORNIA PROPOSITION 65 WARNING. This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

Job Name:	Page No:
Section No:	Contractor:
Schedule No:	Purchase Order No: