



ProLume® GU24 Spirals

Halco
LIGHTING TECHNOLOGIES

Energy Efficient

- Maximum light distribution achieved through compact design
- Save up to 80% in energy costs compared to Incandescent lamps
- Tri-phosphor coating enhances lumen efficacy and color rendering

Technical Data

- Electronic instant start ballast
- End-of-life protection
- 120 volt, 60Hz
- Minimum starting temperature 5°F
- Nickel-plated brass pins

Broad Assortment

- 11, 13, 15, 18, 23 and 26 watt
- 2700, 3500, 4100 and 5000K
- T2, T3, A19, G25, R20 and R30 bulb types

Long Life

- 10,000 hours average rated life

Benefits

- Use of GU24 socket guarantees use of an energy efficient product
- Saves energy
- Low maintenance

- » GU24 base
- » 10,000 hour life
- » Low maintenance

Markets:

- Residential
- Commercial

Applications:

- Table lamps
- Ceiling fixtures
- Down lighting

Contact your account representative at 800.677.3334 for pricing, orders and technical support.

Visit us at halcolighting.com



Ordering Information

Watt	Base	Product #	Product Code	Description	Color Temp.	CRI	Initial Lumens	Avg. Rated Life	Pkg. Qty.	MOL	Equivalent Wattage
R20											
11 Watt	GU24	46542	CFL11/27/R20/GU24	Warm White	2700	82	340	10000	6/24	4.02"	50
R30											
15 Watt	GU24	46538	CFL15/27/R30/GU24	Warm White	2700	82	700	10000	6/24	4.76"	65
A19											
15 Watt	GU24	46540	CFL15/27/A19/GU24	Warm White	2700	82	800	10000	6/24	4.80"	60
G25											
15 Watt	GU24	46536	CFL15/27/G25/GU24	Warm White	2700	82	750	10000	6/24	4.80"	60
T2											
13 Watt	GU24	*46506	CFL13/27/GU24	Warm White	2700	82	800	10000	10/50	3.63"	60
13 Watt	GU24	*46525	CFL13/35/GU24	White	3500	82	800	10000	10/50	3.63"	60
13 Watt	GU24	*46526	CFL13/41/GU24	Cool White	4100	82	800	10000	10/50	3.63"	60
13 Watt	GU24	*46527	CFL13/50/GU24	Natural White	5000	82	800	10000	10/50	3.63"	60
18 Watt	GU24	*46512	CFL18/27/GU24	Warm White	2700	82	1200	10000	10/50	3.90"	75
18 Watt	GU24	*46519	CFL18/35/GU24	White	3500	82	1200	10000	10/50	3.90"	75
18 Watt	GU24	*46520	CFL18/41/GU24	Cool White	4100	82	1200	10000	10/50	3.90"	75
18 Watt	GU24	*46521	CFL18/50/GU24	Natural White	5000	82	1200	10000	10/50	3.90"	75
23 Watt	GU24	*46518	CFL23/27/GU24	Warm White	2700	82	1600	10000	10/50	4.41"	100
23 Watt	GU24	*46522	CFL23/35/GU24	White	3500	82	1600	10000	10/50	4.41"	100
23 Watt	GU24	*46523	CFL23/41/GU24	Cool White	4100	82	1600	10000	10/50	4.41"	100
23 Watt	GU24	*46524	CFL23/50/GU24	Natural White	5000	82	1600	10000	10/50	4.41"	100
23 Watt	GU24	46548	CFL23/27/GU24/DIM	Warm White Dimmable	2700	82	1600	10000	10/50	4.41"	100
T3											
13 Watt	GU24	46544	CFL13/27/GU24/DIM	Warm White Dimmable	2700	82	800	10000	10/50	4.00"	60
18 Watt	GU24	46546	CFL18/27/GU24/DIM	Warm White Dimmable	2700	82	1200	10000	10/50	4.40"	75
26 Watt	GU24	*46528	CFL26/27/GU24	Warm White	2700	82	1750	10000	10/50	5.20"	100
26 Watt	GU24	*46531	CFL26/35/GU24	White	3500	82	1750	10000	10/50	5.20"	100
26 Watt	GU24	*46529	CFL26/41/GU24	Cool White	4100	82	1750	10000	10/50	5.20"	100
26 Watt	GU24	*46530	CFL26/50/GU24	Natural White	5000	82	1750	10000	10/50	5.20"	100

* UL approved for totally enclosed fixtures with a max ballast case temperature of 90°C for GU24 base lamps, 75°C for medium base lamps.

(Hg) Hg-LAMP CONTAINS MERCURY, MANAGE IN ACCORD WITH DISPOSAL LAWS.

Visit www.lamprecycle.org for disposal information for your state or local government.

CAUTION: Should not be used on dimming circuits, timing devices, photo sensors or occupancy sensors.

This device is not intended for use with emergency exit fixtures.

This device complies with Part 18 of the FCC Rules. This product may cause interference with radio equipment and should not be installed near maritime safety communications equipment, ships at sea or other critical navigation or communications equipment operating between 0.45-30 MHz.

WARRANTY - Commercial/Industrial: This product is warranted for 2 years from the date of purchase, based on 10 hours of use per day.