Finestra 6030 RH Soaking Bath



Product Codes beginning with: F4N6030BRX, F7N6030BRX

Also applies to products sold under part numbers: EV09, KC05, EY05, KE05

TECHNICAL SPECIFICATIONS					
	English	Metric			
Outer Dimensions	60" L x 30" W x 38 1/2" H	1524 mm L x 762 mm W x 978 mm H			
Interior Dimensions (bottom of bath) L x W (Mid) x W (End)	28" L x 17" W x 17" W	711 mm L x 432 mm W x 432 mm W			
Drain/Blower Configuration	Right hand drain	Right hand drain			
Bath Weight (empty)	210 lbs	95 kg			
Total Weight/Floor Loading	1,393 lbs 111.4 lbs/ft²	633 kg 543.6 kg/m²			
Operating Gallonage (min-max)	112 (max) U.S. Gals	424 (max) L			
Electrical Specifications	Each component requires a separate, dedicated GCFI protected circuit(s)				
Chromatherapy (if selected)	120V 15A 60HZ				

FEATURES, UPGRADES & ACCESSORIES

Material Type: High-Gloss Acrylic Install Type: Walk-in, Skirted

Available Colors: White (W), Almond (A), Oyster (Y) Standard (Included) Features: Grab bar, chrome rotary drain

Available Control Systems: Chromatherapy lighting

*Control Panel installation is done by installer, location optional

Available Upgrade: Chromatherapy lighting

Available Accessories:

BN21 Finestra Drain Trim Kit (specify metal finish) 826: Brushed Nickel, 845: Oil Rubbed Bronze

5817000 Tile Flange Kit


EK91 21" Straight Pillow (specify color) 959: White, 958: Almond,

969: Oyster

GD56 Light Chromatherapy Control Kit (for EV85 or EY00)

GQ88 Light Chromatherapy Add-on Kit

KEY DIMENSIONS



*Deck width	reflects	only	area	indicated	on detail.
Dook water	10110010	Orny	uicu	maioatoa	on actain.

Letter	Description	English	Metric	
L	Outer Length	60"	1524 mm	
W	Outer Width	30"	762 mm	
Н	Overall Height	38 1/2"	978 mm	
Α	Overflow Height	31 1/2"	800 mm	
В	Long Edge to Drain Center	11 11/16"	297 mm	
С	Short Edge to Drain Center	15"	381 mm	
D	Drain Shoe Length	8 7/8"	224 mm	
Е	Deck Height	2"	51 mm	
F	Deck Width*	5"	127 mm	
G	Service Access Dimensions	12" H x 18" L	305 mm x 457 mm	
I	Floor Cut-out for Drain	12" x 4"	305 mm x 102 mm	

