

# CONNECTIONS (FDC)

FLUSH 2 WAY & 3 WAY CLAPPER INLET TYPE

Model/Series No. 5020-5030 SERIES

# **SPECIFICATIONS**

## **TWO-WAY & THREE-WAY INLETS**

Cast brass body with drop clappers. Size, outlet location and number of inlets as selected by model number. Polished brass plate with lettering as selected. Polished brass 2-1/2" double female snoots with rigid end N.P.T. x pin lug hose thread swivels, pin lug plugs and chains.



### **MODEL SELECTION**

- \*5021 Back Outlet
- \*5022 Bottom Outlet
- \*5023 Top Outlet
- \*5025 Back Outlet
- 5026 Bottom Outlet
- **5027** Top Outlet
- 5031 Back Outlet
- 5032 Bottom Outlet
- 5033 Top Outlet

NOTE: \* = U/L Listed

## MODEL 5021 (Shown)

## **PRODUCT OPTIONS**

#### FINISHES:

-D Polished Chrome Plated

#### VARIATIONS:

-F Sillcock Flange Plate with Sillcock

#### THREADS:

N.S.T.
Other

#### LETTERING AVAILABLE:

AUTO. SPKR.
STANDPIPE
DRY STANDPIPE
AUTO SPKR. STANDPIPE



A WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov



# CONNECTIONS (FDC) FLUSH 2 WAY & 3 WAY CLAPPER INLET TYPE

Model/Series No. 5020-5030 SERIES


## **MODEL DIMENSIONS**


TWO-WAY AND THREE-WAY INLET												
Outlet Location												
Back Outlet Model No.	Bottom Outlet Model No.	Top Outlet Model No.	Size	А	В	с	D	E	F	G	н	No. Inlets
*5021	*5022	*5023	4 x 2-1/2 x 2-1/2	11	6	5-1/2	6	7	11	-	5-3/4	2
*5025	5026	5027	6 x 2-1/2 x 2-1/2	12-3/4	8-3/4	7-3/4	9-1/2	7-1/2	12	-	5-1/4	2
5031	5032	5033	6 x 2-1/2 x 2-1/2 x 2-1/2	17-5/16	-	7-3/8	-	6-5/8	6-3/4	6-3/4	6	3

ALL DIMENSIONS IN INCHES


Back Outlet

Top or Bottom Outlet





TWO-WAY INLET



THREE-WAY INLET

