Hi-Live My. Co. HI-LITE MFG.	H-15312-B Warehouse Shade Collection	Job Name: Type: Quantity:
CO., INC 13450 Monte Vista Avenue Chino, California 91710 Telephone: (909) 465-1999 Toll Free: (800) 465-0211 Fax: (909) 465-0907 web: www.hilitemfg.com e-mail: sales@hilitemfg.com	6 1/4"	13 1/2"

FINISH -Multi-stage pretreatment procedure using materials of polyester/polished powder coat, baking enamel liquid, raw metals, and galvanized finishes.

Standard Finishes are: 91(Black), 93(White), 95(Dark Green), 96(Galvanized), BR47(Powder Coat Rust), BK01(Black Texture), GN20(Powder Coat Patina).

Upgraded Finishes are: 29, 66, 82, 90, 92, 94, 97, 99, 100, 103, 104, 105, 110, 112, 113, 114, 115, 117, 118, 119, 120, 127, 128, 129, 133, 134, 135, 136, 138, 139, 140, 01, 11, 22, 25, 33, 77, 89.

(Custom finishes available).

For interior finish of fixture refer to color chart on pages 344-348.

MOUNTING - Wall Mount.

ACCESSORIES - CGU(Cast Guard and Glass), LCGU(Large Cast Guard and Glass), WGU(Wire Guard and Glass), LWGU(Large Wire Guard and Glass), ARN(Acorn Globe), LARN(Large Acorn Globe) and WGR(Wire Guard) available. **REFLECTOR** - Heavy duty, spun shade,

12

14 1/2"

aluminum 6061-0 and/or 1100-0, galvanized 22 gauge, steel 20/22 gauge, copper 032/040 and brass 032/040 construction. Dependant on finish.

SOCKETS/LAMPS - Available in: Incandescent - rated 200 watt max/120 volt, medium base. Compact Fluorescent(CFL) - rated 13/18/26/32/42/57 watt max/120/277 volt, GX24Q base. Metal Halide(MH) - rated 35/50/70/100/150/175 watt max/120/208/240/277 volt, medium base, 4KV socket. High Pressure Sodium(HPS) - rated 50/70/100/150 watt max/120/277 volt, medium base. Light-Emitted Diode(LED)

-See LED specification sheet.



MADE IN THE U.S.A.

Suitable for wet location.