



HI-LITE MFG. CO., INC.


13450 Monte Vista Avenue
Chino, California 91710
Telephone: (909) 465-1999
Fax: (909) 465-0907

Job Name: _____

Type: _____

Quantity: _____

Angle Shade Collection



Item Number	Height (A)	Width (B)
H-18107	8"	7"
H-18110	10-1/2"	10"
H-18112	12"	12"
H-18114	14-1/2"	14"

Fixture No.	Fixture Color	Mounting	Mounting Color	Optional Accessories	Accessory Color	Wattage/Lamp options	Ballast	Voltage
H-18107 ⁽¹⁾ H-18110 ⁽¹⁾ H-18112 H-18114	Standard ⁽²⁾ 91 (Black) 93 (White) 95 (Dk. Grn) 96 (Galv.) BR47 (Rust) BK01, GN20. Upgraded Finishes. 29, 66, 82, 92, 97, 100, 103, 104, 105, 112, 113, 114, 117, 118, 119, 127, 128, 133, 134, 135, 136, 98, 101, 102, 137, 139, 140, 121, 122, 123, 124, 11, 01, 22, 25, 33, 77, 89, 24, 44, 48, 49, 15, 16. For finish specs see pages 344-348.	Mounting Options 1/2" 3/4" Stem Options (Stem 1/2") ST Specify length and canopy. HSC (Canopy) SMC (Canopy) Flush Mount Options FHSC FSMC Arm Options B-1 HL-K HL-A HL-U HL-H P-1 HL-C P-3 HL-D For all arms and specs see pages 321-344.	Standard 91 (Black) 93 (White) 95 (Dk. Grn) 96 (Galv.) BR47 (Rust) For all finishes see pages 344-348.	CGU (Cast guard & glass) LCGU (Large cast guard & glass) WGU (Wire guard & glass) LWGU (Large wire guard & glass) WGR (Wire guard) SK (Swivel knuckle) For specs and glass color see pages 321-344.	Standard 91 (Black) 93 (White) 95 (Dk. Grn) 96 (Galv.) BR47 (Rust) For all finishes see pages 344-348.	Incandescent (6) (Fixture is standard 200W. Do not specify) CFL (3) (6) (Compact Fluorescent) 13/CFL 18/CFL 26/CFL 26/32/42/CFL 32/CFL 42/CFL 57/CFL DMB (Dimmable Ballast for CFL. Add to Part No.) HID ⁽³⁾ (High Intensity Discharge) MH ⁽³⁾ (6) (Metal Halide) 35/MH 50/MH 70/MH 100/MH 150/MH 175/MH HPS ⁽³⁾ (6) (High Pressure Sodium) 50/HPS 70/HPS 100/HPS 150/HPS LED See LED specification sheet.	Ballast option not available for INC. RB ⁽⁴⁾ (Remote) BCM (Canopy Mount) PLB ⁽⁵⁾ (Postline) For specs see pages 341-343.	Incandescent (Fixture is standard 120V. Do not specify.) CFL M (Multi 120/277V) HID RB and BCM M (Multi 120/208/240/277V) PLB 1 (120V) 2 (277V) LED See specifications for complete part number.

H-18110	-	91	/	1/2"	-	91	/	CGU-CLR	-	91	/	13/CFL	-	BCM	-	M
---------	---	----	---	------	---	----	---	---------	---	----	---	--------	---	-----	---	---

ORDER EXAMPLE

(USE THIS FORMAT TO PLACE ORDER)

Notes:

(1) H-18107 not available with glass enclosures.
H-18107 available for 200W Max INC, 32W Max CFL and 100W Max HID.
H-18110 not available with LWGU, LCGU, ARN or LARN.

(2) For interior finish of fixture refer to color chart on pages 344-348.

(3) Requires Globe Option. (See pages 339-341 for Globe Options)
Max Wattages for CGU and WGU are
100W INC, 32W CFL and 100W HID.
Max Wattages for LWGU, LCGU, ARN and LARN are
200W INC, 57W CFL and 175W HID.

(4) (RB) Remote Ballast not available for Fluorescent Lamping.

(5) (PLB) Post Line Ballast must specify 120V or 277V.
(PLB) 50W MH requires a 3" dia. pole.
(PLB) 70W and 100W MH require a 4" dia. pole.
(PLB) 50W, 70W, 100W and 150W HPS require a 3" dia. pole.

(6) Socket Bases: INC and HID are medium base. CFL is GX24Q.

Stem-hung fixtures: suitable for damp & dry location.
Gooseneck, post mount & wall bracket fixtures:
suitable for wet, damp & dry location.