


# hansgrohe

**EN** Installation / Warranty

**FR** Instructions de montage / Garantie

**ES** Instrucciones de montaje / Garantía



**Rough set for  
Showerpipe**  
16181181

## Technical Information

Recommended water pressure	15 - 75 PSI
Max. water pressure	145 PSI
Recommended hot water temp.	120° - 140° F*
Max. hot water temp	176°F*

\*Please know and follow all applicable local plumbing codes when setting the temperature on the water heater.

## Installation Considerations

- For best results, Hansgrohe recommends that this unit be installed by a licensed, professional plumber.
- Please read over these instructions thoroughly before beginning installation. Make sure that you have all tools and supplies needed to complete the installation.
- This rough set is for use with several models of Hansgrohe showerpipes and wall-mounted mixing valves.
- Read the instructions included with your showerpipe regarding installation recommendations, minimum ceiling height requirements, etc.**
- To prevent scald injury, the maximum output temperature of the shower valve must be no higher than 120°F. In Massachusetts, the maximum output temperature can be no higher than 112° F.
- Keep this booklet and the receipt (or other proof of date and place of purchase) for this product in a safe place. The receipt is required should it be necessary to request warranty parts.

## Données techniques

Pression d'eau recommandée	15 - 75 PSI
Pression d'eau maximum	145 PSI
Température recommandée d'eau chaude	120° - 140° F*
Température maximum d'eau chaude	176°F*

\* Vous devez connaître et respecter tous les codes de plomberie locaux applicables pour le réglage de la température du chauffe-eau.

## À prendre en considération pour l'installation

- Pour de meilleurs résultats, Hansgrohe recommande que ce produit soit installé par un plombier professionnel licencié.
- Veuillez lire attentivement ces instructions avant de procéder à l'installation. Assurez-vous de disposer de tous les outils et du matériel nécessaires pour l'installation.
- Cet ensemble de pièce intérieure est conçu pour l'utilisation avec plusieurs modèles de tuyaux de douche et robinets mélangeurs muraux d'Hansgrohe.
- Lisez les instructions fournies avec votre tuyau de douche ou robinet mélangeur concernant les recommandations d'installation, les exigences de hauteur de plafond minimale, etc.**
- Pour empêcher des blessures par ébouillantement, la température de sortie maximale du robinet de douche ne doit pas excéder 120°F. Au Massachusetts, la température de sortie maximale du robinet de douche ne doit pas excéder 112°F.
- Conservez ce livret et le reçu (ou une autre preuve sur laquelle figurent la date et l'endroit de l'achat) pour ce produit dans un endroit sûr. Le reçu est requis si vous commandez des pièces sous garantie.



## Datos técnicos

Presión recomendada en servicio	15 - 75 PSI
Presión en servicio max.	145 PSI
Temperatura recomendada del agua caliente	120° - 140° F*
Temperatura del agua caliente max.	176°F*


\*Debe conocer y cumplir todos los códigos locales aplicables para ajustar la temperatura del calentador de agua.

## Consideraciones para la instalación


- Para obtener mejores resultados, la instalación debe estar a cargo de un plomero profesional matriculado.
- Antes de comenzar la instalación, lea estas instrucciones detenidamente. Asegúrese de tener las herramientas y los insumos necesarios para completar la instalación.
- Este juego de piezas interiores se puede usar con varios modelos de tubos de ducha y válvulas mezcladoras montadas en la pared de Hansgrohe.
- Lea las instrucciones incluidas con su tubo de ducha o válvula mezcladora respecto de las recomendaciones para la instalación, los requisitos de altura mínima del techo, etc.**
- Para evitar escaldaduras, la máxima temperatura de salida de la válvula de la ducha no debe exceder los 120°F. En Massachusetts, la máxima temperatura de salida de la válvula de la ducha no debe exceder los 112°F.
- Mantenga este folleto y el recibo (u otro comprobante del lugar y fecha de compra) de este producto en lugar seguro. El recibo se requiere en caso de ser necesario solicitar piezas bajo garantía.



## Tools Required / Outiles Utiles / Herramientas Útiles




## Installation Suggestions / Suggestions d'installation / Sugerencias para la instalación




Raindance Select  
27112xx1

## Installation Suggestions / Suggestions d'installation / Sugerencias para la instalación



Raindance  
27160xx1

## Installation Suggestions / Suggestions d'installation / Sugerencias para la instalación




\* Please know and follow all applicable local plumbing codes regarding the air gap between the tub spout and the flood level of the tub.

\* Vous devez connaître et respecter tous les codes de plomberie locaux applicables en installant ce robinet.

\* Debe conocer y cumplir todos los códigos locales aplicables al instalar este chorro.


## Installation Suggestions / Suggestions d'installation / Sugerencias para la instalación




\* Please know and follow all applicable local plumbing codes regarding the air gap between the tub spout and the flood level of the tub.

\* Vous devez connaître et respecter tous les codes de plomberie locaux applicables en installant ce robinet.


\* Debe conocer y cumplir todos los códigos locales aplicables al instalar este chorro.



Raindance  
27165xx1



Raindance  
27169xx1




## Installation

This rough set requires two properly anchored  $\frac{1}{2}$ " NPT drop-eared ell fittings for the hot and cold supplies for the showerpipe.

**⚠ The hot supply must be installed on the left and the cold supply must be installed on the right.**


**❗ If the unit is not supplied correctly, the thermostatic mixer on the showerpipe cannot function correctly.**



The drop-eared ell must be

- level
- parallel to each other
- perpendicular to the finished wall.

If these conditions are not met, the showerpipe cannot be installed.



The ell must be installed a maximum of  $2\frac{3}{4}$ " behind the surface of the finished wall.

## Installation

Cette pièce intérieure nécessite deux coudes appliques filetés NPT de  $\frac{1}{2}$  po correctement fixés pour les conduites d'alimentation d'eau chaude et d'eau froide du tuyau de douche.

 **Installez la conduite d'eau chaude à gauche et la conduite d'eau froide à droite.**

 **Si l'alimentation n'est pas raccordée adéquatement, le mélangeur thermostatique du tuyau de douche ne fonctionnera pas correctement.**

Les coudes appliques doivent être

- au niveau
- installés de manière parallèle
- perpendiculaires au mur fini.

Si ces conditions ne sont pas remplies, le tuyau de douche ne pourra pas être installé.

Les coudes appliques doivent être installés à un maximum de  $2\frac{3}{4}$  po derrière la surface du mur fini.

## Instalación

Este juego de piezas interiores precisa dos codos NPT de  $\frac{1}{2}$ " correctamente anclados para los suministros de agua fría y agua caliente del tubo de ducha.

 **El suministro de agua caliente debe instalarse en la izquierda y el suministro de agua fría a la derecha.**

 **Si los suministros de la unidad no están instalados correctamente, el mezclador termostático del tubo de ducha no funcionará de forma adecuada.**

Los codos deben estar


- nivelados
- paralelos entre sí
- perpendiculares a la pared terminada.

Si no se cumplen estas condiciones, no podrá instalarse el tubo de ducha.

Los codos deben estar instalados a un máximo de  $2\frac{3}{4}$ " por detrás de la superficie de la pared terminada.


**4**

Remove the nuts and the plugs from the nipples.



**5**

Wrap the  $\frac{1}{2}$ " NPT threads with plumbers' tape.




**6**

Install the nipples in the ell.



**Do not over-tighten the nipples or damage may result.**

Install the spacing jig.



Retirez les écrous et les bouchons des raccords filetés.

Retire las tuercas y los tapones de los niples.

Enveloppez les filets NPT de  $\frac{1}{2}$  po avec du ruban de plombier.

Envuelva las roscas NPT de  $\frac{1}{2}$ " con cinta de plomero.

Installez les raccords filetés dans les coudes appliqués.

Instale los niples en los codos.


**!** **Ne serrez pas excessivement les raccords filetés, car vous pourriez les endommager.**

**!** **No apriete los nipes en exceso, ya que podría dañarlos.**

Installez le gabarit d'espacement.

Instale la plantilla espaciadora.

**7**




Make sure that the nipples are level in all planes.

**The nipples must be parallel to each other.**



**If the nipples are not level and/or are not parallel to each other, the showerpipe cannot be installed.**


**8**



Replace the plugs and nuts.

Pressurize the system and test for leaks.

**9**



Assurez-vous que les raccords filetés sont au niveau sur tous les plans.

**!** **Les niples doivent être au niveau, installés de manière parallèle, et perpendiculaires au mur fini.**

**!** **Si ces conditions ne sont pas remplies, le tuyau de douche ne pourra pas être installé.**

Asegúrese de que los niples estén nivelados en todos los planos.

**!** **Los nipes deben estar nivelados, paralelos entre sí, y perpendiculares a la pared terminada.**

**!** **Si no se cumplen estas condiciones, no podrá instalarse el tubo de ducha.**


Réinstallez les bouchons et écrous.

Mettez le système sous pression et faites un essai pour vérifier s'il y a des fuites.

Reemplace los tapones y las tuercas.


Presurice el sistema y verifique que no haya pérdidas.

**10**



Move the spacing jig to the slots on the nuts.

**11**



Install the finished wall.

## **Français**

Placez le gabarit d'espacement sur les ouvertures des écrous.

## **Español**

Mueva la plantilla espaciadora a las ranuras de las tuercas.

Installez le mur fini.

Instale la pared terminada.

## **Limited Consumer Warranty**

---

This product has been manufactured and tested to the highest quality standards by Hansgrohe, Inc. ("Hansgrohe"). This warranty is limited to Hansgrohe products that are purchased by a consumer in the United States or Canada after March 1, 1996, and installed in either in the United States or in Canada.

### **WHO IS COVERED BY THE WARRANTY**

This warranty extends to the original purchaser only. This warranty is non-transferable.

### **WHAT IS COVERED BY THE WARRANTY**

The warranty covers only your Hansgrohe manufactured product. Hansgrohe warrants this product against defects in material or workmanship as follows:

Hansgrohe will replace at no charge for parts only or, at its option, replace any product or part of the product that proves defective because of improper workmanship and/or material, under normal installation, use, service and maintenance. If Hansgrohe is unable to provide a replacement and repair is not practical or cannot be made in timely fashion, Hansgrohe may elect to refund the purchase price in exchange for the return of the product.

### **LENGTH OF WARRANTY**

Replacement or repaired parts of products will be covered for the term of this warranty, as stated in the following two sentences. If you are a consumer who purchased the product for use primarily for personal, family or household purposes, this warranty extends for as long as you own the product and the home in which the product is originally installed. If you purchased the product for use primarily for any other purpose, including, without limitation, a commercial purpose, this warranty extends only (i) for 1 year, with respect to Hansgrohe & Commercial products, and (ii) for 5 years, with respect to Axor products.

### **THIS WARRANTY DOES NOT COVER, AND HANSGROHE WILL NOT PAY FOR:**

- A. Conditions, malfunctions or damage not resulting from defects in material or workmanship.
- B. Conditions, malfunctions or damage resulting from (1) normal wear and tear, improper installation, improper maintenance, misuse, abuse, negligence, accident or alteration; (2) the use of abrasive or caustic cleaning agents or "no-rinse" cleaning products, or the use of the product in any manner contrary to the product instructions; or (3) conditions in the home such as excessive water pressure or corrosion.
- C. Labor and other expenses for disconnection, deinstallation, or return of the product for warranty service (including but not limited to proper packaging and shipping costs), or for installation or reinstallation of the product.
- D. Accessories, connected materials and products, or related products not manufactured by Hansgrohe.
- E. Any Hansgrohe or Axor product sold for display purposes.
- F. Rubbed Bronze finish is subject to a 3-year limited warranty. Chrome and all PVD finishes are covered by the limited lifetime warranty.
- G. Hansgrohe Water Filtration System is subject to a 1-year limited warranty. Warranty does not include replacement filters.

### **TO OBTAIN WARRANTY PARTS OR INFORMATION**

Contact your Hansgrohe retailer, or contact Technical Service at:

Hansgrohe, Inc.  
1492 Bluegrass Lakes Parkway  
Alpharetta, GA 30004  
Toll-free 800-334-0455

In requesting warranty service, you will need to provide:

1. The sales receipt or other evidence of the date and place of purchase.
2. A description of the problem.
3. Delivery of the product or the defective part, postage prepaid and carefully packed and insured, to:

Hansgrohe, Inc.  
1492 Bluegrass Lakes Parkway  
Alpharetta, GA 30004  
Toll-free 800-334-0455

When warranty service is completed, any repaired or replacement product or part will be returned to you postage prepaid.

---

## **EXCLUSIONS AND LIMITATIONS**

**REPAIR OR REPLACEMENT (OR, IN LIMITED CIRCUMSTANCES, REFUND OF THE PURCHASE PRICE) AS PROVIDED UNDER THIS WARRANTY IS THE EXCLUSIVE REMEDY OF THE PURCHASER. HANSGROHE NEITHER ASSUMES NOR AUTHORIZES ANY PERSON TO CREATE FOR IT ANY OTHER OBLIGATION OR LIABILITY IN CONNECTION WITH THIS PRODUCT. HANSGROHE SHALL NOT BE LIABLE TO PURCHASER OR ANY OTHER PERSON FOR ANY INCIDENTAL, SPECIAL OR CONSEQUENTIAL DAMAGES, ARISING OUT OF BREACH OF THIS WARRANTY OR ANY IMPLIED WARRANTY (INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTY OF MERCHANTABILITY).**

Some States do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may also have other rights that vary from state to state.

**TO THE EXTENT PERMITTED BY LAW, ANY IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE LIMITED TO THE DURATION OF THE EXPRESS WARRANTY.**

Some states do not allow limitations on how long an implied warranty may last, so the above limitations may not apply to you. You may be required by law to give us a reasonable opportunity to correct or cure any failure to comply before you can bring any action in court against us under the Magnuson-Moss Warranty Act.

## **PRODUCT INSTRUCTIONS AND QUESTIONS**

Upon purchase or prior to installation, please carefully inspect your Hansgrohe product for any damage or visible defect. Prior to installing, always carefully study the enclosed instructions on the proper installation and the care and maintenance of this product. If you have questions at any time about the use, installation or performance of your Hansgrohe product, or this warranty, please write us or call us toll-free at 800-334-0455.

**hansgrohe**

Hansgrohe, Inc. • 1490 Bluegrass Lakes Parkway • Alpharetta, GA 30004  
Tel. 800-334-0455 • Fax 770-360-9887

**[www.hansgrohe-usa.com](http://www.hansgrohe-usa.com)**