# **Foot Valve**


Sizes 1" & 1-1/4" / 25 mm & 32 mm


#### **Materials**

Enviro Check<sup>®</sup>









Max Temp 180°F (82°C) Max Pressure 250psi (18bar)

Item #	Qty	Description	Material	ASTM
1	1	Body	Unleaded Bronze	C89833
2	1	Screw	Stainless Steel	18-8
3	1	Flat Washer	Stainless Steel	304
4	1	Disc	Buna-n	N-5007
5	1	Spring	Stainless Steel	302
6	1	Guide*	Delrin	8020
7	1	Screen	Stainless Steel	18-8
8	2	Screw	Stainless Steel	18-8
9	1	Сар	Polycarbonate	
			*1-1/4" Guide is D	elrin 100 NC010

### **Dimensions (FNPT)**

Size		Devit #	Α		В		С		Weight	
inch	mm	Part #	inch	mm	inch	mm	inch	mm	lbs	kg
1	25	4101E	1-29/32	49	1-25/32	45	4-59/64	125	51/64	.36
1-1/4	32	4103E	2-17/64	57	1-55/64	47	5	127	1	.45


Flomatic Corporation can accept no responsibility for possible errors in catalogues, brochures and other printed material. Flomatic Corporation reserves the right to alter its products without notices. This also applies to product already agreed. All trademarks in this material are property of the respective companies. All right reserved. ©2019 Flomatic Corporation. The drawings & information on this drawing sheet are the sole & exclusive property of Flomatic Corporation. Any reproduction, distribution, display or use of these drawings or information in whole or in part without written authorization of Flomatic Corporation is strictly prohibited. www.flomatic.com


Patent # 4,971,093

Sizes 1-1/2" / 40 mm

### **Materials**

Enviro Check®





Max Temp 180°F (82°C) Max Pressure 250psi (18bar)

Item #	Qty	Description	Material	ASTM	
1	1	Body	Unleaded Bronze	C89833	
2	1	Screw	Stainless Steel	302	
3	1	Dome	Delrin	M90	
4	1	Disc	Buna-n	N-5007	
5	1	Guide	Delrin	M90	
6	1	Spring	Stainless Steel	302	
7	1	Nut	SS / Nylon Insert	18-8	
8	1	Screen	Stainless Steel	304	
9	2	Screw	Stainless Steel	18-8	
10	1	Сар	Delrin	500	

Model 60SE

# **Dimensions (FNPT)**

	Size		Devit #	Α		В		С		Weight	
	inch	mm	Part #	inch	mm	inch	mm	inch	mm	lbs	kg
ſ	1-1/2	40	4104E	2-33/64	65	2-17/64	58	5-7/16	138	1-19/32	.73

Flomatic Corporation can accept no responsibility for possible errors in catalogues, brochures and other printed material. Flomatic Corporation reserves the right to alter its products without notices. This also applies to product already agreed. All trademarks in this material are property of the respective companies. All right reserved. ©2019 Flomatic Corporation. The drawings & information on this drawing sheet are the sole & exclusive property of Flomatic Corporation, Any reproduction, distribution, display or use of these drawings or information in whole or in part without written authorization of Flomatic Corporation is strictly prohibited, www.flomatic.com





