



REGENCY®  
CEILING FANS

2015





# Ceiling Fans Made Simple

## Quality, Energy Saving Motors

The motor is responsible for supplying the power to drive the fan's blades for maximum performance. Most quality motors have electrical ratings of 1.5 amps or less because top-notch materials like high-grade copper wire, precision bearings and dynamically balanced aluminum rotors give the fan all the power it needs. Regency motors are carefully selected to be the most efficient for the fan's blade size and the room's environment, and all have electrical ratings of 1.5 amps or less.

ENERGY STAR is the government-backed symbol for energy efficiency. With more efficient fan motors and improved blade design, ENERGY STAR qualified ceiling fans provide increased comfort while saving energy. Regency offers a wide selection of ENERGY STAR qualified ceiling fans and light kits.

## Quality Blades

Regency fan blades are finished with the best real wood veneer to keep out moisture and resist warping and are computer balanced to within one gram of each other. Regency's blade arms are made of high-grade, die-cast zinc or steel. They are measured to the exact same pitch and balance and have large mounting screws with lock washers to ensure exact alignment.

## Maximum Performance

Peak performance on any fan is attained by the perfect combination of blade size, motor size, and blade pitch.

Regency's Decor-Match™ system offers endless combinations, so the recommended options for maximum performance are listed for each fan on both the fan's catalog page and the specifications guide in the back of the catalog (pages 72-76).

## Important Features for Quiet Operation

- **Bearings:** Regency only uses double-sealed, lubricated-for-life, high-grade steel bearings. The lubricant stays in and the dust and dirt stay out for quiet, lifelong operation.
- **Speed Control:** Capacitors control the speed of the fan, and Regency uses a separate one for each speed – three in every three-speed fan. Single capacitor fans can be three-speed, but often hum.
- **Vibration Isolators:** Generous use of gaskets and washers throughout a fan will dampen motor vibrations. Regency uses the highest quality rubber hang-bracket isolators, motor gaskets and blade-screw washers for quiet operation.

## Simple Installation

Proper installation is essential to guarantee a quiet, smooth running ceiling fan. All Regency fans are designed to make installation very simple and ensure that every component fits tightly together, stays in alignment and operates silently and wobble-free.

## Table of Contents

<b>Designer Series Fans</b> .....	5-20	<b>Decor-Match™ Unipack Series Fans</b> .....	33-43	<b>Outdoor Blades</b> .....	66-67
Vantage.....	6-7	Grand Marquis.....	34-35	<b>Decor-Match™ Blades</b> .....	68-69
Grander.....	8-9	Lafayette.....	36-37	<b>54" Carved Wood Blades</b> .....	70
Wexford.....	10	Envoy.....	38	<b>Downrods</b> .....	70
Strasburg.....	11	Coronado.....	39	<b>LED Light Kits</b> .....	71
Regulator.....	12	Marquis.....	40-41	<b>Light Kits</b> .....	72-73
Ciara.....	13	Countess.....	42	<b>Damp Location Light Kits</b> .....	73
Vogue.....	14	Kinder.....	43	<b>Energy Saving Light Kits</b> .....	73
Trend.....	14	<b>Outdoor Fans</b> .....	44-55	<b>Wet Location Light Kits</b> .....	73
Freestar.....	15	Vantage.....	45	<b>Energy Saving Wet Location Light Kits</b> .....	73
Bimini.....	16	Ciara.....	46	<b>Fitters</b> .....	74
Quatro.....	17	Cayman.....	47	<b>Glass Shades</b> .....	74
Quad.....	18	Oasis.....	48-49	<b>Bulbs</b> .....	75
Nola.....	19	Vera Cruz.....	50-51	<b>Ceiling Accessories</b> .....	75
Deuce.....	20	Tropic Air Outdoor.....	52	<b>Pull Chains &amp; Fobs</b> .....	75
Deuce Hugger.....	20	Bimini.....	52	<b>Switches</b> .....	75
		Andros.....	53	<b>Wall Controls</b> .....	76-77
<b>Decor-Match™ Series Fans</b> .....	21-32	Cabana.....	54	<b>Remote Controls</b> .....	78
Gladiator.....	22-23	Patio Pro.....	55	<b>Ceiling Fan Features and Specifications</b> .....	79-83
Primo.....	24	<b>Professional Series Fans</b> .....	56-62	<b>Room Size, Ceiling Height and Slope</b> .....	84
MX Excel (MX3).....	25	Professional Series with Light Kit.....	57-59	<b>Light Kit Specifications</b> .....	85-86
LX2.....	26-27	Professional Series.....	60-61	<b>Fitter Specifications</b> .....	86
Lafayette (LF3).....	28	Industrial.....	62	<b>Index</b> .....	87-88
Regatta.....	29	<b>52X Designer Decor-Match™ Blades</b> .....	63		
MX Excel (MX2).....	30-31	<b>Great Room Designer Blades</b> .....	64		
Tropic Air Indoor.....	32	<b>Grander Designer Blades</b> .....	65		

# Designer Series Fans

Designer Series Fans



Vantage  
6-7



Grander  
8-9



Wexford  
10



Strasburg  
11



Regulator  
12



Ciara  
13



Vogue  
14



Trend  
14



Freestar  
15



Bimini  
16



Quatro  
17



Quad  
18



Nola  
19



Deuce  
20



Deuce Hugger  
20

# Decor-Match & Unipack Series Fans

## Decor-Match Fans



Gladiator  
22-23



Primo  
24



MX Excel (MX3)  
25



LX2  
26-27



Lafayette (LF3)  
28



Regatta  
29



MX Excel (MX2)  
30-31



Tropic Air Indoor  
32

## Unipack Series Fans



Grand Marquis  
34-35



Lafayette  
36-37



Envoy  
38



Coronado  
39



Marquis  
40-41



Countess  
42



Kinder  
43



# Outdoor & Professional Series Fans

## Outdoor Series Fans



Vantage  
45



Ciara  
46



Cayman  
47



Oasis  
48-49



Vera Cruz  
50-51



Tropic Air Outdoor  
52



Bimini  
52



Andros  
53



Cabana  
54



Patio Pro  
55



Professional w/light  
57



Professional w/light  
58-59

## Professional Series Fans



Professional  
60-61



Industrial  
62



## Designer Series

Inspired by the latest trends in styles and materials, Regency's comprehensive collection of Designer Series ceiling fans range from classic to progressively modern designs. Designer Series fans feature custom blades to complement the overall design themes, and they are engineered with a meticulous dedication to quality, efficiency and durability.



# Vantage™



## VT-BN

Brushed Nickel fan comes  
with Silver blades  
(Indoor only)

Create a major aesthetic statement with the Vantage ceiling fan's modern industrial design featuring eight, gently curved blades. This enormous fan's whisper quiet DC motor will cool the largest of spaces and the fan's warm white LED light comes with a cover which may be used when the light is not needed.



**VT-ORB**

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades (UL wet location)

**Features:**

- Eight, 66" blades **(Included)**
- **DC-165mm motor**
- 6-speed, reversing
- 12.5° blade pitch
- 6" downrod
- Mounts to sloped ceilings up to 20°, 4/12 pitch
- LED 16W frosted glass
- 2700K Warm white color temperature
- Light output is 1200 lumens-delivered
- L70 - 36,000 hours
- Light kit cover included
- Box weight 27 lb
- Remote Control included



**Options:**

- Select Touch Wall Control (DCWC3) sold separately (Indoor use only)



Note:  
Multiple Vantage fans cannot operate on the same circuit. Each Vantage fan must have its own power switch.



**WHAT IS A DC MOTOR?**

A direct current (DC) motor is a fairly simple electric motor that uses less electrical current by utilizing powerful magnets of opposite polarity. These magnets create an internal magnetic force that works to rotate the motor, resulting in significant energy savings.

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
1	4500.48	6.3	714
2	7637.27	9.3	821
3	6027.82	10.8	558
4	7020.27	15.20	462
5	7637.27	20.60	371
6	8720.73	28.30	308



# Grander™ (MOTOR ONLY)

Select GN60/GN72 blades on page 65



## GN-ORB

Oil Rubbed Bronze fan shown with GN60-ORB  
Oil Rubbed Bronze blades and LK270-ORB  
LED light kit

### Features:

- Light kit adaptable



- Grander fan blades (GN) available in 60" and 72"

#### • DC-165mm motor

- 6-speed
- 13.5° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch



- Box weight 22.05 lb
- Remote Control included

### Options:



- Select Touch Wall Transmitter (DCWC3) sold separately

Note:

Multiple Grander fans cannot operate on the same circuit.  
Each Grander fan must have its own power switch.

## DC MOTOR

### WHAT IS A DC MOTOR?

A direct current (DC) motor is a fairly simple electric motor that uses less electrical current by utilizing powerful magnets of opposite polarity. These magnets create an internal magnetic force that works to rotate the motor, resulting in significant energy savings.



### GN-AC

Antique Copper fan shown with  
GN72-AC Antique Copper blades



### GN-CW

Chalk White fan shown with  
GN72-CW Chalk White blades



### GN-BN

Brushed Nickel fan shown with  
GN60-MH Mahogany blades

## 60 inch blades

Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
1	1901.99	3.2	594.37
2	2789.67	4.2	664.21
3	3517.62	7.0	502.52
4	4703.46	11.6	405.47
5	5505.07	17.4	316.38
6	6791.70	31.2	217.68

## 72 inch blades

Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
1	2837.52	4.1	692.08
2	3460.63	5.9	586.55
3	4314.41	8.6	501.68
4	5449.91	12.6	432.53
5	6136.44	17.4	352.67
6	7682.73	31.2	246.24



# Wexford™ with Mood Glow™ Uplight



## WX-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades

### Features:



- 60" blades **(Included)**
- Mood Glow-Uplight
- 212 x 25mm motor
- 3-speed forward, reversing
- 12° blade pitch
- 6" and 12" downrods included\*
- Mounts to sloped ceilings up to 25°, 5/12 pitch
- 4 x 25W candelabra (E12) upper light included
- 4 x 40W candelabra (E12) lower light included
- Box weight 59.5 lb
- Select Touch Wall Transmitter (2WWCD) included



\*The Wexford downrod is 3/4" diameter. See page 70 for item numbers.

### Options:



- Remote Control Transmitter (RCTD) sold separately

#### Mounting Recommendation

To reduce the risk of fire, electric shock or personal injury, mount this fan to an outlet box marked "ACCEPTABLE FOR FAN SUPPORT OF 70 LBS." and USE MOUNTING SCREWS PROVIDED WITH THE OUTLET BOX.

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2956.00	25.00	118
High	5960.00	90.00	66

# Strasburg™ with Mood Glow™ Uplight



## ST-ORB

Oil Rubbed Bronze fan comes with combination Oil Rubbed Bronze/Cherry blades

### Features:



- Light kit adaptable
- 60" blades **(Included)**
- Mood Glow-Uplight
- 188 x 25mm motor
- 3-speed forward, reversing
- 14° blade pitch
- 6" and 12" downrods included
- Mounts to sloped ceilings up to 25°, 5/12 pitch
- 6 x 15W candelabra (E12) upper light included
- Box weight 38.6 lb
- Select Touch Wall Transmitter (2WWCD) included



### Options:



- Remote Control Transmitter (RCTD) sold separately

#### Mounting Recommendation

To reduce the risk of fire, electric shock or personal injury, mount this fan to an outlet box marked "ACCEPTABLE FOR FAN SUPPORT OF 70 LBS." and USE MOUNTING SCREWS PROVIDED WITH THE OUTLET BOX.


Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2740.00	22.00	124
High	6105.00	80.00	76



# Regulator™


## RL-AC

Antique Copper fan comes with combination Antique Copper/Teak blades



## RL-BN

Brushed Nickel fan comes with combination Cherry/Mahogany blades



## RL-ORB

Oil Rubbed Bronze fan comes with combination Oil Rubbed Bronze/Dark Walnut blades (Shown with LK80A-ORB light kit)



### Features:

- Light kit adaptable
- 60" blades **(Included)**
- 212 x 25mm motor
- 3-speed forward, reversing
- 16° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- Box weight 33.7 lb

### Options:



- Full function remote control (sold separately) requires purchase of RCR-G - receiver, RC2 - housing
- RCT - Remote Control Transmitter
  - or
  - 2WWC - Select Touch Wall Transmitter

#### Mounting Recommendation

To reduce the risk of fire, electric shock or personal injury, mount this fan to an outlet box marked "ACCEPTABLE FOR FAN SUPPORT OF 70 LBS." and USE MOUNTING SCREWS PROVIDED WITH THE OUTLET BOX.

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2805.00	22.00	127
High	5873.00	88.00	67

# Ciara™ (wet location)

## CI-AW

Appliance White fan comes with Appliance White blades (UL wet location)



## CI-MB

Matte Black fan comes with Matte Black blades (Shown with LK95W-MB Matte Black light kit) (UL wet location)



## CI-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades (UL wet location)



### Features:

- Light kit adaptable
- 52" blades **(Included)**
- 172 x 14mm motor
- 3-speed forward, manual reversing from switch
- 13° blade pitch
- 4" downrod
- Mounts to sloped ceilings up to 20°, 4/12 pitch
- Box weight 20 lb



- UL wet location rating

### Options:



- Universal Remote Controls (URC-WL)/ (URC-WLES) sold separately

See page 73 for wet location light kits.

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1832.91	9.7	199
High	5270.39	61	87



# Vogue™ with Mood Glow™ Uplight

## VG-BN

Brushed Nickel fan comes with Cherry blades

### Features:



- Four 60" blades **(Included)**
- Mood Glow-Uplight
- 212 x 25mm motor
- 3-speed forward, reversing
- 14° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 23°, 5/12 pitch
- 4 x 40W candelabra (E12) upper light included\*
- Box weight 37.5 lb



- Remote Control included
- \*replacement bulb - LX-bulb

### Options:



- Optional Blade Set Available (60VGMHS) Mahogany
- Select Touch Wall Transmitter (2WWC) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2640.00	17.00	155
High	5930.00	85.00	70

### Mounting Recommendation

To reduce the risk of fire, electric shock or personal injury, mount this fan to an outlet box marked "ACCEPTABLE FOR FAN SUPPORT OF 70 LBS." and USE MOUNTING SCREWS PROVIDED WITH THE OUTLET BOX.

# Trend™ with Mood Glow™ Uplight

## TN-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades

### Features:



- Four 52" blades **(Included)**
- Mood Glow-Uplight
- 153 x 17mm motor
- 3-speed forward, reversing
- 14° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 23°, 5/12 pitch
- 4 x 25W candelabra (E12) upper light included\*



- Box weight 19.8 lb
- Remote Control included
- \*replacement bulb - LX-bulb

### Options:




- Select Touch Wall Transmitter (2WWC) sold separately



## TN-BN

Brushed Nickel fan comes with Cherry blades



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1549.00	12.00	129
High	4870.00	69.00	71

# Freestar™ with Mood Glow™ Uplight

## FS-SS

Satin Steel fan comes with combination Cherry/Mahogany blades (shown with Cherry blade side)



## FS-SS

Satin Steel fan comes with combination Cherry/Mahogany blades (shown with Mahogany blade side)



## Features:



- 56" blades **(Included)**
- Mood Glow-Uplight
- 188 x 22mm motor
- 3-speed forward, manual reversing from fan switch
- 14° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 29°, 6/12 pitch
- 4 x 25W candelabra (E12) upper light (included)\*
- 1 x 100W "JDE 11" halogen bulb (E11) lower light included
- Box weight 31.5 lb
- Wall Transmitter included
- \*replacement bulb - LX-bulb

## Options:



- Remote Control Transmitter (RCTD) sold separately

### Mounting Recommendation

To reduce the risk of fire, electric shock or personal injury, mount this fan to an outlet box marked "ACCEPTABLE FOR FAN SUPPORT OF 70 LBS." and USE MOUNTING SCREWS PROVIDED WITH THE OUTLET BOX.

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2107.00	14.00	150
High	5609.00	68.00	82

# Bimini™ (indoor only)

## BI-BN

Brushed Nickel fan comes with Silver blades



## BI-BN

Brushed Nickel fan shown with optional (60BIMH) Mahogany blades



See page 52 for BIM fan (Wet Location) Specifications

## BIM-AW

Appliance White fan comes with Appliance White ABS blades and remote control (UL wet location)

## BIM-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze ABS blades and remote control (UL wet location)



## Features:

- Light kit adaptable
- 60" blades **(Included)**
- 188 x 22mm motor
- 3-speed, manual reversing from fan switch
- 14° blade pitch
- 4" downrod included
- Downrod mounting only
- Mounts to sloped ceilings up to 23°, 5/12 pitch
- Box weight 27.6 lb
- Remote Control included



## Options:

- Select Touch Wall Transmitter (2WWC) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2846.00	17.00	167
High	6857.00	72.00	95



# Quatro™

## QU-BN

Brushed Nickel fan comes with combination Cherry/Mahogany blades (shown with Cherry blade side)



## QU-BN

Brushed Nickel fan comes with combination Cherry/Mahogany blades (shown with Mahogany blade side)



## Features:

- Four 52" blades **(Included)**
- 188 x 15mm motor
- 3-speed forward, reversing
- 12° blade pitch
- 4" downrod included
- Optional light kit cap cover included
- Mounts to sloped ceilings up to 30°, 7/12 pitch
- 1 x 100W "JDE 11" halogen bulb (E11)
- Box weight 22.3 lb
- Remote Control included



## Options:

- Select Touch Wall Transmitter (2WWC) sold separately
- Optional Blade Set Available (52QUSS) Silver



Silver  
52QUSS

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1530.00	11.00	137
High	4902.00	58.00	85

# Quad™

## QD-BN

Brushed Nickel fan comes with combination Cherry/Mahogany blades and light kit (shown with Cherry blade side)



## QD-BN

Brushed Nickel fan comes with combination Cherry/Mahogany blades and light kit (shown with Mahogany blade side)



## QD-BN

Brushed Nickel fan comes with combination Cherry/Mahogany blades and light kit (shown with optional Silver blades)



## Features:

- Four 52" blades **(Included)**
- 153 x 18mm motor
- 3-speed, manual reversing from fan switch
- 14° blade pitch
- 6" downrod included
- Optional light kit cap cover included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- 2 x 13W GU-24 CFL
- Box weight 20.5 lb
- Remote Control included



## Options:

- Optional Blade Set Available (52QDSS) Silver



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1806.91	11.30	160
High	5319.70	66.00	81

# NoLa™

## NL-BN

Brushed Nickel fan comes with Silver blades



## NL-CW

Chalk White fan comes with Chalk White blades



## NL-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades



### Features:

- 52" blades **(Included)**
- 172 x 15mm motor
- 3-speed forward, reversing
- 14° blade pitch
- 1 x 100W "JDE 11" halogen bulb (E11)
- Box weight 22.5 lb
- Remote Control included



### Options:

- Select Touch Wall Transmitter (2WWC) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1476.00	18.50	80
High	4133.00	64.00	65



# Deuce™

## DU-BN

Brushed Nickel fan comes with Silver blades



### Features:

- Custom 54" blades **(Included)**
- 153 x 22mm motor
- 3-speed forward, reversing
- 15° blade pitch
- 4" downrod included
- Optional light kit cap cover (included)
- Mounts to sloped ceilings up to 29°, 6/12 pitch
- 1 x 75W halogen bulb (E11) (included)



- Box weight 21.6 lb
- Remote Control included

### Options:

- Select Touch Wall Transmitter (2WWC) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1773.00	10.00	177
High	5968.00	69.00	86

# Deuce Hugger™

## DH-MB

Matte Black fan comes with Matte Black blades



### Features:

- Custom 54" blades **(Included)**
- 153 x 22mm motor
- 3-speed forward, reversing
- 14° blade pitch
- Optional light kit cap cover (included)
- 1 x 75W halogen bulb (E11) lower light included



- Box weight 21.2 lb
- Remote Control included

### Options:

- Select Touch Wall Transmitter (2WWC) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1773.00	10.00	177
High	5968.00	69.00	86



## Decor-Match Series

Regency's Decor-Match™ Series allows for customization to match personal styles and home décors. Select from a large variety of ceiling fan motors, blades, light kits and fan controls. Although the Decor-Match Series fans are shown in the photos with suggested blades, most Decor-Match ceiling fans may accommodate most Decor-Match, Designer and outdoor blades and light kits.

# Gladiator™ (MOTOR ONLY)

Select TB60 blades on page 64

## GL3-AC

Antique Copper fan shown with  
TB60-AC Antique Copper blades and  
LK270-AC LED light kit



## GL3-SS

Satin Steel fan shown with  
TB60-MP Maple blades



### Features:



- Light kit adaptable
- Gladiator TB60 blades on page 64

#### • DC-125mm motor

- 6-speed
- 16° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- Box weight 22.4 lb
- Remote Control included



### Options:



- Select Touch Wall Transmitter (DCWC3) sold separately

Note:  
Multiple GL3 fans cannot operate on the same circuit.  
Each GL3 fan must have its own power switch.



*Decor-Match™*  
SYSTEM

DC MOTOR

#### WHAT IS A DC MOTOR?

A direct current (DC) motor is a fairly simple electric motor that uses less electrical current by utilizing powerful magnets of opposite polarity. These magnets create an internal magnetic force that works to rotate the motor, resulting in significant energy savings.



### GL3-CW

Chalk White fan shown with  
TB60-CW Chalk White blades



### GL3-ORB

Oil Rubbed Bronze fan shown with  
TB60-ORB Oil Rubbed Bronze blades



### GL3-BN

Brushed Nickel fan shown with TB60-CR  
Cherry blades and LK65-BN light kit



Performance and Energy Information					
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)	AMP (A)	RPM
1	2787.6	4.7	633.53	0.08	50
2	3443.94	8.2	529.84	0.14	65
3	4085.43	11.6	408.54	0.18	78
4	4859.42	17.5	373.80	0.25	92
5	5455.99	24.4	272.80	0.33	106
6	6563.5	32.3	218.78	0.45	121

# Primo™ with Mood Glow™ Uplight

(MOTOR ONLY)

Select TB60 blades on page 64

## PR-ORB

Oil Rubbed Bronze fan shown with TB60-ORB Oil Rubbed Bronze blades



## PR-BN

Brushed Nickel fan shown with TB60-MHS Mahogany blades



## Features:



- Light kit adaptable
- Primo TB60 blades on page 64
- Mood Glow-Uplight
- 212 x 25mm motor
- 3-speed, reversing
- 16° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- 4 x 25W candelabra (E12) upper light (included)\*
- Box weight 32.8 lb
- \*replacement bulb - LX-bulb

## Options:



- Full function remote control (sold separately) requires purchase of RCRD-P - receiver, RC2 - housing
- RCTD - Remote Control Transmitter
- or
- 2WWCD - Select Touch Wall Transmitter



### Mounting Recommendation

To reduce the risk of fire, electric shock or personal injury, mount this fan to an outlet box marked "ACCEPTABLE FOR FAN SUPPORT OF 70 LBS." and USE MOUNTING SCREWS PROVIDED WITH THE OUTLET BOX.



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	3015.00	21.00	143
High	8670.00	95.00	91

# MX Excel™ with Mood Glow™ Uplight (MOTOR ONLY)

## MX3-BN

Brushed Nickel fan  
shown with 52CR Cherry blades



## MX3-CW

Chalk White fan  
shown with 52CW Chalk White blades






## MX3-ORB


Oil Rubbed Bronze fan  
shown with 52TK Teak blades  
and LK14A-ORB light kit



### Features:

- Light kit adaptable
-  • Decor-Match™ blade options available. Recommend 52", 56" and designer blades.
-  • Mood Glow-Uplight
- 188 x 22mm motor
- 3-speed, reversing
- 16° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- 4 x 25W candelabra (E12) upper light (included)\*
-  • Box weight 23.1 lb
- Remote Control included
- \*replacement bulb - LX-bulb

### Options:

-  • Select Touch Wall Transmitter (2WWCD) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1985.00	11.00	180
High	5345.00	58.00	92



# LX2™ with Mood Glow™ Uplight (MOTOR ONLY)

## LX2-AC

Antique Copper fan shown with 56AC Antique Copper blades and LK65A-AC light kit



## LX2-BN

Brushed Nickel fan shown with 56AWS Appliance White blades and LK14-BN light kit



### Features:



- Light kit adaptable
- Decor-Match™ blade options available. Recommend 52", 56" and designer blades.



- Mood Glow-Uplight
- 188 x 20mm motor
- 3-speed, reversing
- 14° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 33°, 8/12 pitch
- 4 x 25W candelabra (E12) upper light (included)\*
- Box weight 19.8 lb

\*replacement bulb - LX-bulb

### Options:



Full function remote control (sold separately) requires purchase of RCRD - receiver, RC2 - housing



- RCTD - Remote Control Transmitter
- or
- 2WWCD - Select Touch Wall Transmitter



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	3300.00	25.00	133
High	6540.00	72.00	91

### **LX2-CW**

Chalk White fan shown with  
56CW Chalk White blades



### **LX2-ORB**

Oil Rubbed Bronze fan shown with  
56ORB Oil Rubbed Bronze blades



### **LX2-DI**

Desert Ivory fan shown with  
56DI Desert Ivory blades



**Decor-Match™**  
SYSTEM

# lafayette™ with Mood Glow™ Uplight

(MOTOR ONLY)

## LF3-AC

Antique Copper fan shown with  
52AC Antique Copper blades



## LF3-ORB

Oil Rubbed Bronze fan shown with  
52ORB Oil Rubbed Bronze blades



### Features:

- Light kit adaptable
- Decor-Match™ blade options available. Recommend 44", 52" and designer blades.
- Mood Glow-Uplight
  - 188 x 15mm motor
  - 3-speed, reversing
  - 14° blade pitch
  - 6" downrod included
  - 4 x 25W candelabra (E12) upper light (included)\*
  - Mounts to sloped ceilings up to 22°, 5/12 pitch
  - Box weight 22 lb
- \*replacement bulb - LX-bulb
- Remote Control included

### Options:

- Select Touch Wall Transmitter (2WWCD) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1996.00	10.00	199
High	5220.00	60.00	87



# Regatta™ with Mood Glow™ Uplight

(MOTOR ONLY)

## RT-ORB

Oil Rubbed Bronze fan shown  
with 52ORB Oil Rubbed  
Bronze blades



## RT-BN

Brushed Nickel fan shown  
with 52CR Cherry blades



### Features:



- Light kit adaptable
- Decor-Match™ blade options available. Recommend 44", 52" and designer blades.



- Mood Glow-Uplight
- 188 x 15mm motor
- 3-speed forward, reversing
- 14° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 30°, 7/12 pitch
- 4 x 25W candelabra (E12) upper light (included)\*
- Optional uplight/downlight remote control
- Box weight 19.8 lb

\*replacement bulb - LX-bulb

### Options:



Full function remote control (sold separately)  
requires purchase of RCRD - receiver, RC2 - housing



- RCTD - Remote Control Transmitter
- or
- 2WWCD - Select Touch Wall Transmitter



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1759.00	11.00	160
High	5120.00	55.00	93

# MX Excel™

(MOTOR ONLY)

## MX2-AC

Antique Copper fan shown with 52TK Teak blades and LK60A-AC light kit (without decorative bars)



## MX2-ORB

Oil Rubbed Bronze fan shown with 52TK Teak blades and LK14A-ORB light kit



## MX2-BN

Brushed Nickel fan shown with 52XCR Cherry blades and LK270-BN LED light kit



### Features:

- Light kit adaptable
- Decor-Match™ blade options available. Recommend 52", 56" and designer blades.
- Flush mount capability
- 188 x 22mm motor
- 3-speed, reversing
- 16° blade pitch
- 3" and 6" downrods included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- Box weight 19.8 lb

### Options:

- Full function remote control (sold separately) requires purchase of RCR - receiver, RC2 - housing
- RCT - Remote Control Transmitter
- or
- 2WWC - Select Touch Wall Transmitter



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1985.00	11.00	180
High	5345.00	58.00	92



### **MX2-AB**

Antique Brass fan shown with 52XDW Dark Walnut blades



### **MX2-CW**

Chalk White fan shown with 52XCW Chalk White blades and LK80-CW Chalk White light kit



### **MX2-CW**

Chalk White fan shown with 52CW Chalk White blades and LK60-CW Chalk White light kit



### **MX2-SS**

Satin Steel fan shown with 52MP Maple blades



### **MX2-AW**

Appliance White fan shown with 52AWS Appliance White blades



### **MX2-MB**

Matte Black fan shown with 52MB Matte Black blades



### **MX2-BR**

Polished Brass fan shown with 56LG Medium Oak blades



### **MX2-DI**

Desert Ivory fan shown with 52DI Desert Ivory blades



# Tropic Air™ INDOOR

(MOTOR ONLY)

## TA2-DI

Desert Ivory fan shown with WL52NAT  
Natural carved wood leaf blades



## TA2-DI

Desert Ivory fan shown  
with PP52NAT+ Natural  
palm ABS blades



See page 52 for TA2-ORB (Wet Location) Specifications

## TA2-ORB

Oil Rubbed Bronze fan shown with 52OAORB  
Oil Rubbed Bronze blades (UL wet location)



### Features:



- Light kit adaptable
- Decor-Match™ blade options available.  
Recommend 52", 56" and designer blades.
- 188 x 25mm motor
- 3-speed, reversing
- 20° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 33°, 8/12 pitch
- Box weight 22 lb

### Options:



- Full function remote control (sold separately)  
requires purchase of RCR - receiver, RC2 - housing
- RCT - Remote Control Transmitter
- or
- 2WWC - Select Touch Wall Transmitter



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1100.00	13.00	85
High	5530.00	63.00	88



## Regency's Decor-Match Unipack Fans

Regency's Decor-Match Unipack Series consists of the most popular ceiling fan models with coordinating fan blades included in the box with the fans. The 52X blades are crafted from exquisite wood materials and contoured and tapered to complement all of the Unipack Series fan designs. Optional designer Decor-Match blades may be purchased separately for the Unipack Series fans.



# Grand Marquis™ (UNIPACK)

## GMRP-BN

Brushed Nickel fan comes with 52XCR/MH combination Cherry/Mahogany blades and LK65-BN (with Alabaster glass) light kit. Shown with Cherry blades.



## GMRP-BN

Brushed Nickel fan comes with 52XCR/MH combination Cherry/Mahogany blades and LK65-BN (with Alabaster glass) light kit. Shown with Mahogany blades.



### Features:

- 52X Decor-Match blades **(INCLUDED)**
- Decor-Match™ blade options available. Recommend 44", 52" blades.
- Flush mount capability
- LK65 light kit **(INCLUDED)**
- 188 X 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 4" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- Box weight 22.3 lb

### Options:

- Full function remote control (sold separately) requires purchase of RCR - receiver, RC2 - housing
- RCT - Remote Control Transmitter or
- 2WWC - Select Touch Wall Transmitter



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1829.00	11.30	161
High	5120.00	54.00	94



### **GMRP-CW**

Chalk White fan comes with 52XCW  
Chalk White blades and LK65-CW  
(with Alabaster glass) light kit.



### **GMRP-ORB**

Oil Rubbed Bronze fan comes with  
52XDW/ORB combination Dark  
Walnut/Oil Rubbed Bronze blades and  
LK65-ORB (with Alabaster glass) light  
kit (Shown with Dark Walnut blades)



### **GMRP-ORB**


Oil Rubbed Bronze fan comes with  
52XDW/ORB combination Dark  
Walnut/Oil Rubbed Bronze blades  
and LK65-ORB (with Alabaster glass)  
light kit (Shown with Oil Rubbed  
Bronze blades)



# lafayette™ (UNIPACK)

## LF-AC

Antique Copper fan comes with 52XAC/MH combination Antique Copper/Mahogany blades (Shown with Antique Copper blades)




## LF-ORB

Oil Rubbed Bronze fan comes with 52XDW/ORB combination Dark Walnut/Oil Rubbed Bronze blades (Shown with Oil Rubbed Bronze blades)



## LF-DI

Desert Ivory fan comes with 52XDI Desert Ivory blades



## Features:

- Light kit adaptable
- 52X Decor-Match blades **(INCLUDED)**
- Decor-Match™ blade options available. Recommend 44", 52" and designer blades.
- Flush mount capability
- 188 x 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- Box weight 29 lb



## Options:



Full function remote control (sold separately) requires purchase of RCR - receiver, RC2 - housing

- RCT - Remote Control Transmitter

or

- 2WWC - Select Touch Wall Transmitter



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1620.00	9.90	163
High	5617.00	66.00	85

### **LF-CW**

Chalk White fan comes with  
52XCW Chalk White blades



### **LF-MB**

Matte Black fan comes with  
52XMB Matte Black blades



### **LF-BN**

Brushed Nickel fan comes  
with 52XCR/MH combination  
Cherry/Mahogany blades  
(Shown with Mahogany blades)





# Envoy™ with Mood Glow™ Uplight (UNIPACK)

## EN2-AC

Antique Copper fan comes with 52XAC/MH combination Antique Copper/Mahogany blades (Shown with Antique Copper blades)



## EN2-ORB

Oil Rubbed Bronze fan comes with 52XDW/ORB combination Dark Walnut/Oil Rubbed Bronze blades (Shown with Oil Rubbed Bronze blades)



## EN2-CW

Chalk White fan comes with 52XCW Chalk White blades



## Features:

- Light kit adaptable
- 52X Decor-Match blades **(INCLUDED)**
- Decor-Match™ blade options available. Recommend 44", 52" and designer blades.



- Mood Glow-Uplight
- 188 x 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 33°, 8/12 pitch
- 4 x 25W candelabra (E12) upper light (included)\*
- Box weight 19.8 lb

\*replacement bulb - LX-bulb

## EN2-BN

Brushed Nickel fan comes with 52XCR/MH combination Cherry/Mahogany blades (Shown with Mahogany blades)



## Options:



Full function remote control (sold separately) requires purchase of RCRD - receiver, RC2 - housing

- RCTD - Remote Control Transmitter

or



- 2WWCD - Select Touch Wall Transmitter

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2544.00	13.00	191
High	5655.00	69.00	82

# Coronado™ with Mood Glow™ Uplight (UNIPACK)



## CN-ORB

Oil Rubbed Bronze fan comes with 52XDW/ORB combination Dark Walnut/Oil Rubbed Bronze blades (Shown with Oil Rubbed Bronze blades)

### Features:

- Light kit adaptable
- 52X Decor-Match blades **(INCLUDED)**
- Decor-Match™ blade options available  
Recommend 44", 52" and designer blades.



- Mood Glow-Uplight
- 188 x 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 6" downrod included
- Mounts to sloped ceilings up to 33°, 8/12 pitch
- 4 x 25W candelabra (E12) upper light (included)\*
- Box weight 29.8 lb

\*replacement bulb - LX-bulb

### Options:



- Full function remote control (sold separately)  
requires purchase of RCRD - receiver, RC2 - housing
- RCTD - Remote Control Transmitter  
or
- 2WWCD - Select Touch Wall Transmitter



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2043.00	10.00	200
High	5345.00	62.00	86

# Marquis™ (UNIPACK)

## MR2-BN

Brushed Nickel fan comes with 52XCR/MH combination Cherry/Mahogany blades (Shown with Cherry blades and LK9-BN light kit)



## MR2-AC

Antique Copper fan comes with 52XAC/MH combination Antique Copper/Mahogany blades (Shown with Antique Copper blades)



### Features:

- Light kit adaptable
- 52X Decor-Match blades **(INCLUDED)**
- Decor-Match™ blade options available Recommend 44", 52" and designer blades.
- Flush mount capability
- 188 x 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 4" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- Box weight 21.6 lb

### Options:

- Full function remote control sold separately requires purchase of RCR - receiver, RC2 - housing
- RCT - Remote Control hand held Transmitter or
- 2WWC - Select Touch Wall Transmitter



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1829.00	11.30	161
High	5210.00	54.00	95



### **MR2-ORB**

Oil Rubbed Bronze fan comes with 52XDW/ORB combination Dark Walnut/Oil Rubbed Bronze blades (Shown with Oil Rubbed Bronze blades)



### **MR2-AW**

Appliance White fan comes with 52XAW Appliance White blades



### **MR2-MB**

Matte Black fan comes with 52XMB Matte Black blades



### **MR2-CW**

Chalk White fan comes with 52XCW Chalk White blades



### **MR2-SS**

Satin Steel fan comes with 52XCR/MP combination Cherry/Maple blades (Shown with Cherry blades and LK9-SS light kit)



### **MR2-DI**

Desert Ivory fan comes with 52XDI Desert Ivory blades



### **MR2-MS**

Mojave Sand fan comes with 52XMS Mojave Sand blades



### **MR2-AB**

Antique Brass fan comes with 52XDG/LG combination Walnut/Medium Oak blades (Shown with Medium Oak blades)



### **MR2-BR**


Polished Brass fan comes with 52XDG/LG combination Walnut/Medium Oak blades (Shown with Walnut blades)



# Countess™ (UNIPACK)


## CT-BN

Brushed Nickel fan comes with 42XCR/MH combination Cherry/Mahogany blades (Shown with Cherry blades)



## CT-AW

Appliance White fan comes with 42XAW Appliance White blades



## CT-ORB

Oil Rubbed Bronze fan comes with 42XDW/ORB combination Dark Walnut/Oil Rubbed Bronze blades (Shown with Oil Rubbed Bronze blades)



### Features:

- Light kit adaptable
- 42X Decor-Match blades **(INCLUDED)**
- Decor-Match™ blade options available  
Recommend 27", 36" , 42" blades.
- Flush mount capability
- 153 x 10mm motor
- 3-speed, reversing
- 14° blade pitch
- 4" downrod included
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- Box weight 15 lb

### Options:

- Universal Remote Control (URC) sold separately
- Select Touch Wall Transmitter (2WWC) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1135.00	10.60	107
High	3185.00	49.00	65

# Kinder™ (UNIPACK)

## KD-BN

Brushed Nickel fan comes with 30" CR/MH combination Cherry/Mahogany blades (Shown with Cherry blades)



## KD-CW

Chalk White fan comes with 30" CW Chalk White blades



## KD-ORB

Oil Rubbed Bronze fan comes with 30" DW/ORB combination Dark Walnut/Oil Rubbed Bronze blades (Shown with Oil Rubbed Bronze blades)



## Features:

- Light kit adaptable
- 30" Decor-Match blades **(INCLUDED)**
- Flush mount capability
- 153 x 10mm motor
- 3-speed, manual reversing from fan switch
- 14° blade pitch
- 4.5" downrod included
- Mounts to sloped ceilings up to 28°, 6/12 pitch
- Box weight 13.8 lb



## Options:

- Universal Remote Control (URC) sold separately
- Select Touch Wall Transmitter (2WWC) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	870.76	8.40	104
High	1751.01	42.00	42





## Outdoor Fans

Regency's "damp" and "wet" location Underwriters Laboratories (UL) approved fans are perfect for enjoying the outdoors, no matter how hot and damp the weather. UL tests outdoor fans against a series of quality standards to ensure the electrical and mechanical safety of the fans. Damp rated fans are designed to be hung in completely covered areas that will not be exposed to direct contact with rain or water spray. "Wet" rated fans must pass stricter testing, including water spray tests, while maintaining electrical and mechanical safety.

Designs ranging from contemporary to traditional are offered in a variety of finishes to complement all décor. Custom blades are included with most outdoor fans, and most outdoor fans can accommodate any of Regency's optional designer outdoor blades.

# Vantage™ (wet location)



## VT-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades (UL wet location)

### Features:

- Eight, 66" blades **(Included)**
- **DC-165mm motor**
- 6-speed, reversing
- 12.5° blade pitch
- 6" downrod
- Mounts to sloped ceilings up to 20°, 4/12 pitch
- LED 16W frosted glass
- 2700K Warm white color temperature
- Light output is 1200 lumens-delivered
- L70 - 36,000 hours
- Light kit cover included
- Box weight 27 lb
- Remote Control included
- UL wet location rating



Note:  
Multiple Vantage fans cannot operate on the same circuit.  
Each Vantage fan must have its own power switch.

### DC MOTOR

#### WHAT IS A DC MOTOR?

A direct current (DC) motor is a fairly simple electric motor that uses less electrical current by utilizing powerful magnets of opposite polarity. These magnets create an internal magnetic force that works to rotate the motor, resulting in significant energy savings.

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
1	4500.48	6.3	714
2	7637.27	9.3	821
3	6027.82	10.8	558
4	7020.27	15.20	462
5	7637.27	20.60	371
6	8720.73	28.30	308



# Ciara™ (wet location)

## CI-AW

Appliance White fan comes with Appliance White blades (UL wet location)




## CI-MB

Matte Black fan comes with Matte Black blades. Shown with LK95W-MB Matte Black light kit. (UL wet location)



## CI-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades (UL wet location)



### Features:

- Light kit adaptable
- 52" blades **(Included)**
- 172 x 14mm motor
- 3-speed forward, manual reversing from switch
- 13° blade pitch
- 4" downrod
- Mounts to sloped ceilings up to 20°, 4/12 pitch
- Box weight 20 lb



- UL wet location rating

### Options:



- Universal Remote Controls (URC-WL)/ (URC-WLES) sold separately

See page 73 for wet location light kits.

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1832.91	9.7	199
High	5270.39	61	87

# Cayman™ (wet location)

## CM-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze ABS blades (UL wet location)



## CM-AW

Appliance White fan comes with Appliance White ABS blades. Shown with LK95W-AW Appliance White light kit (UL wet location)



## CM-AW

Appliance White fan comes with Appliance White ABS blades (UL wet location)



### Features:

- Light Kit adaptable
- 52" blades **(Included)**
- Decor-Match™ blade options available. Recommend 52", 56" and designer blades
- 188 x 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 4" downrod included (optional downrods available)
- Mounts to sloped ceilings up to 30°, 7/12 pitch
- Downrod mounting only
- Box weight 36.4 lb
- UL wet location rating



### Options:



- Universal Remote Controls (URC-WL)/ (URC-WLES) sold separately

See page 73 for wet location light kits.

#### Mounting Recommendation

To reduce the risk of fire, electric shock or personal injury, mount this fan to an outlet box marked "ACCEPTABLE FOR FAN SUPPORT OF 70 LBS." and USE MOUNTING SCREWS PROVIDED WITH THE OUTLET BOX.



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2235.00	14.00	159
High	5530.00	75.00	73

# OASIS™ (wet location)

## OA2-AW

Appliance White fan comes with Appliance White ABS blades (UL wet location)



## OA2-AW

Appliance White fan shown with PP52AW+ Appliance White palm ABS blades (UL wet location)



## OA2-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades. Shown with LK90W-ORB Oil Rubbed Bronze light kit (UL wet location)



### Features:

- Light kit adaptable
- ABS fan housing
- 52" blades **(Included)**
- Decor-Match™ blade options available
- 188 x 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 4" downrod included (optional downrods available)
- Mounts to sloped ceilings up to 26°, 6/12 pitch
- Downrod mounting only
- Box weight 22.3 lb
- UL wet location rating



### Options:

- Universal Remote Controls (URC-WL)/ (URC-WLES) sold separately



See page 73 for wet location light kits.



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2276.00	10.00	228
High	6571.00	69.00	95



### OA2-AW

Appliance White fan shown with PL52AW Appliance White leaf ABS blades (UL wet location)




### OA2-MB

Matte Black fan shown with PL52MHS Matte Black Mahogany leaf ABS blades (UL wet location)



### OA2-MB

Matte Black fan comes with Matte Black blades (UL wet location)



### OA2-MS

Mojave Sand fan shown with PP52NAT+ Natural palm ABS blades (UL wet location)



### OA2-MS

Mojave Sand fan comes with Mojave Sand ABS blades (UL wet location)



### OA2-MS

Mojave Sand fan shown with PL52NAT Natural leaf ABS blades (UL wet location)



### OA2-ORB

Oil Rubbed Bronze fan shown with 52CMORB Oil Rubbed Bronze ABS (UL wet location)



### OA2-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades. Shown with LK95W-ORB Oil Rubbed Bronze light kit (UL wet location)



### OA2-ORB

Oil Rubbed Bronze fan shown with PL52MHS Mahogany leaf ABS blades and BRCH-ORB blade arms (UL wet location)



# VERA CRUZ™ (wet location)

## VC2-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze ABS blades (UL wet location)



## VC2-ORB

Oil Rubbed Bronze fan shown with PL52MHS Mahogany leaf ABS blades and BRCH-ORB blade arms (UL wet location)



### Features:



- Light kit adaptable
- 52" blades **(Included)**
- Decor-Match™ blade options available
- Flush mount capability
- 188 x 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 4" downrod included (optional downrods available)
- Mounts to sloped ceilings up to 35°, 8/12 pitch
- Box weight 18.7 lb



- UL wet location rating

### Options:



- Universal Remote Controls (URC-WL)/ (URC-WLES) sold separately

See page 73 for wet location light kits.



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2325.00	11.00	219
High	5871.00	57.00	103

### **VC2-MB**

Matte Black fan comes with  
Matte Black ABS blades  
Shown with LK95W-MB Matte Black light kit  
(UL wet location)



### **VC2-MB**

Matte Black fan shown with  
PL52MHS Mahogany leaf ABS  
blades (UL wet location)



### **VC2-MB**

Matte Black fan comes with  
Matte Black ABS blades  
(UL wet location)



# Tropic Air™ Outdoor

(wet location)  
(MOTOR ONLY)

## TA2-ORB

Oil Rubbed Bronze fan shown with 52OAORB  
Oil Rubbed Bronze blades (UL wet location)

### Features:



- Light kit adaptable
- Decor-Match™ blade options available.  
Recommend 52" and designer blades
- 188 x 25mm motor
- 3-speed, reversing
- 20° blade pitch
- 6" downrod included (optional downrods available)
- Mounts to sloped ceilings up to 33°, 8/12 pitch
- Box weight 22 lb



- UL wet location rating



### Options:

- Universal Remote Controls (URC-WL)/  
(URC-WLES) sold separately

See page 73 for wet location light kits.



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1100.00	13.00	85
High	5530.00	63.00	88

# Bimini™ (wet location)

## BIM-AW

Appliance White fan comes with Appliance White  
ABS blades and remote control (UL wet location)

## BIM-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze  
ABS blades and remote control (UL wet location)

See page 16 for BI-BN fan (Indoor Only)

### Features:




- Light kit adaptable
- 60" blades **(Included)**
- 188 x 22mm motor
- 3-speed, manual reversing from fan switch
- 14° blade pitch
- 4" downrod included (optional downrods available)
- Downrod mounting only
- Mounts to sloped ceilings up to 23°, 5/12 pitch
- Box weight 27.8 lb



- Remote Control included

See page 73 for wet location light kits.



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2846.00	17.00	167
High	6857.00	72.00	95

# Andros™ (wet location)



## AD-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze blades, light kit and remote control (UL wet location)

### Features:

- Custom 52” blades **(Included)**
- 172 x 20mm motor
- 3-speed, manual reversing from fan switch
- 14° blade pitch
- 4” downrod included (optional downrods available)
- Downrod mounting only
- Mounts to sloped ceilings up to 28°, 6/12 pitch
- 3 x 40W candelabra (E12) lower light included



- Box weight 32 lb
- UL wet location rating



- Remote Control included

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2267.00	13.1	173
High	5387.00	59.0	91



# Cabana™ (wet location)


## RC-ORB

Oil Rubbed Bronze fan comes with Oil Rubbed Bronze ABS blades (UL wet location)



## RC-AW

Appliance White fan comes with Appliance White ABS blades (UL wet location)



## RC-MB

Matte Black fan comes with Matte Black ABS blades (UL wet location)



### Features:

- Light kit adaptable
- 36" blades **(Included)**
- Decor-Match™ blade options available.
- Flush mount capability
- 153 x 10mm motor
- 3-speed, reversing
- 14° blade pitch
- 4" downrod included (optional downrods available)
- Mounts to sloped ceilings up to 35°, 8/12 pitch
- Box weight 12.8 lb
- UL wet location rating

### Options:

- Universal Remote Controls (URC-WL)/ (URC-WLES) sold separately
- See page 73 for wet location light kits.

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1350.00	12.00	125
High	3520.00	47.00	74

# Patio Pro™ (wet location)

## VP2-AW

Appliance White fan comes with  
Appliance White ABS blades  
(UL wet location)



## VP2-AW

Appliance White fan shown  
with PL52AW Appliance White  
leaf ABS blades  
(UL wet location)



### Features:

- Light kit adaptable
- 52" blades **(Included)**
- Decor-Match™ blade options available.
- Flush mount capability
- 188 x 15mm motor
- 3-speed, reversing
- 14° blade pitch
- 4" downrod included (optional downrods available)
- Mounts to sloped ceilings up to 35°, 8/12 pitch
- Box weight 15.4 lb
- UL wet location rating

### Options:

- Universal Remote Controls (URC-WL)/  
(URC-WLES) sold separately
- See page 73 for wet location light kits.



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2325.00	11.00	219
High	5871.00	57.00	103



## Professional Series

With consistent quality and durability, professional builders and contractors have come to demand Regency's industrial fans and professional series fans. Simple installation and proven reliability make these builder fans the first choice among the industry.



# Professional Series Fan

With Low Profile  
Light Kit Included in Box

## PFLK10-CW

Chalk White fan comes with Chalk White blades and light kit (all Energy Star)



## PFLK10-ORB

Oil Rubbed Bronze fan comes with combination Oil Rubbed Bronze/ Dark Walnut blades and light kit (all Energy Star)



## PFLK10-SS

Satin Steel fan comes with combination Silver/Cherry blades and light kit (all Energy Star)



### Features:

- 52" blades **(INCLUDED)**
- Energy Star light kit with White Opal glass included, 2 x 13W GU-24 CFL
- 153 x 15mm motor
- 3-speed, manual reversing from fan switch
- Detachable switch housing
- Triple capacitor
- 12° blade pitch
- 4" downrod included
- Flush mount capability
- 6 ft. hookup wires
- Mounts to sloped ceilings up to 28°, 6/12 pitch
- Box weight 17 lb



### Options:

- Universal Remote Control (URC-WLES) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2256.00	9.40	240
High	5265.00	56.5	93

# Professional Series Fan

With Light Kit Included in Box

## PFLK41-ORB

Oil Rubbed Bronze fan comes with combination Oil Rubbed Bronze/Dark Walnut blades and light kit (Amber glass)



## PFLK41-EB

Bronze fan comes with combination Oil Rubbed Bronze/Dark Walnut blades and light kit (White glass)



### Features:

- 52" blades **(INCLUDED)**
- 180 watt light kit included (3 x 60W candelabra - E12)
- 153 x 12mm motor
- 3-speed, reversing
- Detachable switch housing
- Triple capacitor
- 12° blade pitch
- 4" downrod included
- Flush mount capability
- 6 ft. hookup wires
- Mounts to sloped ceilings up to 22°, 5/12 pitch
- Box weight 19.8 lb

### Options:

- Universal Remote Control (URC) sold separately



Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	1807	10	181
High	4570	59	78

### **PFLK41-AW**

Appliance White fan comes with  
Appliance White blades and light kit



### **PFLK41-SS**

Satin Steel fan comes with combination  
Silver/Cherry blades and light kit



### **PFLK41-CW**

Chalk White fan comes with Chalk  
White blades and light kit





# Professional Series Fan

## PFES52-ORB

Oil Rubbed Bronze fan comes with combination Oil Rubbed Bronze/Dark Walnut blades



## PFES52-SS

Satin Steel fan comes with combination Silver/Cherry blades



### Features:

- 52" blades **(INCLUDED)**
- 153 x 15mm motor
- 3-speed, reversing
- Detachable switch housing
- Triple capacitor
- 12° blade pitch
- 4" downrod included
- Light kit adaptable
- Flush mount capability
- 6 ft. hookup wires
- Mounts to sloped ceilings up to 28°, 6/12 pitch
- Box weight 17.6 lb

### Options:

- Universal Remote Control (URC) sold separately



*42" Professional Series Fans			
PF42-AW Appliance White			
(42" blades same finishes as 52" models)			
*NOTE: The 42" Professional Series fans are not ENERGY STAR rated.			

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
Low	2324	9.7	240
High	5820	62.3	93


### **PFES52-AW**

Appliance White fan comes with  
Appliance White blades



### **PFES52-AB**

Antique Brass fan comes with combination  
Walnut/Medium Oak blades



### **PFES52-CW**

Chalk White fan comes with Chalk White blades



# Industrial

## IND-WH

White Industrial ceiling fan with three White 56" metal blades

## IND-MB

Matte Black Industrial ceiling fan with three Matte Black 56" metal blades

## IND-ORB

Oil Rubbed Bronze Industrial ceiling fan with three Oil Rubbed Bronze 56" metal blades

### Features:

- 188 x 15mm high torque motor
- 56" blade span
- 3 metal blades with trailing edge turned down
- 24" downrod included
- Single speed/300 RPM free run
- CFM - 15,000-20,000
- Current draw .75 AMPS
- Lead wires 6 foot
- Box weight 17.0 lb
- UL listed

**Industrial ceiling fans rotate at higher speeds than most household ceiling fans. Their blades are also thinner and made of metal rather than wood. Severe injury can result if any part of the body comes in contact with the rotating blades. Regency industrial ceiling fans are not recommended for use in household applications. Can be connected to 120 volts only.**

### Cooling

Create a cooling breeze of air close to the floor area where most work is done. Hang the fans on long downrods, but at least 7-8 feet off the floor. Special applications may require even greater clearances. Circulate air without pulling hot air down from the ceiling. Since fans do not actually cool the air they move, use more fans per square foot area than the chart recommends.

### Heat Reclamation

Best use is to reclaim heat trapped at the ceiling, often 20-40 feet above the floor where temperatures can vary as much as 20 degrees. Hang fans high, but at least 36" down from the ceiling to force warm air down into the working area.



Uses Industrial Downrods  
I12-FINISH 12"  
I36-FINISH 36"  
I72-FINISH 72"

Effective area served by each fan installed for various ceiling heights:

Ceiling Height	Effective Sq. Ft. Area Served
20 ft.	3500
30 ft.	2800
40 ft.	1700



FC1AW-G\* - White/Almond  
3-speed, fan control, 2-wire.  
\*Includes white and almond knobs.



FCS-2 - White  
FCSA-2 - Almond  
FCSI-2 - Ivory  
4-speed sliding, fan control, 2-wire, 1.5 amp.

### Performance and Energy Information

Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watts)
High	7820.3	74.00	105.7

# 52X Designer Decor-Match™ Blades for Regency's Decor-Match™ Fans

Wide, exquisite wood blades are available in the most popular blade finishes. The 52X blades are the perfect complement to Regency's extensive collection of Decor-Match™ fan motors.



**52XAW** (Appliance White) **52XCR** (Cherry) **52XCW** (Chalk White) **52XDI** (Desert Ivory)



**52XDW** (Dark Walnut) **52XMH** (Mahogany) **52XORB** (Oil Rubbed Bronze) **52XSS** (Satin Steel) **52XTK** (Teak)





# Great Room Designer Blades for the Gladiator and Primo Fans

Thicker and wider than Regency's standard wood blades, the 60" TB60 blades offer the perfect proportions for the powerful Gladiator and Primo fans. Select from many different fan finishes to complement any style and décor.

**Decor-Match™**  
SYSTEM



**TB60-AC**  
(Antique Copper)

**TB60-AW**  
(Appliance White)

**TB60-CR**  
(Cherry)

**TB60-CW**  
(Chalk White)

**TB60-DG**  
(Walnut)



Thicker Beveled Blades



**TB60-DI**  
(Desert Ivory)

**TB60-DW**  
(Dark Walnut)

**TB60-MHS**  
(Mahogany)

**TB60-MP**  
(Maple)

**TB60-ORB**  
(Oil Rubbed Bronze)

**TB60-SS**  
(Satin Steel)

**TB60-TK**  
(Teak)

**REGENCY®**  
CEILING FANS

# Designer Blades for the Grander Fans

Available in 60" and 72" sizes, these custom blades have been handcrafted specifically for the Grander fans. Select from many different blade finishes to customize these Grander fans to match any décor.



Thicker Beveled  
Blades




## Outdoor Blades (ABS Plastic)




**PL52MHS 52"**

Mahogany



**PL52AW 52"**

Appliance White




**PL52NAT 52"**

Natural

**52CMORB 52"**

Oil Rubbed Bronze




**52CMMB 52"**

Matte Black



## Outdoor Blades (ABS Plastic)


**PP52NAT+**  
52" Natural



**PP52AW+**  
52" Appliance White



**PP52MH**  
52" Mahogany



**520AAW 52"**  
Appliance White



**520AWI 52"**  
Matte Black



**520AORB 52"**  
Oil Rubbed Bronze



**Decor-Match™**  
SYSTEM


**REGENCY®**  
CEILING FANS



# Decor-Match Blades



**AC** Antique Copper




**ACW** Antiqued Cherrywood



**AWS** Appliance White



**CW** Chalk White



**CR** Cherry



**DWS** Dark Walnut




**DI** Desert Ivory



**NAT** Light Natural Oak




**HNAT** Gloss Light Natural Oak



**MHS** Mahogany



**MP** Maple




**MB** Matte Black



**LG** Medium Oak




**MS** Mojave Sand



**ORB** Oil Rubbed Bronze



**HR** Gloss Rosewood



**SSS** Satin Steel



**TK** Teak



**UFS** Unfinished Oak



**DG** Walnut



**W** White

## Decor-Match Blades

Size	Color	Description	Blade Tip	Finish
52", 56"	AC	Antique Copper	Square	Matte
44", 52", 56"	ACW	Antiqued Cherrywood	Square	Matte
27", 36", 44", 52", 56"	AWS	Appliance White	Square	Matte
44", 52", 56"	CW	Chalk White	Square	Matte
44", 52", 56"	CR	Cherry	Square	Matte
44", 52", 56"	DWS	Dark Walnut	Square	Matte
44", 52", 56"	DI	Desert Ivory	Square	Matte
52"	NAT	Light Natural Oak	Pointed	Matte
44", 52", 56"	NATS	Light Natural Oak	Square	Matte
52"	HNAT	Gloss Light Natural Oak	Square	Gloss
44", 52", 56"	MHS	Mahogany	Square	Matte
44", 52", 56"	MP	Maple	Square	Matte
44", 52", 56"	MB	Matte Black	Square	Matte
27"	LG	Medium Oak	Square	Matte
36", 44", 52", 56"	LG	Medium Oak	Pointed	Matte
52", 56"	LGS	Medium Oak	Square	Matte
44", 52", 56"	MS	Mojave Sand	Square	Textured
44", 52", 56"	ORB	Oil Rubbed Bronze	Square	Matte
52"	HR	Rosewood	Square	Gloss
52", 56"	SSS	Satin Steel	Square	Matte
52", 56"	TK	Teak	Square	Matte
52"	UFS	Unfinished Oak	Square	Matte
52"	DG	Walnut	Pointed	Matte
52"	W	White	Pointed	Matte
52"	WS	White	Square	Matte

## 54" Carved Wood Blades

Regency's Decor-Match™ wood designer blades have been meticulously carved by hand so that each blade is a unique work of art. The entire collection allows you to truly customize a ceiling fan to match your personal styles.



**WC52LG**  
(Medium Oak)



**WL52MHS**  
(Mahogany)



**WL52NAT**  
(Natural)




**W354MH**  
(Mahogany)



**W454MH+**  
(Mahogany)

## Downrods



### Downrods

Item: D(size)-(Finish)

Example: D12-BR — is 12" Polished Brass Downrod.

Available Sizes: 12", 18", 24", 36", 48", 60" and 72" (available most colors)

### Damp Location Downrods

DL12-AW, MB, MS, ORB  
DL24-AW, MB, ORB  
DL36-AW, ORB  
DL60-MB, ORB

### Wexford Fan (P.10)

#### 3/4" Diameter Downrods

L12-ORB, L18-ORB,  
L24-ORB, L36-ORB,  
L48-ORB, L60-ORB,  
L72-ORB



# LED Light Kit

Compatible with  
Many Popular  
Ceiling Fans



As LED (Light Emitting Diode) lights continue to grow in popularity, it is important that lighting companies change the way they think about light fixtures. Why are customers interested in LED lights? Put simply, they are one of the most energy-efficient lighting sources available and can last decades longer than traditional light bulbs.

Of course, better technology does make LED lighting a bit more expensive. When cost comes up, remind customers how much they will save in the end. According to the U.S. Department of Energy, upgrading 15 bulbs from incandescent to LED can save the average homeowner about \$50 a year. That doesn't even include the savings from not having to replace light bulbs as often. LED light bulbs can last up to 25,000 hours. That's 25 times the lifespan of a traditional incandescent bulb.

So when customers come into your showroom, remember to mention the new Regency LED light kit. It's one of the first LED light kits in the industry which may be sold with many different ceiling fans.

## Features:

- Dimmable 20 Watt LED Light Kit with Alabaster Glass
- Leading Edge Dimmer (Compatible with Traditional Incandescent Dimming)
- 2700K Soft White Color Temperature
- Light Output is 1700 Lumens
- Comparable to 100 Watt Incandescent Bulb
- Lifetime to 70% Luminous Flux - 35,000 hours
- Lifetime to 50% Luminous Flux - 50,000 hours
- Energy Efficient
- Width: 13.5"
- Height: 4"



**LK270 -AC**



**LK270 -BN**



**LK270 -CW**



**LK270 -ORB**





# Light Kits



## CAPS-Finish

Caps and finials available separately in all Regency finishes.

Photos for light kit style only.

Light kit may not be available in color shown.



### LK9-(finish)

10"W x 3-1/2"H, (2-60W E12)  
Available in: AB, AW, BN, CW, ORB, SS



### LK9A-(finish) (Amber Glass)

10"W x 3-1/2"H, (2-60W E12)  
Available in: MB, ORB



### LK14-(finish)

12"W x 3-1/2"H, (1-100W JDE 11)  
Available in: AW, BN, CW, ORB, SS



### LK14A-(finish) (Amber Glass)

12"W x 3-1/2"H, (1-100W JDE 11)  
Available in: AC, ORB



### LK25A-(finish) (Amber Glass)

11-1/4"W x 5"H, (2-60W E12)  
Available in: MB



### LK30A-(finish) (Amber Glass)

13"W x 6-1/2"H, (3-60W E12)  
Available in: MB



### LK32A-(finish) (Amber Glass)

14"W x 6-1/4"H, (3-60W E12)  
Available in: ORB



### LK41P

11"W x 5"H, (3-60W E12)  
Caps and finials available in all colors; comes with AW



### LK41P-A (Amber Glass)

11"W x 5"H, (3-60W E12)  
Caps and finials available in all colors; comes with ORB



### LK54

12"W x 7-1/2"H, (3-60W E12)  
Caps and finials available in all colors; comes with AW



### LK54A (Amber Glass)

12"W x 7-1/2"H, (3-60W E12)  
Caps and finials available in all colors; comes with ORB



### LK60-(finish)

12-1/2"W x 5-1/2"H, (3-60W E12)  
Available in: AW, BN, CW, ORB, SS



### LK60A-(finish) (Amber Glass)

12-1/2"W x 5-1/2"H, (3-60W E12)  
Available in: AC, ORB



### LK65-(finish)

12-1/2"W x 5"H, (3-60W E12)  
Available in: AW, BN, CW, DI, SS



### LK65A-(finish) (Amber Glass)

12-1/2"W x 5"H, (3-60W E12)  
Available in: AB, AC, ORB



### LK80-(finish)

12"W x 4-5/8"H, (3-60W E12)  
Caps and finials available in all colors; comes with BN



### LK80A-(finish) (Amber Glass)

12"W x 4-5/8"H, (3-60W E12)  
Caps and finials available in all colors; comes with ORB



### LK301T-(finish)

12"W x 6-1/2"H, (3-60W E12)  
Available in: AW, ORB, SS

# Light Kits

## Damp Location Light Kits



**LK427D-(finish)**  
9-1/2"W x 6"H, (4-40W E12)  
Available in: AW, ORB

## Wet Location Light Kits



**LK90W-(finish)**  
11"W x 5-3/8"H,  
(2-60W E12)  
Available in: AW, MB, MS, ORB



**LK95W-(finish)**  
10-1/8"W x 6"H,  
(2-13W E26)  
Available in: AW, ORB, MB

## Energy Saving Light Kits



**LK108ES-(finish)**  
13-3/8"W x 3-1/2"H, (1-30W  
4-Pin Circline Fluorescent) Available  
in: AC, CW, DI

## Energy Saving Wet Location Light Kits



**LK101SESW-(finish)** 8"W x 7-1/2"H,  
(1-18W 2-Pin Spiral Fluorescent)  
Available in: AW, ORB



**LK106ESW-(finish)**  
10-1/4"W x 5-3/8"H,  
(1-18W 2-Pin Spiral Fluorescent)  
Available in: MB




**LK109ESW-(finish)**  
10-1/8"W x 5-7/8"H,  
(1-22W 4-Pin Circline Fluorescent)  
Available in: AW

## Fitters



**F401N-AB**  
12-1/2"W x 3-1/2"H,  
(4-40W E12)



**F401N-AW**  
12-1/2"W x 3-1/2"H,  
(4-40W E12)




**F401N-BN**  
12-1/2"W x 3-1/2"H,  
(4-40W E12)



**F401N-CW**  
12-1/2"W x 3-1/2"H,  
(4-40W E12)



**F401N-ORB**  
12-1/2"W x 3-1/2"H,  
(4-40W E12)



**F401N-SS**  
12-1/2"W x 3-1/2"H,  
(4-40W E12)

---

## Glass Shades



**G200B** Bronze Marble Bell  
5-1/2"W x 5"H, (Set of 4)



**G2010** Frosted Ribbed Bell  
4-1/2"W x 4-3/4"H, (Set of 4)



**G2100** Alabaster White Swirl  
6"W x 5"H, (Set of 4)



**G2100A** Amber Glass  
6"W x 5"H, (Set of 4)

## Specialty Bulbs



### LX-BULB

25 watt  
(E12) base,  
clear



### 15W-E12

15 watt  
(E12) base



### 25WGU10

25 watt  
(GU10) bulb



### 40W-E12

40 watt  
candelabra  
(E12) base, clear



### 60W-E12

60 watt  
candelabra  
60 watt  
(E12) base



### 100WHJDE

100 watt "JDE"  
(E11) base

## Energy Saving LED with Driver



### LK270LED Bulb

20 watt  
2700K LED with driver

## Energy Saving Fluorescent Bulbs



### 13W-CFL

13 watt spiral CFL  
(medium base)



### 18W-SF

18 watt spiral  
fluorescent

## K2000 Chroma Bulbs



### 60C-CB

60 watt (E12) base  
clear chroma bulb



### 22W-CF

22 watt single  
circline



### 30W-CF

30 watt  
single circline

## Replacement Switches

### RS-6

Ceiling fan  
reversing  
switch, 6-wire.




### PC-2

On/Off 1 circuit  
switch (for light  
kit, fitters)



### PC-3

A-On, A/B-On,  
B-On, Off (for  
light kits)



### PC-4R\*

For triple  
capacitor fan  
4-wire terminals



\*Universal speed control switches may not work with all brands/models of ceiling fans.

## Pull Chains & Fobs



### TSL1-304

Walnut



### TSL4-304

White



### REGFOB-(finish)

AB, BR, GUN, SS



### TSL6-304

Light Oak

## Ceiling Accessories

### LKCONV-WH - White

**Ceiling Mount Converter**  
Adapts light kits and fitters  
into ceiling fixtures



### SCK-(finish)\*

**Sloped Ceiling Kit** 48° Maximum slope










Available in: AB, AC, AW, BN, BR, CW,  
DI, MB, MS, ORB, SS, WH

Uses 1/2" rod only \*Cannot be used with canopy  
mounted remote fans.





# Wall Controls - Fan and Light

Fan	Page	OPTIONAL SELECT TOUCH WALL TRANSMITTERS		RECEIVER NEEDED	Colors:
		<b>2WWC - White</b> <b>2WWC-A - Almond</b> <b>2WWC-I - Ivory</b> Full fan and light control using a standard 2-wire circuit. Works in place of a single circuit on/off wall switch. Controls 3 speeds, reverse, and light on/off, plus full range dimmer with memory. (Can be used with RCT transmitter.) 	<b>2WWCD - White</b> <b>2WWCD-A - Almond</b> <b>2WWCD-I - Ivory</b> Full fan and light control using a standard 2-wire circuit. Works in place of a single circuit on/off wall switch. Controls 3 speeds, reverse, and uplight and optional downlight independently with full range dimmer with memory. (Can be used with RCTD transmitter.) 	 <b>URC</b>   <b>RCR RCR-G</b>   <b>RCRD RCRD-P</b>	 white  almond  ivory
					<b>RECEIVER HOUSING NEEDED</b>  <b>RC2</b>
Bimini* (Indoor only)	16	X		included with fan	none
Coronado	39		X	RCRD	RC2
Countess	42	X		URC	none
Deuce Hugger	20	X		included with fan	none
Deuce*	20	X		included with fan	none
Envoy	38		X	RCRD	RC2
Gladiator**	22-23	DCWC3 or DCWC3-A (Almond) 6-speed wall control		none	none
Grandeur**	8-9	DCWC3 or DCWC3-A (Almond) 6-speed wall control		none	none
Grand Marquis	34-35	X		RCR	RC2
Kinder	43	X		included with fan	none
Lafayette (LF)	36-37	X		RCR	RC2
Lafayette (LF3)	28		X	included with fan	none
LX (LX2)	26-27		X	RCRD	RC2
Marquis	40-41	X		RCR	RC2
MX2	30-31	X		RCR	RC2
MX3	25		X	included with fan	none
Nola	19	X		URC	none
Primo	24		X	RCRD-P	RC2
Quatro	17	X		included with fan	none
Regatta	29		X	RCRD	RC2
Regulator	12	X		RCR-G	RC2
Trend	14	X		included with fan	none
Tropic Air Indoor	32	X		RCR	RC2
Vantage** (Indoor Only)	6	DCWC3 or DCWC3-A (Almond) 6-speed wall control		none	none
Vogue	14	X		included with fan	none

\* Fans must be put into reverse position manually from fan switch when using the 2WWC.

\*\*Multiple fans cannot operate on the same circuit. Each fan must have its own power switch.

# Wall Controls - Fan and Light

## OPTIONAL FAN & LIGHT WALL CONTROLS

### FCSL-2 - White FCSLA-2 - Almond FCSLI-2 - Ivory

4-speed sliding fan and light control, 3-wire, 1.5 amp/300 watt.



### FCL-E - White FCL-EA - Almond

3-speed fan and on/off light control for operating fans with Energy Star (CFL) light kits, 3-wire, 1.25 amp/300 watt.




Fan	Page	
Cabana	54	X
Cayman	47	X
Ciara	13	X
Countess	42	X
Deuce	20	X
Grand Marquis	34-35	X
Kinder	43	X
Lafayette (LF)	36-37	X
Marquis	40-41	X

Fan	Page	
MX2	30-31	X
Oasis	48-49	X
Patio Pro	55	X
Regatta	29	X
Tropic Air Indoor	32	X
Vera Cruz	50-51	X
Pro Series - 42"	60	X
Pro Series - 52"	60-61	X
Pro Series w/ LK41	58-59	X

Fan	Page	
Quad	18	X
Pro Series w/LK10	57	X

### Colors:



## OPTIONAL FAN ONLY WALL CONTROLS

**FC1AW-G- White/Almond**  
(includes white and almond knobs)  
3-speed fan control, 2-wire.



**FCS-2 - White  
FCSA-2 - Almond  
FCSI-2 - Ivory**  
4-speed sliding fan control, 2-wire, 1.5 amp.











**FC-M - White  
FC-MA - Almond**  
3-speed control for operating multiple fans (3-5) on the same circuit, 5 amp, 2-wire.






Fan	Page	FC1AW-G- White/Almond	FCS-2 - White FCSA-2 - Almond FCSI-2 - Ivory	FC-M - White FC-MA - Almond
Bimini (Indoor Only)	16	X	X	X
Cabana	54	X	X	X
Cayman	47	X	X	X
Ciara	13	X	X	X
Countess	42	X	X	X
Grand Marquis	34-35	X	X	X
Kinder	43	X	X	X
Lafayette (LF)	36-37	X	X	X
Marquis	40-41	X	X	X
MX2	30-31	X	X	X
Oasis	48-49	X	X	X
Patio Pro	55	X	X	X
Regatta	29	X	X	X
Regulator	12	X	X	X
Tropic Air Indoor	32	X	X	X
Vera Cruz	50-51	X	X	X
Pro Series - 42"	60	X	X	X
Pro Series - 52"	60-61	X	X	X

# Remote Controls - Fan and Light

		OPTIONAL FULL FUNCTION REMOTE CONTROL			
		Transmitter <b>RCT</b> 	Receiver <b>RCR</b> 	Receiver <b>RCR-G</b> 	Receiver Housing <b>RC2-(color)</b> 
Fan	Page				
Grand Marquis	34-35	X	X		X
Lafayette (LF)	36-37	X	X		X
MRP	40-41	X	X		X
MX2	30-31	X	X		X
Regulator	12	X		X	X
Tropic Air Indoor	32	X	X		X

		OPTIONAL FULL FUNCTION REMOTE CONTROL (for fans with Mood Glow™ Uplight)			
		Transmitter <b>RCTD</b> 	Receiver <b>RCRD</b> 	Receiver <b>RCRD-P</b> 	Receiver Housing <b>RC2-(color)</b> 
Fan	Page				
Coronado	39	X	X		X
Envoy	38	X	X		X
Freestar	15	X	included with fan		N/A
LX (LX2)	26-27	X	X		X
Primo	24	X		X	X
Regatta	29	X	X		X
Strasburg	11	X	included with fan		N/A
Wexford	10	X	included with fan		N/A

		OPTIONAL UNIVERSAL REMOTE CONTROL	OPTIONAL WET LOCATION UNIVERSAL REMOTE CONTROL	
		Transmitter and Receiver <b>URC*</b> 	Wet Location Transmitter and Receiver <b>URC-WL*</b> 	Transmitter and Receiver <b>URC-WLES**</b> For fans with fluorescent light kits (including wet location) 
Fan	Page			
Cabana	54		X	X
Cayman	47		X	X
Ciara	46		X	X
Countess	42	X		X
Kinder	43	X		X
Oasis	48-49		X	X
Patio Pro	55		X	X
Pro Series - 42"	60	X		X
Pro Series - 52"	60-61	X		X
Pro Series w/ LK10	57			X
Pro Series w/ LK41	58-59	X	X	X
Tropic Air Outdoor	52		X	X
Vera Cruz	50-51		X	X

\* Manual reversing from fan switch

\*\* On/off light only - no dimming

# Ceiling Fan Features & Specifications

Page	53	16	52	54	47	13/46	39	42	20
Fan	Andros (AD)	Bimini Indoor (BI)	Bimini Outdoor (BIM)	Cabana (RC)	Cayman (CM)	Ciara (CI)	Coronado (CN)	Countess (CT)	Deuce (DU)
Designer Series	X	X	X			X			X
Decor-Match™ System					X		X	X	
Energy Star Rated									
Mood Glow™ Included							X		
Specially Designed Blades Included	X	X	X	X	X	X	X	X	X
Recommend 27", 36" and 42" Blades								X	
Recommend 44", 52" and Designer Blades					X		X		
Recommend 52", 56" and Designer Blades									
Recommend GN60/72 Blades									
Recommend 56" and TB60 Blades									
Light Kit Included	X								X
Light Kit Adaptable		X	X	X	X	X	X	X	
Full Function Wall Control Included									
Full Function Remote Control Included									
Non-Reversing Wall Control Included*									
Non-Reversing Remote Control Included*	X	X	X						X
Full Function Remote Control Adaptable							X		
Non-Reversing Remote Control Adaptable*				X	X	X		X	
Downrod Length (inches)	4	4	4	4	4	4	6	4	4
Flush Mount Capability								X	
Motor Size	172x20	188x22	188x22	153x10	188x15	172x14	188x15	153x10	153x22
Blade Pitch	14	14	14	14	14	13	14	14	15
CFM - Low Speed	2267	2846	2846	1350	2235	1833	2043	1135	1773
CFM - High Speed	5387	6857	6857	3520	5530	5270	5345	3185	5968
Watts - Low Speed	13.1	17	17	12	14	9.7	10	10.6	10
Watts - High Speed	59	72	72	47	75	61	62	49	69
CFM/Watt - Low Speed	173	167	167	125	159	199	200	107	177
CFM/Watt - High Speed	91	95	95	74	73	87	86	65	86
RPM - Low Speed	71	58	58	105	50	63	68	75	77
RPM - High Speed	165	158	158	200	160	175	161	172	209
Fan Motor Amp Rating	0.56	0.69	0.69	0.40	0.58	.80	0.53	0.41	0.57
Maximum Mounting Angle **	28	23	23	35	30	20	33	22	29
Measurement "A" (inches)	11.63	15.75	15.75	11	14.5	11.63	14.5	10.8	12.3
Measurement "B" (inches)	21	17.5	17.5	13	17	21	15.5	12.8	15.6
Box Weight (lb)	32	27.6	27.6	12.8	36.4	20	29.8	15	21.6
U.L. Listed Damp (D) or Wet (W) Location	W		W	W	W	W			

\* Receiver (Item: URC) mounts inside ceiling canopy. Reversing function remains manual with fan's reversing switch and remote control transmitting range is limited to 20-25 feet typically. Ceiling slope angle is also restricted to 14 degrees (3/12 ceiling pitch) when canopy mounted remote is used.

**\*\* See Page 84**

(Features and specifications subject to change without notice.)



# Ceiling Fan Features & Specifications

Page	20	38	15	22-23	34-35	8-9	43	36-37	28
Fan	Deuce Hugger (DH)	Envoy (EN2)	Freestar (FS)	Gladiator (GL3)	Grand Marquis (GMRP)	Grander (GN)	Kinder (KD)	Lafayette (LF)	Lafayette (LF3)
Designer Series	X		X			X			
Decor-Match™ System		X		X	X			X	X
Energy Star Rated				X				X	
Mood Glow™ Included		X	X						X
Specially Designed Blades Included	X	X	X		X		X	X	
Recommend 27", 36" and 42" Blades							30"		
Recommend 44", 52" and Designer Blades		X			X			X	X
Recommend 52", 56" and Designer Blades									
Recommend GN60/72 Blades						X			
Recommend 56" and TB60 Blades				X					
Light Kit Included	X		X		X				
Light Kit Adaptable		X		X		X	X	X	X
Full Function Wall Control Included			X						
Full Function Remote Control Included	X			X		X			X
Non-Reversing Wall Control Included*									
Non-Reversing Remote Control Included*									
Full Function Remote Control Adaptable		X	X		X			X	
Non-Reversing Remote Control Adaptable*							X		
Downrod Length (inches)	n/a	6	6	6	4	6	4.5	6	6
Flush Mount Capability	X				X		X	X	
Motor Size	153x22	188x15	188x22	DC-125	188x15	DC-165	153x10	188x15	188x15
Blade Pitch	14	14	14	16	14	13.5	14	14	14
CFM - Low Speed	1773	2544	2107	see chart on page 23	1829	see chart on page 9	871	1620	1996
CFM - High Speed	5968	5655	5609		5120		1751	5617	5220
Watts - Low Speed	10	13	14		11.3		8.4	9.9	10
Watts - High Speed	69	69	68		54		42	66	60
CFM/Watt - Low Speed	177	191	150		161		104	163	199
CFM/Watt - High Speed	86	82	82		94		42	85	87
RPM - Low Speed	77	58	55		86		123	59	64
RPM - High Speed	209	153	140		170		278	162	165
Fan Motor Amp Rating	0.57	0.53	0.60		0.68		0.21	0.53	0.54
Maximum Mounting Angle **		33	29	22	22	22	28	22	22
Measurement "A" (inches)	7.5	13.5	12.5	15.5	14.75	13.3	10.75	15	15
Measurement "B" (inches)	11.25	14.5	19	16	15.75	17	12.25	15.25	15.25
Box Weight (lb)	21.2	24.9	31.5	22.4	22.3	22	13.8	29	22
U.L. Listed Damp (D) or Wet (W) Location									

\* Receiver (Item: URC) mounts inside ceiling canopy. Reversing function remains manual with fan's reversing switch and remote control transmitting range is limited to 20-25 feet typically. Ceiling slope angle is also restricted to 14 degrees (3/12 ceiling pitch) when canopy mounted remote is used.

**\*\* See Page 84**

(Features and specifications subject to change without notice.)

# Ceiling Fan Features & Specifications

Page	26-27	40-41	30-31	25	19	48-49	55	24
Fan	LX (LX2)	Marquis (MR2)	MX2 (MX2)	MX3 (MX3)	Nola (NL)	Oasis (OA2)	Patio Pro (VP2)	Primo (PR)
<b>Designer Series</b>					X			
<b>Decor-Match™ System</b>	X	X	X	X		X	X	X
<b>Energy Star Rated</b>		X	X			X	X	
Mood Glow™ Included	X			X				X
Specially Designed Blades Included		X			X	X	X	
Recommend 27", 36" and 42" Blades								
Recommend 44", 52" and Designer Blades		X				X	X	
Recommend 52", 56" and Designer Blades	X		X	X				
Recommend GN60/72 Blades								
Recommend 56" and TB60 Blades								X
Light Kit Included					X			
Light Kit Adaptable	X	X	X	X		X	X	X
Full Function Wall Control Included								
Full Function Remote Control Included				X	X			
Non-Reversing Wall Control Included*								
Non-Reversing Remote Control Included*								
Full Function Remote Control Adaptable	X	X	X					X
Non-Reversing Remote Control Adaptable*						X	X	
Downrod Length (inches)	6	4	3/6	6	N/A	4	4	6
Flush Mount Capability		X	X					
Motor Size	188x20	188x15	188x22	188x22	172x15	188x15	188x15	212x25
Blade Pitch	14	14	16	16	14	14	14	16
CFM - Low Speed	3300	1829	1599	1599	1476	2276	2325	3015
CFM - High Speed	6540	5210	6380	6380	4133	6571	5871	8670
Watts - Low Speed	25	11.3	9.9	9.9	18.5	10	11	21
Watts - High Speed	72	54	77	77	64	69	57	95
CFM/Watt - Low Speed	133	161	161	161	80	228	219	143
CFM/Watt - High Speed	91	95	82	82	65	95	103	91
RPM - Low Speed	86	63	54	51	74	75	56	57
RPM - High Speed	170	170	166	167	149	182	165	144
Fan Motor Amp Rating	0.68	0.56	0.70	0.68	0.50	0.62	0.54	0.86
Maximum Mounting Angle **	33	22	22	22	N/A	26	35	22
Measurement "A" (inches)	14.75	14.75	14.75	14.75	8.75	12.75	11.38	16
Measurement "B" (inches)	15.75	15.75	15.5	15.5	12.875	14.5	13.5	16
Box Weight (lb)	19.8	21.6	19.8	23.1	22.5	22.3	15.4	32.8
U.L. Listed Damp (D) or Wet (W) Location						W	W	

\* Receiver (Item: URC) mounts inside ceiling canopy. Reversing function remains manual with fan's reversing switch and remote control transmitting range is limited to 20-25 feet typically. Ceiling slope angle is also restricted to 14 degrees (3/12 ceiling pitch) when canopy mounted remote is used.

**\*\* See Page 84**

(Features and specifications subject to change without notice.)

# Ceiling Fan Features & Specifications

Page	60	60-61	57	58-59	18	17	29	12	11
Fan	Pro Series 42" (PF42)	Pro Series 52" (PFES52)	Pro Series w/ LK (PFLK10)	Pro Series w/ LK (PFLK41)	Quad (QD)	Quatro (QU)	Regatta (RT)	Regulator (RL)	Strasburg (ST)
<b>Designer Series</b>					X	X		X	X
<b>Decor-Match™ System</b>							X		
<b>Energy Star Rated</b>		X	X		X				
Mood Glow™ Included							X		X
Specially Designed Blades Included	X	X	X	X		X		X	X
Recommend 27", 36" and 42" Blades									
Recommend 44", 52" and Designer Blades							X		
Recommend 52", 56" and Designer Blades									
Recommend GN60/72 Blades									
Recommend 56" and TB60 Blades									
Light Kit Included			X	X	X	X			
Light Kit Adaptable	X	X					X	X	X
Full Function Wall Control Included									X
Full Function Remote Control Included						X			
Non-Reversing Wall Control Included*									
Non-Reversing Remote Control Included*					X				
Full Function Remote Control Adaptable							X	X	X
Non-Reversing Remote Control Adaptable*	X	X	X	X					
Downrod Length (inches)	4	4	4	4	6	4	6	6	6/12
Flush Mount Capability	X	X	X	X					
Motor Size	153x10	153x15	153x15	153x12	153x18	188x15	188x15	212x25	188x25
Blade Pitch	12	12	12	12	14	12	14	16	14
CFM - Low Speed	1414	1679	2256	1807	1807	1530	1759	2805	2740
CFM - High Speed	2965	5100	5265	4570	5320	4902	5120	5873	6105
Watts - Low Speed	11.4	9.8	9.4	10	11	11	11	22	22
Watts - High Speed	49.5	65.8	56.5	59	66	58	55	88	80
CFM/Watt - Low Speed	124	171	240	181	160	137	160	127	124
CFM/Watt - High Speed	60	78	93	78	81	85	93	67	76
RPM - Low Speed	112	73	65	60	62	60	61	50	62
RPM - High Speed	237	201	186	162	169	158	150	146	136
Fan Motor Amp Rating	0.42	0.55	.55	0.50	0.80	0.48	0.54	0.68	0.74
Maximum Mounting Angle **	28	28	28	22	22	30	30	22	25
Measurement "A" (inches)	11	11.5	10.25	11.75	13	11	15	15	18.75
Measurement "B" (inches)	13	13.5	17.37	17.63	17.25	15.94	16.5	16.5	24.5
Box Weight (lb)	12	15.2	17	19.8	20.5	22.3	19.8	33.7	38.6
U.L. Listed Damp (D) or Wet (W) Location									

\* Receiver (Item: URC) mounts inside ceiling canopy. Reversing function remains manual with fan's reversing switch and remote control transmitting range is limited to 20-25 feet typically. Ceiling slope angle is also restricted to 14 degrees (3/12 ceiling pitch) when canopy mounted remote is used.

**\*\* See Page 84**

(Features and specifications subject to change without notice.)

# Ceiling Fan Features & Specifications

Page	14	32	52	6-7	7/45	50-51	14	10
Fan	Trend (TN)	Tropic Air Indoor (TA2)	Tropic Air Outdoor (TA2)	Vantage (VT)	Vantage Outdoor (VT)	Vera Cruz (VC2)	Vogue (VG)	Wexford (WX)
<b>Designer Series</b>	X			X	X		X	X
<b>Decor-Match™ System</b>		X	X			X		
<b>Energy Star Rated</b>						X		
Mood Glow™ Included	X						X	X
Specially Designed Blades Included	X			X	X	X	X	X
Recommend 27", 36" and 42" Blades								
Recommend 44", 52" and Designer Blades						X		
Recommend 52", 56" and Designer Blades		X	X					
Recommend GN60/72 Blades								
Recommend 56" and TB60 Blades								
Light Kit Included				X	X			X
Light Kit Adaptable		X	X			X		
Full Function Wall Control Included								X
Full Function Remote Control Included	X			X	X		X	
Non-Reversing Wall Control Included*								
Non-Reversing Remote Control Included*								
Full Function Remote Control Adaptable		X						X
Non-Reversing Remote Control Adaptable*			X			X		
Downrod Length (inches)	6	6	6	6	6	4	6	6/12
Flush Mount Capability						X		
Motor Size	153x17	188x25	188x25	DC-165	DC-165	188x15	212x25	212x25
Blade Pitch	14	20	20	12.5	12.5	14	14	12
CFM - Low Speed	1549	1100	1100	see chart on page 7	see chart on page 45	2325	2640	2956
CFM - High Speed	4870	5530	5530			5871	5930	5960
Watts - Low Speed	12	13	13			11	17	25
Watts - High Speed	69	63	63			57	85	90
CFM/Watt - Low Speed	129	85	85			219	155	118
CFM/Watt - High Speed	71	88	88			103	70	66
RPM - Low Speed	59	46	46			56	62	55
RPM - High Speed	162	116	116			165	168	155
Fan Motor Amp Rating	0.55	0.53	0.54			0.54	0.70	0.87
Maximum Mounting Angle **	23	33	33	20	20	35	23	25
Measurement "A" (inches)	15	16	16	14	14	11.38	16.75	20
Measurement "B" (inches)	15	18	18	16.38	16.38	13.5	16.75	24.5
Box Weight (lb)	19.8	22	22	27	27	18.7	37.5	59.5
U.L. Listed Damp (D) or Wet (W) Location			W		W	W		


\* Receiver (Item: URC) mounts inside ceiling canopy. Reversing function remains manual with fan's reversing switch and remote control transmitting range is limited to 20-25 feet typically. Ceiling slope angle is also restricted to 14 degrees (3/12 ceiling pitch) when canopy mounted remote is used.

**\*\* See Page 84**

(Features and specifications subject to change without notice.)


## Measurements (Inches)

- All measurements made using standard supplied downrod
- Measurement "A" is to bottom of edge of blade
- Measurement "B" is to bottom of light kit, if included with fan, otherwise to bottom of switch housing
- For multi-mount fans using close-up mounting, subtract 3-3/4" for fans with 4" downrods, 5-3/4" for fans with 6" downrods.





## Quality & Features That Make a Difference




## Year-Round Comfort

warmer weather

In the summer or hotter weather, operate the fan in the normal direction (counterclockwise). This creates a cooling breeze below the fan. The thermostat may then be raised, resulting in reduced energy consumption.



**SUMMER: DOWN:** Normal mode for creating a cooling breeze below the fan. (Counterclockwise)



cooler weather

In the winter or colder weather, operate the fan in the slow speed in the reverse direction (clockwise). This redistributes the trapped warm air at the ceiling to provide even heat throughout the room. The thermostat may then be lowered for more efficient energy consumption.

**WINTER: UP:** Redistributes trapped warm air during winter months. (Clockwise)



Supplied mounting brackets allow mounting on ceiling slopes from 22° (5/12 pitch), to 39° (10/12 pitch). Regency's optional slope kit shown on page 75 allows mounting on ceilings up to 45° (12/12 pitch). When using canopy installed remote controls, the maximum slope is restricted to 14° (3/12 pitch). Sloped ceiling kits are not adaptable to canopy installed remote control use.


Degree = Ceiling Slope (Pitch)
4-8 degrees = 1/12 pitch
9-13 degrees = 2/12 pitch
14-17 degrees = 3/12 pitch
18-21 degrees = 4/12 pitch
22-25 degrees = 5/12 pitch
26-29 degrees = 6/12 pitch
30-32 degrees = 7/12 pitch
33-35 degrees = 8/12 pitch
36-38 degrees = 9/12 pitch
39-41 degrees = 10/12 pitch
42-44 degrees = 11/12 pitch
45 degrees = 12/12 pitch

## A Regency Fan for Every Room Size

	27", 36", 42"	44"	52"	56", 60"
Blade Sweep	27", 36", 42"	44"	52"	56", 60"
Approximate Room Size	6' x 8' 40-60 sq. ft.	8' x 10' 70-90 sq. ft.	10' x 12' 100-150 sq. ft.	12' x 15' (great room) over 160 sq. ft.

These measurements are for general air flow requirements only. Decorating plans or aesthetic considerations should influence your fan choices beyond these room size specifications. For very large rooms, multiple fans are also recommended.

## What About Ceiling Height?



Be sure there is at least 7 feet of clearance under your ceiling fan blades. The standard 4"-6" downrod should work in most 8 ft. ceiling installations. This will position the blades far enough from the ceiling to have enough "supply" air above the blades to provide good air movement. If greater floor to fan clearance is needed, some fans can be mounted "close-up" without using any downrod. However, air movement is reduced using the close-up mounting. This chart shows recommended downrod lengths for various ceiling heights.

# Light Kit Specifications

Item	Description	Available Finishes	Width	Height	Qty. Bulbs	Max. Watt	Lamp
LK9	Low Profile Frosted Glass	AB, AW, BN, CW, ORB, SS	10"	3-1/2"	2	60	E12
LK9A	Low Profile Amber Glass	MB, ORB	10"	3-1/2"	2	60	E12
LK14	Low Profile Halogen	AW, BN, CW, ORB, SS	12"	3-1/2"	1	100	JDE 11
LK14A	Low Profile Halogen Amber Glass	AC, ORB	12"	3-1/2"	1	100	JDE 11
LK25A	Amber Glass	MB	11-1/4"	5"	2	60	E12
LK30A	Decorative Metal Edged Amber Glass	MB	13"	6-1/2"	3	60	E12
LK32A	Flat Metal Scroll Cradle Amber Glass	ORB	14"	6-1/4"	3	60	E12
LK41P	White on White Swirl Glass	All, comes with AW	11"	5"	3	60	E12
LK41P-A	Amber Glass	All, comes with ORB	11"	5"	3	60	E12
LK54	Alabaster Curved White Glass	All, comes with AW	12"	7-1/2"	3	60	E12
LK54A	Amber Curved Glass	All, comes with ORB	12"	7-1/2"	3	60	E12
LK60	Low Profile Alabaster Bowl with Handcrafted Scrollwork	AW, BN, CW, ORB, SS	12-1/2"	5-1/2"	3	60	E12
LK60A	Low Profile Amber Bowl with Handcrafted Scrollwork	AC, ORB	12-1/2"	5-1/2"	3	60	E12
LK65	Very Low Profile Alabaster Bowl with Handcrafted Scrollwork	AW, BN, CW, DI, SS	12-1/2"	5"	3	60	E12
LK65A	Very Low Profile Amber Bowl with Handcrafted Scrollwork	AB, AC, ORB	12-1/2"	5"	3	60	E12
LK80	Very Low Profile Alabaster Bowl	All, comes with BN	12"	4-5/8"	3	60	E12
LK80A	Very Low Profile Amber Bowl	All, comes with ORB	12"	4-5/8"	3	60	E12
LK301T	3-Light Frosted Ribbed	AW, ORB, SS	12"	6-1/2"	3	60	E12

## Light Kit Specifications

Item	Description	Available Finishes	Width	Height	Bulbs	Max Watt	Lamp
Damp Location Light Kits							
LK427D	Damp Location 4-Light Spot	AW, ORB	9-1/2"	6"	4	40	E12
Wet Location Light Kits							
LK90W	Wet Location Low Profile Bowl	AW, MB, MS, ORB	11"	5-3/8"	2	60	E12
LK95W	Wet Location Low Profile Bowl	AW, MB, ORB	10-1/8"	6"	2	13	E26
Energy Saving Light Kits							
LK108ES	Energy Star Low Profile Bowl	AC, CW, DI	13-3/8"	3-1/2"	1	30	4 pin
Energy Saving Wet Location Light Kits							
LK101SESW	Energy Saving Wet Location Schoolhouse	AW, ORB	8"	7-1/2"	1	18	2 pin
LK106ESW	Energy Saving Wet Location	MB	10-1/4"	5-3/8"	1	18	2 pin
LK109ESW	Energy Saving Wet Location	AW	10-1/8"	5-7/8"	1	22	2 pin
LED Dimmable Light Kits							
LK270	Energy Saving LED Low Profile Bowl	AC, BN, CW, ORB	13-1/2"	4"	20 Watt LED		

## Fitter Specifications

Item	Description	Available Finishes	Width	Height	Bulbs	Max Watt	Lamp
F401N	4-Light Bent Arm	AB, AW, BN, CW, ORB, SS	12-1/2"	3-1/2"	4	40	E12

# Index

## DESIGNER SERIES FANS

### Bimini

BI-BN ..... 16

### Ciara

CI-AW ..... 13

CI-MB ..... 13

CI-ORB ..... 13

### Deuce

DU-BN ..... 20

### Deuce Hugger

DH-MB ..... 20

### Freestar

FS-SS ..... 15

### Grander

GN-AC ..... 9

GN-BN ..... 9

GN-CW ..... 9

GN-ORB ..... 8

### Nola

NL-BN ..... 19

NL-CW ..... 19

NL-ORB ..... 19

### Quad

QD-BN ..... 18

### Quatro

QU-BN ..... 17

### Regulator

RL-AC ..... 12

RL-BN ..... 12

RL-ORB ..... 12

### Strasburg

ST-ORB ..... 11

### Trend

TN-BN ..... 14

TN-ORB ..... 14

### Vantage

VT-BN ..... 6

VT-ORB ..... 7

### Vogue

VG-BN ..... 14

### Wexford

WX-ORB ..... 10

## DECOR-MATCH™ SERIES FANS

### Gladiator

GL3-AC ..... 22

GL3-BN ..... 23

GL3-CW ..... 23

GL3-ORB ..... 23

GL3-SS ..... 22

### Lafayette (LF3)

LF3-AC ..... 28

LF3-ORB ..... 28

### LX2

LX2-AC ..... 26

LX2-BN ..... 26

LX2-CW ..... 27

LX2-DI ..... 27

LX2-ORB ..... 27

### MX Excel (MX2)

MX2-AB ..... 31

MX2-AC ..... 30

MX2-AW ..... 31

MX2-BN ..... 30

MX2-BR ..... 31

MX2-CW ..... 31

MX2-DI ..... 31

MX2-MB ..... 31

MX2-ORB ..... 30

MX2-SS ..... 31

### MX Excel (MX3)

MX3-BN ..... 25

MX3-CW ..... 25

MX3-ORB ..... 25

### Primo

PR-BN ..... 24

PR-ORB ..... 24

### Regatta

RT-BN ..... 29

RT-ORB ..... 29

### Tropic Air Indoor

TA2-DI ..... 32

## DECOR-MATCH™ UNIPACK SERIES FANS

### Coronado

CN-ORB ..... 39

### Countess

CT-AW ..... 42

CT-BN ..... 42

CT-ORB ..... 42

### Envoy

EN2-AC ..... 38

EN2-BN ..... 38

EN2-CW ..... 38

EN2-ORB ..... 38

### Grand Marquis

GMRP-BN ..... 34

GMRP-CW ..... 35

GMRP-ORB ..... 35

### Kinder

KD-BN ..... 43

KD-CW ..... 43

KD-ORB ..... 43

### Lafayette (LF)

LF-AC ..... 36

LF-BN ..... 37

LF-CW ..... 37

LF-DI ..... 36

LF-MB ..... 37

LF-ORB ..... 36

### Marquis

MR2-AB ..... 41

MR2-AC ..... 40

MR2-AW ..... 41

MR2-BN ..... 40

MR2-BR ..... 41

MR2-CW ..... 41

MR2-DI ..... 41

MR2-MB ..... 41

MR2-MS ..... 41

MR2-ORB ..... 41

MR2-SS ..... 41



# Index

## OUTDOOR FANS

### Andros

AD-ORB..... 53

### Bimini

BIM-AW ..... 52

BIM-ORB ..... 52

### Cabana

RC-AW ..... 54

RC-MB ..... 54

RC-ORB ..... 54

### Cayman

CM-AW ..... 47

CM-ORB ..... 47

### Ciara

CI-AW ..... 46

CI-MB ..... 46

CI-ORB ..... 46

### Oasis

OA2-AW ..... 48-49

OA2-MB ..... 49

OA2-MS ..... 49

OA2-ORB ..... 48-49

### Patio Pro

VP2-AW ..... 55

### Tropic Air Outdoor

TA2-ORB ..... 52

### Vantage

VT-ORB ..... 45

### Vera Cruz

VC2-MB ..... 51

VC2-ORB ..... 50

## PROFESSIONAL SERIES FANS

### Industrial

IND-MB ..... 62

IND-ORB ..... 62

IND-WH ..... 62

### Professional Series

PFES52-AB ..... 61

PFES52-AW ..... 61

PFES52-CW ..... 61

PFES52-ORB ..... 60

PFES52-SS ..... 60

### Professional Series with Light Kit

PFLK41-AW ..... 59

PFLK41-CW ..... 59

PFLK41-EB ..... 58

PFLK41-ORB ..... 58

PFLK41-SS ..... 59

### Professional Series with Light Kit

PFLK10-CW ..... 57

PFLK10-ORB ..... 57

PFLK10-SS ..... 57

## BLADES

52X Designer Blades ..... 63

54" Carved Wood Blades ..... 70

Decor-Match™ Blades ..... 68-69

Grander Designer Blades ..... 65

Great Room Designer Blades ..... 64

Outdoor Blades ..... 66-67

## CEILING FAN LIGHTING

Damp Location Light Kits ..... 73

Energy Saving Light Kits ..... 73

Energy Saving Wet Location Light Kits ..... 73

Fitters ..... 74

Glass Shades ..... 74

LED Light Kits ..... 71

Light Kits ..... 71-73

Wet Location Light Kits ..... 73

## FAN ACCESSORIES

Bulbs ..... 75

Ceiling Accessories ..... 75

Downrods ..... 70

Pull Chains & Fobs ..... 75

Remote Controls ..... 78

Switches ..... 75

Wall Controls ..... 76-77

## FEATURES AND SPECIFICATIONS

Ceiling Fan Features

and Specifications ..... 79-83

Fitter Specifications ..... 86

Light Kit Specifications ..... 85-86

Room Size, Ceiling Height

and Slope ..... 84



A division of Tacony Corporation  
St. Louis • Jacksonville • Los Angeles  
**[www.regencyfans.com](http://www.regencyfans.com)**

Features and Specifications Subject  
To Change Without Notice

© 2015 Regency Ceiling Fans

Authorized Regency Dealer

