
Classic Picture Lights



Classic Picture Lights


CONTEMPORARY

Craftsmanship and reliability are hallmarks of House of Troy products.

C9-52



Features



Traditional LED Picture Lights




TLED14-1

Benefits of LED

- No UV or IR
- Energy Efficient
- Long Life: 30,000 Hours
- Warm White Output





LED SPECIFICATIONS


Shade Sizes	CRI	ССТ	Watts	Lumens	Lifetime	Equivalent Incandescent
10"	93	3400K	1.6	38.4	30,000 hrs	(1) 25 Watt
14"	93	3400K	2.4	57.6	30,000 hrs	(2) 25 Watt
24"	93	3400K	4	96	30,000 hrs	(3) 25 Watt
36"	93	3400K	6.4	153.6	30,000 hrs	(5) 25 Watt


TLED14-71


Finishes
Gold #1
Gold Wrinkle #2
Bronze #5
Pewter #31
Satin Brass #51
Statuary Bronze #56
Polished Brass #61
Antique Brass #71
Weathered Brass #76
Mahogany Bronze #81


SIZE SELECTION Shade length should be one half the width of the image it is illuminating.

Richardson Reflector











SLED29-51

Benefits of LED

- No UV or IR
- Energy Efficient
- Long Life: 30,000 Hours
- Warm White Output

LED SPECIFICATIONS

Shade Size	CRI	CCT	Watts	Lumens	Lifetime	Equivalent Incandescent
15"	85	3000K	4	220	50,000 hrs	(2) 25 Watt
29"	85	3000K	8	440	50,000 hrs	(4) 25 Watt

Finishes Satin Brass #51 Satin Nickel #52 Polished Brass #61 Antique Brass #71 Oil Rubbed Bronze #91

|^{1"|}

-13/4


33/4"


New!

SIZE SELECTION Shade length should be one half the width of the image it is illuminating.









HALOGEN

The Halogen Profile light is UV filtered and gives off a more natural and whiter light. Transformer included.




Direct Wire Picture Lights

to be permanently affixed to the wall. Direct $Wire^{TM}$ is also a solution for those who object **TRADITIONAL** to seeing the cord. DT24-61 Finishes Polished Brass #61 Mahogany Bronze #81 **Features** Direct Wire[™] Picture Lights Metal Safety are designed to mount over standard 2" x 4", 4" x 4" or octagonal boxes. Backplate Sleeve Specifications $7\frac{1}{2}$ " arm Soldered Seamless DT8" shade End Caps one 25 or 40T10F bulb Ball Swivel for Backplate: 41/2" x 41/2" x 3/8" Switch Lockup Stud (III) Polished Metal shade positioning Reflector DT14" shade two 25 or 40T10F bulbs Junction Backplate: 41/2" x 41/2" x 3/8" Box 10" center to center DT24" shade SIZE SELECTION Shade length should be one half the width of the image it is illuminating. three 25 or 40T10F bulbs Backplate: 4" x 15" x ³/₈ 11" center to cente 11" center to cente DT 36" shade five 25 or 40T10F bulbs Backplate: 4" x 26" x ³/₈" **CONTEMPORARY** 3 **Finishes** an Polished Brass #61 Chrome #62 DC9-62 Specifications DC9" shade one 25 or 40T10F bulbs Backplate: 41/2" x 41/2" x 3/8" \bigcirc Contemporary Shade Profile DC16" shade NOTE: Custom orders available two 25 or 40T10F bulbs on request. Backplate: 41/2" x 41/2" x 3/8"

Our Direct WireTM Picture Lights are ideal in

a commercial setting where lighting needs



Direct WireTM LED Picture Lights

STREET

TRADITIONAL

Benefits of LED

- No UV or IR
- Energy Efficient
- Long Life: 30,000 Hours
- Warm White Output

Finishes Polished Brass #61 Mahogany Bronze #81



DTLED14-61

LED SPECIFICATIONS


Shade Sizes	CRI	ССТ	Watts	Lumens	Lifetime	Equivalent Incandescent	Backplate Dimensions
10"	93	3400K	1.6	38.4	30,000 hrs	(1) 25 Watt	4½" x 4½" x ½"
14"	93	3400K	2.4	57.6	30,000 hrs	(2) 25 Watt	4½" x 4½" x ½"
24"	93	3400K	4	96	30,000 hrs	(3) 25 Watt	4" x 15" x ½"
36"	93	3400K	6.4	153.6	30,000 hrs	(5) 25 Watt	4" x 26" x ½"

NOTE: Custom orders available on request.

SLIM-LINETM

Finishes Satin Brass #51 Satin Nickel #52 Antique Brass #71 Oil Rubbed Bronze #91

SIZE SELECTION Shade length should be one half the width of the image it is illuminating.



DSLED14-71

LED SPECIFICATIONS

 Shade Size	CRI	CCT	Watts	Lumens	Lifetime	Equivalent Incandescent	Backplate Dimensions
14"	85	3000K	4	220	50,000 hrs	(2) 25 Watt	3¼"H x 4½"W x 1"D
24"	85	3000K	8	440	50,000 hrs	(4) 25 Watt	3¼"H x 4½"W x 1"D

Battery Operated LED Picture Lights



BTLED14-51

Uses 4 C Batteries (not included). Switch on backplate.

SIZE SELECTION Shade length should be one half the width of the image it is illuminating.

SLIN

Finishes Gold #1 Satin Brass #51 Polished Brass #61 Antique Brass #71 Mahogany Bronze #81



LED SPECIFICATIONS

it is illuminating.					B	TLED/BSLED		
	Shade Size	CRI	ССТ	Watts	Lumens	Lifetime	Equivalent Incandescent	Backplate Dimensions
	14"	75	3000K	1.6	44	30,000 hrs	(2) 25 Watt	3¼"H x 4½"W x 1"D
	24"	75	3000K	3.2	88	30,000 hrs	(2) 25 Watt	3¼"H x 4½"W x 1"D



Battery Operated Picture Lights





LED SPECIFICATIONS

Built in ____

hanger on

mounting clip.

picture



ALED15-7


LED Multi-task Light

- Switch on back of shade
- 24 Hours on 4 AA batteries (not included)
- 30,000 hours LED life

Shade Size	CRI	CCT	Watts	Lumens	Lifetime	Equivalent Incandescent
15"	75	8000K	1.9	59.5	30,000 hrs	(1) 15 Watt

Clip: $2\frac{3}{8}$ "W x 3"H, Expands to fit surfaces up to $\frac{3}{4}$ " wide.





TRADITIONAL RECHARGABLE

Rechargable Battery Operates 6–8 hours per charge. Recharger included.

Shade Length and Bulb Information



RT8" One #40, 8 hour and one #46, 6 hour bulb included



Practical only where power is not available.

Finishes Gold #1 Statuary Bronze #56 Polished Brass #61

Mantel Light





HEIGHT: 41/2" BASE: 15" wide, 3" deep 10' Brown Cord Exits Back of Shade. In-Line Switch 15" from Fixture.

Finishes

Polished Brass (B) Antique Brass (AB) Mahogany Bronze (MB)

Shade Length and Bulb Location



MA14" two 25 or 40T10F bulbs

MA14-AB

Advent. Cabinet Light



AC7-61

Finishes Polished Brass #61 Antique Brass #71


Lectern Light

Designed to be permanently installed on surfaces up to 2" thick.

L10-61 FINISH: Polished Brass HEIGHT: 7 1¾" Between Arms SWITCH: On Shade SHADE: 10" CORD: 10' Brown with Snap-On Plug Included

Bed Light

→ BL10-AB FINISH: Antique Brass HEIGHT: Gooseneck Adjusts from 0" to 8 1/2" BASE: Adjustable clip Up to 2 1/2" Wide BULB: One 40T10 SWITCH: On Shade SHADE: 10"




L10

one 40T10F or 60T10 bulb

CORD: 10' Brown






1¹/2" diameter

FLUORESCENT SPECIFICATIONS

Shade Size	Bulb	CRI	CCT	Watts	Lumens	Lifetime
24"	F14-T5	82	3000K	14	1200	15,000 hrs.
36"	F21-T5	82	3000K	21	1900	15,000 hrs.
48"	F28-T5	82	3000K	28	2600	15,000 hrs.

Bulbs not included. Non stock item, call for lead time and availability.



UC SERIES Under Cabinet Lights

• Line Voltage Incandescent System • 10' Cord with Snap-on Plug • Hardware to convert to Direct Wire • 1 1/8" H x 13/4" D UC-13-9 Finishes Specifications White #9 Bulbs sold separately Brushed Aluminum #32 Polished Brass #61 UC 13" \bigcirc two 25T6 bulbs UC 18" three 25T6 bulbs UC 22" \cap four 25T6 bulbs UC 28" five 25T6 bulbs UC 34" UC-18-32 six 25T6 bulbs UC 45" \cap eight 25T6 bulbs



Product Finishes

Our Classic and Slim-line[™] picture lights are offered in the most popular finishes. If you would like a finish that is not stocked, call our customer service department for lead time and cost.

The antique and weathered brass finishes are applied then rubbed by hand to achieve the proper effect. For this reason there are slight surface variations which are expected and desirable.

The stocked finishes are listed on the product page. Refer to this page for a color representation of finish.

Gold #1	Satin Nickel #52	Antique Silver (AS)
		est of a meridia
Gold Wrinkle #2	Statuary Bronze #56	Chestnut Bronze (CHB)
Bronze #5	Polished Brass #61	Granite (GT)
		and the second second
Black #7	Chrome #62	Hammered Bronze (HB)
White #9	Antique Brass #71	Polished Nickel (PN)
Pewter #31	Weathered Brass #76	Polished Silver (PS)
Brushed Aluminum #32	Mahogany Bronze #81	Raw Brass (RB)
Satin Brass #51	Oil Rubbed Bronze #91	

Custom Direct Mount Lighting

Customizing House of Troy Picture Lights.

We are often asked for custom versions of existing products, especially picture lights. Picture Lights are easily adapted to lighting book cases and display areas. We have developed hardware to mount through any hard surface. These products are designed as cord and plug items and will require a receptacle to plug them into behind the soffit. Call our Customer Service department at 800-428-5367 for assistance in designing your direct mount product.








Illuminate bookshelves with our Slim-line Library Lighting. The

Slim-line Library Lighting. The slim lamp profile is designed for interiors where reduced lamp visibility is desired.

Slim-line[™] Styles

Mounting Options

Arm Styles







CD-DL10-OB


Classic style lamps are an effective way to enhance traditional decor in either a residential or commercial setting.



Classic Styles

Mounting Options

Arm & Shade Styles



Phone: 800-428-5367 www.houseoftroy.com