


**Submitted Model No.:** 

Specific Features:



▲ Designate proper finish suffix



## LAVATORY FAUCETS

- Leland® Series
- Two Handle Deck Mount
- 3 Hole Sink Applications
- 4" Centerset

## **STANDARD SPECIFICATIONS:**

- Solid brass cast body.
- 4" (102 mm) centerset.
- 5 1/16" (129 mm) long, 3 7/8" (98 mm) high rigid spout.
- 1/4 turn handle stops.
- Hot and cold stems are interchangeable.
- Control mechanism is the rotating cylinder type with stainless steel plate and 90° rotation, with replaceable non-metallic seats operating in stainless steel lined sockets.
- 1/2"-14 NPSM threaded male inlet shanks.
- Models include polypropylene pop-up type drain fitting with plated metal flange and stopper cap.
- Models with "MPU" suffix include metal drain with pop-up type drain fitting with plated flange and stopper cap.
- Maximum flow rate 1.5 gpm @ 60 PSI.

## **WARRANTY**

- Lifetime Faucet and Finish Limited Warranty to the original consumer purchaser to be free from defects in material and workmanship.
- 5 Year Limited Warranty for usage in all industrial, commercial and business applications.







## **COMPLIES WITH:**

- ASME A112 18 1 / CSA B125 1
- ASME A112.18.2 / CSA B125.2
- Indicates compliance to ICC/ANSI A117.1
- EPA WaterSense®
- Verified compliant with .25% weighted average Pb content regulations.

